



# MASTER LED candles and lusters

## MASTER LEDcandle DT 6-40W E14 B38 CL\_AP

Delivering incandescent-like sparkling light effects, MASTER LED candles and lusters are ideal for general and decorative lighting in the hospitality industry as well as in home environments. Mounted in full view in chandeliers, wall scones or modern luminaires, the clear or frosted glass candles and lusters fit all existing fixtures with an E14, B15, B22 or E27 socket, and enhance the aesthetic appeal of the chandelier or luminaire both when on and off, with their unique, eye-catching lens design. They produce a beautiful sparkling warm light that delivers huge energy savings and minimizes maintenance cost.

### Product data

General Information	
Cap-Base	E14 [ E14]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	25000 h
Switching Cycle	50000X
Technical Type	6-40W
Light Technical	
Color Code	822-827 [ tunable warm white]
Luminous Flux (Nom)	470 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	- K
Luminous Efficacy (rated) (Nom)	75 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Nom)	6 W
Lamp Current (Nom)	35 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.7
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	95 °C
Controls and Dimming	
Dimmable	Yes

# MASTER LED candles and lusters

## Mechanical and Housing

Bulb Finish	Clear
Bulb Shape	B38

## Approval and Application

Suitable For Accent Lighting	No
Energy Consumption kWh/1000 h	6 kWh

## Product Data

Full product code	871869645352000
-------------------	-----------------

Order product name	MASTER LEDcandle DT 6-40W E14 B38 CL_AP
EAN/UPC - Product	8718696453520
Order code	929001140408
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001140408
Net Weight (Piece)	0.063 kg

## Dimensional drawing



Product	D	C
MASTER LEDcandle DT 6-40W E14 B38 CL_AP	38 mm	113 mm

LED DT 6-40W E14 2200-2700K B38 CL

## Photometric data

