

# Essential LEDtube

## LEDtube 1200mm 16W 740 T8 AP I G

Essential LEDtube is an affordable LED tube that is suitable for replacing T8 fluorescent lamps. The product provides a natural lighting effect for use in general lighting applications, as well as instant energy savings – an environmentally friendly solution.

### Product data

General information		Voltage (Nom)	
Cap-Base	G13 [ Medium Bi-Pin Fluorescent]	220-240 V	
EU RoHS compliant	Yes	Temperature	
Nominal Lifetime (Nom)	15000 h	T-Ambient (Max)	45 °C
Switching Cycle	50000	T-Ambient (Min)	-20 °C
Light technical		T-Storage (Max)	65 °C
Color Code	740 [ CCT of 4000K]	T-Storage (Min)	-40 °C
Beam Angle (Nom)	240 °	T-Case Maximum (Nom)	60 °C
Luminous Flux (Nom)	1600 lm	Controls and dimming	
Color Designation	Cool White (CW)	Dimmable	No
Correlated Color Temperature (Nom)	4000 K	Mechanical and housing	
Luminous Efficacy (rated) (Nom)	100.00 lm/W	Product Length	1200 mm
Color Consistency	<7	Bulb Shape	Tube, double-ended
Color Rendering Index (Nom)	73	Approval and application	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Energy Saving Product	Yes
Operating and electrical		Suitable For Accent Lighting	No
Input Frequency	50 to 60 Hz	Approval Marks	RoHS compliance KEMA Keur certificate
Power (Nom)	16 W	Energy Consumption kWh/1000 h	16 kWh
Starting Time (Nom)	0.5 s		
Warm Up Time to 60% Light (Nom)	0.5 s		
Power Factor (Nom)	0.5		


# Essential LEDtube

## Product data

Full product code	871869659996900
Order product name	LEDtube 1200mm 16W 740 T8 AP I G
EAN/UPC - Product	8718696599969
Order code	929001184538
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	20
Material Nr. (12NC)	929001184538
Net Weight (Piece)	0.222 kg


## Dimensional drawing




LEDtube 1200mm 16W 740 T8 AP I G

Product	D1	D2	A1	A2	A3	C	D
LEDtube 1200mm 16W 740 T8 AP I G	25.68 mm	28 mm	1198 mm	1205 mm	1212 mm	1212 mm	27.8 mm


## Photometric data



LEDtube 600mm 8W 740 T8 CN I G





LEDtube 1200mm 16W 740 T8 CN I G



LEDtube 1200mm 16W G13 T8 740 1600lm AP C G



# Essential LEDtube

## Lifetime




LEDtube 16W G13 740 T8 AP I G

LEDtube 16W G13 740 T8 AP I G



LEDtube 16W G13 740 T8 AP I G

LEDtube 16W G13 740 T8 AP I G



LEDtube 16W G13 740 T8 AP I G

## Essential LEDtube

