



Ecofit Ledtubes T8

LEDtube 600mm 8W 740 T8 AP C G

Upgrade to efficient, long-lasting LED tubes with the Ecofit LED tubes. Ecofit LED tubes are a fast and easy way to replace your old fluorescent tubes with modern, efficient LED technology. Good quality of light with a natural lighting effect for use in general lighting applications with low initial investment – an environmentally friendly solution.

Product data


General Information		Power Factor (Nom)		0.5
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Voltage (Nom)	220-240 V	
EU RoHS compliant	Yes	Temperature		
Nominal Lifetime (Nom)	15000 h	T-Ambient (Max)	45 °C	
Switching Cycle	50000X	T-Ambient (Min)	-20 °C	
Light Technical		T-Storage (Max)	65 °C	
Color Code	740 [CCT of 4000K]	T-Storage (Min)	-40 °C	
Beam Angle (Nom)	240 °	T-Case Maximum (Nom)	60 °C	
Luminous Flux (Nom)	800 lm	Controls and Dimming		
Color Designation	Cool White (CW)	Dimmable	No	
Correlated Color Temperature (Nom)	4000 K	Mechanical and Housing		
Luminous Efficacy (rated) (Nom)	100.00 lm/W	Product Length	600 mm	
Color Consistency	<7	Bulb Shape	Tube, double-ended	
Color Rendering Index (Nom)	73	Approval and Application		
LLMF At End Of Nominal Lifetime (Nom)	70 %	Energy Saving Product	Yes	
Operating and Electrical		Suitable For Accent Lighting	No	
Input Frequency	50 to 60 Hz	Approval Marks	RoHS compliance KEMA Keur certificate	
Power (Nom)	8 W			
Starting Time (Nom)	0.5 s			
Warm Up Time to 60% Light (Nom)	0.5 s			

Ecofit Ledtubes T8

Energy Consumption kWh/1000 h	8 kWh
Product Data	
Full product code	871869652505000
Order product name	LEDtube 600mm 8W 740 T8 AP C G
EAN/UPC - Product	8718696525050
Order code	929001184708

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001184708
Net Weight (Piece)	0.124 kg



Dimensional drawing



TLED 600mm 2ft T8 8W-18W 4000K G13 ND


Product	D1	D2	A1	A2	A3	C	D
LEDtube 600mm	25.68	28	588.5	595.5	602.5	602.5	27.8
8W 740 T8 AP C	mm	mm	mm	mm	mm	mm	mm
G							

Photometric data



LEDtube 600mm 8W 740 T8 CN I G



LEDtube 600mm 8W 765 T8 CN I G



LEDtube 600mm 8W G13 T8 740 800lm AP C G



Ecofit Ledtubes T8

Lifetime




LEDtube 16W G13 740 T8 AP I G

LEDtube 16W G13 740 T8 AP I G



LEDtube 16W G13 740 T8 AP I G

LEDtube 16W G13 740 T8 AP I G



LEDtube 16W G13 740 T8 AP I G

Ecofit Ledtubes T8

