



Ecofit Ledtubes T8

LEDtube 600mm 8W 765 T8 AP C G

Upgrade to efficient, long-lasting LED tubes with the Ecofit LED tubes. Ecofit LED tubes are a fast and easy way to replace your old fluorescent tubes with modern, efficient LED technology. Good quality of light with a natural lighting effect for use in general lighting applications with low initial investment – an environmentally friendly solution.

Product data


General Information		Power Factor (Nom)	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]		0.5
EU RoHS compliant	Yes	Voltage (Nom)	220-240 V
Nominal Lifetime (Nom)	15000 h	Temperature	
Switching Cycle	50000X	T-Ambient (Max)	45 °C
		T-Ambient (Min)	-20 °C
		T-Storage (Max)	65 °C
		T-Storage (Min)	-40 °C
		T-Case Maximum (Nom)	60 °C
		Controls and Dimming	
		Dimmable	No
		Mechanical and Housing	
		Product Length	600 mm
		Bulb Shape	Tube, double-ended
		Approval and Application	
		Energy Saving Product	Yes
		Suitable For Accent Lighting	No
		Approval Marks	RoHS compliance KEMA Keur certificate
Light Technical			
Color Code	765 [CCT of 6500K]		
Beam Angle (Nom)	240 °		
Luminous Flux (Nom)	800 lm		
Color Designation	Cool Daylight		
Correlated Color Temperature (Nom)	6500 K		
Luminous Efficacy (rated) (Nom)	100.00 lm/W		
Color Consistency	<7		
Color Rendering Index (Nom)	73		
LLMF At End Of Nominal Lifetime (Nom)	70 %		
Operating and Electrical			
Input Frequency	50 to 60 Hz		
Power (Nom)	8 W		
Starting Time (Nom)	0.5 s		
Warm Up Time to 60% Light (Nom)	0.5 s		

Ecofit Ledtubes T8

Energy Consumption kWh/1000 h	8 kWh
Product Data	
Full product code	871869652507400
Order product name	LEDtube 600mm 8W 765 T8 AP C G
EAN/UPC - Product	8718696525074
Order code	929001184808

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001184808
Net Weight (Piece)	0.100 kg



Dimensional drawing



TLED 600mm 2ft T8 8W-18W 6500K G13 ND


Product	D1	D2	A1	A2	A3	C	D
LEDtube 600mm	25.68	28	588.5	595.5	602.5	602.5	27.8
8W 765 T8 AP C	mm	mm	mm	mm	mm	mm	mm
G							

Photometric data



LEDtube 600mm 8W 765 T8 CN I G



LEDtube 1200mm 16W 765 T8 CN I G



LEDtube 600mm 8W G13 T8 765 800lm AP C G



Ecofit Ledtubes T8

Lifetime




LEDtube 16W G13 740 T8 AP I G

LEDtube 16W G13 740 T8 AP I G



LEDtube 16W G13 740 T8 AP I G

LEDtube 16W G13 740 T8 AP I G



LEDtube 16W G13 740 T8 AP I G

Ecofit Ledtubes T8

