



Classic filament LEDbulbs

CLA LEDBulb ND 4-40W ST64 E27 827 CL

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General Information	
Cap-Base	E27 [E27]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	20000X
Technical Type	4-40W
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux (Nom)	470 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	118.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Nom)	4 W


Lamp Current (Nom)	33 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.4
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	70 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	ST64
Approval and Application	
Energy Saving Product	Yes
Suitable For Accent Lighting	No

Classic filament LEDbulbs

Energy Consumption kWh/1000 h	4 kWh
Product Data	
Full product code	871869657403400
Order product name	CLA LEDBulb ND 4-40W ST64 E27 827 CL
EAN/UPC - Product	8718696574034
Order code	929001237302

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001237302
Net Weight (Piece)	0.030 kg


Dimensional drawing




filament 4.5W-40W 470lm NAD 2700K E27ND

Product	D	C
CLA LEDBulb ND 4-40W ST64 E27 827 CL	64 mm	140 mm


Photometric data



LED Lamps, Lightcolour /827 ND CL



CorePro LEDbulb ND 4-40W ST64 827



CorePro LEDbulb ND 4-40W ST64 827

Classic filament LEDbulbs

Lifetime



15K LED

15K LMP

