

Ecofit Ledtubes T8

Ecofit LEDtube 600mm 8W 840 T8 I RCA

Upgrade to efficient, long-lasting LED tubes with the Ecofit LED tubes. Ecofit LED tubes are a fast and easy way to replace your old fluorescent tubes with modern, efficient LED technology. Good quality of light with a natural lighting effect for use in general lighting applications with low initial investment – an environmentally friendly solution.

Product data


General Information		Starting Time (Nom)	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]		0.5 s
EU RoHS compliant	Yes	Warm Up Time to 60% Light (Nom)	0.5 s
Nominal Lifetime (Nom)	15000 h	Power Factor (Nom)	0.5
Switching Cycle	50000X	Voltage (Nom)	220-240 V
Technical Type	8-18W		
Light Technical		Temperature	
Color Code	840 [CCT of 4000K]	T-Ambient (Max)	45 °C
Beam Angle (Nom)	240 °	T-Ambient (Min)	-20 °C
Luminous Flux (Nom)	800 lm	T-Storage (Max)	65 °C
Color Designation	Cool White (CW)	T-Storage (Min)	-40 °C
Correlated Color Temperature (Nom)	4000 K	T-Case Maximum (Nom)	55 °C
Luminous Efficacy (rated) (Nom)	100.00 lm/W		
Color Consistency	<6	Controls and Dimming	
Color Rendering Index (Nom)	80	Dimmable	No
LLMF At End Of Nominal Lifetime (Nom)	70 %		
Operating and Electrical		Mechanical and Housing	
Input Frequency	50 to 60 Hz	Product Length	600 mm
Power (Nom)	8 W	Bulb Shape	Tube, single-ended
Lamp Current (Nom)	70 mA		
		Approval and Application	
		Energy Saving Product	Yes

Ecofit Ledtubes T8

Approval Marks	RoHS compliance CE marking KEMA Keur certificate
Energy Consumption kWh/1000 h	8 kWh
Product Data	
Full product code	871951425782500
Order product name	Ecofit LEDtube 600mm 8W 840 T8 I RCA
EAN/UPC - Product	8719514257825

Order code	929001276237
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	20
Material Nr. (12NC)	929001276237
Net Weight (Piece)	0.120 kg



Dimensional drawing



Product	D1	D2	A1	A2	A3
Ecofit LEDtube 600mm 8W 840 T8 I RCA	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm


TLED Ecofit EU 600mm 8W 800lm 4000K

Photometric data



LEDtube Ecofit 16W G13 840 24D ND



LEDtube Ecofit 8W G13 840 24D ND



LEDtube Ecofit 16W G13 840 24D ND



Ecofit Ledtubes T8

Lifetime




LEDtube Ecofit 16W G13 840 24D ND

LEDtube Ecofit 16W G13 840 24D ND



LEDtube Ecofit 16W G13 840 24D ND

LEDtube Ecofit 16W G13 840 24D ND



LEDtube Ecofit 16W G13 840 24D ND

Ecofit Ledtubes T8

