



# Ecofit Ledtubes T8

## Ecofit LEDtube HO 1200mm 20W 765 T8 RCA

Upgrade to efficient, long-lasting LED tubes with the Ecofit LED tubes. Ecofit LED tubes are a fast and easy way to replace your old fluorescent tubes with modern, efficient LED technology. Good quality of light with a natural lighting effect for use in general lighting applications with low initial investment – an environmentally friendly solution.

### Product data


General Information		Power Factor (Nom)		0.5
Cap-Base	G13 [ Medium Bi-Pin Fluorescent]	Voltage (Nom)	220-240 V	
EU RoHS compliant	Yes	<b>Temperature</b>		
Nominal Lifetime (Nom)	15000 h	T-Ambient (Max)	45 °C	
Switching Cycle	50000X	T-Ambient (Min)	-20 °C	
<b>Light Technical</b>		T-Storage (Max)	65 °C	
Color Code	765 [ CCT of 6500K]	T-Storage (Min)	-40 °C	
Beam Angle (Nom)	240 °	T-Case Maximum (Nom)	60 °C	
Luminous Flux (Nom)	2100 lm	<b>Controls and Dimming</b>		
Color Designation	Cool Daylight	Dimmable	No	
Correlated Color Temperature (Nom)	6500 K	<b>Mechanical and Housing</b>		
Luminous Efficacy (rated) (Nom)	105.00 lm/W	Product Length	1200 mm	
Color Consistency	<7	Bulb Shape	Tube, double-ended	
Color Rendering Index (Nom)	70	<b>Approval and Application</b>		
LLMF At End Of Nominal Lifetime (Nom)	70 %	Energy Saving Product	Yes	
<b>Operating and Electrical</b>		Approval Marks	RoHS compliance KEMA Keur certificate	
Input Frequency	50 to 60 Hz	Energy Consumption kWh/1000 h	20 kWh	
Power (Nom)	20 W			
Starting Time (Nom)	0.5 s			
Warm Up Time to 60% Light (Nom)	0.5 s			

# Ecofit Ledtubes T8

Product Data	
Full product code	871869970087400
Order product name	Ecofit LEDtube HO 1200mm 20W 765 T8 RCA
EAN/UPC - Product	8718699700874
Order code	929001277367
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	20
Material Nr. (12NC)	929001277367
Net Weight (Piece)	0.215 kg


## Dimensional drawing




TLED Ecofit APR HO 1200mm 4ft T8 220-240

Product	D1	D2	A1	A2	A3
Ecofit LEDtube HO 1200mm 20W 765 T8 RCA	25.7 mm	28 mm	1198 mm	1205 mm	1212 mm


## Photometric data



LEDtube HO 20W G13 765 T8 AP I G



LEDtube HO 20W G13 730 T8 AP I G





General Lighting Information

LEDtube HO 20W G13 765 T8 AP I G



# Ecofit Ledtubes T8

## Lifetime




LEDtube HO 20W G13 730 T8 AP I G

LEDtube HO 20W G13 730 T8 AP I G



LEDtube HO 20W G13 730 T8 AP I G

LEDtube HO 20W G13 730 T8 AP I G



LEDtube HO 20W G13 730 T8 AP I G

## Ecofit Ledtubes T8

