



MASTER LEDtube EM/ Mains T8

MASTER LEDtube 1200mm UO 16W 840 T8

The Philips MASTER LEDtube integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance which cannot be distinguished from traditional fluorescent. For those that are looking for value for money within limited budget and re-lamping efforts for better light effect and lifetime.

Warnings and Safety

- NOTES: The overall energy efficiency and light distribution of any installation that uses these lamps are determined by the design of the installation.

Product data


General Information		LLMF At End Of Nominal Lifetime (Nom) 70 %	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Operating and Electrical	
EU RoHS compliant	Yes	Input Frequency	50 to 60 Hz
Nominal Lifetime (Nom)	50000 h	Power (Nom)	16 W
Switching Cycle	200000X	Lamp Current (Max)	75 mA
Light Technical		Lamp Current (Min)	68 mA
Color Code	840 [CCT of 4000K]	Starting Time (Nom)	0.5 s
Beam Angle (Nom)	160 °	Warm Up Time to 60% Light (Nom)	0.5 s
Luminous Flux (Nom)	2500 lm	Power Factor (Nom)	0.9
Color Designation	Cool White (CW)	Voltage (Nom)	220-240 V
Correlated Color Temperature (Nom)	4000 K	Temperature	
Luminous Efficacy (rated) (Nom)	156.00 lm/W	T-Ambient (Max)	35 °C
Color Consistency	<6	T-Ambient (Min)	-20 °C
Color Rendering Index (Nom)	83	T-Storage (Max)	65 °C

MASTER LEDtube EM/Mains T8

T-Storage (Min)	-40 °C
T-Case Maximum (Nom)	55 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Product Length	1200 mm
Approval and Application	
Energy Efficiency Label (EEL)	A++
Energy Saving Product	Yes
Approval Marks	TUV CE marking RoHS compliance KEMA Keur certificate

Energy Consumption kWh/1000 h	16 kWh
Product Data	
Full product code	871869668738300
Order product name	MASTER LEDtube 1200mm UO 16W 840 T8
EAN/UPC - Product	8718696687383
Order code	929001297902
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001297902
Net Weight (Piece)	0.251 kg


Dimensional drawing



TLED 4ft 16W-36W 2500lm 160D 4000K G13ND


Product	D1	D2	A1	A2	A3
MASTER LEDtube 1200mm UO 16W 840 T8	25.78 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm

Photometric data



General Uniform Lighting
1 x 16W 16W 4000K 160D 1200mm
Page 11


LEDtube 1200mm UO 16W 840 T8



LEDtube 1200mm UO 16W 840 T8


MASTER LEDtube EM/Mains T8

Photometric data




LEDtube 600mm 1200mm 1500mm UO T8

Lifetime



LEDtube 600mm 1200mm 1500mm UO T8



LEDtube 600mm 1200mm 1500mm UO T8

