



MASTER LEDtube EM/ Mains T8

MASTER LEDtube 1200mm HO 14W830 T8

The Philips MASTER LEDtube integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance which cannot be distinguished from traditional fluorescent. For those that are looking for value for money within limited budget and re-lamping efforts for better light effect and lifetime.

Warnings and Safety

- NOTES: The overall energy efficiency and light distribution of any installation that uses these lamps are determined by the design of the installation.

Product data


General Information		LLMF At End Of Nominal Lifetime (Nom) 70 %	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]		
EU RoHS compliant	Yes		
Nominal Lifetime (Nom)	50000 h		
Switching Cycle	200000X		
Light Technical		Operating and Electrical	
Color Code	830 [CCT of 3000K]	Input Frequency	50 to 60 Hz
Beam Angle (Nom)	160 °	Power (Nom)	14 W
Luminous Flux (Nom)	2000 lm	Lamp Current (Max)	65 mA
Color Designation	White (WH)	Lamp Current (Min)	60 mA
Correlated Color Temperature (Nom)	3000 K	Starting Time (Nom)	0.5 s
Luminous Efficacy (rated) (Nom)	142.00 lm/W	Warm Up Time to 60% Light (Nom)	0.5 s
Color Consistency	<6	Power Factor (Nom)	0.9
Color Rendering Index (Nom)	83	Voltage (Nom)	220-240 V
		Temperature	
		T-Ambient (Max)	45 °C
		T-Ambient (Min)	-20 °C
		T-Storage (Max)	65 °C

MASTER LEDtube EM/Mains T8

T-Storage (Min)	-40 °C
T-Case Maximum (Nom)	55 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Product Length	1200 mm
Approval and Application	
Energy Efficiency Label (EEL)	A++
Energy Saving Product	Yes
Approval Marks	CE marking RoHS compliance KEMA Keur certificate

Energy Consumption kWh/1000 h	14 kWh
Product Data	
Full product code	871869668724600
Order product name	MASTER LEDtube 1200mm HO 14W830 T8
EAN/UPC - Product	8718696687246
Order code	929001299208
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001299208
Net Weight (Piece)	0.215 kg



Dimensional drawing



TLED 4ft 14W-36W 2000lm 150D 3000K G13ND

Product	D1	D2	A1	A2	A3
MASTER LEDtube 1200mm HO 14W830 T8	25.8 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm

Photometric data




MAS LEDtube HO 14W G13 830 T8



MAS LEDtube HO 14W G13 830-865 T8

MASTER LEDtube EM/Mains T8

Photometric data





Lifetime



MAS LEDtube HO 14W G13 830-865 T8

MAS LEDtube HO 14W G13 830-865 T8




MAS LEDtube HO 14W G13 830-865 T8

MAS LEDtube HO 14W G13 830-865 T8

MASTER LEDtube EM/Mains T8

Lifetime



MAS LEDtube HO 14W G13 830-865 T8

