

T8

35T8/96-4000 IF FA8 10/1

Our TLEDs are available in InstantFit (Type A / Type C) or MainsFit (Ballast bypass / Type B) versions. The InstantFit lamps work on a broad variety of ballasts and LED drivers. Only InstantFit has over 15,000 lamp & ballast combinations delivering even light output, energy savings and a long lifetime. Our MainsFit products feature a double-ended design, simplifying installation while a proprietary safety circuit minimizes a shock risk. Lamp sizes range from 2-foot to 8-foot and U-bend with a variety of lumen outputs.

Product data

General Information		Lamp Current (Max)	
Cap-Base	FA8 [FA8]		260 mA
EU RoHS compliant	Yes	Lamp Current (Min)	160 mA
Nominal Lifetime (Nom)	50000 h	Warm Up Time to 60% Light (Nom)	0.5 s
Switching Cycle	50000X	UL Type	Type A - works on ballast
		Power Factor (Nom)	0.9
		Voltage (Nom)	280-410 V
Light Technical		Temperature	
Color Code	840 [CCT of 4000K]	T-Ambient (Max)	45 °C
Beam Angle (Nom)	180 °	T-Ambient (Min)	-20 °C
Luminous Flux (Nom)	4200 lm	T-Storage (Max)	65 °C
Color Designation	Cool White (CW)	T-Storage (Min)	-40 °C
Correlated Color Temperature (Nom)	4000 K	T-Case Maximum (Nom)	45 °C
Luminous Efficacy (rated) (Nom)	120.00 lm/W		
Color Consistency	<6	Controls and Dimming	
Color Rendering Index (Nom)	82	Dimmable	No
LLMF At End Of Nominal Lifetime (Nom)	70 %		
Operating and Electrical		Mechanical and Housing	
Input Frequency	50000-64000 Hz	Bulb Material	Plastic
Power (Nom)	35 W		

T8

Product Length	2400 mm
----------------	---------

Approval and Application


Energy Efficiency Label (EEL)	Not applicable
Energy Saving Product	Yes
Approval Marks	UL certificate
Energy Consumption kWh/1000 h	- kWh

Product Data

Order product name	35T8/96-4000 IF FA8 10/1
--------------------	--------------------------

EAN/UPC - Product	046677472580
Order code	929001314604
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001314604
Net Weight (Piece)	0.540 kg


Dimensional drawing




TLED Ess IF 3200lm 4000K 8ft single pin

Product	D	A1	A2	A3
35T8/96-4000 IF FA8 10/1	27.9 mm	2366.9 mm	2375.2 mm	2383.5 mm

Photometric data




TLED Ess 35W FA8 840 4200lm T8



TLED Ess 35W FA8 840 4200lm T8


T8

Photometric data



TLED Ess 35W FA8 840 4200lm T8

Lifetime



TLED Ess 35W FA8 T8 IF

TLED Ess 35W FA8 T8 IF

