

Ecofit Ledtubes T8

Ecofit LEDtube 1500mm 20W 840 T8 I

Upgrade to efficient, long-lasting LED tubes with the Ecofit LED tubes. Ecofit LED tubes are a fast and easy way to replace your old fluorescent tubes with modern, efficient LED technology. Good quality of light with a natural lighting effect for use in general lighting applications with low initial investment – an environmentally friendly solution.

Product data


General Information		Warm Up Time to 60% Light (Nom)	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]		0.5 s
EU RoHS compliant	Yes	Power Factor (Nom)	0.5
Nominal Lifetime (Nom)	15000 h	Voltage (Nom)	220-240 V
Switching Cycle	50000X	Temperature	
Flux measurement reference	Sphere	T-Ambient (Max)	45 °C
Light Technical		T-Ambient (Min)	-20 °C
Color Code	840 [CCT of 4000K]	T-Storage (Max)	65 °C
Beam Angle (Nom)	240 °	T-Storage (Min)	-40 °C
Luminous Flux (Nom)	2000 lm	T-Case Maximum (Nom)	60 °C
Color Designation	Cool White (CW)	Controls and Dimming	
Correlated Color Temperature (Nom)	4000 K	Dimmable	No
Luminous Efficacy (rated) (Nom)	100.00 lm/W	Mechanical and Housing	
Color Consistency	<6	Bulb Material	Glass
Color Rendering Index (Nom)	80	Product Length	1500 mm
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Shape	Tube, double-ended
Operating and Electrical		Approval and Application	
Input Frequency	50 to 60 Hz	Energy Efficiency Class	F
Power (Nom)	20 W	Energy Saving Product	Yes
Starting Time (Nom)	0.5 s		

Ecofit Ledtubes T8

Approval Marks	RoHS compliance CE marking KEMA Keur certificate
Energy Consumption kWh/1000 h	20 kWh
EPREL Registration Number	491860
Product Data	
Full product code	871869969708200
Order product name	Ecofit LEDtube 1500mm 20W 840 T8 I

EAN/UPC - Product	8718699697082
Order code	929001338122
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	20
Material Nr. (12NC)	929001338122
Net Weight (Piece)	0.310 kg


Dimensional drawing




TLED 5ft 220-240V 20-57W 2000lm 4000K

Product	D1	D2	A1	A2	A3
Ecofit LEDtube 1500mm 20W 840 T8 I	25.7 mm	28 mm	1500 mm	1507.1 mm	1514.2 mm


Photometric data



LEDtube Ecofit 16W G13 840 24D ND





LEDtube Ecofit 16W G13 840 24D ND



LEDtube Ecofit 20W G13 840 24D ND



Ecofit Ledtubes T8

Lifetime




LEDtube Ecofit 16W G13 840 24D ND

LEDtube Ecofit 16W G13 840 24D ND



LEDtube Ecofit 16W G13 840 24D ND

LEDtube Ecofit 16W G13 840 24D ND



LEDtube Ecofit 16W G13 840 24D ND

Ecofit Ledtubes T8

