



# MASTER LEDtube InstantFit HF T5

## Master LEDtube HF 1500mm UO 36W 830 T5

Philips MASTER LEDtube InstantFit T5 integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance which cannot be distinguished from traditional fluorescent. The Philips MASTER LEDtube InstantFit T5 is the ideal solution for customers who have higher light output requirements and want to maximize value over lifetime. Full energy savings & longer lifetime result in attractive payback times and TCO benefits.

### Product data

General Information		Power (Nom)	
Cap-Base	G5 [ G5]		36 W
EU RoHS compliant	Yes	Lamp Current (Max)	750 mA
Nominal Lifetime (Nom)	60000 h	Lamp Current (Min)	550 mA
Switching Cycle	50000X	Starting Time (Nom)	0.5 s
		Warm Up Time to 60% Light (Nom)	0.5 s
Light Technical		Power Factor (Nom)	0.9
Color Code	830 [ CCT of 3000K]	Voltage (Nom)	65-75 V
Beam Angle (Nom)	160 °	Temperature	
Luminous Flux (Nom)	5200 lm	T-Ambient (Max)	45 °C
Color Designation	White (WH)	T-Ambient (Min)	-20 °C
Correlated Color Temperature (Nom)	3000 K	T-Storage (Max)	65 °C
Luminous Efficacy (rated) (Nom)	144.00 lm/W	T-Storage (Min)	-40 °C
Color Consistency	<6	T-Case Maximum (Nom)	75 °C
Color Rendering Index (Nom)	80	Controls and Dimming	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Dimmable	No
Operating and Electrical			
Input Frequency	40000-75000 Hz		

# MASTER LEDtube InstantFit HF T5

## Mechanical and Housing

Bulb Finish	Frosted
Bulb Material	Plastic
Product Length	1500 mm


## Approval and Application

Energy Efficiency Label (EEL)	A++
Energy Saving Product	Yes
Approval Marks	RoHS compliance TUV CE marking KEMA Keur certificate
Energy Consumption kWh/1000 h	42 kWh

## Product Data

Full product code	871869670599500
Order product name	Master LEDtube HF 1500mm UO 36W 830 T5
EAN/UPC - Product	8718696705995
Order code	929001346102
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001346102
Net Weight (Piece)	0.170 kg



## Dimensional drawing



TLED 230V 37-80W 5600lm 160D 3000K G5 ND

Product	D1	D2	A1	A2	A3
Master LEDtube HF 1500mm UO 36W 830 T5	15.2 mm	21 mm	1447.8 mm	1454.9 mm	1462 mm

## Photometric data




LEDtube 1500mm 36W G5 830 5200lm



LEDtube 1200mm 26W G5

# MASTER LEDtube InstantFit HF T5

## Photometric data




## Lifetime



LEDtube 1500mm 36W G5 5600lm

LEDtube 1500mm 36W G5 5600lm




LEDtube 1500mm 36W G5 5600lm

LEDtube 1200mm 26W G5 3900lm

# MASTER LEDtube InstantFit HF T5

## Lifetime



LEDtube 1500mm 36W G5 5600lm

