



MASTER VALUE LEDspot MV

Master LED 4.9-50W GU10 930 36D Dim

Delivering a warm, halogen-like accent beam, MASTER VALUE is a perfect fit for spot lighting. Thanks to its high CRI, it realizes more natural colors, creating cozy and comfortable ambiances for residential and hospitality projects, and emphasizing the beauty of merchandise in retail. These LED spots MV GU10 have the familiar look and feel of spot lamps, keeping the classic beauty of glass spots and adding the strong performance of LED technology. The dimming function enables you to create the atmosphere you desire, and it works with broad selection of dimmers. MASTER VALUE also offers more energy savings that normal LED spots.

Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights

Product data

General Information		Luminous Intensity (Nom)	
Cap-Base	GU10		650 cd
Nominal lifetime	25,000 hour(s)	Color Designation	White (WH)
Switching Cycle	50,000	Correlated Color Temperature (Nom)	3000 K
Lighting Technology	LED	Luminous Efficacy (rated) (Nom)	81.00 lm/W
EU RoHS compliant	Yes	Color Consistency	<6
		Color rendering index (CRI)	90
		LLMF At End Of Nominal Lifetime (Nom)	70 %
		Luminous Flux in 90° Cone (Rated)	365 lm
Light Technical		Operating and Electrical	
Color Code	930 [CCT of 3000K]	Line Frequency	50 to 60 Hz
Beam Angle (Nom)	36 degree(s)		
Luminous Flux	405 lm		

MASTER VALUE LEDspot MV

Input Frequency	50 to 60 Hz
Power Consumption	5 W
Lamp Current (Nom)	27 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.8
Voltage (Nom)	220-240 V

Temperature

T-Case Maximum (Nom)	80 °C
----------------------	-------

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Bulb Shape	PAR16
------------	-------


Approval and Application

Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	5 kWh

Product Data


Order product name	Master LED 4.9-50W GU10 930 36D Dim
Full product name	Master LED 4.9-50W GU10 930 36D Dim
Full product code	871869675592100
Order code	929001348908
Material Nr. (12NC)	929001348908
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696755921
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696755938

Dimensional drawing




Product	D	C
Master LED 4.9-50W GU10 930 36D Dim	50 mm	54 mm

Photometric data



CELESTRONICS LTD. PAR16/LED 11




Accent Lighting Spots - Master LED 4.9-50W GU10 930 36D Dim

Spectral Power Distribution Colour - Master LED 4.9-50W GU10 930 36D Dim

MASTER VALUE LEDspot MV

Photometric data



Light Distribution Diagram - Master LED 4.9-50W GU10 930 36D Dim

Lifetime



Life Expectancy Diagram - Master LED 4.9-50W GU10 930 36D Dim



Lumen Maintenance Diagram - Master LED 4.9-50W GU10 930 36D Dim

