



Essential LED tubes T5 Mains

CorePro LEDtube 600mm 8W830 G5 I MX

The Essential LEDtube T5 is an affordable LED solution suitable for replacing T5 fluorescent lamps. Thanks to a unique design, Philips Essential LED tube T5 Mains can be directly installed in luminaires operating on mains power connection. The product provides a natural lighting effect for use in general lighting applications, as well as instant energy savings – an environmentally friendly solution.

Product data


General Information		Lamp Current (Max)	
Cap-Base	G5 [G5]	Lamp Current (Min)	75 mA
EU RoHS compliant	Yes	Starting Time (Nom)	30 mA
Nominal Lifetime (Nom)	30000 h	Warm Up Time to 60% Light (Nom)	0.5 s
Switching Cycle	50000X	Power Factor (Nom)	0.92
Voltage (Nom)		100-240 V	
Light Technical		Temperature	
Color Code	830 [CCT of 3000K]	T-Ambient (Max)	45 °C
Beam Angle (Nom)	200 °	T-Ambient (Min)	-20 °C
Luminous Flux (Nom)	1000 lm	T-Storage (Max)	65 °C
Color Designation	White (WH)	T-Storage (Min)	-40 °C
Correlated Color Temperature (Nom)	3000 K	T-Case Maximum (Nom)	70 °C
Luminous Efficacy (rated) (Nom)	112.00 lm/W	Controls and Dimming	
Color Consistency	<6	Dimmable	No
Color Rendering Index (Nom)	80	Mechanical and Housing	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Product Length	600 mm
Operating and Electrical			
Input Frequency	50 to 60 Hz		
Power (Nom)	8 W		

Essential LED tubes T5 Mains

Bulb Shape	Tube, double-ended
Approval and Application	
Energy Saving Product	Yes
Approval Marks	CE marking RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	- kWh
Product Data	
Full product code	871869673414800

Order product name	CorePro LEDtube 600mm 8W830 G5 I MX
EAN/UPC - Product	8718696734148
Order code	929001380612
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	20
Material Nr. (12NC)	929001380612
Net Weight (Piece)	0.080 kg


Dimensional drawing




TLED 600mm 100-240V 8-14W 1050lm 3000K

Product	D1	D2	A1	A2	A3
CorePro LEDtube 600mm 8W830 G5 I MX	15.8 mm	19 mm	549 mm	556.1 mm	563.2 mm

Photometric data




ESSENTIAL LEDtube 8W G5 830 APR



ESSENTIAL LEDtube 8W G5 830 APR


Essential LED tubes T5 Mains

Photometric data




ESSENTIAL LEDtube 8W G5 830 APR


Lifetime




ESSENTIAL LEDtube 8-16W G5 830-865 APR



ESSENTIAL LEDtube 8-16W G5 830-865 APR




ESSENTIAL LEDtube 8-16W G5 830-865 APR



ESSENTIAL LEDtube 8-16W G5 830-865 APR

Essential LED tubes T5 Mains

Lifetime



ESSENTIAL LEDtube 8W G5 830-865 APR

