



Essential LEDtube

CorePro LEDtube 1200mm 16W830 G5 I APR

Essential LEDtube is an affordable LED tube that is suitable for replacing T8 fluorescent lamps. The product provides a natural lighting effect for use in general lighting applications, as well as instant energy savings – an environmentally friendly solution.

Product data


General Information		Warm Up Time to 60% Light (Nom)	
Cap-Base	G5 [G5]		0.5 s
EU RoHS compliant	Yes	Power Factor (Nom)	0.92
Nominal Lifetime (Nom)	30000 h	Voltage (Nom)	100-240 V
Switching Cycle	50000X	Temperature	
Light Technical		T-Ambient (Max)	45 °C
Color Code	830 [CCT of 3000K]	T-Ambient (Min)	-20 °C
Beam Angle (Nom)	200 °	T-Storage (Max)	65 °C
Luminous Flux (Nom)	2000 lm	T-Storage (Min)	-40 °C
Color Designation	White (WH)	T-Case Maximum (Nom)	70 °C
Correlated Color Temperature (Nom)	3000 K	Controls and Dimming	
Luminous Efficacy (rated) (Nom)	125.00 lm/W	Dimmable	No
Color Consistency	<6	Mechanical and Housing	
Color Rendering Index (Nom)	80	Product Length	1200 mm
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Shape	Tube, double-ended
Operating and Electrical		Approval and Application	
Input Frequency	50 to 60 Hz	Energy Saving Product	Yes
Power (Nom)	16 W	Approval Marks	CE marking RoHS compliance KEMA Keur certificate
Lamp Current (Max)	177 mA		
Lamp Current (Min)	77 mA		
Starting Time (Nom)	0.5 s		

Essential LEDtube

Energy Consumption kWh/1000 h	16 kWh
Product Data	
Full product code	871869673202100
Order product name	CorePro LEDtube 1200mm 16W830 G5 I APR
EAN/UPC - Product	8718696732021
Order code	929001380908

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	20
Material Nr. (12NC)	929001380908
Net Weight (Piece)	0.162 kg


Dimensional drawing




TLED 1200mm 100-240V 16-28W 3000K

Product	D1	D2	A1	A2	A3
CorePro LEDtube 1200mm 16W830 G5 I APR	15.8 mm	19 mm	1149 mm	1156.1 mm	1163.2 mm


Photometric data



ESSENTIAL LEDtube 16W G5 830 APR





ESSENTIAL LEDtube 16W G5 830 APR



ESSENTIAL LEDtube 16W G5 830 APR



Essential LEDtube

Lifetime




ESSENTIAL LEDtube 8-16W G5 830-865 APR

ESSENTIAL LEDtube 8-16W G5 830-865 APR



ESSENTIAL LEDtube 8-16W G5 830-865 APR

ESSENTIAL LEDtube 8-16W G5 830-865 APR



ESSENTIAL LEDtube 16W G5 830-865 APR

Essential LEDtube

