

Ecofit Ledtubes T8

LEDtube 1500mm 20W 740 T8 AP SL G

Upgrade to efficient, long-lasting LED tubes with the Ecofit LED tubes. Ecofit LED tubes are a fast and easy way to replace your old fluorescent tubes with modern, efficient LED technology. Good quality of light with a natural lighting effect for use in general lighting applications with low initial investment – an environmentally friendly solution.

Product data

General Information		Starting Time (Nom)	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Starting Time (Nom)	0.5 s
Nominal lifetime	15,000 hour(s)	Warm-up time to 60% light	0.5 s
Switching Cycle	50,000	Power Factor (Fraction)	0.5
Lighting Technology	LED	Voltage (Nom)	220-240 V
EU RoHS compliant	Yes	Temperature	
Light Technical		Ambient temperature range	-20 °C to 45 °C
Color Code	740 [CCT of 4000K]	T-Case Maximum (Nom)	45 °C
Beam Angle (Nom)	240 degree(s)	Controls and Dimming	
Luminous Flux	2,000 lumen	Dimmable	No
Color Designation	Cool White (CW)	Mechanical and Housing	
Correlated Color Temperature (Nom)	4000 K	Product Length	1,500 mm
Luminous Efficacy (rated) (Nom)	100.00 lm/W	Bulb Shape	Tube, double-ended
Color Consistency	<7	Approval and Application	
Color rendering index (CRI)	70	Energy Saving Product	Yes
LLMF At End Of Nominal Lifetime (Nom)	70 %	Approval Marks	RoHS compliance KEMA Keur certificate
Operating and Electrical		Energy Consumption kWh/1000 h	20 kWh
Line Frequency	50 to 60 Hz		
Input Frequency	50 to 60 Hz		
Power Consumption	20 W		


Ecofit Ledtubes T8

Product Data

Full product code	871869959607100
Order product name	LEDtube 1500mm 20W 740 T8 AP SL G
Order code	929001940568
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10



Material Nr. (12NC)	929001940568
Full product name	LEDtube 1500mm 20W 740 T8 AP SL G
EAN/UPC - Case	8718699596088

Dimensional drawing




Product	D1	D2	A1	A2	A3
LEDtube 1500mm 20W 740 T8 AP SL G	25.7 mm	28 mm	1,498.5 mm	1,505.9 mm	1,513 mm

Photometric data



General uniform lighting - LEDtube 1500mm 20W 740 T8 AP SL G



Light Distribution Diagram - LEDtube 1500mm 20W 740 T8 AP SL G




Spectral Power Distribution Colour - LEDtube 1500mm 20W 740 T8 AP SL G

Ecofit Ledtubes T8


Lifetime




Life Expectancy Diagram - LEDtube 1500mm 20W 740 T8 AP SL G



Life Expectancy Diagram



Lumen Maintenance Diagram - LEDtube 1500mm 20W 740 T8 AP SL G



Life Expectancy Diagram - LEDtube 1500mm 20W 740 T8 AP SL G

Lumen Maintenance Diagram

Ecofit Ledtubes T8

