



# T12

## 16T8/LED/48-850/UF18/G 10/1

Philips UniversalFit TLEDs offer unique ballast compatibility working with both electronic (instant-start) and magnetic ballasts while meeting the revised UL1993 standards. The UniversalFit TLEDs are engineered to deliver excellent lighting effects and substantial energy savings while providing unmatched user & installer safety.

### Product data


General Information		Warm Up Time to 60% Light (Nom)	
Cap-Base	G13 [ Medium Bi-Pin Fluorescent]		0.5 s
EU RoHS compliant	Yes	UL Type	
Nominal Lifetime (Nom)	36000 h		Type A - works on ballast
Switching Cycle	50000X	Power Factor (Nom)	
			0.9
		Voltage (Nom)	
			40-330 V
Light Technical		Temperature	
Color Code	850 [ CCT of 5000K]	T-Ambient (Max)	45 °C
Beam Angle (Nom)	240 °	T-Ambient (Min)	-20 °C
Luminous Flux (Nom)	1800 lm	T-Storage (Max)	65 °C
Color Designation	Daylight	T-Storage (Min)	-40 °C
Correlated Color Temperature (Nom)	5000 K	T-Case Maximum (Nom)	60 °C
Luminous Efficacy (rated) (Nom)	112.00 lm/W	Controls and Dimming	
Color Consistency	<5	Dimmable	No
Color Rendering Index (Nom)	80	Mechanical and Housing	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Material	Glass
		Product Length	1200 mm
		Bulb Shape	Tube, double-ended
Operating and Electrical		Approval and Application	
Input Frequency	50-120000 Hz	Energy Saving Product	Yes
Power (Nom)	16 W	Approval Marks	RoHS compliance UL certificate
Lamp Current (Max)	600 mA		
Lamp Current (Min)	110 mA		
Starting Time (Nom)	0.5 s		

# T12

Energy Consumption kWh/1000 h	- kWh
<b>Product Data</b>	
Order product name	16T8/LED/48-850/UF18/G 10/1
EAN/UPC - Product	046677539986
Order code	929001966004

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001966004
Net Weight (Piece)	0.220 kg


## Dimensional drawing




4ft T8 16-32W 1800lm 240D 5000K G13 ND

Product	D1	D2	A1	A2	A3
16T8/LED/48-850/UF18/G 10/1	25.7 mm	28 mm	1198 mm	1205 mm	1212 mm


## Photometric data



LEDtube 16T8 UF18 48-850





LEDtube 16T8 UF18



© 2021 Philips Lighting B.V. Page 11



LEDtube 16T8 UF18 48-850

Lifetime




LEDtube 16T8 UF18

LEDtube 16T8 UF18



LEDtube 16T8 UF18 LifetimeVsTc

LEDtube 16T8 UF18 FailureRate



LEDtube 16T8 UF18 LumenVsTc

