



## 10T8/COR/48-840/IF16/G/DIM 10/1

The CorePro InstantFit LED lamps provide hassle-free installation with simple lamp-for-lamp replacements. They deliver what we promise, with at least 40% energy savings, flicker-free performance, and the life you would expect .Other lamps claim compatibility but only CorePro InstantFit (UL Type A) has been proven to work with over 200 ballasts and drivers, delivering even light output, with proven energy savings and a long average lifetime. End users will be delighted being under these comfortable and high quality CorePro InstantFit lamps with no visible flicker and optimized optics. Energy managers will enjoy these lamps too as they can count the savings delivered by our lamps. To enjoy more energy savings, the CorePro InstantFit lamps can be paired with the Advance TLED drivers to create a Type C system.

#### **Product data**

General Information				
Cap-Base	G13 [Medium Bi-Pin Fluorescent]			
Nominal lifetime	70,000 hour(s)			
Switching Cycle	50,000			
Lighting Technology	LED			
EU RoHS compliant	Yes			
Light Technical				
Color Code	840 [CCT of 4000K]			
Beam Angle (Nom)	240 degree(s)			
Luminous Flux	1,600 lm			
Color Designation	Cool White (CW)			
Correlated Color Temperature (Nom)	4000 K			
Luminous Efficacy (rated) (Nom)	160.00 lm/W			


Color Consistency	<6			
Color rendering index (CRI)	82			
LLMF At End Of Nominal Lifetime (Nom) 70 %				
Operating and Electrical				
Line Frequency	25000-105000 Hz			
Input Frequency	25000-105000 Hz			
Power Consumption	10 W			
Lamp Current (Max)	260 mA			
Lamp Current (Min)	100 mA			
Wattage Equivalent	32 W			
Starting Time (Nom)	0.5 s			
Warm-up time to 60% light	0.5 s			
Power Factor (Fraction)	0.9			

Datasheet, 2024, January 3 data subject to change

Voltage (Nom)	120-277, 347 V			
UL Type	UL Type A			
Temperature				
Ambient temperature range	-20 °C to 45 °C			
T-Case Maximum (Nom)	50 °C			
Controls and Dimming				
Dimmable	Yes			
Mechanical and Housing				
Bulb Finish	Frosted			
Bulb Material	Glass			
Product Length	1,200 mm			
Bulb Shape	Т8			
Approval and Application				
Energy Saving Product	Yes			


Approval Marks	RoHS compliance UL certificate DLC				
	compliance				
Energy Consumption kWh/1000 h	- kWh				
Application Conditions					
can it be used in closed luminaires	Yes				
Product Data					
Order product name	10T8/COR/48-840/IF16/G/DIM 10/1				
Full product name	10T8/COR/48-840/IF16/G/DIM 10/1				
Order code	929001991734				
Material Nr. (12NC)	929001991734				
Numerator - Quantity Per Pack	1				
EAN/UPC - Product/Case	046677553234				
Numerator - Packs per outer box	10				
EAN/UPC - Case	50046677553239				

## Dimensional drawing




Product	D1	D2	A1	A2	А3
10T8/COR/48-840/IF16/G/DIM	25.7 mm	28 mm	1,198.1 mm	1,205.2 mm	1,212.3 mm
10/1					

### Photometric data








Light Distribution Diagram - 10T8/COR/48-840/IF16/G/DIM 10/1


### Photometric data




Colodus Photometric 45 Philips Lighting B.V. Pages 19


General uniform lighting - 10T8/COR/48-840/IF16/G/DIM 10/1

## Lifetime






Life Expectancy Diagram - 10T8/COR/48-840/IF16/G/DIM 10/1




Life Expectancy Diagram - 10T8/COR/48-840/IF16/G/DIM 10/1



Life Expectancy Diagram - 10T8/COR/48-840/IF16/G/DIM 10/1

Lumen Maintenance Diagram - 10T8/COR/48-840/IF16/G/DIM 10/1

## Lifetime



Lumen Maintenance Diagram - 10T8/COR/48-840/IF16/G/DIM 10/1

