



Classic filament LEDbulbs

LED classic 150W A67 E27 CW FR ND 1SRT4

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

| General Information | |
|---|--------------------|
| Cap-Base | E27 |
| Nominal lifetime | 15,000 hour(s) |
| Switching Cycle | 20,000 |
| Rated Lifetime (Hours) | 15,000 hour(s) |
| Lighting Technology | LED |
| Flux measurement reference | Sphere |
| EU RoHS compliant | Yes |
| Light Technical | |
| Color Code | 840 [CCT of 4000K] |
| Color Code | 840 [CCT of 4000K] |
| Luminous Flux | 2,452 lm |
| Color Designation | Cool White (CW) |
| Correlated Color Temperature (Nom) | 4000 K |
| Luminous Efficacy (rated) (Nom) | 140.00 lm/W |
| Color Consistency | <6 |
| Color rendering index (CRI) | 80 |
| LLMF At End Of Nominal Lifetime (Nom) | 70 % |
| Flickering value (PstLM) - Flickering value as per EN 61000-3-3 | 1 |

| Stroboscopic effect visibility measure (SVM) | 0.4 |
|--|-------------|
| Photobiological safety according to EN 62471 | RGO |
| Operating and Electrical | |
| Line Frequency | 50 to 60 Hz |
| Input Frequency | 50 to 60 Hz |
| Power Consumption | 17.5 W |
| Lamp Current (Nom) | 150 mA |
| Wattage Equivalent | 150 W |
| Starting Time (Nom) | 0.5 s |
| Warm-up time to 60% light | 0.5 s |
| Power Factor (Fraction) | 0.51 |
| Voltage (Nom) | 220-240 V |
| Temperature | |
| T-Case Maximum (Nom) | 60 °C |
| Controls and Dimming | |
| Dimmable | No |

Classic filament LEDbulbs

Mechanical and Housing

| | |
|---------------|---------|
| Bulb Finish | Frosted |
| Bulb Material | Glass |
| Bulb Shape | A67 |

Approval and Application

| | |
|-------------------------------|------------|
| Energy Efficiency Class | D |
| Energy Consumption kWh/1000 h | 18 kWh |
| EPREL Registration Number | 374906 |
| EyeComfort | Yes |
| LED Innovations | EyeComfort |


Application Conditions

| | |
|-------------------------------------|----|
| can it be used in closed luminaires | No |
|-------------------------------------|----|

Product Data



| | |
|---------------------------------|---|
| Order product name | LED classic 150W A67 E27 CW FR ND 1SRT4 |
| Full product name | LED classic 150W A67 E27 CW FR ND 1SRT4 |
| Full product code | 871869976459300 |
| Order code | 929002372701 |
| Material Nr. (12NC) | 929002372701 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8718699764593 |
| Numerator - Packs per outer box | 4 |
| EAN/UPC - Case | 8718699764609 |

Dimensional drawing



| Product | D | C |
|---|-------|--------|
| LED classic 150W A67 E27 CW FR ND 1SRT4 | 70 mm | 121 mm |

Photometric data




General uniform lighting - LED classic 150W A67 E27 CW FR ND 1SRT4

Light Distribution Diagram - LED classic 150W A67 E27 CW FR ND 1SRT4


Classic filament LEDbulbs

Photometric data



Spectral Power Distribution Colour - LED classic 150W A67 E27 CW FR ND 1SRT4

Lifetime



Life Expectancy Diagram - LED classic 150W A67 E27 CW FR ND 1SRT4



Lumen Maintenance Diagram - LED classic 150W A67 E27 CW FR ND 1SRT4

