



## D ↑ G

# TrueForce Core LED Industrial and Retail (Highbay – HPI/SON/HPL)

### TForce Core HB MV ND 35W E27 840 G3

Philips TrueForce Core LED I&R lamps offer an easy and short payback LED solution to replace High Intensity Discharge (HID) lamps. The products bring the energy efficiency and long lifetime benefits of LED to HID replacement and provide instant saving and low initial investment. With the right lamp size and light distribution, you can easily retrofit TrueForce Core LED I&R lamps and bypass the existing ballast while enhancing the lighting quality.

#### **Product data**

General Information	
Cap-Base	E27
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
Flux measurement reference	Sphere
CE mark	Yes
EU RoHS compliant	Yes
Light Technical	
Color Code	840 [CCT of 4000K]
Beam Angle (Nom)	180 degree(s)
Luminous Flux	5,000 lm

Color Designation	Cool White (CW)	
Correlated Color Temperature (Nom)	4000 K	
Luminous Efficacy (rated) (Nom)	142.00 lm/W	
Color Consistency	<6	
Color rendering index (CRI)	80	
LLMF At End Of Nominal Lifetime (Nom)	70 %	
Operating and Electrical		
Line Frequency	50 to 60 Hz	
Input Frequency	50 to 60 Hz	
Power Consumption	35 W	
Lamp Current (Nom)	178 mA	
Starting Time (Nom)	0.5 s	


Datasheet, 2024, March 15 data subject to change

# TrueForce Core LED Industrial and Retail (Highbay - HPI/SON/HPL)

Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	220-240 V
Inrush current at mains	20.5
Max. lamp no. on MCB B type 10A - Mains	7
Max. lamp no. on MCB B type 10A – EM ballast	-
without Comp. Cap.	
Max. lamp no. on MCB B type 10A – EM ballast	-
with Comp. Cap.	
Max. lamp no. on MCB B type 16A - Mains	11
Max. lamp no. on MCB B type 16A – EM ballast	-
without Comp. Cap.	
Max. lamp no. on MCB B type 16A – EM ballast	-
with Comp. Cap.	
Ballast Compatibility	Mains
Temperature	
Ambient temperature range	-20 °C to 45 °C
T-Case Maximum (Nom)	76 °C
Controls and Dimming	
Dimmable	No

Mechanical and Housing		
Bulb Finish	Frosted	
Bulb Shape	T-shape	
Approval and Application		
Energy Efficiency Class	D	
Energy Consumption kWh/1000 h	35 kWh	
EPREL Registration Number	403633	
Product Data		
Order product name	TForce Core HB MV ND 35W E27 840	
	G3	
Full product name	TForce Core HB MV ND 35W E27 840	
	G3	
Full product code	871869978107100	
Order code	929002406702	
Material Nr. (12NC)	929002406702	
Numerator - Quantity Per Pack	1	
EAN/UPC - Product/Case	8718699781071	
Numerator - Packs per outer box	6	
EAN/UPC - Case	8718699781088	


## Dimensional drawing




Product	D	С
TForce Core HB MV ND 35W E27 840 G3	118 mm	193 mm

## TrueForce Core LED Industrial and Retail (Highbay - HPI/SON/HPL)


#### Photometric data






Light Distribution Diagram - TForce Core HB MV ND 35W E27 840 G3


General uniform lighting - TForce Core HB MV ND 35W E27 840 G3



Spectral Power Distribution Colour - TForce Core HB MV ND 35W E27 840 G3

## Lifetime





Life Expectancy Diagram - TForce Core HB MV ND 35W E27 840 G3

Lumen Maintenance Diagram - TForce Core HB MV ND 35W E27 840 G3

# TrueForce Core LED Industrial and Retail (Highbay - HPI/SON/HPL)



© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.