



Ecofit Ledtubes T8



Ecofit LEDtube 600mm HO 9W 865 T8

Upgrade to efficient, long-lasting LED tubes with the Ecofit LED tubes. Ecofit LED tubes are a fast and easy way to replace your old fluorescent tubes with modern, efficient LED technology. Good quality of light with a natural lighting effect for use in general lighting applications with low initial investment – an environmentally friendly solution.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	30000 h
Switching Cycle	50000X
Technical Type	9-18W
Flux measurement reference	Sphere
Light Technical	
Color Code	865 [CCT of 6500K]
Beam Angle (Nom)	240 °
Luminous Flux (Nom)	900 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	100.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Nom)	9 W

Lamp Current (Nom)	78 mA
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.5
Voltage (Nom)	220-240 V
Temperature	
T-Ambient (Max)	45 °C
T-Ambient (Min)	-20 °C
T-Storage (Max)	65 °C
T-Storage (Min)	-40 °C
T-Case Maximum (Nom)	55 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Glass
Product Length	600 mm
Bulb Shape	Tube, single-ended

Ecofit Ledtubes T8

Approval and Application


Energy Efficiency Class	F
Energy Saving Product	Yes
Approval Marks	RoHS compliance CE marking KEMA Keur certificate
Energy Consumption kWh/1000 h	9 kWh
EPREL Registration Number	491857

Product Data

Full product code	871951426606300
-------------------	-----------------

Order product name	Ecofit LEDtube 600mm HO 9W 865 T8
EAN/UPC - Product	8719514266063
Order code	929002445802
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	20
Material Nr. (12NC)	929002445802
Net Weight (Piece)	0.135 kg


Dimensional drawing




LEDtube 600mm 9-18W 900lm 6500K G13

Product	D1	D2	A1	A2	A3
Ecofit LEDtube 600mm HO 9W 865 T8	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm

Photometric data




LEDtube 9W G13 900lm 2



LEDtube 9W G13 900lm 865

Ecofit Ledtubes T8



Photometric data



©2020 Osram Opto Semiconductors AG, Regensburg, DE Page 10



LEDtube ECO 9W G13 900lm 865

Lifetime



LEDtube 30K

LEDtube 30K FailureRate




LEDtube 30K LifetimeVsTc

LEDtube 9W 30K LumenVsTc

Ecofit Ledtubes T8

Lifetime



LEDtube 30K

