



LuxSpace Pro

DN594B LED36/CED P31PSD D200 VWB G2

LuxSpace Pro, 30.7 W, Tunable White Bio-up Cyan Enhanced Spectrum CRI80, DALI, IP20 | Finger-protected

Philips LuxSpace Pro builds on the LuxSpace family's reputation for superb performance, extremely low energy use, high visual comfort and appearance design. This next generation of reliable LED downlights comes in an elegant design with a deep, recessed architecture and increased reflector depth to highlight the smallest of details. LuxSpace Pro is also a shining example of versatility. This energy-saving LED downlight is available in a comprehensive range of configurations from 450 to 8,000 lumen, 3inch to 8inch, with the option to choose fixed, dimmable, or Interact Ready variants. This makes LuxSpace Pro the perfect 'mix and match' solution for potentially broad and extended applications that require different lighting ambiances, with one cohesive luminaire look and feel.

Product data

General Information		Operating and Electrical	
Light source engine type	LED	Input Voltage	220 to 240 V
Light Technical		Line Frequency	50 or 60 Hz
Luminous Flux	3,600 lm	Power Consumption	30.7 W
Correlated Color Temperature (Nom)	Tunable white 2700-6500 K	Power Factor (Fraction)	0.9
Luminous Efficacy (rated) (Nom)	106 lm/W	Number of products on MCB of 16 A type B	100
Color rendering index (CRI)	>80	Protection class IEC	Safety class II
Light source color	Tunable White Bio-up Cyan Enhanced Spectrum CRI80	Controls and Dimming	
Optic type	Beam angle 60 to 120°	Dimmable	DALI
Unified glare rating CEN	26	Control interface	DALI

LuxSpace Pro

Mechanical and Housing

Housing Material	Aluminum Alloy
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	White
Optical cover finish	Matte
Overall height	125 mm
Overall diameter	212 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.35 J reinforced]
Optical cover type	Polycarbonate Diffuser
Net Weight (Piece)	1.260 kg

Approval and Application

CE mark	Yes
---------	-----

Ambient temperature range	-20 to +40 °C
---------------------------	---------------

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	DN594B LED36/CED P31PSD D200 VWB G2
Full product name	DN594B LED36/CED P31PSD D200 VWB G2
Order code	911401504944
Material Nr. (12NC)	911401504944
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

