



# CoreLine Downlight gen5

## DN142B 20S/830 PSU-E WR

CoreLine Downlight gen5, 19.2 W, D200 mm, 2350 lm, 3000 K, White reflector, IP20

Philips CoreLine Downlight delivers on the CoreLine promise of innovative, easy to use and high-quality recessed downlights. The CoreLine Downlight range is suitable for one-to-one conventional luminaire replacements, with an attractive TCO that helps your customers make the switch to LED. These recessed indoor downlights offer uniform light distribution for use in general lighting and office applications (UGR 19). They also deliver instant energy savings and have a much longer lifetime, creating a solution that's environmentally friendly and real value-for-money. CoreLine DN142B recessed downlights are easy to install thanks to their standard cut-out size and push-in connectors. An Interact ready option with integrated wireless communications is also available in this family, which can be used with Interact gateways, sensors and software.

### Warnings and Safety

- Do not apply excessive force to the cable & DC connector, make sure the connector clip is locked before the power is on.

### Product data

General Information		Light Technical	
Light source replaceable	No	Luminous Flux	2,350 lm
Number of gear units	1 unit	Luminous Efficacy (rated) (Nom)	122 lm/W
Driver included	Yes	Saturated Red (R9)	<50
Lighting Technology	LED	Correlated Color Temperature (Nom)	3000 K
Value ladder	Performance	Color rendering index (CRI)	>80

# CoreLine Downlight gen5

Flickering value (PstLM) - Flickering value as per EN 61000-3-3	0.5
Stroboscopic effect visibility measure (SVM)	1
Beam angle of light source	- degree(s)
Light source color	830 warm white
Optic type	-
Luminaire light beam spread	84°
Unified glare rating CEN	25
Total harmonic distortion	35 %

## Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	- W W
Average CLO power consumption	- W W
Inrush current	10 A
Inrush time	0.002 ms
Power Consumption	19.2 W
Power Factor (Fraction)	0.9
Connection	Push-in connector 4-pole
Cable	2 cables 0.15m with connectors 2-pole
Number of products on MCB of 16 A type B	100

## Temperature

Ambient temperature range	-20 to +40 °C
---------------------------	---------------

## Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit external (On/Off)
Control interface	-
Constant light output	No

## Mechanical and Housing

Housing Material	Polycarbonate
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	-
Housing Color	White
Optical cover finish	-
Reflector Finish	White reflector
Overall height	105 mm
Overall diameter	216 mm

## Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Sustainability rating	-
Protection class IEC	Safety class II
Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	CE mark
ENEC mark	-
Warranty period	5 years
Photobiological risk	Photobiological risk group 1 @ 200mm to EN62471
EU RoHS compliant	Yes

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.435,0.404) SDCM≤5
Power consumption tolerance	+/-10%

## Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	50 %
Lumen maintenance at median useful life* 50000 h	L80

## Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	Not applicable
Suitable for random switching	Yes

## Product Data

Order product name	DN142B 20S/830 PSU-E WR
Full product name	DN142B 20S/830 PSU-E WR
Full product code	872016950297099
Order code	911401551832
Material Nr. (12NC)	911401551832
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.410 kg
EAN/UPC - Product/Case	8720169502970
Numerator - Packs per outer box	6
EAN/UPC - Case	8720169503298

# CoreLine Downlight gen5

## Dimensional drawing

