



CoreView G4 RC420B

RC420V G4 LED35/940 W60L60 PSU

CoreView G4 RC420B, 100 lm/W, 940 neutral white

RC420B G4 inherits the elegant and classic indirect light design from previous generation but with slimmer outlook. It offers 3 types, 600x600, 300x1200, and 600x1200 (Customized offer)mm with max: 108lm/w. Air slot option applies to 600x1200mm type to give fast and easy support to the projects where air outlet is required from the office lighting fittings. Full indirect light design provides visual comfort in the office area as well.

Product data

General Information		Protection class IEC	
Color Code	940 neutral white	Safety class II	
Light source engine type	LED	Controls and Dimming	
Value ladder	Performance	Dimmable	No
Light Technical		Control interface	-
Luminous Flux	3,600 lm	Mechanical and Housing	
Correlated Color Temperature (Nom)	4000 K	Housing Material	Steel
Luminous Efficacy (rated) (Nom)	100 lm/W	Optical cover material	Polycarbonate
Color rendering index (CRI)	>90	Housing Color	White RAL 9003
Light source color	940 neutral white	Optical cover finish	Frosted
Operating and Electrical		Ingress protection code	IP20 [Finger-protected]
Input Voltage	220 to 240 V	Mech. impact protection code	-
Line Frequency	50 or 60 Hz	Optical cover type	-
Power Consumption	36 W	Net Weight (Piece)	3,340 kg
Power Factor (Fraction)	0.9	Approval and Application	
Number of products on MCB of 16 A type B	40	CE mark	Yes

CoreView G4 RC420B

Ambient temperature range	-20 to +45 °C
---------------------------	---------------

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	RC420V G4 LED35/940 W60L60 PSU
--------------------	--------------------------------

Full product name	RC420V G4 LED35/940 W60L60 PSU
-------------------	--------------------------------

Order code	911401595071
------------	--------------

Material Nr. (12NC)	911401595071
---------------------	--------------

Numerator - Quantity Per Pack	1
-------------------------------	---

Numerator - Packs per outer box	2
---------------------------------	---

Dimensional drawing

