



# CoreLine Recessed Spot gen2

**RS151B LED6-WB-/830 D78HALOX PSR PI6 WH**

CoreLine Recessed Spot gen2, Adjustable, 7.2 W, D78 mm, HALOX, 680 lm, 3000 K, Phase-cut dim, Wide beam, White, IP20/44

CoreLine Recessed Spot gen2 delivers on the CoreLine promise of innovative, easy to use and high-quality luminaires. Its modular design allows “configure to fit” option that better responds to your specific needs. The range offers a wide range choice on light color (CCT), light output, color finish, frame types and connectivity options. The compact and lite design of CoreLine Recessed Spot gen2, always incorporating a push in connector allowing through-wiring and supporting a wide range of wire diameters/cross-sectional area, makes installation hassle-free. High quality of light, numerous connectivity options, long luminaire lifetime and high system efficacy makes CoreLine Recessed Spot gen2 an ideal accent solution for your indoor spot lighting applications.

## Warnings and Safety

- The luminaire should be installed and disassembled by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements, as per the product mounting instructions.

## Product data

General Information		Value ladder	Performance
Light source replaceable	Yes		
Number of gear units	1 unit		
Driver included	Yes		
Lighting Technology	LED		
Light Technical			
Luminous Flux			680 lm
Luminous Efficacy (rated) (Nom)			94 lm/W
Saturated Red (R9)			<50

## CoreLine Recessed Spot gen2

Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	>80
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Beam angle of light source	120 degree(s)
Light source color	830 warm white
Optic type	Wide beam
Luminaire light beam spread	38°
Unified glare rating CEN	21
Total harmonic distortion	45 %

### Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Average CLO power consumption	- W
Inrush current	2.5 A
Inrush time	0.1 ms
Power Consumption	7.2 W
Power Factor (Fraction)	0.9
Connection	Push-in connector 3-pole
Cable	Cable 0.25 m with connector 3-pole
Number of products on MCB of 16 A type B	40

### Temperature

Ambient temperature range	0 to +35 °C
---------------------------	-------------

### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit regulating
Control interface	Phase-cut dim
Constant light output	No

### Mechanical and Housing

Housing Material	Aluminum die-cast
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	White
Optical cover finish	-
Overall height	60 mm
Overall diameter	95 mm
Compatible ceiling or ceiling installation accessory type	Halox®100 concrete ceiling installation accessory version ("tunnel 190" needed for external drivers)

### Approval and Application

Ingress protection code	IP20/44 [Finger-protected; wire-protected, splash-proof]
-------------------------	--

Mech. impact protection code	IK03 [0.3 J]
Protection class IEC	Safety class II
Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
Warranty period	5 years
Photobiological risk	Photobiological risk group 1 @200mm to EN62778
Photobiological risk specification	0.2 m
EU RoHS compliant	Yes

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.43, 0.40) SDCM <5
Power consumption tolerance	+/-10%
Standard Deviation of Colour Matching (McAdam ellipse)	SDCM≤5

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	70

### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	10% (depends on dimmer, ELV)
Suitable for random switching	No

### Product Data

Order product name	RS151B LED6-WB-/830 D78HALOX PSR P16 WH
Full product name	RS151B LED6-WB-/830 D78HALOX PSR P16 WH
Full product code	871951493843499
Order code	911401811284
Material Nr. (12NC)	911401811284
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.330 kg
EAN/UPC - Product/Case	8719514938434
Numerator - Packs per outer box	18
EAN/UPC - Case	8719514938540

# CoreLine Recessed Spot gen2

## Dimensional drawing

