



Coreline tempo large

BVP130 LED210-4S/830 PSU OFA52 ALU C1KC3

Coreline tempo large, Floodlight, 178 W, 20000 lm, 3000 K, CRI80, Asymmetrical, IP66

CoreLine tempo large delivers on the CoreLine promise of innovative, easy to use and high quality luminaires. A narrow range of options makes it easy to find the best lux-for-lux replacement for 150W, 250W, and 400W HID lamps. The CoreLine tempo large floodlighting range offers lumen packages for many different application areas as well as a choice of high-performance asymmetrical and symmetrical optics. The installation is made easy thanks to the U-shaped universal mounting bracket and the external quick 3-poles connector. It is an ideal solution for outdoor areas such as tempo floodlights for industrial/commercial areas, parking lots, etc.

Product data

General Information		Operating and Electrical	
Lamp family code	LED210-4S [LED module, system flux 21000 lm]	Correlated Color Temperature (Nom)	3000 K
Number of gear units	1 unit	Luminous Efficacy (rated) (Nom)	115 lm/W
Driver included	Yes	Color rendering index (CRI)	80
Light source engine type	LED	Light source color	830 warm white
Value ladder	Performance	Luminaire light beam spread	52° x 102°
Serviceability class	Class C, luminaire without serviceable parts, not serviceable	Optic type outdoor	Asymmetrical
Warranty period	5 years	Effective projected area	0.15 m²
Sustainability rating	-		
Light Technical		Operating and Electrical	
Upward light output ratio	0	Input Voltage	220 to 240 V
Luminous Flux	20,000 lm	Line Frequency	50 to 60 Hz
		Inrush current	58 A
		Inrush time	0.34 ms
		Power Consumption	178 W
		Power Factor (Fraction)	0.96

Coreline tempo large

Connection	External connector
Cable	Cable 1.0 m with plug Wieland/Adels compatible 3-pole
Number of products on MCB of 16 A type B	7
Protection class IEC	Safety class I
Surge Protection (Common/Differential)	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Glass
Fixation material	Aluminum
Housing Color	Grey
Mounting device	Wall-mounting bracket
Optical cover shape	Flat
Optical cover finish	Clear
Overall length	340.5 mm
Overall width	422 mm
Overall height	40 mm
Dimensions (Height x Width x Depth)	40 x 422 x 341 mm
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Optical cover type	Flat glass
Net Weight (Piece)	7.500 kg

Emergency Operation

Central Emergency	No
Emergency lighting	-

Approval and Application

Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
Photobiological risk	Photobiological risk group 1 @200mm to EN62778
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Ambient temperature range	-40 to +45 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.382, 0.379) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L80

Product Data

Order product name	BVP130 LED210-4S/830 PSU OFA52 ALU C1KC3
Full product name	BVP130 LED210-4S/830 PSU OFA52 ALU C1KC3
Full product code	872016979983700
Order code	912300060606
Material Nr. (12NC)	912300060606
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169799837
Numerator - Packs per outer box	1
EAN/UPC - Case	8720169799837
Product family code	BVP130 [CORELINE TEMPO LARGE]

Coreline tempo large

Dimensional drawing

