



# GreenSpace

## DN470T LED20S/830 DIA-VLC D22H16 5C6 GR

GreenSpace, Track-mounted, 16.2 W, D218 mm, 2200 lm, 3000 K, DALI, Interact Ready, High-gloss reflector, VLC, IP20

GreenSpace is a perfect solution where customers want to strike the ideal balance between their initial investment and the cost of the installation during its lifetime while they are covering multiple applications. GreenSpace features the latest LED technology which enables extremely low power consumption. With its perfect fit you'll get the LED downlight that always fits and looks perfect at the same time. This perfect fit is available for cut out sizes from 150mm to 280mm which is the ideal solution for your renovation project. It saves the hassle, avoids time consuming and costly adaptor rings. GreenSpace is designed for Circular Economy with optimized performance, extended lifetime through upgradability and integration options, ease of customization, recycling and disassembly. Housing and rim are made with at least 55% recycled or mass-balanced bio-circular material, making it a conscious choice for those that want to contribute to a circular economy. GreenSpace can be connected to wireless systems to create a smart office lighting solution with optional integrated sensors as well.

### Product data

General Information	
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Connectivity	Interact Ready
Lighting Technology	LED
Value ladder	Specification
Light Technical	
Luminous Flux	2,200 lm

Luminous Efficacy (rated) (Nom)	134 lm/W
Saturated Red (R9)	<50
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	>80
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Beam angle of light source	120 degree(s)
Light source color	830 warm white
Optic type	-

Luminaire light beam spread	120°
Unified glare rating CEN	22
Total harmonic distortion	20 %

## Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	- W
Average CLO power consumption	- W
Inrush current	20.4 A
Inrush time	0.195 ms
Power Consumption	16.2 W
Power Factor (Fraction)	0.9
Connection	Connection unit 5-pole
Cable	-
Number of products on MCB of 16 A type B	24

## Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

## Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Dali dimming Intaract System ready visual light communicaton enabled
Control interface	DALI
Constant light output	No
DALI Standard	D4i™ DALI-2™

## Mechanical and Housing

Housing Material	Polycarbonate
Reflector material	Polycarbonate aluminum coated
Optic material	-
Optical cover material	-
Fixation material	-
Housing Color	Gray
Optical cover finish	-
Reflector Finish	High-gloss reflector
Overall height	157 mm
Overall diameter	218 mm

## Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Sustainability rating	Lighting for circularity
Protection class IEC	Safety class II
Glow-wire test	Temperature 650 °C, duration 5 s

Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
Warranty period	5 years
EU RoHS compliant	Yes

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.43, 0.40) SDCM<3
Power consumption tolerance	+/-10%
Standard Deviation of Colour Matching (McAdam ellipse)	SDCM≤3

## Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	1 %
Lumen maintenance at median useful life* 35000 h	-
Lumen maintenance at median useful life* 50000 h	L90
Lumen maintenance at median useful life* 75000 h	-
Lumen maintenance at median useful life* 100000 h	L80

## Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	No

## Product Data

Order product name	DN470T LED20S/830 DIA-VLC D22H16 5C6 GR
Full product name	DN470T LED20S/830 DIA-VLC D22H16 5C6 GR
Full product code	871951456485500
Order code	912500103030
Material Nr. (12NC)	912500103030
Numerator - Quantity Per Pack	1
Net Weight (Piece)	1.300 kg
EAN/UPC - Product/Case	8719514564855
Numerator - Packs per outer box	1
EAN/UPC - Case	8719514564855

## Dimensional drawing

