



# PL-T Triple 4-Pin Base Energy Advantage

## PL-T 42W/835/XEW/A/4P/33W 1CT/5X10 ALTO

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.


### Product data

General Information		Controls and Dimming	
Cap-Base	GX24q-4	Dimmable	Yes
Features	ALTO® (ALTO)		
Light Technical		Mechanical and Housing	
Color Code	835 [CCT of 3500K]	Net Weight (Piece)	83.000 g
Luminous Flux	2,300 lm		
Color Designation	White (WH)	Approval and Application	
Correlated Color Temperature (Nom)	3500 K	Mercury (Hg) Content (Nom)	1.4 mg
Luminous Efficacy (rated) (Nom)	67 lm/W		
Color rendering index (CRI)	82	Product Data	
Operating and Electrical		Order product name	PL-T 42W/835/XEW/A/4P/33W 1CT/5X10 ALTO
Power Consumption	34.5 W	Full product name	PL-T 42W/835/XEW/A/4P/33W 1CT/5X10 ALTO
Lamp Current (Nom)	0.320 A	Order code	927908183520
		Material Nr. (12NC)	927908183520
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	046677220280

## PL-T Triple 4-Pin Base Energy Advantage


Numerator - Packs per outer box	10
EAN/UPC - Case	50046677220285

### Dimensional drawing



Product	D (max)	B (max)	C (max)
PL-T 42W/835/XEW/A/4P/33W 1CT/5X10 ALTO	41.0 mm	145.0 mm	160.7 mm

### Photometric data



Spectral Power Distribution Colour - PL-T 42W/835/XEW/A/4P/33W 1CT/5X10 ALTO

