



TL-E LIFEMAX

Standard Colours

22 W G10q Cool daylight Circular fluorescent

This circular TL lamp (tube diameter 29 mm) enables omni-directional light distribution. It is suitable for use in a wide range of luminaires for various purposes where color rendering is not important.

Product data

General Information	
Cap-Base	G10q
Nominal lifetime	8,000 hour(s)
Life to 50% Failures (Nom)	13,000 hour(s)

Light Technical	
Color Code	54-765
Luminous Flux	1,050 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6200 K
Luminous Efficacy (rated) (Nom)	48 lm/W
Color rendering index (CRI)	72

Operating and Electrical	
Power Consumption	22.0 W
Lamp Current (Nom)	0.400 A
Voltage (Nom)	62 V

Controls and Dimming	
Dimmable	Yes


Mechanical and Housing	
Bulb Shape	C-T29
Net Weight (Piece)	0.110 kg

Approval and Application	
Mercury (Hg) Content (Nom)	9 mg

Product Data	
Order product name	22 W G10q Cool daylight Circular fluorescent
Full product name	22 W G10q Cool daylight Circular fluorescent
Full product code	871150063390300
Order code	928026205436
Material Nr. (12NC)	928026205436
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500633903
Numerator - Packs per outer box	20
EAN/UPC - Case	8711500633910


TL-E LIFEMAX Standard Colours

Dimensional drawing



Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
22 W G10q Cool daylight	30.9 mm	26.2 mm	205.0 mm	213.5 mm	149.1 mm	155.6 mm
Circular fluorescent						

Photometric data



Spectral Power Distribution Colour - TL-E 22W/54-765 1CT/20

