



MSD Platinum (Touring/Stage)

MSD Silver 330W UNP/24

The MSD Platinum lamps open up new levels of creative freedom in entertainment lighting, with powerful, compact and brilliantly intense light. Their compact, lightweight design provides the freedom to create smaller, lighter luminaires – for use at any location on stage. And their short arc, high color temperature and innovative reflector produce a sparkling, high beam intensity for outstanding color reproduction. They also offer long and reliable lifetime, high efficacy and fast replacement times. It all adds up to an intensely exciting creative experience.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	-
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	1,000 hour(s)

Light Technical	
Color Code	2
Luminous Flux	14,400 lm
Chromaticity Coordinate X (Nom)	299
Chromaticity Coordinate Y (Nom)	303
Correlated Color Temperature (Nom)	8000 K
Color rendering index (CRI)	-

Arc Length O (Nom)	1.3 mm
--------------------	--------

Operating and Electrical	
Power Consumption	330 W

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Net Weight (Piece)	83.000 g


Product Data	
Order product name	MSD Silver 330W UNP/24

MSD Platinum (Touring/Stage)

Full product name	MSD Silver 330W UNP/24
Full product code	871869676770200
Order code	928495505308
Material Nr. (12NC)	928495505308
Numerator - Quantity Per Pack	1

EAN/UPC - Product/Case	8718696767702
Numerator - Packs per outer box	24
EAN/UPC - Case	8718696767702

Dimensional drawing



Product	D (max)	O	C (max)
MSD Silver 330W UNP/24	56.5 mm	1.3 mm	62.6 mm

