



# MSD Platinum (Touring/Stage)

## MSD Silver 480W LL UNP/24

The MSD Platinum lamps open up new levels of creative freedom in entertainment lighting, with powerful, compact and brilliantly intense light. Their compact, lightweight design provides the freedom to create smaller, lighter luminaires – for use at any location on stage. And their short arc, high color temperature and innovative reflector produce a sparkling, high beam intensity for outstanding color reproduction. They also offer long and reliable lifetime, high efficacy and fast replacement times. It all adds up to an intensely exciting creative experience.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	1,500 hour(s)
Life to 50% Failures entertainment cycle (Nom)	4,000 hour(s)
Light Technical	
Color Code	2
Luminous Flux	25,000 lm
Chromaticity Coordinate X (Nom)	297
Chromaticity Coordinate Y (Nom)	303
Correlated Color Temperature (Nom)	7800 K
Arc Length O (Nom)	1.2 mm


Operating and Electrical	
Power Consumption	480 W
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Net Weight (Piece)	138.000 g
Product Data	
Order product name	MSD Silver 480W LL UNP/24
Full product name	MSD Silver 480W LL UNP/24
Full product code	692234199969700

## MSD Platinum (Touring/Stage)

Order code	928498305308
Material Nr. (12NC)	928498305308
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6922341999697

Numerator - Packs per outer box	24
EAN/UPC - Case	6922341993305

### Dimensional drawing



Product	D (max)	O	C (max)
MSD Silver 480W LL UNP/24	58.5 mm	1.2 mm	72 mm

