



CorePro LED spot MV



Corepro LEDspot 4.6-50W GU10 830 36D

CorePro, LEDspot, PAR16, 50 W, GU10, 3000 K, 370 lm, CRI 80, 15000 hour(s), Glass

CorePro LEDspots are a perfect fit for spot lighting and deliver warm halogen-like light. These GU10 LED spot lights are compatible with most existing fixtures with a GU10 LED base and are designed as a retrofit replacement for halogen or incandescent spots. CorePro LEDspots deliver significant energy savings and minimize maintenance costs.

Product data

General Information	
Cap-Base	GU10
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDspot
Flux measurement reference	Narrow Cone
Warranty period	2 years
Light Technical	
Color Code	830 [CCT of 3000K]
Beam Angle (Nom)	36 degree(s)
Luminous Flux	370 lm
Luminous Intensity (Nom)	740 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	80.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80

LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux in 90° Cone (Rated)	370 lm
Photobiological safety according to EN 62471	RG1

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	4.6 W
Lamp Current (Nom)	39 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	220-240 V

Temperature	
T-Case Maximum (Nom)	72 °C

CorePro LED spot MV

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Finish	Clear
Bulb Material	Glass
Bulb Shape	PAR16
Net Weight (Piece)	0.045 kg

Approval and Application

Energy Efficiency Class	F
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	5 kWh
EPREL Registration Number	391858
CE mark	Yes
EU RoHS compliant	Yes
EyeComfort	Yes
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4

Ambient temperature range	-20 to +45 °C
---------------------------	---------------


Application Conditions

can it be used in closed luminaires	No
Wireless Technology	Not applicable

Product Data



Order product name	Corepro LEDspot 4.6-50W GU10 830 36D
Full product name	Corepro LEDspot 4.6-50W GU10 830 36D
Full product code	871869672837600
Order code	929001218102
Material Nr. (12NC)	929001218102
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696728376
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696728383

Dimensional drawing



Product	D	C
Corepro LEDspot 4.6-50W GU10 830 36D	50 mm	54 mm

Photometric data



© 2024 Philips Lighting B.V. All rights reserved. Page 10

Spectral Power Distribution Colour - Corepro LEDspot 4.6-50W GU10 830 36D

Accent Lighting Spots - Corepro LEDspot 4.6-50W GU10 830 36D

