



# Xitanium LED downlight and spotlight drivers

## Xitanium 40W/m 0.7-1.05A 44V DS I 230V

Xitanium LED drivers are leading the way in terms of reliability

### Product data

General Information	
Lighting Technology	LED
Operating and Electrical	
Output Current Ripple (Max)	4 %
Output Current (Max)	1050 mA
Open Circuit Voltage (DC) (Max)	60 V
Output Power (Max)	40 W
Output Power (Min)	12 W
Output Current (Min)	700 mA
Output Voltage (Max)	44 V
Output Voltage (Min)	5 V
Protection class IEC	Safety class I/II
System characteristics	
Central DC Operation	Yes
YellowDot ready	No
Temperature	
T-Case Lifetime (Max)	80 °C

T-Case Maximum (Max)	80 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Product Length	156 mm
Overall length	156 mm
Overall width	43 mm
Overall height	30 mm
Dimensions (Height x Width x Depth)	30 x 43 x 156 mm
Ingress protection code	IP20 [Finger-protected]
Net Weight (Piece)	0.135 kg
Approval and Application	
Isolation Classification	Class I and Class II
Approval Marks	CE marking CB Certificate ENEC certificate CCC certificate RCM compliance
Output Current Set Options	Dipswitch

## Xtanium LED downlight and spotlight drivers

### Product Data

Order product name	Xtanium 40W/m 0.7-1.05A 44V DS I 230V
Full product name	Xtanium 40W/m 0.7-1.05A 44V DS I 230V
Full product code	871951439632600
Order code	929002880206
Material Nr. (12NC)	929002880206

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514396326
Numerator - Packs per outer box	40
EAN/UPC - Case	8719514396333

