



CertaFlux LED strip HV4



CertaFlux LED Strip 2ft MF 840 HV5

The CertaFlux LED Strip is an ideal product for several different applications: office, industry and waterproof. CertaFlux LED strip is upgraded with a higher lm/W performance, now reaching up to 165lm/W. The CertaFlux LED strips offer a good product performance and functionality meeting the market needs for basic lighting. The system is cost effective when combined with CertaDrive linear LED drivers.

Product data

General Information	
Lighting Technology	LED
Light Technical	
Luminous Flux	2,200 lm
Life to 70% Lumen Maintenance	60,000 hour(s)
Color Consistency Initial	3
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	177 lm/W
Color rendering index (CRI)	80
Temperature	
T-Case Lifetime (Max)	85 °C
T-Case Maximum (Max)	85 °C
Mechanical and Housing	
Overall length	559.2 mm
Overall width	20 mm
Overall height	2.7 mm
Dimensions (Height x Width x Depth)	3 x 20 x 559 mm

Net Weight (Piece)	0.040 kg
Approval and Application	
Energy Efficiency Class	C
Approval Marks	CE marking ENEC certificate
EPREL Registration Number	1342506
Product Data	
Order product name	CertaFlux LED Strip 2ft MF 840 HV5
Full product name	CertaFlux LED Strip 2ft MF 840 HV5
Full product code	871951447085900
Order code	929002938306
Material Nr. (12NC)	929002938306
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514470859
Numerator - Packs per outer box	110
EAN/UPC - Case	8719514470866