

LED Glass HID lamps

34GC/LED/850 EX39 BB 6/1

Philips Glass HID lamps offer you an easy, short-payback LED solution to replace High Intensity Discharge (HID) lamps. Thanks to our High-Power LED filament technology, this new generation of indoor/outdoor glass lamps brings all the energy-efficiency and long-lifetime benefits of LED to HID replacement, while providing instant savings with a low initial investment. They are designed to have the same aesthetics, lamp size and light distribution as the HID lamps they are replacing, so the upgrade to LED is easier than ever!

Product data

General Information		Power Consumption	
Cap-Base	EX39 [Exclusionary Mogul Screw]	Lamp Current (Max)	352 A
Nominal lifetime	50,000 hour(s)	Lamp Current (Nom)	120 277 mA A
Switching Cycle	50,000	Starting Time (Nom)	0.5 s
Lighting Technology	LED	Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.9
		Voltage (Nom)	120-277 V
		UL Type	HIB_UL Type B (UL Listed+Classified)
Light Technical		Temperature	
Color Code	850 [CCT of 5000K]	T-Case Maximum (Nom)	55.96 °C
Beam Angle (Nom)	300 degree(s)		
Luminous Flux	6,000 lm	Controls and Dimming	
Color Designation	Daylight	Dimmable	Only with specific dimmers
Correlated Color Temperature (Nom)	5000 K		
Luminous Efficacy (rated) (Nom)	176 lm/W	Mechanical and Housing	
Color Consistency	<6	Bulb Finish	Clear
Color rendering index (CRI)	80	Bulb Shape	ED28
LLMF At End Of Nominal Lifetime (Nom)	70 %	Net Weight (Piece)	0.195 kg
Photobiological safety according to EN 62471	RG1		
Operating and Electrical			
Input Frequency	50 to 60 Hz		

LED Glass HID lamps

Approval and Application

Approval Marks	DLC compliance
EU RoHS compliant	Yes
Ambient temperature range	-20 to +45 °C

Application Conditions


can it be used in closed luminaires	Yes
-------------------------------------	-----

Product Data

Order product name	34GC/LED/850 EX39 BB 6/1
--------------------	--------------------------



Full product name	34GC/LED/850 EX39 BB 6/1
Order code	929003773204
Material Nr. (12NC)	929003773204
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677588212
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677588217

Dimensional drawing



Product	D	C
34GC/LED/850 EX39 BB 6/1	91.5 mm	216 mm

Photometric data




Spectral Power Distribution Colour - 34GC/LED/850 EX39 BB 6/1

Light Distribution Diagram - 34GC/LED/850 EX39 BB 6/1

LED Glass HID lamps

Photometric data



Technical Parameters 43 Philips Lighting B.V. Page 10

General uniform lighting - 34GC/LED/850 EX39 BB 6/1

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 34GC/LED/850 EX39 BB 6/1

