

# CERTIFICATE

No. U6 102213 0262 Rev. 00

**Holder of Certificate:** **Signify (China) Investment Co., Ltd.**

Building No. 9, Lane 888, Tianlin Road  
Minhang  
200233 Shanghai  
PEOPLE'S REPUBLIC OF CHINA

**Certification Mark:**




**Product:** **Power supply  
(LED Driver)**

The product was voluntarily tested according to the listed standards. The product can be marked with the certification mark shown above. It is not permitted to alter the certification mark in any way. In addition, the certificate holder must not transfer the certificate to third parties. All applicable requirements of the Testing, Certification, Validation and Verification Regulations of TÜV SÜD Group have to be complied. For details see: [www.tuvsud.com/ps-cert](http://www.tuvsud.com/ps-cert)

**Test report no.:** 64142200108105A

**Date,** 2024-11-08

  
( Michael Xu )

# CERTIFICATE

No. U6 102213 0262 Rev. 00

**Model(s):**

Xi LED Transformer 30W TD 24VDC G2,  
Xi LED Transformer 100W TD 24VDC G2,  
Xi LED Transformer 60W TD 24VDC G2,  
Xi LED Transformer 200W TD 24VDC G2

**Brand Name:**

PHILIPS

# PHILIPS

**Parameters:**

|                                    |                  |
|------------------------------------|------------------|
| Rated Voltage:                     | 220-240V~        |
| Rated Frequency:                   | 50/60Hz          |
| Rated input current:               | See model list   |
| Rated output:                      | See model list   |
| Protection against Electric Shock: | Class II; SELV   |
| Degree of Protection:              | IP20             |
| Method of Installation:            | Independent      |
| Type of Output:                    | Constant voltage |
| ta, tc:                            | See model list   |

# CERTIFICATE

No. U6 102213 0262 Rev. 00

Model list:

| Item | Model                               | Rated input current (A) | Power factor | Rated output voltage (Vdc) | Rated output current (A) | Rated output power (W) | ta/tc (°C)   | Dimming method |
|------|-------------------------------------|-------------------------|--------------|----------------------------|--------------------------|------------------------|--------------|----------------|
| 1    | Xi LED Transformer 30W TD 24VDC G2  | 0.19                    | 0.95         | 24                         | 0.5-1.25                 | 12-30                  | -25 to 45/80 | DALI           |
| 2    | Xi LED Transformer 100W TD 24VDC G2 | 0.6                     | 0.95         | 24                         | 1.25-4.17                | 30-100                 | -25 to 45/90 | DALI           |
| 3    | Xi LED Transformer 60W TD 24VDC G2  | 0.35                    | 0.95         | 24                         | 1-2.5                    | 24-60                  | -25 to 45/80 | DALI           |
| 4    | Xi LED Transformer 200W TD 24VDC G2 | 1.2                     | 0.95         | 24                         | 2.5-8.34                 | 60-200                 | -25 to 45/85 | DALI           |

**Tested according to:**

EN 61347-1:2015/A1:2021  
EN 61347-2-13:2014/A1:2017  
EN IEC 62384:2020

**Production Facility(ies):**

120928