



Luminaire : BWP601 LED56 722 40W DTA-WB  
 Lamp : 1 x LED  
 Lampflux : 1 x 5600 lm  
 Measurement code : P202308290  
 Measurement date : 2023/8/29  
 Measurement status : Released

## Polar intensity diagram




Luminaire : BWP601 LED65 CW 40W DTA-WB  
 Lamp : 1 x LED  
 Lampflux : 1 x 6500 lm  
 Measurement code : P202308290  
 Measurement date : 2023/8/29  
 Measurement status : Released

## Polar intensity diagram




Luminaire : BWP601 LED65 NW 40W DTA-WB  
 Lamp : 1 x LED  
 Lampflux : 1 x 6500 lm  
 Measurement code : P202308290  
 Measurement date : 2023/8/29  
 Measurement status : Released

## Polar intensity diagram




Luminaire : BWP601 LED63 WW 40W DTA-WB  
 Lamp : 1 x LED  
 Lampflux : 1 x 6300 lm  
 Measurement code : P202308290  
 Measurement date : 2023/8/29  
 Measurement status : Released

## Polar intensity diagram




Luminaire : BWP601 LED61 727 40W DTA-WB  
 Lamp : 1 x LED  
 Lampflux : 1 x 6100 lm  
 Measurement code : P202308290  
 Measurement date : 2023/8/29  
 Measurement status : Released

## Polar intensity diagram




Luminaire : BWP602 LED168 CW 100W DTA-WB  
 Lamp : 1 x LED  
 Lampflux : 1 x 16800 lm  
 Measurement code : P202308290  
 Measurement date : 2023/8/29  
 Measurement status : Released

## Polar intensity diagram




Luminaire : BWP602 LED162 727 100W DTA-WB  
 Lamp : 1 x LED  
 Lampflux : 1 x 16200 lm  
 Measurement code : P202308290  
 Measurement date : 2023/8/29  
 Measurement status : Released

## Polar intensity diagram



Luminaire : BWP602 LED147 722 100W DTA-WB  
 Lamp : 1 x LED  
 Lampflux : 1 x 14700 lm  
 Measurement code : P202308290  
 Measurement date : 2023/8/29  
 Measurement status : Released


## Polar intensity diagram






Luminaire : BWP602 LED170 NW 100W DTA-WB  
 Lamp : 1 x LED  
 Lampflux : 1 x 17000 lm  
 Measurement code : P202308290  
 Measurement date : 2023/8/29  
 Measurement status : Released

## Polar intensity diagram




Luminaire : BWP602 LED165 WW 100W DTA-WB  
 Lamp : 1 x LED  
 Lampflux : 1 x 16500 lm  
 Measurement code : P202308290  
 Measurement date : 2023/8/29  
 Measurement status : Released

## Polar intensity diagram




Luminaire : BWP603 LED282 NW 170W DTA-WB  
 Lamp : 1 x LED  
 Lampflux : 1 x 28200 lm  
 Measurement code : P202308290  
 Measurement date : 2023/8/29  
 Measurement status : Released

## Polar intensity diagram




Luminaire : BWP603 LED267 727 170W DTA-WB  
 Lamp : 1 x LED  
 Lampflux : 1 x 26700 lm  
 Measurement code : P202308290  
 Measurement date : 2023/8/29  
 Measurement status : Released

## Polar intensity diagram




Luminaire : BWP603 LED274 WW 170W DTA-WB  
 Lamp : 1 x LED  
 Lampflux : 1 x 27400 lm  
 Measurement code : P202308290  
 Measurement date : 2023/8/29  
 Measurement status : Released

## Polar intensity diagram




Luminaire : BWP603 LED278 CW 170W DTA-WB  
 Lamp : 1 x LED  
 Lampflux : 1 x 27800 lm  
 Measurement code : P202308290  
 Measurement date : 2023/8/29  
 Measurement status : Released

## Polar intensity diagram




Luminaire : BWP603 LED243 722 170W DTA-WB  
 Lamp : 1 x LED  
 Lampflux : 1 x 24300 lm  
 Measurement code : P202308290  
 Measurement date : 2023/8/29  
 Measurement status : Released

## Polar intensity diagram



Luminaire : BWP604 LED311 722 220W DTA-WB  
 Lamp : 1 x LED  
 Lampflux : 1 x 31100 lm  
 Measurement code : P202308290  
 Measurement date : 2023/8/29  
 Measurement status : Released


## Polar intensity diagram






Luminaire : BWP604 LED355 CW 220W DTA-WB  
 Lamp : 1 x LED  
 Lampflux : 1 x 35500 lm  
 Measurement code : P202308290  
 Measurement date : 2023/8/29  
 Measurement status : Released

## Polar intensity diagram




Luminaire : BWP604 LED392 NW 250W DTA-WB  
 Lamp : 1 x LED  
 Lampflux : 1 x 39200 lm  
 Measurement code : P202308290  
 Measurement date : 2023/8/29  
 Measurement status : Released

## Polar intensity diagram




Luminaire : BWP604 LED372 727 250W DTA-WB  
 Lamp : 1 x LED  
 Lampflux : 1 x 37200 lm  
 Measurement code : P202308290  
 Measurement date : 2023/8/29  
 Measurement status : Released

## Polar intensity diagram




Luminaire : BWP604 LED342 727 220W DTA-WB  
 Lamp : 1 x LED  
 Lampflux : 1 x 34200 lm  
 Measurement code : P202308290  
 Measurement date : 2023/8/29  
 Measurement status : Released

## Polar intensity diagram




Luminaire : BWP604 LED381 WW 250W DTA-WB  
 Lamp : 1 x LED  
 Lampflux : 1 x 38100 lm  
 Measurement code : P202308290  
 Measurement date : 2023/8/29  
 Measurement status : Released

## Polar intensity diagram




Luminaire : BWP604 LED360 NW 220W DTA-WB  
 Lamp : 1 x LED  
 Lampflux : 1 x 36000 lm  
 Measurement code : P202308290  
 Measurement date : 2023/8/29  
 Measurement status : Released

## Polar intensity diagram




Luminaire : BWP604 LED349 WW 220W DTA-WB  
 Lamp : 1 x LED  
 Lampflux : 1 x 34900 lm  
 Measurement code : P202308290  
 Measurement date : 2023/8/29  
 Measurement status : Released

## Polar intensity diagram



Luminaire : BWP604 LED387 CW 250W DTA-WB  
 Lamp : 1 x LED  
 Lampflux : 1 x 38700 lm  
 Measurement code : P202308290  
 Measurement date : 2023/8/29  
 Measurement status : Released


## Polar intensity diagram






Luminaire : BWP604 LED339 722 250W DTA-WB  
 Lamp : 1 x LED  
 Lampflux : 1 x 33900 lm  
 Measurement code : P202308290  
 Measurement date : 2023/8/29  
 Measurement status : Released

## Polar intensity diagram




Luminaire : BWP605 LED547 CW 340W DTA-WB  
 Lamp : 1 x LED  
 Lampflux : 1 x 54700 lm  
 Measurement code : P202308290  
 Measurement date : 2023/8/29  
 Measurement status : Released

## Polar intensity diagram




Luminaire : BWP605 LED527 727 340W DTA-WB  
 Lamp : 1 x LED  
 Lampflux : 1 x 52700 lm  
 Measurement code : P202308290  
 Measurement date : 2023/8/29  
 Measurement status : Released

## Polar intensity diagram




Luminaire : BWP605 LED556 NW 340W DTA-WB  
 Lamp : 1 x LED  
 Lampflux : 1 x 55600 lm  
 Measurement code : P202308290  
 Measurement date : 2023/8/29  
 Measurement status : Released

## Polar intensity diagram




Luminaire : BWP605 LED539 WW 340W DTA-WB  
 Lamp : 1 x LED  
 Lampflux : 1 x 53900 lm  
 Measurement code : P202308290  
 Measurement date : 2023/8/29  
 Measurement status : Released

## Polar intensity diagram




Luminaire : BWP605 LED480 722 340W DTA-WB  
 Lamp : 1 x LED  
 Lampflux : 1 x 48000 lm  
 Measurement code : P202308290  
 Measurement date : 2023/8/29  
 Measurement status : Released

## Polar intensity diagram




Luminaire : BWP606 LED683 722 480W DTA-WB  
 Lamp : 1 x LED  
 Lampflux : 1 x 68300 lm  
 Measurement code : P202308290  
 Measurement date : 2023/8/29  
 Measurement status : Released

## Polar intensity diagram



Luminaire : BWP606 LED820 CW 510W DTA-WB  
 Lamp : 1 x LED  
 Lampflux : 1 x 82000 lm  
 Measurement code : P202308290  
 Measurement date : 2023/8/29  
 Measurement status : Released


## Polar intensity diagram






Luminaire : BWP606 LED832 NW 510W DTA-WB  
 Lamp : 1 x LED  
 Lampflux : 1 x 83200 lm  
 Measurement code : P202308290  
 Measurement date : 2023/8/29  
 Measurement status : Released

## Polar intensity diagram




Luminaire : BWP606 LED791 NW 480W DTA-WB  
 Lamp : 1 x LED  
 Lampflux : 1 x 79100 lm  
 Measurement code : P202308290  
 Measurement date : 2023/8/29  
 Measurement status : Released

## Polar intensity diagram




Luminaire : BWP606 LED808 WW 510W DTA-WB  
 Lamp : 1 x LED  
 Lampflux : 1 x 80800 lm  
 Measurement code : P202308290  
 Measurement date : 2023/8/29  
 Measurement status : Released

## Polar intensity diagram




Luminaire : BWP606 LED790 727 510W DTA-WB  
 Lamp : 1 x LED  
 Lampflux : 1 x 79000 lm  
 Measurement code : P202308290  
 Measurement date : 2023/8/29  
 Measurement status : Released

## Polar intensity diagram




Luminaire : BWP606 LED767 WW 480W DTA-WB  
 Lamp : 1 x LED  
 Lampflux : 1 x 76700 lm  
 Measurement code : P202308290  
 Measurement date : 2023/8/29  
 Measurement status : Released

## Polar intensity diagram




Luminaire : BWP606 LED750 727 480W DTA-WB  
 Lamp : 1 x LED  
 Lampflux : 1 x 75000 lm  
 Measurement code : P202308290  
 Measurement date : 2023/8/29  
 Measurement status : Released

## Polar intensity diagram



Luminaire : BWP606 LED719 722 510W DTA-WB  
 Lamp : 1 x LED  
 Lampflux : 1 x 71900 lm  
 Measurement code : P202308290  
 Measurement date : 2023/8/29  
 Measurement status : Released

## Polar intensity diagram



Luminaire : BWP606 LED779 CW 480W DTA-WB  
 Lamp : 1 x LED  
 Lampflux : 1 x 77900 lm  
 Measurement code : P202308290  
 Measurement date : 2023/8/29  
 Measurement status : Released

## Polar intensity diagram

