



Luminaire : BWP601 LED59 727 40W DSM
 Lamp : 1 x LED
 Lampflux : 1 x 5900 lm
 Measurement code : LVC2231096
 Measurement date : 2023/8/29
 Measurement status : Released

Polar intensity diagram




Luminaire : BWP601 LED54 722 40W DSM
 Lamp : 1 x LED
 Lampflux : 1 x 5400 lm
 Measurement code : LVC2231096
 Measurement date : 2023/8/29
 Measurement status : Released

Polar intensity diagram




Luminaire : BWP601 LED61 WW 40W DSM
 Lamp : 1 x LED
 Lampflux : 1 x 6100 lm
 Measurement code : LVC2231096
 Measurement date : 2023/8/29
 Measurement status : Released

Polar intensity diagram




Luminaire : BWP601 LED63 NW 40W DSM
 Lamp : 1 x LED
 Lampflux : 1 x 6300 lm
 Measurement code : LVC2231096
 Measurement date : 2023/8/29
 Measurement status : Released

Polar intensity diagram




Luminaire : BWP601 LED62 CW 40W DSM
 Lamp : 1 x LED
 Lampflux : 1 x 6200 lm
 Measurement code : LVC2231096
 Measurement date : 2023/8/29
 Measurement status : Released

Polar intensity diagram




Luminaire : BWP602 LED166 NW 100W DSM
 Lamp : 1 x LED
 Lampflux : 1 x 16600 lm
 Measurement code : LVC2231096
 Measurement date : 2023/8/29
 Measurement status : Released

Polar intensity diagram




Luminaire : BWP602 LED161 WW 100W DSM
 Lamp : 1 x LED
 Lampflux : 1 x 16100 lm
 Measurement code : LVC2231096
 Measurement date : 2023/8/29
 Measurement status : Released

Polar intensity diagram




Luminaire : BWP602 LED157 727 100W DSM
 Lamp : 1 x LED
 Lampflux : 1 x 15700 lm
 Measurement code : LVC2231096
 Measurement date : 2023/8/29
 Measurement status : Released

Polar intensity diagram




Luminaire : BWP602 LED143 722 100W DSM
 Lamp : 1 x LED
 Lampflux : 1 x 14300 lm
 Measurement code : LVC2231096
 Measurement date : 2023/8/29
 Measurement status : Released

Polar intensity diagram




Luminaire : BWP602 LED163 CW 100W DSM
 Lamp : 1 x LED
 Lampflux : 1 x 16300 lm
 Measurement code : LVC2231096
 Measurement date : 2023/8/29
 Measurement status : Released

Polar intensity diagram




Luminaire : BWP603 LED270 CW 170W DSM
 Lamp : 1 x LED
 Lampflux : 1 x 27000 lm
 Measurement code : LVC2231096
 Measurement date : 2023/8/29
 Measurement status : Released

Polar intensity diagram




Luminaire : BWP603 LED274 NW 170W DSM
 Lamp : 1 x LED
 Lampflux : 1 x 27400 lm
 Measurement code : LVC2231096
 Measurement date : 2023/8/29
 Measurement status : Released

Polar intensity diagram




Luminaire : BWP603 LED260 727 170W DSM
 Lamp : 1 x LED
 Lampflux : 1 x 26000 lm
 Measurement code : LVC2231096
 Measurement date : 2023/8/29
 Measurement status : Released

Polar intensity diagram




Luminaire : BWP603 LED266 WW 170W DSM
 Lamp : 1 x LED
 Lampflux : 1 x 26600 lm
 Measurement code : LVC2231096
 Measurement date : 2023/8/29
 Measurement status : Released

Polar intensity diagram




Luminaire : BWP603 LED237 722 170W DSM
 Lamp : 1 x LED
 Lampflux : 1 x 23700 lm
 Measurement code : LVC2231096
 Measurement date : 2023/8/29
 Measurement status : Released

Polar intensity diagram




Luminaire : BWP606 LED786 WW 510W DSM
 Lamp : 1 x LED
 Lampflux : 1 x 78600 lm
 Measurement code : LVC2231096
 Measurement date : 2023/8/29
 Measurement status : Released

Polar intensity diagram




Luminaire : BWP606 LED768 NW 480W DSM
 Lamp : 1 x LED
 Lampflux : 1 x 76800 lm
 Measurement code : LVC2231096
 Measurement date : 2023/8/29
 Measurement status : Released

Polar intensity diagram




Luminaire : BWP606 LED664 722 480W DSM
 Lamp : 1 x LED
 Lampflux : 1 x 66400 lm
 Measurement code : LVC2231096
 Measurement date : 2023/8/29
 Measurement status : Released

Polar intensity diagram




Luminaire : BWP604 LED376 CW 250W DSM
 Lamp : 1 x LED
 Lampflux : 1 x 37600 lm
 Measurement code : LVC2231096
 Measurement date : 2023/8/29
 Measurement status : Released

Polar intensity diagram




Luminaire : BWP604 LED302 722 220W DSM
 Lamp : 1 x LED
 Lampflux : 1 x 30200 lm
 Measurement code : LVC2231096
 Measurement date : 2023/8/29
 Measurement status : Released

Polar intensity diagram




Luminaire : BWP604 LED345 CW 220W DSM
 Lamp : 1 x LED
 Lampflux : 1 x 34500 lm
 Measurement code : LVC2231096
 Measurement date : 2023/8/29
 Measurement status : Released

Polar intensity diagram




Luminaire : BWP604 LED362 727 250W DSM
 Lamp : 1 x LED
 Lampflux : 1 x 36200 lm
 Measurement code : LVC2231096
 Measurement date : 2023/8/29
 Measurement status : Released

Polar intensity diagram




Luminaire : BWP604 LED332 727 220W DSM
 Lamp : 1 x LED
 Lampflux : 1 x 33200 lm
 Measurement code : LVC2231096
 Measurement date : 2023/8/29
 Measurement status : Released

Polar intensity diagram




Luminaire : BWP604 LED370 WW 250W DSM
 Lamp : 1 x LED
 Lampflux : 1 x 37000 lm
 Measurement code : LVC2231096
 Measurement date : 2023/8/29
 Measurement status : Released

Polar intensity diagram




Luminaire : BWP604 LED381 NW 250W DSM
 Lamp : 1 x LED
 Lampflux : 1 x 38100 lm
 Measurement code : LVC2231096
 Measurement date : 2023/8/29
 Measurement status : Released

Polar intensity diagram




Luminaire : BWP604 LED350 NW 220W DSM
 Lamp : 1 x LED
 Lampflux : 1 x 35000 lm
 Measurement code : LVC2231096
 Measurement date : 2023/8/29
 Measurement status : Released

Polar intensity diagram




Luminaire : BWP604 LED340 WW 220W DSM
 Lamp : 1 x LED
 Lampflux : 1 x 34000 lm
 Measurement code : LVC2231096
 Measurement date : 2023/8/29
 Measurement status : Released

Polar intensity diagram




Luminaire : BWP604 LED329 722 250W DSM
 Lamp : 1 x LED
 Lampflux : 1 x 32900 lm
 Measurement code : LVC2231096
 Measurement date : 2023/8/29
 Measurement status : Released

Polar intensity diagram




Luminaire : BWP605 LED532 CW 340W DSM
 Lamp : 1 x LED
 Lampflux : 1 x 53200 lm
 Measurement code : LVC2231096
 Measurement date : 2023/8/29
 Measurement status : Released

Polar intensity diagram




Luminaire : BWP605 LED524 WW 340W DSM
 Lamp : 1 x LED
 Lampflux : 1 x 52400 lm
 Measurement code : LVC2231096
 Measurement date : 2023/8/29
 Measurement status : Released

Polar intensity diagram




Luminaire : BWP605 LED540 NW 340W DSM
 Lamp : 1 x LED
 Lampflux : 1 x 54000 lm
 Measurement code : LVC2231096
 Measurement date : 2023/8/29
 Measurement status : Released

Polar intensity diagram




Luminaire : BWP605 LED466 722 340W DSM
 Lamp : 1 x LED
 Lampflux : 1 x 46600 lm
 Measurement code : LVC2231096
 Measurement date : 2023/8/29
 Measurement status : Released

Polar intensity diagram




Luminaire : BWP605 LED512 727 340W DSM
 Lamp : 1 x LED
 Lampflux : 1 x 51200 lm
 Measurement code : LVC2231096
 Measurement date : 2023/8/29
 Measurement status : Released

Polar intensity diagram




Luminaire : BWP606 LED699 722 510W DSM
 Lamp : 1 x LED
 Lampflux : 1 x 69900 lm
 Measurement code : LVC2231096
 Measurement date : 2023/8/29
 Measurement status : Released

Polar intensity diagram




Luminaire : BWP606 LED757 CW 480W DSM
 Lamp : 1 x LED
 Lampflux : 1 x 75700 lm
 Measurement code : LVC2231096
 Measurement date : 2023/8/29
 Measurement status : Released

Polar intensity diagram




Luminaire : BWP606 LED729 727 480W DSM
 Lamp : 1 x LED
 Lampflux : 1 x 72900 lm
 Measurement code : LVC2231096
 Measurement date : 2023/8/29
 Measurement status : Released

Polar intensity diagram




Luminaire : BWP606 LED768 727 510W DSM
 Lamp : 1 x LED
 Lampflux : 1 x 76800 lm
 Measurement code : LVC2231096
 Measurement date : 2023/8/29
 Measurement status : Released

Polar intensity diagram




Luminaire : BWP606 LED809 NW 510W DSM
 Lamp : 1 x LED
 Lampflux : 1 x 80900 lm
 Measurement code : LVC2231096
 Measurement date : 2023/8/29
 Measurement status : Released

Polar intensity diagram



Luminaire : BWP606 LED797 CW 510W DSM
 Lamp : 1 x LED
 Lampflux : 1 x 79700 lm
 Measurement code : LVC2231096
 Measurement date : 2023/8/29
 Measurement status : Released

Polar intensity diagram



Luminaire : BWP606 LED746 WW 480W DSM
 Lamp : 1 x LED
 Lampflux : 1 x 74600 lm
 Measurement code : LVC2231096
 Measurement date : 2023/8/29
 Measurement status : Released

Polar intensity diagram

