

# Built for performance - Waterproof Lighting solution for Dusty and Humid application

## Smartbright WT200/201 waterproof

Smartbright Waterproof luminaire is a special application luminaire designed to provide uninterrupted lighting for dusty and humid indoor application. It is a perfect solution for lighting up indoor spaces like multilevel car park, open canopies in bus stations and general industrial applications. The luminaire has all-weather polycarbonate housing and highly efficient electronics with LED system to offer long useful life even in adverse application and environmental conditions. With unique design, variety of options in lumen packs and color temperature makes it suitable for diverse applications.

### Benefits

- Rugged & Suitable for dusty and humid environment
- Ensures long useful life and reliable performance even in extreme conditions
- Greater energy savings help end users to reduce ROI
- Application & Design freedom provides flexibility to user
- Creates a diffused natural light, ensuring visual comfort
- Easy to install

# Smartbright WT200/201 waterproof

## Features

- High ingress protection – IP65
- High Impact resistance- IK08
- Compact integral design with superior efficacy > 120lm/w
- Multiple lumen packs & CCT
- Light color: 4000K, 6500K, SDCM<5
- High Surge Protection – 4KV
- Ripple < 5% & THD < 10%
- EMI-EMC Compliance
- Over Voltage Cut-off@ 325V
- Co-extruded polycarbonate housing
- Easy to install-External click fixing mounting arrangement


## Application

- Multi-level parking lots
- Industrial sheds
- Public areas
- Damp Areas

## Warnings and Safety

- Meant for Indoor Application Only. Should not be used in outdoor exposed to Sun and Rain.

## Dimensional drawing



## Product details

Smartbright\_Waterproof Batten-  
WT201C



# Smartbright WT200/201 waterproof

General Information	
Driver included	Yes
Light Technical	
Beam angle of light source	120 degree(s)
Optical cover type	Polycarbonate
Color rendering index (CRI)	>80
Optic type	Beam angle 120°
Operating and Electrical	
Input Voltage	140-270 V
Temperature	
Ambient temperature range	0 to +45 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Housing Color	Gray
Approval and Application	
Protection class IEC	Safety class I
Flammability mark	For mounting on normally flammable surfaces
Mech. impact protection code	IK08
Ingress protection code	IP65
Initial Performance (IEC Compliant)	
Initial chromaticity	<5

## Light Technical

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	
		Temperature (Nom)	(rated) (Nom)	Luminous Flux
919515812984	WT201C LED44S-6500 PSU L120 S2	6500 K	120 lm/W	4,400 lm
919515812985	WT201C LED44S-4000 PSU L120 S2	4000 K	120 lm/W	4,400 lm
919515813273	WT201C LED24S-6500 PSU L120 S2	6500 K	130 lm/W	2,400 lm
919515813274	WT201C LED24S-4000 PSU L120 S2	4000 K	130 lm/W	2,400 lm

## Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
919515812984	WT201C LED44S-6500 PSU L120 S2	36 W	919515813273	WT201C LED24S-6500 PSU L120 S2	18 W
919515812985	WT201C LED44S-4000 PSU L120 S2	36 W	919515813274	WT201C LED24S-4000 PSU L120 S2	18 W

