



Reliable, mood setting Batten

Smart Bright Twin Glow Batten

The Essential SmartBright Twin Glow Batten was designed with aesthetical curve, which makes it so fascinates. This batten provides unique, flexible, and mood-setting environment. The mood changes with simple toggle switch, memory of last setting. Easy to operate and blend into room ambiance.

Benefits

- Batten that provides unique, flexible, mood setting environment
- Uplight/Indirect light provides very comfortable lighting
- Easy to operate and blend into room ambiance
- Safe & reliable solution

Features

- 2000Lm uplight, 2000Lm Downlight, >2000 Lm Uplight &Downlight
- CCT: Downlight 6500K,Uplight 3000K
- 100lm/W up / Downlight, 110lm/W Uplight &Downlight
- CRI:80; Color consistence: SDCM ≤6
- 20000h@L70B50@Ta25C, 2 Years Warranty
- Class II, 220-240V;50/60Hz, Pf > 0.9
- 1184*32*67.5mm
- 1 in 1 box, 50pcs(L600), 24 box/Carton
- Approbation: CB, (photobiology safety - RG0) /EMC compliance

Application

- Residential
- Light Commercial
- Municipal Buildings
- Architectural light
- Office
- Shop

Smart Bright Twin Glow Batten

Versions



SMARTBRIGHT TWIN GLOW BATTEN T8 L1200

Dimensional drawing



BN040C

