



# SmartBright Lumen & Colour Select Highbay – Trusted performance. Everyday.

## SmartBright Lumen & Colour Select Highbay

The SmartBright Lumen and Colour Selectable Highbay delivers unparalleled flexibility for a wide range of applications. Colour selectable (4000K/4500K/5000K) and lumen selectable from 15K to 28K lumens in the one handy package makes this the only highbay you need for almost any application. An optional motion sensor adds strong energy saving credentials.

### Benefits

- High efficacy maximum energy saving
- Robust and reliable
- Long Time, Long warranty

### Features

- High Efficiency, up to 140lm/W
- Robust design, diecast housing, IP65 & IK07
- 50,000hrs and 5yr warranty as standard
- Optional Motion Sensor & programmer
- Daylight regulation functionality (with sensor option)

# SmartBright Lumen & Colour Select Highbay

## Application


- Warehouses
- Distribution Centres
- General Manufacturing Centres
- Exhibition Halls
- High Ceiling Applications

## Versions



BY240P G2

## Dimensional drawing



## Product details



BY240P G2



BY240P G2

# SmartBright Lumen & Colour Select Highbay

## Product details



BY240P G2 Selector

