



# The next generation in retail lighting -Simply irresistible

## MASTERColor CDM-Rm Elite Mini

The Elite family is at the very top of the MasterColor CDM range, and gives a unique combination of unbeatable light quality and consistent performance over lifetime, while keeping running costs low. The MasterColor DCM Elite MR16 combines the familiar compact shape of MR16 halogen lamps with the performance of ceramic metal halide MasterColor Elite lamps. Suited for accent/decorative lighting, general lighting and downlighting in retail applications; or for outdoor landscaping and architectural effects.

### Benefits

- Easy to install and replace, 100% compatible with existing HID systems in markets today
- Miniaturized reflector eliminates need for optical design
- Excellent choice for today's lighting designs

### Features

- Sparkling light - 90 CRI with crisp white light (3000K)
- Long life- 12,000 hours rated average life\*
- Lamp-to-lamp color consistency
- GX10 twist-and-lock design locks base into place
- Miniaturized
- \* Rated average life is the life obtained on the average, from large representative groups of lamps in laboratory tests under controlled conditions at 10 or more operating hours per start. It is based on survival of at least 50% of the lamps and allows for individual lamps or groups of lamps to vary considerably from the average.

# MASTERCOLOR CDM-Rm Elite Mini


## Application

- Ideal for display lighting, and accent lighting, general lighting and down lighting in retail applications; and for outdoor landscaping and architectural effects in retail and hospitality applications.

## Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)

## Dimensional drawing



Product	D (max)	D	C (max)	C	C1 (max)	A (max)
CDM-Rm Elite Mini 20W/830 GX10 MR16 25D	51 mm	50 mm	65.4 mm	62.75 mm	60.9 mm	59 mm
CDM-Rm Elite Mini 35W/930 GX10 MR16 25D	51 mm	50 mm	65.4 mm	62.75 mm	60.9 mm	59 mm

General Information	
Cap-Base	GX10
Switching Cycle	1,350
Operating Position	UNIVERSAL
Light Technical	
Beam Angle (Nom)	25 degree(s)
Chromaticity Coordinate X (Nom)	0.439
Chromaticity Coordinate Y (Nom)	0.403
Correlated Color Temperature (Nom)	3000 K
Operating and Electrical	
Warm-up time to 60% light	120 s
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	MR16

## Light Technical

Order Code	Full Product Name	Color rendering index (CRI)	LLMF At End Of Nominal Lifetime (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Intensity (Nom)
928191105315	CDM-Rm Elite Mini 20W/830 GX10 MR16 25D	84	70 %	50 lm/W	4,000 cd
928194705315	CDM-Rm Elite Mini 35W/930 GX10 MR16 25D	90	80 %	60 lm/W	7,600 cd



## Operating and Electrical

Order Code	Full Product Name	Voltage (Nom)	Power Consumption	Order Code	Full Product Name	Voltage (Nom)	Power Consumption
928191105315	CDM-Rm Elite Mini 20W/830 GX10 MR16 25D	95 V	20.1 W	928194705315	CDM-Rm Elite Mini 35W/930 GX10 MR16 25D	87 V	39.1 W



# MASTERCOLOR CDM-Rm Elite Mini

## Approval and Application

Order Code	Full Product Name	Energy Consumption	Mercury (Hg)
		kWh/1000 h	Content (Nom)
928191105315	CDM-Rm Elite Mini 20W/830	22 kWh	3.5 mg
	GX10 MR16 25D		
928194705315	CDM-Rm Elite Mini 35W/930	43 kWh	4.7 mg
	GX10 MR16 25D		





## Accent Diagrams



Accent Diagram - CDM-Rm Elite Mini 20W/830  
GX10 MR16 25D

Accent Diagram - CDM-Rm Elite Mini 35W/930  
GX10 MR16 25D

## Beam Diagrams



Beam diagram - CDM-Rm Elite Mini 20W/830  
GX10 MR16 25D

Beam diagram - CDM-Rm Elite Mini 35W/930  
GX10 MR16 25D

## MASTERColor CDM-Rm Elite Mini

