



Product Description

CLASSICTONE Lustre

Spherical vacuum- or gas-filled incandescent lamps with a clear, white or inside-frosted glass bulb

Benefits

- Clear lamps: brilliant, visible filament adds small points of brightness for an enriched lighting effect
- White and frosted lamps: softly diffused light sets the scene for cosiness and comfort, and meets both aesthetic and functional requirements

Features

- Clear lamps
- Small, crystal-clear lamps designed for sparkling highlights
- At their best in decorative small luminaires such as table models and wall brackets with clear glass bowls
- Creates a sparkling atmosphere
- White and frosted lamps
- Lamps with reduced size and neat shape
- Extremely popular for use around mirrors or in chandeliers, candelabras, floor lamps and wall brackets, fitted with small, decorative shades
- Creates a pleasant low glare atmosphere
- Universal burning position except for some 60W types which must be operated vertically, base-down (tolerance 90°)

Application

- Home use in living and dining rooms, bedrooms, halls and studies
- Hotel lounges, restaurants, bedrooms, halls, conference rooms and foyers
- Clubs and social areas
- Shops, boutiques and department stores
- Other similar areas


CLASSICTONE Lustré

Versions



LPPR ILUSBSTD B22 P45 CL

Dimensional drawing



Product	D	C (max)
CLAS 25W B22 240V P45 CL 1CT/10X10F	45 mm	71.5 mm

