



# Slim and reliable

## RC160V

GreenPerform Panel RC160V is an edge lit slim panel with high efficacy in the market. It offers 3 typical dimensions: 600x600; 300x1200 and 600x1200mm to fit most of indoor applications. Its lower UGR offers better visual comfort as well. In addition, RC160V offers easy connection to control system to bring better energy saving.

### Benefits

- High lm/w provides better energy saving
- Dali and Interact interfaces available for easy internet connection
- Lower UGR offer for WELL building certificate
- Multiple mountings to cater for various applications

### Features

- System efficiency: max 130lm/W
- CRI 80 and 90 available with SDCM 4
- UGR19 / 16 available for certain types
- IP54 front/IP20 back available for certain types









### Application

- Open plan office
- Public indoor area
- Meeting/training room

### Specifications








|                           |                           |                     |          |
|---------------------------|---------------------------|---------------------|----------|
| <b>Ingress protection</b> | IP20/IP54 front/IP20 back | <b>Installation</b> | Recessed |
|---------------------------|---------------------------|---------------------|----------|

Dimensional drawing



# RC160V

## Dimensional drawing



## General Information

|                      |        |
|----------------------|--------|
| Driver included      | Yes    |
| Gear                 | -      |
| Number of gear units | 1 unit |

## Light Technical

|                             |                 |
|-----------------------------|-----------------|
| Color rendering index (CRI) | 80              |
| Optic type                  | Beam angle 100° |

## Operating and Electrical

|                               |                 |
|-------------------------------|-----------------|
| Protection class IEC          | Safety class II |
| Input Voltage                 | 200 to 240 V    |
| Line Frequency                | 50 to 60 Hz     |
| Suitable for random switching | Not applicable  |

## Mechanical and Housing

|                              |                |
|------------------------------|----------------|
| Housing Color                | White RAL 9003 |
| Mech. impact protection code | IK03           |

## Approval and Application

|                           |                                   |
|---------------------------|-----------------------------------|
| Ambient temperature range | -20 to +40 °C                     |
| CE mark                   | Yes                               |
| ENEC mark                 | -                                 |
| Flammability mark         | -                                 |
| Glow-wire test            | Temperature 650 °C, duration 30 s |

## Initial Performance (IEC Compliant)

|                         |        |
|-------------------------|--------|
| Luminous flux tolerance | +/-10% |
|-------------------------|--------|

## Light Technical

| Order Code   | Full Product Name                         | Correlated Color  |                                 | Number of light sources |     |
|--------------|---|-------------------|---------------------------------|-------------------------|-----|
|              |   | Temperature (Nom) | Luminous Efficacy (rated) (Nom) |                         |     |
| 911401505543 | RC160V LED37/940<br>W303L1210 PSU OC UVG  | 4000 K            | 125 lm/W                        | 3,750 lm                | 288 |
| 911401505643 | RC160V LED37/965<br>W303L1210 PSU OC UVG  | 6500 K            | 125 lm/W                        | 3,750 lm                | 288 |
| 911401510132 | RC160V LED37/830<br>W30L120 PSU           | 3000 K            | 122 lm/W                        | 3,700 lm                | 288 |
| 911401510232 | RC160V LED39/840<br>W30L120 PSU           | 4000 K            | 130 lm/W                        | 3,900 lm                | 288 |
| 911401510332 | RC160V LED39/865<br>W30L120 PSU           | 6500 K            | 130 lm/W                        | 3,900 lm                | 288 |
| 911401511032 | RC160V LED37/830<br>W30L120 PSU OC        | 3000 K            | 122 lm/W                        | 3,700 lm                | 288 |
| 911401511132 | RC160V LED39/840<br>W30L120 PSU OC        | 4000 K            | 130 lm/W                        | 3,900 lm                | 288 |
| 911401511232 | RC160V LED39/865<br>W30L120 PSU OC        | 6500 K            | 130 lm/W                        | 3,900 lm                | 288 |
| 911401511932 | RC160V LED27/830<br>W30L120 PSU 16        | 3000 K            | 125 lm/W                        | 2,740 lm                | 288 |
| 911401512032 | RC160V LED29/840<br>W30L120 PSU 16        | 4000 K            | 133 lm/W                        | 2,900 lm                | 288 |
| 911401512132 | RC160V LED29/865<br>W30L120 PSU 16        | 6500 K            | 133 lm/W                        | 2,900 lm                | 288 |
| 911401512832 | RC160V LED37/830<br>W30L120 PSU 54        | 3000 K            | 122 lm/W                        | 3,700 lm                | 288 |
| 911401512932 | RC160V LED39/840<br>W30L120 PSU 54        | 4000 K            | 130 lm/W                        | 3,900 lm                | 288 |
| 911401513032 | RC160V LED39/865<br>W30L120 PSU 54        | 6500 K            | 130 lm/W                        | 3,900 lm                | 288 |
| 911401513732 | RC160V LED37/830<br>W30L120 PSU OC 54     | 3000 K            | 122 lm/W                        | 3,700 lm                | 288 |
| 911401513832 | RC160V LED39/840<br>W30L120 PSU OC 54     | 4000 K            | 130 lm/W                        | 3,900 lm                | 288 |
| 911401513932 | RC160V LED39/865<br>W30L120 PSU OC 54     | 6500 K            | 130 lm/W                        | 3,900 lm                | 288 |
| 911401514632 | RC160V LED27/830<br>W30L120 PSU 16 54     | 3000 K            | 125 lm/W                        | 2,740 lm                | 288 |
| 911401514732 | RC160V LED29/840<br>W30L120 PSU 16 54     | 4000 K            | 133 lm/W                        | 2,900 lm                | 288 |
| 911401514832 | RC160V LED29/865<br>W30L120 PSU 16 54     | 6500 K            | 133 lm/W                        | 2,900 lm                | 288 |
| 911401516432 | RC160V LED37/830<br>W30L120 PSU OC CPC    | 3000 K            | 122 lm/W                        | 3,700 lm                | 288 |
| 911401516532 | RC160V LED39/840<br>W30L120 PSU OC CPC    | 4000 K            | 130 lm/W                        | 3,900 lm                | 288 |
| 911401516632 | RC160V LED39/865<br>W30L120 PSU OC CPC    | 6500 K            | 130 lm/W                        | 3,900 lm                | 288 |
| 911401519132 | RC160V LED37/830<br>W30L120 PSU OC 54 CPC | 3000 K            | 122 lm/W                        | 3,700 lm                | 288 |

| Order Code   | Full Product Name                         | Correlated Color  |                                 | Luminous Flux | Number of light sources |
|--------------|---|-------------------|---------------------------------|---------------|-------------------------|
|              |   | Temperature (Nom) | Luminous Efficacy (rated) (Nom) |               |                         |
| 911401519232 | RC160V LED39/840<br>W30L120 PSU OC 54 CPC | 4000 K            | 130 lm/W                        | 3,900 lm      | 288                     |
| 911401519332 | RC160V LED39/865<br>W30L120 PSU OC 54 CPC | 6500 K            | 130 lm/W                        | 3,900 lm      | 288                     |
| 911401520932 | RC160V LED37/830<br>W30L120 PSD           | 3000 K            | 122 lm/W                        | 3,700 lm      | 288                     |
| 911401521032 | RC160V LED39/840<br>W30L120 PSD           | 4000 K            | 130 lm/W                        | 3,900 lm      | 288                     |
| 911401521132 | RC160V LED39/865<br>W30L120 PSD           | 6500 K            | 130 lm/W                        | 3,900 lm      | 288                     |
| 911401521832 | RC160V LED37/830<br>W30L120 PSD OC        | 3000 K            | 122 lm/W                        | 3,700 lm      | 288                     |
| 911401521932 | RC160V LED39/840<br>W30L120 PSD OC        | 4000 K            | 130 lm/W                        | 3,900 lm      | 288                     |
| 911401522032 | RC160V LED39/865<br>W30L120 PSD OC        | 6500 K            | 130 lm/W                        | 3,900 lm      | 288                     |
| 911401522732 | RC160V LED27/830<br>W30L120 PSD 16        | 3000 K            | 125 lm/W                        | 2,740 lm      | 288                     |
| 911401522832 | RC160V LED29/840<br>W30L120 PSD 16        | 4000 K            | 133 lm/W                        | 2,900 lm      | 288                     |
| 911401522932 | RC160V LED29/865<br>W30L120 PSD 16        | 6500 K            | 133 lm/W                        | 2,900 lm      | 288                     |
| 911401523632 | RC160X LED37/830<br>W30L120 WIA           | 3000 K            | 122 lm/W                        | 3,700 lm      | 288                     |
| 911401523732 | RC160X LED39/840<br>W30L120 WIA           | 4000 K            | 130 lm/W                        | 3,900 lm      | 288                     |
| 911401523832 | RC160X LED39/865<br>W30L120 WIA           | 6500 K            | 130 lm/W                        | 3,900 lm      | 288                     |
| 911401524832 | RC160X LED37/830<br>W30L120 SIA           | 3000 K            | 122 lm/W                        | 3,700 lm      | 288                     |
| 911401524932 | RC160X LED39/840<br>W30L120 SIA           | 4000 K            | 130 lm/W                        | 3,900 lm      | 288                     |
| 911401525032 | RC160X LED39/865<br>W30L120 SIA           | 6500 K            | 130 lm/W                        | 3,900 lm      | 288                     |
| 911401525532 | RC160V LED38/8TW<br>W30L120               | 2700 K            | 122 lm/W                        | 3,800 lm      | 480                     |
| 911401526032 | RC160V LED37/830<br>W30L120 PSU CAU       | 3000 K            | 122 lm/W                        | 3,700 lm      | 288                     |
| 911401526132 | RC160V LED39/840<br>W30L120 PSU CAU       | 4000 K            | 130 lm/W                        | 3,900 lm      | 288                     |
| 911401526232 | RC160V LED39/865<br>W30L120 PSU CAU       | 6500 K            | 130 lm/W                        | 3,900 lm      | 288                     |
| 911401526932 | RC160V LED37/830<br>W30L120 PSD CAU       | 3000 K            | 122 lm/W                        | 3,700 lm      | 288                     |
| 911401527032 | RC160V LED39/840<br>W30L120 PSD CAU       | 4000 K            | 130 lm/W                        | 3,900 lm      | 288                     |
| 911401527132 | RC160V LED39/865<br>W30L120 PSD CAU       | 6500 K            | 130 lm/W                        | 3,900 lm      | 288                     |
| 911401527832 | RC160X LED37/830<br>W30L120 WIA CAU       | 3000 K            | 122 lm/W                        | 3,700 lm      | 288                     |

| Order Code   | Full Product Name                         | Correlated Color  |                                 | Number of light sources |     |
|--------------|---|-------------------|---------------------------------|-------------------------|-----|
|              |   | Temperature (Nom) | Luminous Efficacy (rated) (Nom) |                         |     |
| 911401527932 | RC160X LED39/840<br>W30L120 WIA CAU       | 4000 K            | 130 lm/W                        | 3,900 lm                | 288 |
| 911401528032 | RC160X LED39/865<br>W30L120 WIA CAU       | 6500 K            | 130 lm/W                        | 3,900 lm                | 288 |
| 911401528432 | RC160X LED37/830<br>W30L120 SIA CAU       | 3000 K            | 122 lm/W                        | 3,700 lm                | 288 |
| 911401528532 | RC160X LED39/840<br>W30L120 SIA CAU       | 4000 K            | 130 lm/W                        | 3,900 lm                | 288 |
| 911401528632 | RC160X LED39/865<br>W30L120 SIA CAU       | 6500 K            | 130 lm/W                        | 3,900 lm                | 288 |
| 911401529332 | RC160V LED37/830<br>W30L120 PSU OC CAU    | 3000 K            | 122 lm/W                        | 3,700 lm                | 288 |
| 911401529432 | RC160V LED39/840<br>W30L120 PSU OC CAU    | 4000 K            | 130 lm/W                        | 3,900 lm                | 288 |
| 911401529532 | RC160V LED39/865<br>W30L120 PSU OC CAU    | 6500 K            | 130 lm/W                        | 3,900 lm                | 288 |
| 911401530232 | RC160V LED37/830<br>W30L120 PSD OC CAU    | 3000 K            | 122 lm/W                        | 3,700 lm                | 288 |
| 911401530332 | RC160V LED39/840<br>W30L120 PSD OC CAU    | 4000 K            | 130 lm/W                        | 3,900 lm                | 288 |
| 911401530432 | RC160V LED39/865<br>W30L120 PSD OC CAU    | 6500 K            | 130 lm/W                        | 3,900 lm                | 288 |
| 911401531432 | RC160V LED27/830<br>W30L120 PSU 16 CAU    | 3000 K            | 125 lm/W                        | 2,740 lm                | 288 |
| 911401531532 | RC160V LED29/840<br>W30L120 PSU 16 CAU    | 4000 K            | 133 lm/W                        | 2,900 lm                | 288 |
| 911401531632 | RC160V LED29/865<br>W30L120 PSU 16 CAU    | 6500 K            | 133 lm/W                        | 2,900 lm                | 288 |
| 911401532332 | RC160V LED27/830<br>W30L120 PSD 16 CAU    | 3000 K            | 125 lm/W                        | 2,740 lm                | 288 |
| 911401532432 | RC160V LED29/840<br>W30L120 PSD 16 CAU    | 4000 K            | 133 lm/W                        | 2,900 lm                | 288 |
| 911401532532 | RC160V LED29/865<br>W30L120 PSD 16 CAU    | 6500 K            | 133 lm/W                        | 2,900 lm                | 288 |
| 911401533532 | RC160V LED37/830<br>W30L120 PSU 54 CAU    | 3000 K            | 122 lm/W                        | 3,700 lm                | 288 |
| 911401533632 | RC160V LED39/840<br>W30L120 PSU 54 CAU    | 4000 K            | 130 lm/W                        | 3,900 lm                | 288 |
| 911401533732 | RC160V LED39/865<br>W30L120 PSU 54 CAU    | 6500 K            | 130 lm/W                        | 3,900 lm                | 288 |
| 911401534432 | RC160V LED37/830<br>W30L120 PSU OC 54 CAU | 3000 K            | 122 lm/W                        | 3,700 lm                | 288 |
| 911401534532 | RC160V LED39/840<br>W30L120 PSU OC 54 CAU | 4000 K            | 130 lm/W                        | 3,900 lm                | 288 |
| 911401534632 | RC160V LED39/865<br>W30L120 PSU OC 54 CAU | 6500 K            | 130 lm/W                        | 3,900 lm                | 288 |
| 911401535332 | RC160V LED27/830<br>W30L120 PSU 16 54 CAU | 3000 K            | 125 lm/W                        | 2,740 lm                | 288 |
| 911401535432 | RC160V LED29/840<br>W30L120 PSU 16 54 CAU | 4000 K            | 133 lm/W                        | 2,900 lm                | 288 |

| Order Code   | Full Product Name                         | Correlated Color  |                                 | Number of light sources |     |
|--------------|---|-------------------|---------------------------------|-------------------------|-----|
|              |   | Temperature (Nom) | Luminous Efficacy (rated) (Nom) |                         |     |
| 911401535532 | RC160V LED29/865<br>W30L120 PSU 16 54 CAU | 6500 K            | 133 lm/W                        | 2,900 lm                | 288 |
| 911401536232 | RC160V LED37/830<br>W303L1210 PSU UVG     | 3000 K            | 122 lm/W                        | 3,700 lm                | 288 |
| 911401536332 | RC160V LED39/840<br>W303L1210 PSU UVG     | 4000 K            | 130 lm/W                        | 3,900 lm                | 288 |
| 911401536432 | RC160V LED39/865<br>W303L1210 PSU UVG     | 6500 K            | 130 lm/W                        | 3,900 lm                | 288 |
| 911401536832 | RC160V LED35/930<br>W30L120 PSU           | 3000 K            | 118 lm/W                        | 3,500 lm                | 288 |
| 911401536932 | RC160V LED37/940<br>W30L120 PSU           | 4000 K            | 126 lm/W                        | 3,750 lm                | 288 |
| 911401537032 | RC160V LED37/965<br>W30L120 PSU           | 6500 K            | 126 lm/W                        | 3,750 lm                | 288 |
| 911401537732 | RC160V LED35/930<br>W30L120 PSU 54        | 3000 K            | 118 lm/W                        | 3,500 lm                | 288 |
| 911401537832 | RC160V LED37/940<br>W30L120 PSU 54        | 4000 K            | 126 lm/W                        | 3,750 lm                | 288 |
| 911401537932 | RC160V LED37/965<br>W30L120 PSU 54        | 6500 K            | 126 lm/W                        | 3,750 lm                | 288 |
| 911401538632 | RC160V LED35/930<br>W30L120 PSD           | 3000 K            | 118 lm/W                        | 3,500 lm                | 288 |
| 911401538732 | RC160V LED37/940<br>W30L120 PSD           | 4000 K            | 126 lm/W                        | 3,750 lm                | 288 |
| 911401538832 | RC160V LED37/965<br>W30L120 PSD           | 6500 K            | 126 lm/W                        | 3,750 lm                | 288 |
| 911401539532 | RC160X LED35/930<br>W30L120 WIA           | 3000 K            | 118 lm/W                        | 3,500 lm                | 288 |
| 911401539632 | RC160X LED37/940<br>W30L120 WIA           | 4000 K            | 126 lm/W                        | 3,750 lm                | 288 |
| 911401539732 | RC160X LED37/965<br>W30L120 WIA           | 6500 K            | 126 lm/W                        | 3,750 lm                | 288 |
| 911401540132 | RC160X LED35/930<br>W30L120 SIA           | 3000 K            | 118 lm/W                        | 3,500 lm                | 288 |
| 911401540232 | RC160X LED37/940<br>W30L120 SIA           | 4000 K            | 126 lm/W                        | 3,750 lm                | 288 |
| 911401540332 | RC160X LED37/965<br>W30L120 SIA           | 6500 K            | 126 lm/W                        | 3,750 lm                | 288 |
| 911401541032 | RC160V LED35/930<br>W30L120 PSU CAU       | 3000 K            | 118 lm/W                        | 3,500 lm                | 288 |
| 911401541132 | RC160V LED37/940<br>W30L120 PSU CAU       | 4000 K            | 126 lm/W                        | 3,750 lm                | 288 |
| 911401541232 | RC160V LED37/965<br>W30L120 PSU CAU       | 6500 K            | 126 lm/W                        | 3,750 lm                | 288 |
| 911401541932 | RC160V LED35/930<br>W30L120 PSD CAU       | 3000 K            | 118 lm/W                        | 3,500 lm                | 288 |
| 911401542032 | RC160V LED37/940<br>W30L120 PSD CAU       | 4000 K            | 126 lm/W                        | 3,750 lm                | 288 |
| 911401542132 | RC160V LED37/965<br>W30L120 PSD CAU       | 6500 K            | 126 lm/W                        | 3,750 lm                | 288 |

| Order Code   | Full Product Name                        | Correlated Color  |                                 | Number of light sources |     |
|--------------|--|-------------------|---------------------------------|-------------------------|-----|
|              |  | Temperature (Nom) | Luminous Efficacy (rated) (Nom) |                         |     |
| 911401542832 | RC160X LED35/930<br>W30L120 WIA CAU      | 3000 K            | 118 lm/W                        | 3,500 lm                | 288 |
| 911401542932 | RC160X LED37/940<br>W30L120 WIA CAU      | 4000 K            | 126 lm/W                        | 3,750 lm                | 288 |
| 911401543032 | RC160X LED37/965<br>W30L120 WIA CAU      | 6500 K            | 126 lm/W                        | 3,750 lm                | 288 |
| 911401543432 | RC160X LED35/930<br>W30L120 SIA CAU      | 3000 K            | 118 lm/W                        | 3,500 lm                | 288 |
| 911401543532 | RC160X LED37/940<br>W30L120 SIA CAU      | 4000 K            | 126 lm/W                        | 3,750 lm                | 288 |
| 911401543632 | RC160X LED37/965<br>W30L120 SIA CAU      | 6500 K            | 126 lm/W                        | 3,750 lm                | 288 |
| 911401544332 | RC160V LED35/930<br>W30L120 PSU 54 CAU   | 3000 K            | 118 lm/W                        | 3,500 lm                | 288 |
| 911401544432 | RC160V LED37/940<br>W30L120 PSU 54 CAU   | 4000 K            | 126 lm/W                        | 3,750 lm                | 288 |
| 911401544532 | RC160V LED37/965<br>W30L120 PSU 54 CAU   | 6500 K            | 126 lm/W                        | 3,750 lm                | 288 |
| 911401545632 | RC160V LED37/9TW<br>W30L120              | 2700 K            | 123 lm/W                        | 3,700 lm                | 480 |
| 911401545932 | RC160V LED37/9TW<br>W30L120 54           | 2700 K            | 123 lm/W                        | 3,700 lm                | 480 |
| 911401546232 | RC160V LED37/9TW<br>W30L120 CAU          | 2700 K            | 123 lm/W                        | 3,700 lm                | 480 |
| 911401546532 | RC160V LED37/9TW<br>W30L120 54 CAU       | 2700 K            | 123 lm/W                        | 3,700 lm                | 480 |
| 911401578942 | RC160V LED37/830<br>W303L1210 PSU OC UVG | 3000 K            | 122 lm/W                        | 3,700 lm                | 288 |
| 911401579042 | RC160V LED39/840<br>W303L1210 PSU OC UVG | 4000 K            | 130 lm/W                        | 3,900 lm                | 288 |
| 911401579142 | RC160V LED39/865<br>W303L1210 PSU OC UVG | 6500 K            | 130 lm/W                        | 3,900 lm                | 288 |
| 911401510432 | RC160V LED57/830<br>W60L120 PSU          | 3000 K            | 123 lm/W                        | 5,700 lm                | 384 |
| 911401510532 | RC160V LED60/840<br>W60L120 PSU          | 4000 K            | 131 lm/W                        | 6,000 lm                | 384 |
| 911401510632 | RC160V LED60/865<br>W60L120 PSU          | 6500 K            | 131 lm/W                        | 6,000 lm                | 384 |
| 911401511332 | RC160V LED57/830<br>W60L120 PSU OC       | 3000 K            | 123 lm/W                        | 5,700 lm                | 384 |
| 911401511432 | RC160V LED60/840<br>W60L120 PSU OC       | 4000 K            | 131 lm/W                        | 6,000 lm                | 384 |
| 911401511532 | RC160V LED60/865<br>W60L120 PSU OC       | 6500 K            | 131 lm/W                        | 6,000 lm                | 384 |
| 911401512232 | RC160V LED54/830<br>W60L120 PSU 16       | 3000 K            | 119 lm/W                        | 5,450 lm                | 384 |
| 911401512332 | RC160V LED58/840<br>W60L120 PSU 16       | 4000 K            | 126 lm/W                        | 5,800 lm                | 384 |
| 911401512432 | RC160V LED58/865<br>W60L120 PSU 16       | 6500 K            | 126 lm/W                        | 5,800 lm                | 384 |



| Order Code   | Full Product Name                     | Correlated Color  |                                 | Luminous Flux | Number of light sources |
|--------------|---------------------------------------|-------------------|---------------------------------|---------------|-------------------------|
|              |                                       | Temperature (Nom) | Luminous Efficacy (rated) (Nom) |               |                         |
| 911401513132 | RC160V LED57/830<br>W60L120 PSU 54    | 3000 K            | 123 lm/W                        | 5,700 lm      | 384                     |
| 911401513232 | RC160V LED60/840<br>W60L120 PSU 54    | 4000 K            | 131 lm/W                        | 6,000 lm      | 384                     |
| 911401513332 | RC160V LED60/865<br>W60L120 PSU 54    | 6500 K            | 131 lm/W                        | 6,000 lm      | 384                     |
| 911401514032 | RC160V LED57/830<br>W60L120 PSU OC 54 | 3000 K            | 123 lm/W                        | 5,700 lm      | 384                     |
| 911401514132 | RC160V LED60/840<br>W60L120 PSU OC 54 | 4000 K            | 131 lm/W                        | 6,000 lm      | 384                     |
| 911401514232 | RC160V LED60/865<br>W60L120 PSU OC 54 | 6500 K            | 131 lm/W                        | 6,000 lm      | 384                     |
| 911401514932 | RC160V LED54/830<br>W60L120 PSU 16 54 | 3000 K            | 119 lm/W                        | 5,450 lm      | 384                     |
| 911401515032 | RC160V LED58/840<br>W60L120 PSU 16 54 | 4000 K            | 126 lm/W                        | 5,800 lm      | 384                     |
| 911401515132 | RC160V LED58/865<br>W60L120 PSU 16 54 | 6500 K            | 126 lm/W                        | 5,800 lm      | 384                     |
| 911401521232 | RC160V LED57/830<br>W60L120 PSD       | 3000 K            | 123 lm/W                        | 5,700 lm      | 384                     |
| 911401521332 | RC160V LED60/840<br>W60L120 PSD       | 4000 K            | 131 lm/W                        | 6,000 lm      | 384                     |
| 911401521432 | RC160V LED60/865<br>W60L120 PSD       | 6500 K            | 131 lm/W                        | 6,000 lm      | 384                     |
| 911401522132 | RC160V LED57/830<br>W60L120 PSD OC    | 3000 K            | 123 lm/W                        | 5,700 lm      | 384                     |
| 911401522232 | RC160V LED60/840<br>W60L120 PSD OC    | 4000 K            | 131 lm/W                        | 6,000 lm      | 384                     |
| 911401522332 | RC160V LED60/865<br>W60L120 PSD OC    | 6500 K            | 131 lm/W                        | 6,000 lm      | 384                     |
| 911401523032 | RC160V LED54/830<br>W60L120 PSD 16    | 3000 K            | 119 lm/W                        | 5,450 lm      | 384                     |
| 911401523132 | RC160V LED58/840<br>W60L120 PSD 16    | 4000 K            | 126 lm/W                        | 5,800 lm      | 384                     |
| 911401523232 | RC160V LED58/865<br>W60L120 PSD 16    | 6500 K            | 126 lm/W                        | 5,800 lm      | 384                     |
| 911401525132 | RC160X LED57/830<br>W60L120 SIA       | 3000 K            | 123 lm/W                        | 5,700 lm      | 384                     |
| 911401525232 | RC160X LED60/840<br>W60L120 SIA       | 4000 K            | 131 lm/W                        | 6,000 lm      | 384                     |
| 911401525332 | RC160X LED60/865<br>W60L120 SIA       | 6500 K            | 131 lm/W                        | 6,000 lm      | 384                     |
| 911401526332 | RC160V LED57/830<br>W60L120 PSU CAU   | 3000 K            | 123 lm/W                        | 5,700 lm      | 384                     |
| 911401526432 | RC160V LED60/840<br>W60L120 PSU CAU   | 4000 K            | 131 lm/W                        | 6,000 lm      | 384                     |
| 911401526532 | RC160V LED60/865<br>W60L120 PSU CAU   | 6500 K            | 131 lm/W                        | 6,000 lm      | 384                     |
| 911401527232 | RC160V LED57/830<br>W60L120 PSD CAU   | 3000 K            | 123 lm/W                        | 5,700 lm      | 384                     |

| Order Code   | Full Product Name                         | Correlated Color  |                                 | Luminous Flux | Number of light sources |
|--------------|---|-------------------|---------------------------------|---------------|-------------------------|
|              |   | Temperature (Nom) | Luminous Efficacy (rated) (Nom) |               |                         |
| 911401527332 | RC160V LED60/840<br>W60L120 PSD CAU       | 4000 K            | 131 lm/W                        | 6,000 lm      | 384                     |
| 911401527432 | RC160V LED60/865<br>W60L120 PSD CAU       | 6500 K            | 131 lm/W                        | 6,000 lm      | 384                     |
| 911401528732 | RC160X LED57/830<br>W60L120 SIA CAU       | 3000 K            | 123 lm/W                        | 5,700 lm      | 384                     |
| 911401528832 | RC160X LED60/840<br>W60L120 SIA CAU       | 4000 K            | 131 lm/W                        | 6,000 lm      | 384                     |
| 911401528932 | RC160X LED60/865<br>W60L120 SIA CAU       | 6500 K            | 131 lm/W                        | 6,000 lm      | 384                     |
| 911401529632 | RC160V LED57/830<br>W60L120 PSU OC CAU    | 3000 K            | 123 lm/W                        | 5,700 lm      | 384                     |
| 911401529732 | RC160V LED60/840<br>W60L120 PSU OC CAU    | 4000 K            | 131 lm/W                        | 6,000 lm      | 384                     |
| 911401529832 | RC160V LED60/865<br>W60L120 PSU OC CAU    | 6500 K            | 131 lm/W                        | 6,000 lm      | 384                     |
| 911401530532 | RC160V LED57/830<br>W60L120 PSD OC CAU    | 3000 K            | 123 lm/W                        | 5,700 lm      | 384                     |
| 911401530632 | RC160V LED60/840<br>W60L120 PSD OC CAU    | 4000 K            | 131 lm/W                        | 6,000 lm      | 384                     |
| 911401530732 | RC160V LED60/865<br>W60L120 PSD OC CAU    | 6500 K            | 131 lm/W                        | 6,000 lm      | 384                     |
| 911401531732 | RC160V LED54/830<br>W60L120 PSU 16 CAU    | 3000 K            | 119 lm/W                        | 5,450 lm      | 384                     |
| 911401531832 | RC160V LED58/840<br>W60L120 PSU 16 CAU    | 4000 K            | 126 lm/W                        | 5,800 lm      | 384                     |
| 911401531932 | RC160V LED58/865<br>W60L120 PSU 16 CAU    | 6500 K            | 126 lm/W                        | 5,800 lm      | 384                     |
| 911401532632 | RC160V LED54/830<br>W60L120 PSD 16 CAU    | 3000 K            | 119 lm/W                        | 5,450 lm      | 384                     |
| 911401532732 | RC160V LED58/840<br>W60L120 PSD 16 CAU    | 4000 K            | 126 lm/W                        | 5,800 lm      | 384                     |
| 911401532832 | RC160V LED58/865<br>W60L120 PSD 16 CAU    | 6500 K            | 126 lm/W                        | 5,800 lm      | 384                     |
| 911401533832 | RC160V LED57/830<br>W60L120 PSU 54 CAU    | 3000 K            | 123 lm/W                        | 5,700 lm      | 384                     |
| 911401533932 | RC160V LED60/840<br>W60L120 PSU 54 CAU    | 4000 K            | 131 lm/W                        | 6,000 lm      | 384                     |
| 911401534032 | RC160V LED60/865<br>W60L120 PSU 54 CAU    | 6500 K            | 131 lm/W                        | 6,000 lm      | 384                     |
| 911401534732 | RC160V LED57/830<br>W60L120 PSU OC 54 CAU | 3000 K            | 123 lm/W                        | 5,700 lm      | 384                     |
| 911401534832 | RC160V LED60/840<br>W60L120 PSU OC 54 CAU | 4000 K            | 131 lm/W                        | 6,000 lm      | 384                     |
| 911401534932 | RC160V LED60/865<br>W60L120 PSU OC 54 CAU | 6500 K            | 131 lm/W                        | 6,000 lm      | 384                     |
| 911401535632 | RC160V LED54/830<br>W60L120 PSU 16 54 CAU | 3000 K            | 119 lm/W                        | 5,450 lm      | 384                     |
| 911401535732 | RC160V LED58/840<br>W60L120 PSU 16 54 CAU | 4000 K            | 126 lm/W                        | 5,800 lm      | 384                     |

| Order Code   | Full Product Name                         | Correlated Color  |                                 | Number of light sources |     |
|--------------|---|-------------------|---------------------------------|-------------------------|-----|
|              |   | Temperature (Nom) | Luminous Efficacy (rated) (Nom) |                         |     |
| 911401535832 | RC160V LED58/865<br>W60L120 PSU 16 54 CAU | 6500 K            | 126 lm/W                        | 5,800 lm                | 384 |
| 911401537132 | RC160V LED54/930<br>W60L120 PSU           | 3000 K            | 119 lm/W                        | 5,450 lm                | 384 |
| 911401537232 | RC160V LED58/940<br>W60L120 PSU           | 4000 K            | 126 lm/W                        | 5,800 lm                | 384 |
| 911401537332 | RC160V LED58/965<br>W60L120 PSU           | 6500 K            | 126 lm/W                        | 5,800 lm                | 384 |
| 911401538032 | RC160V LED54/930<br>W60L120 PSU 54        | 3000 K            | 119 lm/W                        | 5,450 lm                | 384 |
| 911401538132 | RC160V LED58/940<br>W60L120 PSU 54        | 4000 K            | 126 lm/W                        | 5,800 lm                | 384 |
| 911401538232 | RC160V LED58/965<br>W60L120 PSU 54        | 6500 K            | 126 lm/W                        | 5,800 lm                | 384 |
| 911401538932 | RC160V LED54/930<br>W60L120 PSD           | 3000 K            | 119 lm/W                        | 5,450 lm                | 384 |
| 911401539032 | RC160V LED58/940<br>W60L120 PSD           | 4000 K            | 126 lm/W                        | 5,800 lm                | 384 |
| 911401539132 | RC160V LED58/965<br>W60L120 PSD           | 6500 K            | 126 lm/W                        | 5,800 lm                | 384 |
| 911401540432 | RC160X LED54/930<br>W60L120 SIA           | 3000 K            | 119 lm/W                        | 5,450 lm                | 384 |
| 911401540532 | RC160X LED58/940<br>W60L120 SIA           | 4000 K            | 126 lm/W                        | 5,800 lm                | 384 |
| 911401540632 | RC160X LED58/965<br>W60L120 SIA           | 6500 K            | 126 lm/W                        | 5,800 lm                | 384 |
| 911401541332 | RC160V LED54/930<br>W60L120 PSU CAU       | 3000 K            | 119 lm/W                        | 5,450 lm                | 384 |
| 911401541432 | RC160V LED58/940<br>W60L120 PSU CAU       | 4000 K            | 126 lm/W                        | 5,800 lm                | 384 |
| 911401541532 | RC160V LED58/965<br>W60L120 PSU CAU       | 6500 K            | 126 lm/W                        | 5,800 lm                | 384 |
| 911401542232 | RC160V LED54/930<br>W60L120 PSD CAU       | 3000 K            | 119 lm/W                        | 5,450 lm                | 384 |
| 911401542332 | RC160V LED58/940<br>W60L120 PSD CAU       | 4000 K            | 126 lm/W                        | 5,800 lm                | 384 |
| 911401542432 | RC160V LED58/965<br>W60L120 PSD CAU       | 6500 K            | 126 lm/W                        | 5,800 lm                | 384 |
| 911401543732 | RC160X LED54/930<br>W60L120 SIA CAU       | 3000 K            | 119 lm/W                        | 5,450 lm                | 384 |
| 911401543832 | RC160X LED58/940<br>W60L120 SIA CAU       | 4000 K            | 126 lm/W                        | 5,800 lm                | 384 |
| 911401543932 | RC160X LED58/965<br>W60L120 SIA CAU       | 6500 K            | 126 lm/W                        | 5,800 lm                | 384 |
| 911401544632 | RC160V LED54/930<br>W60L120 PSU 54 CAU    | 3000 K            | 119 lm/W                        | 5,450 lm                | 384 |
| 911401544732 | RC160V LED58/940<br>W60L120 PSU 54 CAU    | 4000 K            | 126 lm/W                        | 5,800 lm                | 384 |
| 911401544832 | RC160V LED58/965<br>W60L120 PSU 54 CAU    | 6500 K            | 126 lm/W                        | 5,800 lm                | 384 |

| Order Code       | Full Product Name                       | Correlated Color  |                                 | Number of light sources |     |
|------------------|---|-------------------|---------------------------------|-------------------------|-----|
|                  |   | Temperature (Nom) | Luminous Efficacy (rated) (Nom) |                         |     |
| 911401544932     | RC160X LED48/930<br>W60L120 WIA         | 3000 K            | 121 lm/W                        | 4,800 lm                | 384 |
| 911401545032     | RC160X LED51/940<br>W60L120 WIA         | 4000 K            | 129 lm/W                        | 5,100 lm                | 384 |
| 911401545132     | RC160X LED51/965<br>W60L120 WIA         | 6500 K            | 129 lm/W                        | 5,100 lm                | 384 |
| 911401545232     | RC160X LED48/930<br>W60L120 WIA CAU     | 3000 K            | 121 lm/W                        | 4,800 lm                | 384 |
| 911401545332     | RC160X LED51/940<br>W60L120 WIA CAU     | 4000 K            | 129 lm/W                        | 5,100 lm                | 384 |
| 911401545432     | RC160X LED51/965<br>W60L120 WIA CAU     | 6500 K            | 129 lm/W                        | 5,100 lm                | 384 |
| 911401505343     | RC160V LED37/940<br>W603L603 PSU OC UVG | 4000 K            | 125 lm/W                        | 3,750 lm                | 240 |
| 911401505443     | RC160V LED37/965<br>W603L603 PSU OC UVG | 6500 K            | 125 lm/W                        | 3,750 lm                | 240 |
| 91140150983<br>2 | RC160V LED37/830<br>W60L60 PSU          | 3000 K            | 122 lm/W                        | 3,700 lm                | 240 |
| 91140150993<br>2 | RC160V LED39/840<br>W60L60 PSU          | 4000 K            | 130 lm/W                        | 3,900 lm                | 240 |
| 911401510032     | RC160V LED39/865<br>W60L60 PSU          | 6500 K            | 130 lm/W                        | 3,900 lm                | 240 |
| 911401510732     | RC160V LED37/830<br>W60L60 PSU OC       | 3000 K            | 122 lm/W                        | 3,700 lm                | 240 |
| 911401510832     | RC160V LED39/840<br>W60L60 PSU OC       | 4000 K            | 130 lm/W                        | 3,900 lm                | 240 |
| 911401510932     | RC160V LED39/865<br>W60L60 PSU OC       | 6500 K            | 130 lm/W                        | 3,900 lm                | 240 |
| 911401511632     | RC160V LED27/830<br>W60L60 PSU 16       | 3000 K            | 124 lm/W                        | 2,740 lm                | 240 |
| 911401511732     | RC160V LED29/840<br>W60L60 PSU 16       | 4000 K            | 132 lm/W                        | 2,900 lm                | 240 |
| 911401511832     | RC160V LED29/865<br>W60L60 PSU 16       | 6500 K            | 132 lm/W                        | 2,900 lm                | 240 |
| 911401512532     | RC160V LED37/830<br>W60L60 PSU 54       | 3000 K            | 122 lm/W                        | 3,700 lm                | 240 |
| 911401512632     | RC160V LED39/840<br>W60L60 PSU 54       | 4000 K            | 130 lm/W                        | 3,900 lm                | 240 |
| 911401512732     | RC160V LED39/865<br>W60L60 PSU 54       | 6500 K            | 130 lm/W                        | 3,900 lm                | 240 |
| 911401513432     | RC160V LED37/830<br>W60L60 PSU OC 54    | 3000 K            | 122 lm/W                        | 3,700 lm                | 240 |
| 911401513532     | RC160V LED39/840<br>W60L60 PSU OC 54    | 4000 K            | 130 lm/W                        | 3,900 lm                | 240 |
| 911401513632     | RC160V LED39/865<br>W60L60 PSU OC 54    | 6500 K            | 130 lm/W                        | 3,900 lm                | 240 |
| 911401514332     | RC160V LED27/830<br>W60L60 PSU 16 54    | 3000 K            | 124 lm/W                        | 2,740 lm                | 240 |
| 911401514432     | RC160V LED29/840<br>W60L60 PSU 16 54    | 4000 K            | 132 lm/W                        | 2,900 lm                | 240 |

| Order Code   | Full Product Name                        | Correlated Color  |                                 | Luminous Flux | Number of light sources |
|--------------|--|-------------------|---------------------------------|---------------|-------------------------|
|              |  | Temperature (Nom) | Luminous Efficacy (rated) (Nom) |               |                         |
| 911401514532 | RC160V LED29/865<br>W60L60 PSU 16 54     | 6500 K            | 132 lm/W                        | 2,900 lm      | 240                     |
| 911401516132 | RC160V LED37/830<br>W60L60 PSU OC CPC    | 3000 K            | 122 lm/W                        | 3,700 lm      | 240                     |
| 911401516232 | RC160V LED39/840<br>W60L60 PSU OC CPC    | 4000 K            | 130 lm/W                        | 3,900 lm      | 240                     |
| 911401516332 | RC160V LED39/865<br>W60L60 PSU OC CPC    | 6500 K            | 130 lm/W                        | 3,900 lm      | 240                     |
| 911401518832 | RC160V LED37/830<br>W60L60 PSU OC 54 CPC | 3000 K            | 122 lm/W                        | 3,700 lm      | 240                     |
| 911401518932 | RC160V LED39/840<br>W60L60 PSU OC 54 CPC | 4000 K            | 130 lm/W                        | 3,900 lm      | 240                     |
| 911401519032 | RC160V LED39/865<br>W60L60 PSU OC 54 CPC | 6500 K            | 130 lm/W                        | 3,900 lm      | 240                     |
| 911401520632 | RC160V LED37/830<br>W60L60 PSD           | 3000 K            | 122 lm/W                        | 3,700 lm      | 240                     |
| 911401520732 | RC160V LED39/840<br>W60L60 PSD           | 4000 K            | 130 lm/W                        | 3,900 lm      | 240                     |
| 911401520832 | RC160V LED39/865<br>W60L60 PSD           | 6500 K            | 130 lm/W                        | 3,900 lm      | 240                     |
| 911401521532 | RC160V LED37/830<br>W60L60 PSD OC        | 3000 K            | 122 lm/W                        | 3,700 lm      | 240                     |
| 911401521632 | RC160V LED39/840<br>W60L60 PSD OC        | 4000 K            | 130 lm/W                        | 3,900 lm      | 240                     |
| 911401521732 | RC160V LED39/865<br>W60L60 PSD OC        | 6500 K            | 130 lm/W                        | 3,900 lm      | 240                     |
| 911401522432 | RC160V LED27/830<br>W60L60 PSD 16        | 3000 K            | 124 lm/W                        | 2,740 lm      | 240                     |
| 911401522532 | RC160V LED29/840<br>W60L60 PSD 16        | 4000 K            | 132 lm/W                        | 2,900 lm      | 240                     |
| 911401522632 | RC160V LED29/865<br>W60L60 PSD 16        | 6500 K            | 132 lm/W                        | 2,900 lm      | 240                     |
| 911401523332 | RC160X LED37/830<br>W60L60 WIA           | 3000 K            | 122 lm/W                        | 3,700 lm      | 240                     |
| 911401523432 | RC160X LED39/840<br>W60L60 WIA           | 4000 K            | 130 lm/W                        | 3,900 lm      | 240                     |
| 911401523532 | RC160X LED39/865<br>W60L60 WIA           | 6500 K            | 130 lm/W                        | 3,900 lm      | 240                     |
| 911401523932 | RC160X LED37/830<br>W60L60 WIA OC        | 3000 K            | 122 lm/W                        | 3,700 lm      | 240                     |
| 911401524032 | RC160X LED39/840<br>W60L60 WIA OC        | 4000 K            | 130 lm/W                        | 3,900 lm      | 240                     |
| 911401524132 | RC160X LED39/865<br>W60L60 WIA OC        | 6500 K            | 130 lm/W                        | 3,900 lm      | 240                     |
| 911401524232 | RC160X LED27/830<br>W60L60 WIA 16        | 3000 K            | 124 lm/W                        | 2,740 lm      | 240                     |
| 911401524332 | RC160X LED29/840<br>W60L60 WIA 16        | 4000 K            | 132 lm/W                        | 2,900 lm      | 240                     |
| 911401524432 | RC160X LED29/865<br>W60L60 WIA 16        | 6500 K            | 132 lm/W                        | 2,900 lm      | 240                     |

| Order Code       | Full Product Name                     | Correlated Color  |                                 | Luminous Flux | Number of light sources |
|------------------|---------------------------------------|-------------------|---------------------------------|---------------|-------------------------|
|                  |                                       | Temperature (Nom) | Luminous Efficacy (rated) (Nom) |               |                         |
| 911401524532     | RC160X LED37/830<br>W60L60 SIA        | 3000 K            | 122 lm/W                        | 3,700 lm      | 240                     |
| 911401524632     | RC160X LED39/840<br>W60L60 SIA        | 4000 K            | 130 lm/W                        | 3,900 lm      | 240                     |
| 911401524732     | RC160X LED39/865<br>W60L60 SIA        | 6500 K            | 130 lm/W                        | 3,900 lm      | 240                     |
| 911401525432     | RC160V LED37/8TW<br>W60L60            | 2700 K            | 112 lm/W                        | 3,700 lm      | 240                     |
| 911401525732     | RC160V LED37/830<br>W60L60 PSU CAU    | 3000 K            | 122 lm/W                        | 3,700 lm      | 240                     |
| 911401525832     | RC160V LED39/840<br>W60L60 PSU CAU    | 4000 K            | 130 lm/W                        | 3,900 lm      | 240                     |
| 911401525932     | RC160V LED39/865<br>W60L60 PSU CAU    | 6500 K            | 130 lm/W                        | 3,900 lm      | 240                     |
| 911401526632     | RC160V LED37/830<br>W60L60 PSD CAU    | 3000 K            | 122 lm/W                        | 3,700 lm      | 240                     |
| 911401526732     | RC160V LED39/840<br>W60L60 PSD CAU    | 4000 K            | 130 lm/W                        | 3,900 lm      | 240                     |
| 911401526832     | RC160V LED39/865<br>W60L60 PSD CAU    | 6500 K            | 130 lm/W                        | 3,900 lm      | 240                     |
| 911401527532     | RC160X LED37/830<br>W60L60 WIA CAU    | 3000 K            | 122 lm/W                        | 3,700 lm      | 240                     |
| 911401527632     | RC160X LED39/840<br>W60L60 WIA CAU    | 4000 K            | 130 lm/W                        | 3,900 lm      | 240                     |
| 911401527732     | RC160X LED39/865<br>W60L60 WIA CAU    | 6500 K            | 130 lm/W                        | 3,900 lm      | 240                     |
| 911401528132     | RC160X LED37/830<br>W60L60 SIA CAU    | 3000 K            | 122 lm/W                        | 3,700 lm      | 240                     |
| 911401528232     | RC160X LED39/840<br>W60L60 SIA CAU    | 4000 K            | 130 lm/W                        | 3,900 lm      | 240                     |
| 911401528332     | RC160X LED39/865<br>W60L60 SIA CAU    | 6500 K            | 130 lm/W                        | 3,900 lm      | 240                     |
| 911401529032     | RC160V LED37/830<br>W60L60 PSU OC CAU | 3000 K            | 122 lm/W                        | 3,700 lm      | 240                     |
| 911401529132     | RC160V LED39/840<br>W60L60 PSU OC CAU | 4000 K            | 130 lm/W                        | 3,900 lm      | 240                     |
| 911401529232     | RC160V LED39/865<br>W60L60 PSU OC CAU | 6500 K            | 130 lm/W                        | 3,900 lm      | 240                     |
| 911401529932     | RC160V LED37/830<br>W60L60 PSD OC CAU | 3000 K            | 122 lm/W                        | 3,700 lm      | 240                     |
| 91140153003<br>2 | RC160V LED39/840<br>W60L60 PSD OC CAU | 4000 K            | 130 lm/W                        | 3,900 lm      | 240                     |
| 911401530132     | RC160V LED39/865<br>W60L60 PSD OC CAU | 6500 K            | 130 lm/W                        | 3,900 lm      | 240                     |
| 911401530832     | RC160X LED37/830<br>W60L60 WIA OC CAU | 3000 K            | 122 lm/W                        | 3,700 lm      | 240                     |
| 911401530932     | RC160X LED39/840<br>W60L60 WIA OC CAU | 4000 K            | 130 lm/W                        | 3,900 lm      | 240                     |
| 911401531032     | RC160X LED39/865<br>W60L60 WIA OC CAU | 6500 K            | 130 lm/W                        | 3,900 lm      | 240                     |

| Order Code   | Full Product Name                        | Correlated Color  |                                 | Number of light sources |     |
|--------------|--|-------------------|---------------------------------|-------------------------|-----|
|              |  | Temperature (Nom) | Luminous Efficacy (rated) (Nom) |                         |     |
| 911401531132 | RC160V LED27/830<br>W60L60 PSU 16 CAU    | 3000 K            | 124 lm/W                        | 2,740 lm                | 240 |
| 911401531232 | RC160V LED29/840<br>W60L60 PSU 16 CAU    | 4000 K            | 132 lm/W                        | 2,900 lm                | 240 |
| 911401531332 | RC160V LED29/865<br>W60L60 PSU 16 CAU    | 6500 K            | 132 lm/W                        | 2,900 lm                | 240 |
| 911401532032 | RC160V LED27/830<br>W60L60 PSD 16 CAU    | 3000 K            | 124 lm/W                        | 2,740 lm                | 240 |
| 911401532132 | RC160V LED29/840<br>W60L60 PSD 16 CAU    | 4000 K            | 132 lm/W                        | 2,900 lm                | 240 |
| 911401532232 | RC160V LED29/865<br>W60L60 PSD 16 CAU    | 6500 K            | 132 lm/W                        | 2,900 lm                | 240 |
| 911401532932 | RC160X LED27/830<br>W60L60 WIA 16 CAU    | 3000 K            | 124 lm/W                        | 2,740 lm                | 240 |
| 911401533032 | RC160X LED29/840<br>W60L60 WIA 16 CAU    | 4000 K            | 132 lm/W                        | 2,900 lm                | 240 |
| 911401533132 | RC160X LED29/865<br>W60L60 WIA 16 CAU    | 6500 K            | 132 lm/W                        | 2,900 lm                | 240 |
| 911401533232 | RC160V LED37/830<br>W60L60 PSU 54 CAU    | 3000 K            | 122 lm/W                        | 3,700 lm                | 240 |
| 911401533332 | RC160V LED39/840<br>W60L60 PSU 54 CAU    | 4000 K            | 130 lm/W                        | 3,900 lm                | 240 |
| 911401533432 | RC160V LED39/865<br>W60L60 PSU 54 CAU    | 6500 K            | 130 lm/W                        | 3,900 lm                | 240 |
| 911401534132 | RC160V LED37/830<br>W60L60 PSU OC 54 CAU | 3000 K            | 122 lm/W                        | 3,700 lm                | 240 |
| 911401534232 | RC160V LED39/840<br>W60L60 PSU OC 54 CAU | 4000 K            | 130 lm/W                        | 3,900 lm                | 240 |
| 911401534332 | RC160V LED39/865<br>W60L60 PSU OC 54 CAU | 6500 K            | 130 lm/W                        | 3,900 lm                | 240 |
| 911401535032 | RC160V LED27/830<br>W60L60 PSU 16 54 CAU | 3000 K            | 124 lm/W                        | 2,740 lm                | 240 |
| 911401535132 | RC160V LED29/840<br>W60L60 PSU 16 54 CAU | 4000 K            | 132 lm/W                        | 2,900 lm                | 240 |
| 911401535232 | RC160V LED29/865<br>W60L60 PSU 16 54 CAU | 6500 K            | 132 lm/W                        | 2,900 lm                | 240 |
| 911401535932 | RC160V LED37/830<br>W603L603 PSU UVG     | 3000 K            | 122 lm/W                        | 3,700 lm                | 240 |
| 911401536032 | RC160V LED39/840<br>W603L603 PSU UVG     | 4000 K            | 130 lm/W                        | 3,900 lm                | 240 |
| 911401536132 | RC160V LED39/865<br>W603L603 PSU UVG     | 6500 K            | 130 lm/W                        | 3,900 lm                | 240 |
| 911401536532 | RC160V LED35/930<br>W60L60 PSU           | 3000 K            | 118 lm/W                        | 3,500 lm                | 240 |
| 911401536632 | RC160V LED37/940<br>W60L60 PSU           | 4000 K            | 125 lm/W                        | 3,750 lm                | 240 |
| 911401536732 | RC160V LED37/965<br>W60L60 PSU           | 6500 K            | 125 lm/W                        | 3,750 lm                | 240 |
| 911401537432 | RC160V LED35/930<br>W60L60 PSU 54        | 3000 K            | 118 lm/W                        | 3,500 lm                | 240 |

| Order Code       | Full Product Name                     | Correlated Color  |                                 | Number of light sources |     |
|------------------|---------------------------------------|-------------------|---------------------------------|-------------------------|-----|
|                  |                                       | Temperature (Nom) | Luminous Efficacy (rated) (Nom) |                         |     |
| 911401537532     | RC160V LED37/940<br>W60L60 PSU 54     | 4000 K            | 125 lm/W                        | 3,750 lm                | 240 |
| 911401537632     | RC160V LED37/965<br>W60L60 PSU 54     | 6500 K            | 125 lm/W                        | 3,750 lm                | 240 |
| 911401538332     | RC160V LED35/930<br>W60L60 PSD        | 3000 K            | 118 lm/W                        | 3,500 lm                | 240 |
| 911401538432     | RC160V LED37/940<br>W60L60 PSD        | 4000 K            | 125 lm/W                        | 3,750 lm                | 240 |
| 911401538532     | RC160V LED37/965<br>W60L60 PSD        | 6500 K            | 125 lm/W                        | 3,750 lm                | 240 |
| 911401539232     | RC160X LED35/930<br>W60L60 WIA        | 3000 K            | 118 lm/W                        | 3,500 lm                | 240 |
| 911401539332     | RC160X LED37/940<br>W60L60 WIA        | 4000 K            | 125 lm/W                        | 3,750 lm                | 240 |
| 911401539432     | RC160X LED37/965<br>W60L60 WIA        | 6500 K            | 125 lm/W                        | 3,750 lm                | 240 |
| 911401539832     | RC160X LED35/930<br>W60L60 SIA        | 3000 K            | 118 lm/W                        | 3,500 lm                | 240 |
| 911401539932     | RC160X LED37/940<br>W60L60 SIA        | 4000 K            | 125 lm/W                        | 3,750 lm                | 240 |
| 91140154003<br>2 | RC160X LED37/965<br>W60L60 SIA        | 6500 K            | 125 lm/W                        | 3,750 lm                | 240 |
| 911401540732     | RC160V LED35/930<br>W60L60 PSU CAU    | 3000 K            | 118 lm/W                        | 3,500 lm                | 240 |
| 911401540832     | RC160V LED37/940<br>W60L60 PSU CAU    | 4000 K            | 125 lm/W                        | 3,750 lm                | 240 |
| 91140154093<br>2 | RC160V LED37/965<br>W60L60 PSU CAU    | 6500 K            | 125 lm/W                        | 3,750 lm                | 240 |
| 911401541632     | RC160V LED35/930<br>W60L60 PSD CAU    | 3000 K            | 118 lm/W                        | 3,500 lm                | 240 |
| 911401541732     | RC160V LED37/940<br>W60L60 PSD CAU    | 4000 K            | 125 lm/W                        | 3,750 lm                | 240 |
| 911401541832     | RC160V LED37/965<br>W60L60 PSD CAU    | 6500 K            | 125 lm/W                        | 3,750 lm                | 240 |
| 911401542532     | RC160X LED35/930<br>W60L60 WIA CAU    | 3000 K            | 118 lm/W                        | 3,500 lm                | 240 |
| 911401542632     | RC160X LED37/940<br>W60L60 WIA CAU    | 4000 K            | 125 lm/W                        | 3,750 lm                | 240 |
| 911401542732     | RC160X LED37/965<br>W60L60 WIA CAU    | 6500 K            | 125 lm/W                        | 3,750 lm                | 240 |
| 911401543132     | RC160X LED35/930<br>W60L60 SIA CAU    | 3000 K            | 118 lm/W                        | 3,500 lm                | 240 |
| 911401543232     | RC160X LED37/940<br>W60L60 SIA CAU    | 4000 K            | 125 lm/W                        | 3,750 lm                | 240 |
| 911401543332     | RC160X LED37/965<br>W60L60 SIA CAU    | 6500 K            | 125 lm/W                        | 3,750 lm                | 240 |
| 911401544032     | RC160V LED35/930<br>W60L60 PSU 54 CAU | 3000 K            | 118 lm/W                        | 3,500 lm                | 240 |
| 911401544132     | RC160V LED37/940<br>W60L60 PSU 54 CAU | 4000 K            | 125 lm/W                        | 3,750 lm                | 240 |



| Order Code   | Full Product Name                       | Correlated Color  |                                 | Number of light sources |
|--------------|---|-------------------|---------------------------------|-------------------------|
|              |   | Temperature (Nom) | Luminous Efficacy (rated) (Nom) |                         |
| 911401544232 | RC160V LED37/965<br>W60L60 PSU 54 CAU   | 6500 K            | 125 lm/W                        | 3,750 lm                |
| 911401545532 | RC160V LED36/9TW<br>W60L60              | 2700 K            | 120 lm/W                        | 3,600 lm                |
| 911401545832 | RC160V LED36/9TW<br>W60L60 54           | 2700 K            | 120 lm/W                        | 3,600 lm                |
| 911401546132 | RC160V LED36/9TW<br>W60L60 CAU          | 2700 K            | 120 lm/W                        | 3,600 lm                |
| 911401546432 | RC160V LED36/9TW<br>W60L60 54 CAU       | 2700 K            | 120 lm/W                        | 3,600 lm                |
| 911401578642 | RC160V LED37/830<br>W603L603 PSU OC UVG | 3000 K            | 122 lm/W                        | 3,700 lm                |
| 911401578742 | RC160V LED39/840<br>W603L603 PSU OC UVG | 4000 K            | 130 lm/W                        | 3,900 lm                |
| 911401578842 | RC160V LED39/865<br>W603L603 PSU OC UVG | 6500 K            | 130 lm/W                        | 3,900 lm                |

Operating and Electrical

| Order Code   | Full Product Name                      | Power Consumption | Order Code   | Full Product Name                   | Power Consumption |
|--------------|--|-------------------|--------------|-------------------------------------|-------------------|
| 911401505543 | RC160V LED37/940 W303L1210 PSU OC UVG  | 30 W              | 911401521932 | RC160V LED39/840 W30L120 PSD OC     | 30 W              |
| 911401505643 | RC160V LED37/965 W303L1210 PSU OC UVG  | 30 W              | 911401522032 | RC160V LED39/865 W30L120 PSD OC     | 30 W              |
| 911401510132 | RC160V LED37/830 W30L120 PSU           | 30 W              | 911401522732 | RC160V LED27/830 W30L120 PSD 16     | 22 W              |
| 911401510232 | RC160V LED39/840 W30L120 PSU           | 30 W              | 911401522832 | RC160V LED29/840 W30L120 PSD 16     | 22 W              |
| 911401510332 | RC160V LED39/865 W30L120 PSU           | 30 W              | 911401522932 | RC160V LED29/865 W30L120 PSD 16     | 22 W              |
| 911401511032 | RC160V LED37/830 W30L120 PSU OC        | 30 W              | 911401523632 | RC160X LED37/830 W30L120 WIA        | 30 W              |
| 911401511132 | RC160V LED39/840 W30L120 PSU OC        | 30 W              | 911401523732 | RC160X LED39/840 W30L120 WIA        | 30 W              |
| 911401511232 | RC160V LED39/865 W30L120 PSU OC        | 30 W              | 911401523832 | RC160X LED39/865 W30L120 WIA        | 30 W              |
| 911401511932 | RC160V LED27/830 W30L120 PSU 16        | 22 W              | 911401524832 | RC160X LED37/830 W30L120 SIA        | 30 W              |
| 911401512032 | RC160V LED29/840 W30L120 PSU 16        | 22 W              | 911401524932 | RC160X LED39/840 W30L120 SIA        | 30 W              |
| 911401512132 | RC160V LED29/865 W30L120 PSU 16        | 22 W              | 911401525032 | RC160X LED39/865 W30L120 SIA        | 30 W              |
| 911401512832 | RC160V LED37/830 W30L120 PSU 54        | 30 W              | 911401525532 | RC160V LED38/8TW W30L120            | 30 W              |
| 911401512932 | RC160V LED39/840 W30L120 PSU 54        | 30 W              | 911401526032 | RC160V LED37/830 W30L120 PSU CAU    | 30 W              |
| 911401513032 | RC160V LED39/865 W30L120 PSU 54        | 30 W              | 911401526132 | RC160V LED39/840 W30L120 PSU CAU    | 30 W              |
| 911401513732 | RC160V LED37/830 W30L120 PSU OC 54     | 30 W              | 911401526232 | RC160V LED39/865 W30L120 PSU CAU    | 30 W              |
| 911401513832 | RC160V LED39/840 W30L120 PSU OC 54     | 30 W              | 911401526932 | RC160V LED37/830 W30L120 PSD CAU    | 30 W              |
| 911401513932 | RC160V LED39/865 W30L120 PSU OC 54     | 30 W              | 911401527032 | RC160V LED39/840 W30L120 PSD CAU    | 30 W              |
| 911401514632 | RC160V LED27/830 W30L120 PSU 16 54     | 22 W              | 911401527132 | RC160V LED39/865 W30L120 PSD CAU    | 30 W              |
| 911401514732 | RC160V LED29/840 W30L120 PSU 16 54     | 22 W              | 911401527832 | RC160X LED37/830 W30L120 WIA CAU    | 30 W              |
| 911401514832 | RC160V LED29/865 W30L120 PSU 16 54     | 22 W              | 911401527932 | RC160X LED39/840 W30L120 WIA CAU    | 30 W              |
| 911401516432 | RC160V LED37/830 W30L120 PSU OC CPC    | 30 W              | 911401528032 | RC160X LED39/865 W30L120 WIA CAU    | 30 W              |
| 911401516532 | RC160V LED39/840 W30L120 PSU OC CPC    | 30 W              | 911401528432 | RC160X LED37/830 W30L120 SIA CAU    | 30 W              |
| 911401516632 | RC160V LED39/865 W30L120 PSU OC CPC    | 30 W              | 911401528532 | RC160X LED39/840 W30L120 SIA CAU    | 30 W              |
| 911401519132 | RC160V LED37/830 W30L120 PSU OC 54 CPC | 30 W              | 911401528632 | RC160X LED39/865 W30L120 SIA CAU    | 30 W              |
| 911401519232 | RC160V LED39/840 W30L120 PSU OC 54 CPC | 30 W              | 911401529332 | RC160V LED37/830 W30L120 PSU OC CAU | 30 W              |
| 911401519332 | RC160V LED39/865 W30L120 PSU OC 54 CPC | 30 W              | 911401529432 | RC160V LED39/840 W30L120 PSU OC CAU | 30 W              |
| 911401520932 | RC160V LED37/830 W30L120 PSD           | 30 W              | 911401529532 | RC160V LED39/865 W30L120 PSU OC CAU | 30 W              |
| 911401521032 | RC160V LED39/840 W30L120 PSD           | 30 W              | 911401530232 | RC160V LED37/830 W30L120 PSD OC CAU | 30 W              |
| 911401521132 | RC160V LED39/865 W30L120 PSD           | 30 W              | 911401530332 | RC160V LED39/840 W30L120 PSD OC CAU | 30 W              |
| 911401521832 | RC160V LED37/830 W30L120 PSD OC        | 30 W              | 911401530432 | RC160V LED39/865 W30L120 PSD OC CAU | 30 W              |

# RC160V

| Order Code   | Full Product Name                      | Power Consumption |
|--------------|--|-------------------|
| 911401531432 | RC160V LED27/830 W30L120 PSU 16 CAU    | 22 W              |
| 911401531532 | RC160V LED29/840 W30L120 PSU 16 CAU    | 22 W              |
| 911401531632 | RC160V LED29/865 W30L120 PSU 16 CAU    | 22 W              |
| 911401532332 | RC160V LED27/830 W30L120 PSD 16 CAU    | 22 W              |
| 911401532432 | RC160V LED29/840 W30L120 PSD 16 CAU    | 22 W              |
| 911401532532 | RC160V LED29/865 W30L120 PSD 16 CAU    | 22 W              |
| 911401533532 | RC160V LED37/830 W30L120 PSU 54 CAU    | 30 W              |
| 911401533632 | RC160V LED39/840 W30L120 PSU 54 CAU    | 30 W              |
| 911401533732 | RC160V LED39/865 W30L120 PSU 54 CAU    | 30 W              |
| 911401534432 | RC160V LED37/830 W30L120 PSU OC 54 CAU | 30 W              |
| 911401534532 | RC160V LED39/840 W30L120 PSU OC 54 CAU | 30 W              |
| 911401534632 | RC160V LED39/865 W30L120 PSU OC 54 CAU | 30 W              |
| 911401535332 | RC160V LED27/830 W30L120 PSU 16 54 CAU | 22 W              |
| 911401535432 | RC160V LED29/840 W30L120 PSU 16 54 CAU | 22 W              |
| 911401535532 | RC160V LED29/865 W30L120 PSU 16 54 CAU | 22 W              |
| 911401536232 | RC160V LED37/830 W30L1210 PSU UVG      | 30 W              |
| 911401536332 | RC160V LED39/840 W30L1210 PSU UVG      | 30 W              |
| 911401536432 | RC160V LED39/865 W30L1210 PSU UVG      | 30 W              |
| 911401536832 | RC160V LED35/930 W30L120 PSU           | 30 W              |
| 911401536932 | RC160V LED37/940 W30L120 PSU           | 30 W              |
| 911401537032 | RC160V LED37/965 W30L120 PSU           | 30 W              |
| 911401537732 | RC160V LED35/930 W30L120 PSU 54        | 30 W              |
| 911401537832 | RC160V LED37/940 W30L120 PSU 54        | 30 W              |
| 911401537932 | RC160V LED37/965 W30L120 PSU 54        | 30 W              |
| 911401538632 | RC160V LED35/930 W30L120 PSD           | 30 W              |
| 911401538732 | RC160V LED37/940 W30L120 PSD           | 30 W              |
| 911401538832 | RC160V LED37/965 W30L120 PSD           | 30 W              |
| 911401539532 | RC160X LED35/930 W30L120 WIA           | 30 W              |
| 911401539632 | RC160X LED37/940 W30L120 WIA           | 30 W              |
| 911401539732 | RC160X LED37/965 W30L120 WIA           | 30 W              |
| 911401540132 | RC160X LED35/930 W30L120 SIA           | 30 W              |
| 911401540232 | RC160X LED37/940 W30L120 SIA           | 30 W              |
| 911401540332 | RC160X LED37/965 W30L120 SIA           | 30 W              |
| 911401541032 | RC160V LED35/930 W30L120 PSU CAU       | 30 W              |
| 911401541132 | RC160V LED37/940 W30L120 PSU CAU       | 30 W              |
| 911401541232 | RC160V LED37/965 W30L120 PSU CAU       | 30 W              |
| 911401541932 | RC160V LED35/930 W30L120 PSD CAU       | 30 W              |
| 911401542032 | RC160V LED37/940 W30L120 PSD CAU       | 30 W              |
| 911401542132 | RC160V LED37/965 W30L120 PSD CAU       | 30 W              |
| 911401542832 | RC160X LED35/930 W30L120 WIA CAU       | 30 W              |
| 911401542932 | RC160X LED37/940 W30L120 WIA CAU       | 30 W              |
| 911401543032 | RC160X LED37/965 W30L120 WIA CAU       | 30 W              |
| 911401543432 | RC160X LED35/930 W30L120 SIA CAU       | 30 W              |
| 911401543532 | RC160X LED37/940 W30L120 SIA CAU       | 30 W              |
| 911401543632 | RC160X LED37/965 W30L120 SIA CAU       | 30 W              |
| 911401544332 | RC160V LED35/930 W30L120 PSU 54 CAU    | 30 W              |
| 911401544432 | RC160V LED37/940 W30L120 PSU 54 CAU    | 30 W              |
| 911401544532 | RC160V LED37/965 W30L120 PSU 54 CAU    | 30 W              |
| 911401545632 | RC160V LED37/9TW W30L120               | 30 W              |
| 911401545932 | RC160V LED37/9TW W30L120 54            | 30 W              |
| 911401546232 | RC160V LED37/9TW W30L120 CAU           | 30 W              |
| 911401546532 | RC160V LED37/9TW W30L120 54 CAU        | 30 W              |

| Order Code   | Full Product Name                    | Power Consumption |
|--------------|--------------------------------------|-------------------|
| 911401578942 | RC160V LED37/830 W30L1210 PSU OC UVG | 30 W              |
| 911401579042 | RC160V LED39/840 W30L1210 PSU OC UVG | 30 W              |
| 911401579142 | RC160V LED39/865 W30L1210 PSU OC UVG | 30 W              |
| 911401510432 | RC160V LED57/830 W60L120 PSU         | 46 W              |
| 911401510532 | RC160V LED60/840 W60L120 PSU         | 46 W              |
| 911401510632 | RC160V LED60/865 W60L120 PSU         | 46 W              |
| 911401511332 | RC160V LED57/830 W60L120 PSU OC      | 46 W              |
| 911401511432 | RC160V LED60/840 W60L120 PSU OC      | 46 W              |
| 911401511532 | RC160V LED60/865 W60L120 PSU OC      | 46 W              |
| 911401512232 | RC160V LED54/830 W60L120 PSU 16      | 46 W              |
| 911401512332 | RC160V LED58/840 W60L120 PSU 16      | 46 W              |
| 911401512432 | RC160V LED58/865 W60L120 PSU 16      | 46 W              |
| 911401513132 | RC160V LED57/830 W60L120 PSU 54      | 46 W              |
| 911401513232 | RC160V LED60/840 W60L120 PSU 54      | 46 W              |
| 911401513332 | RC160V LED60/865 W60L120 PSU 54      | 46 W              |
| 911401514032 | RC160V LED57/830 W60L120 PSU OC 54   | 46 W              |
| 911401514132 | RC160V LED60/840 W60L120 PSU OC 54   | 46 W              |
| 911401514232 | RC160V LED60/865 W60L120 PSU OC 54   | 46 W              |
| 911401514932 | RC160V LED54/830 W60L120 PSU 16 54   | 46 W              |
| 911401515032 | RC160V LED58/840 W60L120 PSU 16 54   | 46 W              |
| 911401515132 | RC160V LED58/865 W60L120 PSU 16 54   | 46 W              |
| 911401521232 | RC160V LED57/830 W60L120 PSD         | 46 W              |
| 911401521332 | RC160V LED60/840 W60L120 PSD         | 46 W              |
| 911401521432 | RC160V LED60/865 W60L120 PSD         | 46 W              |
| 911401522132 | RC160V LED57/830 W60L120 PSD OC      | 46 W              |
| 911401522232 | RC160V LED60/840 W60L120 PSD OC      | 46 W              |
| 911401522332 | RC160V LED60/865 W60L120 PSD OC      | 46 W              |
| 911401523032 | RC160V LED54/830 W60L120 PSD 16      | 46 W              |
| 911401523132 | RC160V LED58/840 W60L120 PSD 16      | 46 W              |
| 911401523232 | RC160V LED58/865 W60L120 PSD 16      | 46 W              |
| 911401525132 | RC160X LED57/830 W60L120 SIA         | 46 W              |
| 911401525232 | RC160X LED60/840 W60L120 SIA         | 46 W              |
| 911401525332 | RC160X LED60/865 W60L120 SIA         | 46 W              |
| 911401526332 | RC160V LED57/830 W60L120 PSU CAU     | 46 W              |
| 911401526432 | RC160V LED60/840 W60L120 PSU CAU     | 46 W              |
| 911401526532 | RC160V LED60/865 W60L120 PSU CAU     | 46 W              |
| 911401527232 | RC160V LED57/830 W60L120 PSD CAU     | 46 W              |
| 911401527332 | RC160V LED60/840 W60L120 PSD CAU     | 46 W              |
| 911401527432 | RC160V LED60/865 W60L120 PSD CAU     | 46 W              |
| 911401528732 | RC160X LED57/830 W60L120 SIA CAU     | 46 W              |
| 911401528832 | RC160X LED60/840 W60L120 SIA CAU     | 46 W              |
| 911401528932 | RC160X LED60/865 W60L120 SIA CAU     | 46 W              |
| 911401529632 | RC160V LED57/830 W60L120 PSU OC CAU  | 46 W              |
| 911401529732 | RC160V LED60/840 W60L120 PSU OC CAU  | 46 W              |
| 911401529832 | RC160V LED60/865 W60L120 PSU OC CAU  | 46 W              |
| 911401530532 | RC160V LED57/830 W60L120 PSD OC CAU  | 46 W              |
| 911401530632 | RC160V LED60/840 W60L120 PSD OC CAU  | 46 W              |
| 911401530732 | RC160V LED60/865 W60L120 PSD OC CAU  | 46 W              |
| 911401531732 | RC160V LED54/830 W60L120 PSU 16 CAU  | 46 W              |
| 911401531832 | RC160V LED58/840 W60L120 PSU 16 CAU  | 46 W              |
| 911401531932 | RC160V LED58/865 W60L120 PSU 16 CAU  | 46 W              |
| 911401532632 | RC160V LED54/830 W60L120 PSD 16 CAU  | 46 W              |

# RC160V

| Order Code   | Full Product Name                      | Power Consumption |
|--------------|--|-------------------|
| 911401532732 | RC160V LED58/840 W60L120 PSD 16 CAU    | 46 W              |
| 911401532832 | RC160V LED58/865 W60L120 PSD 16 CAU    | 46 W              |
| 911401533832 | RC160V LED57/830 W60L120 PSU 54 CAU    | 46 W              |
| 911401533932 | RC160V LED60/840 W60L120 PSU 54 CAU    | 46 W              |
| 911401534032 | RC160V LED60/865 W60L120 PSU 54 CAU    | 46 W              |
| 911401534732 | RC160V LED57/830 W60L120 PSU OC 54 CAU | 46 W              |
| 911401534832 | RC160V LED60/840 W60L120 PSU OC 54 CAU | 46 W              |
| 911401534932 | RC160V LED60/865 W60L120 PSU OC 54 CAU | 46 W              |
| 911401535632 | RC160V LED54/830 W60L120 PSU 16 54 CAU | 46 W              |
| 911401535732 | RC160V LED58/840 W60L120 PSU 16 54 CAU | 46 W              |
| 911401535832 | RC160V LED58/865 W60L120 PSU 16 54 CAU | 46 W              |
| 911401537132 | RC160V LED54/930 W60L120 PSU           | 46 W              |
| 911401537232 | RC160V LED58/940 W60L120 PSU           | 46 W              |
| 911401537332 | RC160V LED58/965 W60L120 PSU           | 46 W              |
| 911401538032 | RC160V LED54/930 W60L120 PSU 54        | 46 W              |
| 911401538132 | RC160V LED58/940 W60L120 PSU 54        | 46 W              |
| 911401538232 | RC160V LED58/965 W60L120 PSU 54        | 46 W              |
| 911401538932 | RC160V LED54/930 W60L120 PSD           | 46 W              |
| 911401539032 | RC160V LED58/940 W60L120 PSD           | 46 W              |
| 911401539132 | RC160V LED58/965 W60L120 PSD           | 46 W              |
| 911401540432 | RC160X LED54/930 W60L120 SIA           | 46 W              |
| 911401540532 | RC160X LED58/940 W60L120 SIA           | 46 W              |
| 911401540632 | RC160X LED58/965 W60L120 SIA           | 46 W              |
| 911401541332 | RC160V LED54/930 W60L120 PSU CAU       | 46 W              |
| 911401541432 | RC160V LED58/940 W60L120 PSU CAU       | 46 W              |
| 911401541532 | RC160V LED58/965 W60L120 PSU CAU       | 46 W              |
| 911401542232 | RC160V LED54/930 W60L120 PSD CAU       | 46 W              |
| 911401542332 | RC160V LED58/940 W60L120 PSD CAU       | 46 W              |
| 911401542432 | RC160V LED58/965 W60L120 PSD CAU       | 46 W              |
| 911401543732 | RC160X LED54/930 W60L120 SIA CAU       | 46 W              |
| 911401543832 | RC160X LED58/940 W60L120 SIA CAU       | 46 W              |
| 911401543932 | RC160X LED58/965 W60L120 SIA CAU       | 46 W              |
| 911401544632 | RC160V LED54/930 W60L120 PSU 54 CAU    | 46 W              |
| 911401544732 | RC160V LED58/940 W60L120 PSU 54 CAU    | 46 W              |
| 911401544832 | RC160V LED58/965 W60L120 PSU 54 CAU    | 46 W              |
| 911401544932 | RC160X LED48/930 W60L120 WIA           | 40 W              |
| 911401545032 | RC160X LED51/940 W60L120 WIA           | 40 W              |
| 911401545132 | RC160X LED51/965 W60L120 WIA           | 40 W              |
| 911401545232 | RC160X LED48/930 W60L120 WIA CAU       | 40 W              |
| 911401545332 | RC160X LED51/940 W60L120 WIA CAU       | 40 W              |
| 911401545432 | RC160X LED51/965 W60L120 WIA CAU       | 40 W              |
| 911401505343 | RC160V LED37/940 W603L603 PSU OC UVG   | 30 W              |
| 911401505443 | RC160V LED37/965 W603L603 PSU OC UVG   | 30 W              |
| 911401509832 | RC160V LED37/830 W60L60 PSU            | 30 W              |
| 911401509932 | RC160V LED39/840 W60L60 PSU            | 30 W              |
| 911401510032 | RC160V LED39/865 W60L60 PSU            | 30 W              |
| 911401510732 | RC160V LED37/830 W60L60 PSU OC         | 30 W              |
| 911401510832 | RC160V LED39/840 W60L60 PSU OC         | 30 W              |
| 911401510932 | RC160V LED39/865 W60L60 PSU OC         | 30 W              |
| 911401511632 | RC160V LED27/830 W60L60 PSU 16         | 22 W              |
| 911401511732 | RC160V LED29/840 W60L60 PSU 16         | 22 W              |
| 911401511832 | RC160V LED29/865 W60L60 PSU 16         | 22 W              |

| Order Code   | Full Product Name                     | Power Consumption |
|--------------|---------------------------------------|-------------------|
| 911401512532 | RC160V LED37/830 W60L60 PSU 54        | 30 W              |
| 911401512632 | RC160V LED39/840 W60L60 PSU 54        | 30 W              |
| 911401512732 | RC160V LED39/865 W60L60 PSU 54        | 30 W              |
| 911401513432 | RC160V LED37/830 W60L60 PSU OC 54     | 30 W              |
| 911401513532 | RC160V LED39/840 W60L60 PSU OC 54     | 30 W              |
| 911401513632 | RC160V LED39/865 W60L60 PSU OC 54     | 30 W              |
| 911401514332 | RC160V LED27/830 W60L60 PSU 16 54     | 22 W              |
| 911401514432 | RC160V LED29/840 W60L60 PSU 16 54     | 22 W              |
| 911401514532 | RC160V LED29/865 W60L60 PSU 16 54     | 22 W              |
| 911401516132 | RC160V LED37/830 W60L60 PSU OC CPC    | 30 W              |
| 911401516232 | RC160V LED39/840 W60L60 PSU OC CPC    | 30 W              |
| 911401516332 | RC160V LED39/865 W60L60 PSU OC CPC    | 30 W              |
| 911401518832 | RC160V LED37/830 W60L60 PSU OC 54 CPC | 30 W              |
| 911401518932 | RC160V LED39/840 W60L60 PSU OC 54 CPC | 30 W              |
| 911401519032 | RC160V LED39/865 W60L60 PSU OC 54 CPC | 30 W              |
| 911401520632 | RC160V LED37/830 W60L60 PSD           | 30 W              |
| 911401520732 | RC160V LED39/840 W60L60 PSD           | 30 W              |
| 911401520832 | RC160V LED39/865 W60L60 PSD           | 30 W              |
| 911401521532 | RC160V LED37/830 W60L60 PSD OC        | 30 W              |
| 911401521632 | RC160V LED39/840 W60L60 PSD OC        | 30 W              |
| 911401521732 | RC160V LED39/865 W60L60 PSD OC        | 30 W              |
| 911401522432 | RC160V LED27/830 W60L60 PSD 16        | 22 W              |
| 911401522532 | RC160V LED29/840 W60L60 PSD 16        | 22 W              |
| 911401522632 | RC160V LED29/865 W60L60 PSD 16        | 22 W              |
| 911401523332 | RC160X LED37/830 W60L60 WIA           | 30 W              |
| 911401523432 | RC160X LED39/840 W60L60 WIA           | 30 W              |
| 911401523532 | RC160X LED39/865 W60L60 WIA           | 30 W              |
| 911401523932 | RC160X LED37/830 W60L60 WIA OC        | 30 W              |
| 911401524032 | RC160X LED39/840 W60L60 WIA OC        | 30 W              |
| 911401524132 | RC160X LED39/865 W60L60 WIA OC        | 30 W              |
| 911401524232 | RC160X LED27/830 W60L60 WIA 16        | 22 W              |
| 911401524332 | RC160X LED29/840 W60L60 WIA 16        | 22 W              |
| 911401524432 | RC160X LED29/865 W60L60 WIA 16        | 22 W              |
| 911401524532 | RC160X LED37/830 W60L60 SIA           | 30 W              |
| 911401524632 | RC160X LED39/840 W60L60 SIA           | 30 W              |
| 911401524732 | RC160X LED39/865 W60L60 SIA           | 30 W              |
| 911401525432 | RC160V LED37/8TW W60L60               | 30 W              |
| 911401525732 | RC160V LED37/830 W60L60 PSU CAU       | 30 W              |
| 911401525832 | RC160V LED39/840 W60L60 PSU CAU       | 30 W              |
| 911401525932 | RC160V LED39/865 W60L60 PSU CAU       | 30 W              |
| 911401526632 | RC160V LED37/830 W60L60 PSD CAU       | 30 W              |
| 911401526732 | RC160V LED39/840 W60L60 PSD CAU       | 30 W              |
| 911401526832 | RC160V LED39/865 W60L60 PSD CAU       | 30 W              |
| 911401527532 | RC160X LED37/830 W60L60 WIA CAU       | 30 W              |
| 911401527632 | RC160X LED39/840 W60L60 WIA CAU       | 30 W              |
| 911401527732 | RC160X LED39/865 W60L60 WIA CAU       | 30 W              |
| 911401528132 | RC160X LED37/830 W60L60 SIA CAU       | 30 W              |
| 911401528232 | RC160X LED39/840 W60L60 SIA CAU       | 30 W              |
| 911401528332 | RC160X LED39/865 W60L60 SIA CAU       | 30 W              |
| 911401529032 | RC160V LED37/830 W60L60 PSU OC CAU    | 30 W              |
| 911401529132 | RC160V LED39/840 W60L60 PSU OC CAU    | 30 W              |
| 911401529232 | RC160V LED39/865 W60L60 PSU OC CAU    | 30 W              |

# RC160V

| Order Code   | Full Product Name                     | Power Consumption |
|--------------|---------------------------------------|-------------------|
| 911401529932 | RC160V LED37/830 W60L60 PSD OC CAU    | 30 W              |
| 911401530032 | RC160V LED39/840 W60L60 PSD OC CAU    | 30 W              |
| 911401530132 | RC160V LED39/865 W60L60 PSD OC CAU    | 30 W              |
| 911401530832 | RC160X LED37/830 W60L60 WIA OC CAU    | 30 W              |
| 911401530932 | RC160X LED39/840 W60L60 WIA OC CAU    | 30 W              |
| 911401531032 | RC160X LED39/865 W60L60 WIA OC CAU    | 30 W              |
| 911401531132 | RC160V LED27/830 W60L60 PSU 16 CAU    | 22 W              |
| 911401531232 | RC160V LED29/840 W60L60 PSU 16 CAU    | 22 W              |
| 911401531332 | RC160V LED29/865 W60L60 PSU 16 CAU    | 22 W              |
| 911401532032 | RC160V LED27/830 W60L60 PSD 16 CAU    | 22 W              |
| 911401532132 | RC160V LED29/840 W60L60 PSD 16 CAU    | 22 W              |
| 911401532232 | RC160V LED29/865 W60L60 PSD 16 CAU    | 22 W              |
| 911401532932 | RC160X LED27/830 W60L60 WIA 16 CAU    | 22 W              |
| 911401533032 | RC160X LED29/840 W60L60 WIA 16 CAU    | 22 W              |
| 911401533132 | RC160X LED29/865 W60L60 WIA 16 CAU    | 22 W              |
| 911401533232 | RC160V LED37/830 W60L60 PSU 54 CAU    | 30 W              |
| 911401533332 | RC160V LED39/840 W60L60 PSU 54 CAU    | 30 W              |
| 911401533432 | RC160V LED39/865 W60L60 PSU 54 CAU    | 30 W              |
| 911401534132 | RC160V LED37/830 W60L60 PSU OC 54 CAU | 30 W              |
| 911401534232 | RC160V LED39/840 W60L60 PSU OC 54 CAU | 30 W              |
| 911401534332 | RC160V LED39/865 W60L60 PSU OC 54 CAU | 30 W              |
| 911401535032 | RC160V LED27/830 W60L60 PSU 16 54 CAU | 22 W              |
| 911401535132 | RC160V LED29/840 W60L60 PSU 16 54 CAU | 22 W              |
| 911401535232 | RC160V LED29/865 W60L60 PSU 16 54 CAU | 22 W              |
| 911401535932 | RC160V LED37/830 W603L603 PSU UVG     | 30 W              |
| 911401536032 | RC160V LED39/840 W603L603 PSU UVG     | 30 W              |
| 911401536132 | RC160V LED39/865 W603L603 PSU UVG     | 30 W              |
| 911401536532 | RC160V LED35/930 W60L60 PSU           | 30 W              |
| 911401536632 | RC160V LED37/940 W60L60 PSU           | 30 W              |
| 911401536732 | RC160V LED37/965 W60L60 PSU           | 30 W              |
| 911401537432 | RC160V LED35/930 W60L60 PSU 54        | 30 W              |
| 911401537532 | RC160V LED37/940 W60L60 PSU 54        | 30 W              |

| Order Code   | Full Product Name                    | Power Consumption |
|--------------|--------------------------------------|-------------------|
| 911401537632 | RC160V LED37/965 W60L60 PSU 54       | 30 W              |
| 911401538332 | RC160V LED35/930 W60L60 PSD          | 30 W              |
| 911401538432 | RC160V LED37/940 W60L60 PSD          | 30 W              |
| 911401538532 | RC160V LED37/965 W60L60 PSD          | 30 W              |
| 911401539232 | RC160X LED35/930 W60L60 WIA          | 30 W              |
| 911401539332 | RC160X LED37/940 W60L60 WIA          | 30 W              |
| 911401539432 | RC160X LED37/965 W60L60 WIA          | 30 W              |
| 911401539832 | RC160X LED35/930 W60L60 SIA          | 30 W              |
| 911401539932 | RC160X LED37/940 W60L60 SIA          | 30 W              |
| 911401540032 | RC160X LED37/965 W60L60 SIA          | 30 W              |
| 911401540732 | RC160V LED35/930 W60L60 PSU CAU      | 30 W              |
| 911401540832 | RC160V LED37/940 W60L60 PSU CAU      | 30 W              |
| 911401540932 | RC160V LED37/965 W60L60 PSU CAU      | 30 W              |
| 911401541632 | RC160V LED35/930 W60L60 PSD CAU      | 30 W              |
| 911401541732 | RC160V LED37/940 W60L60 PSD CAU      | 30 W              |
| 911401541832 | RC160V LED37/965 W60L60 PSD CAU      | 30 W              |
| 911401542532 | RC160X LED35/930 W60L60 WIA CAU      | 30 W              |
| 911401542632 | RC160X LED37/940 W60L60 WIA CAU      | 30 W              |
| 911401542732 | RC160X LED37/965 W60L60 WIA CAU      | 30 W              |
| 911401543132 | RC160X LED35/930 W60L60 SIA CAU      | 30 W              |
| 911401543232 | RC160X LED37/940 W60L60 SIA CAU      | 30 W              |
| 911401543332 | RC160X LED37/965 W60L60 SIA CAU      | 30 W              |
| 911401544032 | RC160V LED35/930 W60L60 PSU 54 CAU   | 30 W              |
| 911401544132 | RC160V LED37/940 W60L60 PSU 54 CAU   | 30 W              |
| 911401544232 | RC160V LED37/965 W60L60 PSU 54 CAU   | 30 W              |
| 911401545532 | RC160V LED36/9TW W60L60              | 30 W              |
| 911401545832 | RC160V LED36/9TW W60L60 54           | 30 W              |
| 911401546132 | RC160V LED36/9TW W60L60 CAU          | 30 W              |
| 911401546432 | RC160V LED36/9TW W60L60 54 CAU       | 30 W              |
| 911401578642 | RC160V LED37/830 W603L603 PSU OC UVG | 30 W              |
| 911401578742 | RC160V LED39/840 W603L603 PSU OC UVG | 30 W              |
| 911401578842 | RC160V LED39/865 W603L603 PSU OC UVG | 30 W              |

## Controls and Dimming

| Order Code   | Full Product Name                        | Dimmable | Maximum dim level |
|--------------|--|----------|-------------------|
| 911401505543 | RC160V LED37/940 W303L1210 PSU<br>OC UVG | Fixed    | 0% (digital)      |
| 911401505643 | RC160V LED37/965 W303L1210 PSU<br>OC UVG | Fixed    | 0% (digital)      |
| 911401510132 | RC160V LED37/830 W30L120 PSU             | Fixed    | 0% (digital)      |
| 911401510232 | RC160V LED39/840 W30L120 PSU             | Fixed    | 0% (digital)      |
| 911401510332 | RC160V LED39/865 W30L120 PSU             | Fixed    | 0% (digital)      |
| 911401511032 | RC160V LED37/830 W30L120 PSU<br>OC       | Fixed    | 0% (digital)      |
| 911401511132 | RC160V LED39/840 W30L120 PSU<br>OC       | Fixed    | 0% (digital)      |
| 911401511232 | RC160V LED39/865 W30L120 PSU<br>OC       | Fixed    | 0% (digital)      |
| 911401511932 | RC160V LED27/830 W30L120 PSU 16          | Fixed    | 0% (digital)      |
| 911401512032 | RC160V LED29/840 W30L120 PSU<br>16       | Fixed    | 0% (digital)      |

| Order Code   | Full Product Name                     | Dimmable | Maximum dim level |
|--------------|---------------------------------------|----------|-------------------|
| 911401512132 | RC160V LED29/865 W30L120 PSU<br>16    | Fixed    | 0% (digital)      |
| 911401512832 | RC160V LED37/830 W30L120 PSU<br>54    | Fixed    | 0% (digital)      |
| 911401512932 | RC160V LED39/840 W30L120 PSU<br>54    | Fixed    | 0% (digital)      |
| 911401513032 | RC160V LED39/865 W30L120 PSU<br>54    | Fixed    | 0% (digital)      |
| 911401513732 | RC160V LED37/830 W30L120 PSU<br>OC 54 | Fixed    | 0% (digital)      |
| 911401513832 | RC160V LED39/840 W30L120 PSU<br>OC 54 | Fixed    | 0% (digital)      |
| 911401513932 | RC160V LED39/865 W30L120 PSU<br>OC 54 | Fixed    | 0% (digital)      |
| 911401514632 | RC160V LED27/830 W30L120 PSU 16<br>54 | Fixed    | 0% (digital)      |

# RC160V

| Order Code   | Full Product Name                      | Dimmable     | Maximum dim level |
|--------------|--|--------------|-------------------|
| 911401514732 | RC160V LED29/840 W30L120 PSU 16 54     | Fixed        | 0% (digital)      |
| 911401514832 | RC160V LED29/865 W30L120 PSU 16 54     | Fixed        | 0% (digital)      |
| 911401516432 | RC160V LED37/830 W30L120 PSU OC CPC    | Fixed        | 0% (digital)      |
| 911401516532 | RC160V LED39/840 W30L120 PSU OC CPC    | Fixed        | 0% (digital)      |
| 911401516632 | RC160V LED39/865 W30L120 PSU OC CPC    | Fixed        | 0% (digital)      |
| 911401519132 | RC160V LED37/830 W30L120 PSU OC 54 CPC | Fixed        | 0% (digital)      |
| 911401519232 | RC160V LED39/840 W30L120 PSU OC 54 CPC | Fixed        | 0% (digital)      |
| 911401519332 | RC160V LED39/865 W30L120 PSU OC 54 CPC | Fixed        | 0% (digital)      |
| 911401520932 | RC160V LED37/830 W30L120 PSD           | DALI         | Programmable      |
| 911401521032 | RC160V LED39/840 W30L120 PSD           | DALI         | Programmable      |
| 911401521132 | RC160V LED39/865 W30L120 PSD           | DALI         | Programmable      |
| 911401521832 | RC160V LED37/830 W30L120 PSD OC        | DALI         | Programmable      |
| 911401521932 | RC160V LED39/840 W30L120 PSD OC        | DALI         | Programmable      |
| 911401522032 | RC160V LED39/865 W30L120 PSD OC        | DALI         | Programmable      |
| 911401522732 | RC160V LED27/830 W30L120 PSD 16        | DALI         | Programmable      |
| 911401522832 | RC160V LED29/840 W30L120 PSD 16        | DALI         | Programmable      |
| 911401522932 | RC160V LED29/865 W30L120 PSD 16        | DALI         | Programmable      |
| 911401523632 | RC160X LED37/830 W30L120 WIA           | Wireless Dim | Programmable      |
| 911401523732 | RC160X LED39/840 W30L120 WIA           | Wireless Dim | Programmable      |
| 911401523832 | RC160X LED39/865 W30L120 WIA           | Wireless Dim | Programmable      |
| 911401524832 | RC160X LED37/830 W30L120 SIA           | Auto-Dim     | 0% (digital)      |
| 911401524932 | RC160X LED39/840 W30L120 SIA           | Auto-Dim     | 0% (digital)      |
| 911401525032 | RC160X LED39/865 W30L120 SIA           | Auto-Dim     | 0% (digital)      |
| 911401525532 | RC160V LED38/8TW W30L120               | DALI         | Programmable      |
| 911401526032 | RC160V LED37/830 W30L120 PSU CAU       | Fixed        | 0% (digital)      |
| 911401526132 | RC160V LED39/840 W30L120 PSU CAU       | Fixed        | 0% (digital)      |
| 911401526232 | RC160V LED39/865 W30L120 PSU CAU       | Fixed        | 0% (digital)      |
| 911401526932 | RC160V LED37/830 W30L120 PSD CAU       | DALI         | Programmable      |
| 911401527032 | RC160V LED39/840 W30L120 PSD CAU       | DALI         | Programmable      |
| 911401527132 | RC160V LED39/865 W30L120 PSD CAU       | DALI         | Programmable      |
| 911401527832 | RC160X LED37/830 W30L120 WIA CAU       | Wireless Dim | Programmable      |

| Order Code   | Full Product Name                      | Dimmable     | Maximum dim level |
|--------------|--|--------------|-------------------|
| 911401527932 | RC160X LED39/840 W30L120 WIA CAU       | Wireless Dim | Programmable      |
| 911401528032 | RC160X LED39/865 W30L120 WIA CAU       | Wireless Dim | Programmable      |
| 911401528432 | RC160X LED37/830 W30L120 SIA CAU       | Auto-Dim     | 0% (digital)      |
| 911401528532 | RC160X LED39/840 W30L120 SIA CAU       | Auto-Dim     | 0% (digital)      |
| 911401528632 | RC160X LED39/865 W30L120 SIA CAU       | Auto-Dim     | 0% (digital)      |
| 911401529332 | RC160V LED37/830 W30L120 PSU OC CAU    | Fixed        | 0% (digital)      |
| 911401529432 | RC160V LED39/840 W30L120 PSU OC CAU    | Fixed        | 0% (digital)      |
| 911401529532 | RC160V LED39/865 W30L120 PSU OC CAU    | Fixed        | 0% (digital)      |
| 911401530232 | RC160V LED37/830 W30L120 PSD OC CAU    | DALI         | Programmable      |
| 911401530332 | RC160V LED39/840 W30L120 PSD OC CAU    | DALI         | Programmable      |
| 911401530432 | RC160V LED39/865 W30L120 PSD OC CAU    | DALI         | Programmable      |
| 911401531432 | RC160V LED27/830 W30L120 PSU 16 CAU    | Fixed        | 0% (digital)      |
| 911401531532 | RC160V LED29/840 W30L120 PSU 16 CAU    | Fixed        | 0% (digital)      |
| 911401531632 | RC160V LED29/865 W30L120 PSU 16 CAU    | Fixed        | 0% (digital)      |
| 911401532332 | RC160V LED27/830 W30L120 PSD 16 CAU    | DALI         | Programmable      |
| 911401532432 | RC160V LED29/840 W30L120 PSD 16 CAU    | DALI         | Programmable      |
| 911401532532 | RC160V LED29/865 W30L120 PSD 16 CAU    | DALI         | Programmable      |
| 911401533532 | RC160V LED37/830 W30L120 PSU 54 CAU    | Fixed        | 0% (digital)      |
| 911401533632 | RC160V LED39/840 W30L120 PSU 54 CAU    | Fixed        | 0% (digital)      |
| 911401533732 | RC160V LED39/865 W30L120 PSU 54 CAU    | Fixed        | 0% (digital)      |
| 911401534432 | RC160V LED37/830 W30L120 PSU OC 54 CAU | Fixed        | 0% (digital)      |
| 911401534532 | RC160V LED39/840 W30L120 PSU OC 54 CAU | Fixed        | 0% (digital)      |
| 911401534632 | RC160V LED39/865 W30L120 PSU OC 54 CAU | Fixed        | 0% (digital)      |
| 911401535332 | RC160V LED27/830 W30L120 PSU 54 CAU    | Fixed        | 0% (digital)      |
| 911401535432 | RC160V LED29/840 W30L120 PSU 16 54 CAU | Fixed        | 0% (digital)      |
| 911401535532 | RC160V LED29/865 W30L120 PSU 16 54 CAU | Fixed        | 0% (digital)      |

# RC160V

| Order Code   | Full Product Name                   | Dimmable     | Maximum dim level |
|--------------|-------------------------------------|--------------|-------------------|
| 911401536232 | RC160V LED37/830 W303L1210 PSU UVG  | Fixed        | 0% (digital)      |
| 911401536332 | RC160V LED39/840 W303L1210 PSU UVG  | Fixed        | 0% (digital)      |
| 911401536432 | RC160V LED39/865 W303L1210 PSU UVG  | Fixed        | 0% (digital)      |
| 911401536832 | RC160V LED35/930 W30L120 PSU        | Fixed        | 0% (digital)      |
| 911401536932 | RC160V LED37/940 W30L120 PSU        | Fixed        | 0% (digital)      |
| 911401537032 | RC160V LED37/965 W30L120 PSU        | Fixed        | 0% (digital)      |
| 911401537732 | RC160V LED35/930 W30L120 PSU 54     | Fixed        | 0% (digital)      |
| 911401537832 | RC160V LED37/940 W30L120 PSU 54     | Fixed        | 0% (digital)      |
| 911401537932 | RC160V LED37/965 W30L120 PSU 54     | Fixed        | 0% (digital)      |
| 911401538632 | RC160V LED35/930 W30L120 PSD        | DALI         | Programmable      |
| 911401538732 | RC160V LED37/940 W30L120 PSD        | DALI         | Programmable      |
| 911401538832 | RC160V LED37/965 W30L120 PSD        | DALI         | Programmable      |
| 911401539532 | RC160X LED35/930 W30L120 WIA        | Wireless Dim | Programmable      |
| 911401539632 | RC160X LED37/940 W30L120 WIA        | Wireless Dim | Programmable      |
| 911401539732 | RC160X LED37/965 W30L120 WIA        | Wireless Dim | Programmable      |
| 911401540132 | RC160X LED35/930 W30L120 SIA        | Auto-Dim     | 0% (digital)      |
| 911401540232 | RC160X LED37/940 W30L120 SIA        | Auto-Dim     | 0% (digital)      |
| 911401540332 | RC160X LED37/965 W30L120 SIA        | Auto-Dim     | 0% (digital)      |
| 911401541032 | RC160V LED35/930 W30L120 PSU CAU    | Fixed        | 0% (digital)      |
| 911401541132 | RC160V LED37/940 W30L120 PSU CAU    | Fixed        | 0% (digital)      |
| 911401541232 | RC160V LED37/965 W30L120 PSU CAU    | Fixed        | 0% (digital)      |
| 911401541932 | RC160V LED35/930 W30L120 PSD CAU    | DALI         | Programmable      |
| 911401542032 | RC160V LED37/940 W30L120 PSD CAU    | DALI         | Programmable      |
| 911401542132 | RC160V LED37/965 W30L120 PSD CAU    | DALI         | Programmable      |
| 911401542832 | RC160X LED35/930 W30L120 WIA CAU    | Wireless Dim | Programmable      |
| 911401542932 | RC160X LED37/940 W30L120 WIA CAU    | Wireless Dim | Programmable      |
| 911401543032 | RC160X LED37/965 W30L120 WIA CAU    | Wireless Dim | Programmable      |
| 911401543432 | RC160X LED35/930 W30L120 SIA CAU    | Auto-Dim     | 0% (digital)      |
| 911401543532 | RC160X LED37/940 W30L120 SIA CAU    | Auto-Dim     | 0% (digital)      |
| 911401543632 | RC160X LED37/965 W30L120 SIA CAU    | Auto-Dim     | 0% (digital)      |
| 911401544332 | RC160V LED35/930 W30L120 PSU 54 CAU | Fixed        | 0% (digital)      |
| 911401544432 | RC160V LED37/940 W30L120 PSU 54 CAU | Fixed        | 0% (digital)      |

| Order Code   | Full Product Name                     | Dimmable | Maximum dim level |
|--------------|---------------------------------------|----------|-------------------|
| 911401544532 | RC160V LED37/965 W30L120 PSU 54 CAU   | Fixed    | 0% (digital)      |
| 911401545632 | RC160V LED37/9TW W30L120              | DALI     | Programmable      |
| 911401545932 | RC160V LED37/9TW W30L120 54           | DALI     | Programmable      |
| 911401546232 | RC160V LED37/9TW W30L120 CAU          | DALI     | Programmable      |
| 911401546532 | RC160V LED37/9TW W30L120 54 CAU       | DALI     | Programmable      |
| 911401578942 | RC160V LED37/830 W303L1210 PSU OC UVG | Fixed    | 0% (digital)      |
| 911401579042 | RC160V LED39/840 W303L1210 PSU OC UVG | Fixed    | 0% (digital)      |
| 911401579142 | RC160V LED39/865 W303L1210 PSU OC UVG | Fixed    | 0% (digital)      |
| 911401510432 | RC160V LED57/830 W60L120 PSU          | Fixed    | 0% (digital)      |
| 911401510532 | RC160V LED60/840 W60L120 PSU          | Fixed    | 0% (digital)      |
| 911401510632 | RC160V LED60/865 W60L120 PSU          | Fixed    | 0% (digital)      |
| 911401511332 | RC160V LED57/830 W60L120 PSU OC       | Fixed    | 0% (digital)      |
| 911401511432 | RC160V LED60/840 W60L120 PSU OC       | Fixed    | 0% (digital)      |
| 911401511532 | RC160V LED60/865 W60L120 PSU OC       | Fixed    | 0% (digital)      |
| 911401512232 | RC160V LED54/830 W60L120 PSU 16       | Fixed    | 0% (digital)      |
| 911401512332 | RC160V LED58/840 W60L120 PSU 16       | Fixed    | 0% (digital)      |
| 911401512432 | RC160V LED58/865 W60L120 PSU 16       | Fixed    | 0% (digital)      |
| 911401513132 | RC160V LED57/830 W60L120 PSU 54       | Fixed    | 0% (digital)      |
| 911401513232 | RC160V LED60/840 W60L120 PSU 54       | Fixed    | 0% (digital)      |
| 911401513332 | RC160V LED60/865 W60L120 PSU 54       | Fixed    | 0% (digital)      |
| 911401514032 | RC160V LED57/830 W60L120 PSU OC 54    | Fixed    | 0% (digital)      |
| 911401514132 | RC160V LED60/840 W60L120 PSU OC 54    | Fixed    | 0% (digital)      |
| 911401514232 | RC160V LED60/865 W60L120 PSU OC 54    | Fixed    | 0% (digital)      |
| 911401514932 | RC160V LED54/830 W60L120 PSU 16 54    | Fixed    | 0% (digital)      |
| 911401515032 | RC160V LED58/840 W60L120 PSU 16 54    | Fixed    | 0% (digital)      |
| 911401515132 | RC160V LED58/865 W60L120 PSU 16 54    | Fixed    | 0% (digital)      |
| 911401521232 | RC160V LED57/830 W60L120 PSD DALI     | DALI     | Programmable      |
| 911401521332 | RC160V LED60/840 W60L120 PSD DALI     | DALI     | Programmable      |
| 911401521432 | RC160V LED60/865 W60L120 PSD DALI     | DALI     | Programmable      |
| 911401522132 | RC160V LED57/830 W60L120 PSD OC       | DALI     | Programmable      |



# RC160V

| Order Code   | Full Product Name                      | Dimmable | Maximum dim level |
|--------------|--|----------|-------------------|
| 911401522232 | RC160V LED60/840 W60L120 PSD<br>OC     | DALI     | Programmable      |
| 911401522332 | RC160V LED60/865 W60L120 PSD<br>OC     | DALI     | Programmable      |
| 911401523032 | RC160V LED54/830 W60L120 PSD<br>16     | DALI     | Programmable      |
| 911401523132 | RC160V LED58/840 W60L120 PSD<br>16     | DALI     | Programmable      |
| 911401523232 | RC160V LED58/865 W60L120 PSD<br>16     | DALI     | Programmable      |
| 911401525132 | RC160X LED57/830 W60L120 SIA           | Auto-Dim | 0% (digital)      |
| 911401525232 | RC160X LED60/840 W60L120 SIA           | Auto-Dim | 0% (digital)      |
| 911401525332 | RC160X LED60/865 W60L120 SIA           | Auto-Dim | 0% (digital)      |
| 911401526332 | RC160V LED57/830 W60L120 PSU<br>CAU    | Fixed    | 0% (digital)      |
| 911401526432 | RC160V LED60/840 W60L120 PSU<br>CAU    | Fixed    | 0% (digital)      |
| 911401526532 | RC160V LED60/865 W60L120 PSU<br>CAU    | Fixed    | 0% (digital)      |
| 911401527232 | RC160V LED57/830 W60L120 PSD<br>CAU    | DALI     | Programmable      |
| 911401527332 | RC160V LED60/840 W60L120 PSD<br>CAU    | DALI     | Programmable      |
| 911401527432 | RC160V LED60/865 W60L120 PSD<br>CAU    | DALI     | Programmable      |
| 911401528732 | RC160X LED57/830 W60L120 SIA<br>CAU    | Auto-Dim | 0% (digital)      |
| 911401528832 | RC160X LED60/840 W60L120 SIA<br>CAU    | Auto-Dim | 0% (digital)      |
| 911401528932 | RC160X LED60/865 W60L120 SIA<br>CAU    | Auto-Dim | 0% (digital)      |
| 911401529632 | RC160V LED57/830 W60L120 PSU<br>OC CAU | Fixed    | 0% (digital)      |
| 911401529732 | RC160V LED60/840 W60L120 PSU<br>OC CAU | Fixed    | 0% (digital)      |
| 911401529832 | RC160V LED60/865 W60L120 PSU<br>OC CAU | Fixed    | 0% (digital)      |
| 911401530532 | RC160V LED57/830 W60L120 PSD<br>OC CAU | DALI     | Programmable      |
| 911401530632 | RC160V LED60/840 W60L120 PSD<br>OC CAU | DALI     | Programmable      |
| 911401530732 | RC160V LED60/865 W60L120 PSD<br>OC CAU | DALI     | Programmable      |
| 911401531732 | RC160V LED54/830 W60L120 PSU<br>16 CAU | Fixed    | 0% (digital)      |
| 911401531832 | RC160V LED58/840 W60L120 PSU<br>16 CAU | Fixed    | 0% (digital)      |
| 911401531932 | RC160V LED58/865 W60L120 PSU<br>16 CAU | Fixed    | 0% (digital)      |
| 911401532632 | RC160V LED54/830 W60L120 PSD<br>16 CAU | DALI     | Programmable      |

| Order Code   | Full Product Name                         | Dimmable | Maximum dim level |
|--------------|---|----------|-------------------|
| 911401532732 | RC160V LED58/840 W60L120 PSD<br>16 CAU    | DALI     | Programmable      |
| 911401532832 | RC160V LED58/865 W60L120 PSD<br>16 CAU    | DALI     | Programmable      |
| 911401533832 | RC160V LED57/830 W60L120 PSU<br>54 CAU    | Fixed    | 0% (digital)      |
| 911401533932 | RC160V LED60/840 W60L120 PSU<br>54 CAU    | Fixed    | 0% (digital)      |
| 911401534032 | RC160V LED60/865 W60L120 PSU<br>54 CAU    | Fixed    | 0% (digital)      |
| 911401534732 | RC160V LED57/830 W60L120 PSU<br>OC 54 CAU | Fixed    | 0% (digital)      |
| 911401534832 | RC160V LED60/840 W60L120 PSU<br>OC 54 CAU | Fixed    | 0% (digital)      |
| 911401534932 | RC160V LED60/865 W60L120 PSU<br>OC 54 CAU | Fixed    | 0% (digital)      |
| 911401535632 | RC160V LED54/830 W60L120 PSU<br>16 54 CAU | Fixed    | 0% (digital)      |
| 911401535732 | RC160V LED58/840 W60L120 PSU<br>16 54 CAU | Fixed    | 0% (digital)      |
| 911401535832 | RC160V LED58/865 W60L120 PSU<br>16 54 CAU | Fixed    | 0% (digital)      |
| 911401537132 | RC160V LED54/930 W60L120 PSU              | Fixed    | 0% (digital)      |
| 911401537232 | RC160V LED58/940 W60L120 PSU              | Fixed    | 0% (digital)      |
| 911401537332 | RC160V LED58/965 W60L120 PSU              | Fixed    | 0% (digital)      |
| 911401538032 | RC160V LED54/930 W60L120 PSU<br>54        | Fixed    | 0% (digital)      |
| 911401538132 | RC160V LED58/940 W60L120 PSU<br>54        | Fixed    | 0% (digital)      |
| 911401538232 | RC160V LED58/965 W60L120 PSU<br>54        | Fixed    | 0% (digital)      |
| 911401538932 | RC160V LED54/930 W60L120 PSD              | DALI     | Programmable      |
| 911401539032 | RC160V LED58/940 W60L120 PSD              | DALI     | Programmable      |
| 911401539132 | RC160V LED58/965 W60L120 PSD              | DALI     | Programmable      |
| 911401540432 | RC160X LED54/930 W60L120 SIA              | Auto-Dim | 0% (digital)      |
| 911401540532 | RC160X LED58/940 W60L120 SIA              | Auto-Dim | 0% (digital)      |
| 911401540632 | RC160X LED58/965 W60L120 SIA              | Auto-Dim | 0% (digital)      |
| 911401541332 | RC160V LED54/930 W60L120 PSU<br>CAU       | Fixed    | 0% (digital)      |
| 911401541432 | RC160V LED58/940 W60L120 PSU<br>CAU       | Fixed    | 0% (digital)      |
| 911401541532 | RC160V LED58/965 W60L120 PSU<br>CAU       | Fixed    | 0% (digital)      |
| 911401542232 | RC160V LED54/930 W60L120 PSD<br>CAU       | DALI     | Programmable      |
| 911401542332 | RC160V LED58/940 W60L120 PSD<br>CAU       | DALI     | Programmable      |
| 911401542432 | RC160V LED58/965 W60L120 PSD<br>CAU       | DALI     | Programmable      |
| 911401543732 | RC160X LED54/930 W60L120 SIA<br>CAU       | Auto-Dim | 0% (digital)      |

# RC160V

| Order Code   | Full Product Name                    | Dimmable     | Maximum dim level |
|--------------|--------------------------------------|--------------|-------------------|
| 911401543832 | RC160X LED58/940 W60L120 SIA CAU     | Auto-Dim     | 0% (digital)      |
| 911401543932 | RC160X LED58/965 W60L120 SIA CAU     | Auto-Dim     | 0% (digital)      |
| 911401544632 | RC160V LED54/930 W60L120 PSU 54 CAU  | Fixed        | 0% (digital)      |
| 911401544732 | RC160V LED58/940 W60L120 PSU 54 CAU  | Fixed        | 0% (digital)      |
| 911401544832 | RC160V LED58/965 W60L120 PSU 54 CAU  | Fixed        | 0% (digital)      |
| 911401544932 | RC160X LED48/930 W60L120 WIA         | Wireless Dim | Programmable      |
| 911401545032 | RC160X LED51/940 W60L120 WIA         | Wireless Dim | Programmable      |
| 911401545132 | RC160X LED51/965 W60L120 WIA         | Wireless Dim | Programmable      |
| 911401545232 | RC160X LED48/930 W60L120 WIA CAU     | Wireless Dim | Programmable      |
| 911401545332 | RC160X LED51/940 W60L120 WIA CAU     | Wireless Dim | Programmable      |
| 911401545432 | RC160X LED51/965 W60L120 WIA CAU     | Wireless Dim | Programmable      |
| 911401505343 | RC160V LED37/940 W603L603 PSU OC UVG | Fixed        | 0% (digital)      |
| 911401505443 | RC160V LED37/965 W603L603 PSU OC UVG | Fixed        | 0% (digital)      |
| 911401509832 | RC160V LED37/830 W60L60 PSU 2        | Fixed        | 0% (digital)      |
| 911401509932 | RC160V LED39/840 W60L60 PSU 2        | Fixed        | 0% (digital)      |
| 911401510032 | RC160V LED39/865 W60L60 PSU          | Fixed        | 0% (digital)      |
| 911401510732 | RC160V LED37/830 W60L60 PSU OC       | Fixed        | 0% (digital)      |
| 911401510832 | RC160V LED39/840 W60L60 PSU OC       | Fixed        | 0% (digital)      |
| 911401510932 | RC160V LED39/865 W60L60 PSU OC       | Fixed        | 0% (digital)      |
| 911401511632 | RC160V LED27/830 W60L60 PSU 16       | Fixed        | 0% (digital)      |
| 911401511732 | RC160V LED29/840 W60L60 PSU 16       | Fixed        | 0% (digital)      |
| 911401511832 | RC160V LED29/865 W60L60 PSU 16       | Fixed        | 0% (digital)      |
| 911401512532 | RC160V LED37/830 W60L60 PSU 54       | Fixed        | 0% (digital)      |
| 911401512632 | RC160V LED39/840 W60L60 PSU 54       | Fixed        | 0% (digital)      |
| 911401512732 | RC160V LED39/865 W60L60 PSU 54       | Fixed        | 0% (digital)      |
| 911401513432 | RC160V LED37/830 W60L60 PSU OC 54    | Fixed        | 0% (digital)      |
| 911401513532 | RC160V LED39/840 W60L60 PSU OC 54    | Fixed        | 0% (digital)      |
| 911401513632 | RC160V LED39/865 W60L60 PSU OC 54    | Fixed        | 0% (digital)      |
| 911401514332 | RC160V LED27/830 W60L60 PSU 16 54    | Fixed        | 0% (digital)      |
| 911401514432 | RC160V LED29/840 W60L60 PSU 16 54    | Fixed        | 0% (digital)      |

| Order Code   | Full Product Name                     | Dimmable     | Maximum dim level |
|--------------|---------------------------------------|--------------|-------------------|
| 911401514532 | RC160V LED29/865 W60L60 PSU 16 54     | Fixed        | 0% (digital)      |
| 911401516132 | RC160V LED37/830 W60L60 PSU OC CPC    | Fixed        | 0% (digital)      |
| 911401516232 | RC160V LED39/840 W60L60 PSU OC CPC    | Fixed        | 0% (digital)      |
| 911401516332 | RC160V LED39/865 W60L60 PSU OC CPC    | Fixed        | 0% (digital)      |
| 911401518832 | RC160V LED37/830 W60L60 PSU OC 54 CPC | Fixed        | 0% (digital)      |
| 911401518932 | RC160V LED39/840 W60L60 PSU OC 54 CPC | Fixed        | 0% (digital)      |
| 911401519032 | RC160V LED39/865 W60L60 PSU OC 54 CPC | Fixed        | 0% (digital)      |
| 911401520632 | RC160V LED37/830 W60L60 PSD           | DALI         | Programmable      |
| 911401520732 | RC160V LED39/840 W60L60 PSD           | DALI         | Programmable      |
| 911401520832 | RC160V LED39/865 W60L60 PSD           | DALI         | Programmable      |
| 911401521532 | RC160V LED37/830 W60L60 PSD OC        | DALI         | Programmable      |
| 911401521632 | RC160V LED39/840 W60L60 PSD OC        | DALI         | Programmable      |
| 911401521732 | RC160V LED39/865 W60L60 PSD OC        | DALI         | Programmable      |
| 911401522432 | RC160V LED27/830 W60L60 PSD 16        | DALI         | Programmable      |
| 911401522532 | RC160V LED29/840 W60L60 PSD 16        | DALI         | Programmable      |
| 911401522632 | RC160V LED29/865 W60L60 PSD 16        | DALI         | Programmable      |
| 911401523332 | RC160X LED37/830 W60L60 WIA           | Wireless Dim | Programmable      |
| 911401523432 | RC160X LED39/840 W60L60 WIA           | Wireless Dim | Programmable      |
| 911401523532 | RC160X LED39/865 W60L60 WIA           | Wireless Dim | Programmable      |
| 911401523932 | RC160X LED37/830 W60L60 WIA OC        | Wireless Dim | Programmable      |
| 911401524032 | RC160X LED39/840 W60L60 WIA OC        | Wireless Dim | Programmable      |
| 911401524132 | RC160X LED39/865 W60L60 WIA OC        | Wireless Dim | Programmable      |
| 911401524232 | RC160X LED27/830 W60L60 WIA 16        | Wireless Dim | Programmable      |
| 911401524332 | RC160X LED29/840 W60L60 WIA 16        | Wireless Dim | Programmable      |
| 911401524432 | RC160X LED29/865 W60L60 WIA 16        | Wireless Dim | Programmable      |
| 911401524532 | RC160X LED37/830 W60L60 SIA           | Auto-Dim     | 0% (digital)      |
| 911401524632 | RC160X LED39/840 W60L60 SIA           | Auto-Dim     | 0% (digital)      |
| 911401524732 | RC160X LED39/865 W60L60 SIA           | Auto-Dim     | 0% (digital)      |
| 911401525432 | RC160V LED37/8TW W60L60               | DALI         | Programmable      |
| 911401525732 | RC160V LED37/830 W60L60 PSU CAU       | Fixed        | 0% (digital)      |
| 911401525832 | RC160V LED39/840 W60L60 PSU CAU       | Fixed        | 0% (digital)      |
| 911401525932 | RC160V LED39/865 W60L60 PSU CAU       | Fixed        | 0% (digital)      |
| 911401526632 | RC160V LED37/830 W60L60 PSD CAU       | DALI         | Programmable      |
| 911401526732 | RC160V LED39/840 W60L60 PSD CAU       | DALI         | Programmable      |



# RC160V

| Order Code   | Full Product Name                  | Dimmable     | Maximum dim level |
|--------------|------------------------------------|--------------|-------------------|
| 911401526832 | RC160V LED39/865 W60L60 PSD CAU    | DALI         | Programmable      |
| 911401527532 | RC160X LED37/830 W60L60 WIA CAU    | Wireless Dim | Programmable      |
| 911401527632 | RC160X LED39/840 W60L60 WIA CAU    | Wireless Dim | Programmable      |
| 911401527732 | RC160X LED39/865 W60L60 WIA CAU    | Wireless Dim | Programmable      |
| 911401528132 | RC160X LED37/830 W60L60 SIA CAU    | Auto-Dim     | 0% (digital)      |
| 911401528232 | RC160X LED39/840 W60L60 SIA CAU    | Auto-Dim     | 0% (digital)      |
| 911401528332 | RC160X LED39/865 W60L60 SIA CAU    | Auto-Dim     | 0% (digital)      |
| 911401529032 | RC160V LED37/830 W60L60 PSU OC CAU | Fixed        | 0% (digital)      |
| 911401529132 | RC160V LED39/840 W60L60 PSU OC CAU | Fixed        | 0% (digital)      |
| 911401529232 | RC160V LED39/865 W60L60 PSU OC CAU | Fixed        | 0% (digital)      |
| 911401529932 | RC160V LED37/830 W60L60 PSD OC CAU | DALI         | Programmable      |
| 911401530032 | RC160V LED39/840 W60L60 PSD OC CAU | DALI         | Programmable      |
| 911401530132 | RC160V LED39/865 W60L60 PSD OC CAU | DALI         | Programmable      |
| 911401530832 | RC160X LED37/830 W60L60 WIA OC CAU | Wireless Dim | Programmable      |
| 911401530932 | RC160X LED39/840 W60L60 WIA OC CAU | Wireless Dim | Programmable      |
| 911401531032 | RC160X LED39/865 W60L60 WIA OC CAU | Wireless Dim | Programmable      |
| 911401531132 | RC160V LED27/830 W60L60 PSU 16 CAU | Fixed        | 0% (digital)      |
| 911401531232 | RC160V LED29/840 W60L60 PSU 16 CAU | Fixed        | 0% (digital)      |
| 911401531332 | RC160V LED29/865 W60L60 PSU 16 CAU | Fixed        | 0% (digital)      |
| 911401532032 | RC160V LED27/830 W60L60 PSD 16 CAU | DALI         | Programmable      |
| 911401532132 | RC160V LED29/840 W60L60 PSD 16 CAU | DALI         | Programmable      |
| 911401532232 | RC160V LED29/865 W60L60 PSD 16 CAU | DALI         | Programmable      |
| 911401532932 | RC160X LED27/830 W60L60 WIA 16 CAU | Wireless Dim | Programmable      |
| 911401533032 | RC160X LED29/840 W60L60 WIA 16 CAU | Wireless Dim | Programmable      |
| 911401533132 | RC160X LED29/865 W60L60 WIA 16 CAU | Wireless Dim | Programmable      |
| 911401533232 | RC160V LED37/830 W60L60 PSU 54 CAU | Fixed        | 0% (digital)      |

| Order Code   | Full Product Name                     | Dimmable     | Maximum dim level |
|--------------|---------------------------------------|--------------|-------------------|
| 911401533332 | RC160V LED39/840 W60L60 PSU 54 CAU    | Fixed        | 0% (digital)      |
| 911401533432 | RC160V LED39/865 W60L60 PSU 54 CAU    | Fixed        | 0% (digital)      |
| 911401534132 | RC160V LED37/830 W60L60 PSU OC 54 CAU | Fixed        | 0% (digital)      |
| 911401534232 | RC160V LED39/840 W60L60 PSU OC 54 CAU | Fixed        | 0% (digital)      |
| 911401534332 | RC160V LED39/865 W60L60 PSU OC 54 CAU | Fixed        | 0% (digital)      |
| 911401535032 | RC160V LED27/830 W60L60 PSU 16 54 CAU | Fixed        | 0% (digital)      |
| 911401535132 | RC160V LED29/840 W60L60 PSU 16 54 CAU | Fixed        | 0% (digital)      |
| 911401535232 | RC160V LED29/865 W60L60 PSU 16 54 CAU | Fixed        | 0% (digital)      |
| 911401535932 | RC160V LED37/830 W60L60 PSU UVG       | Fixed        | 0% (digital)      |
| 911401536032 | RC160V LED39/840 W60L60 PSU UVG       | Fixed        | 0% (digital)      |
| 911401536132 | RC160V LED39/865 W60L60 PSU UVG       | Fixed        | 0% (digital)      |
| 911401536532 | RC160V LED35/930 W60L60 PSU           | Fixed        | 0% (digital)      |
| 911401536632 | RC160V LED37/940 W60L60 PSU           | Fixed        | 0% (digital)      |
| 911401536732 | RC160V LED37/965 W60L60 PSU           | Fixed        | 0% (digital)      |
| 911401537432 | RC160V LED35/930 W60L60 PSU 54        | Fixed        | 0% (digital)      |
| 911401537532 | RC160V LED37/940 W60L60 PSU 54        | Fixed        | 0% (digital)      |
| 911401537632 | RC160V LED37/965 W60L60 PSU 54        | Fixed        | 0% (digital)      |
| 911401538332 | RC160V LED35/930 W60L60 PSD           | DALI         | Programmable      |
| 911401538432 | RC160V LED37/940 W60L60 PSD           | DALI         | Programmable      |
| 911401538532 | RC160V LED37/965 W60L60 PSD           | DALI         | Programmable      |
| 911401539232 | RC160X LED35/930 W60L60 WIA           | Wireless Dim | Programmable      |
| 911401539332 | RC160X LED37/940 W60L60 WIA           | Wireless Dim | Programmable      |
| 911401539432 | RC160X LED37/965 W60L60 WIA           | Wireless Dim | Programmable      |
| 911401539832 | RC160X LED35/930 W60L60 SIA           | Auto-Dim     | 0% (digital)      |
| 911401539932 | RC160X LED37/940 W60L60 SIA           | Auto-Dim     | 0% (digital)      |
| 911401540032 | RC160X LED37/965 W60L60 SIA 2         | Auto-Dim     | 0% (digital)      |
| 911401540732 | RC160V LED35/930 W60L60 PSU CAU       | Fixed        | 0% (digital)      |
| 911401540832 | RC160V LED37/940 W60L60 PSU CAU       | Fixed        | 0% (digital)      |
| 911401540932 | RC160V LED37/965 W60L60 PSU CAU       | Fixed        | 0% (digital)      |
| 911401541632 | RC160V LED35/930 W60L60 PSD CAU       | DALI         | Programmable      |
| 911401541732 | RC160V LED37/940 W60L60 PSD CAU       | DALI         | Programmable      |
| 911401541832 | RC160V LED37/965 W60L60 PSD CAU       | DALI         | Programmable      |
| 911401542532 | RC160X LED35/930 W60L60 WIA CAU       | Wireless Dim | Programmable      |

# RC160V

| Order Code   | Full Product Name                  | Dimmable     | Maximum dim level |
|--------------|------------------------------------|--------------|-------------------|
| 911401542632 | RC160X LED37/940 W60L60 WIA CAU    | Wireless Dim | Programmable      |
| 911401542732 | RC160X LED37/965 W60L60 WIA CAU    | Wireless Dim | Programmable      |
| 911401543132 | RC160X LED35/930 W60L60 SIA CAU    | Auto-Dim     | 0% (digital)      |
| 911401543232 | RC160X LED37/940 W60L60 SIA CAU    | Auto-Dim     | 0% (digital)      |
| 911401543332 | RC160X LED37/965 W60L60 SIA CAU    | Auto-Dim     | 0% (digital)      |
| 911401544032 | RC160V LED35/930 W60L60 PSU 54 CAU | Fixed        | 0% (digital)      |
| 911401544132 | RC160V LED37/940 W60L60 PSU 54 CAU | Fixed        | 0% (digital)      |

| Order Code   | Full Product Name                    | Dimmable | Maximum dim level |
|--------------|--------------------------------------|----------|-------------------|
| 911401544232 | RC160V LED37/965 W60L60 PSU 54 CAU   | Fixed    | 0% (digital)      |
| 911401545532 | RC160V LED36/9TW W60L60              | DALI     | Programmable      |
| 911401545832 | RC160V LED36/9TW W60L60 54           | DALI     | Programmable      |
| 911401546132 | RC160V LED36/9TW W60L60 CAU          | DALI     | Programmable      |
| 911401546432 | RC160V LED36/9TW W60L60 54 CAU       | DALI     | Programmable      |
| 911401578642 | RC160V LED37/830 W603L603 PSU OC UVG | Fixed    | 0% (digital)      |
| 911401578742 | RC160V LED39/840 W603L603 PSU OC UVG | Fixed    | 0% (digital)      |
| 911401578842 | RC160V LED39/865 W603L603 PSU OC UVG | Fixed    | 0% (digital)      |

## Mechanical and Housing

| Order Code   | Full Product Name                     | Optical cover type       | Ingress protection code |
|--------------|---------------------------------------|--------------------------|-------------------------|
| 911401505543 | RC160V LED37/940 W303L1210 PSU OC UVG | PS                       | IP20                    |
| 911401505643 | RC160V LED37/965 W303L1210 PSU OC UVG | PS                       | IP20                    |
| 911401510132 | RC160V LED37/830 W30L120 PSU          | PS                       | IP20                    |
| 911401510232 | RC160V LED39/840 W30L120 PSU          | PS                       | IP20                    |
| 911401510332 | RC160V LED39/865 W30L120 PSU          | PS                       | IP20                    |
| 911401511032 | RC160V LED37/830 W30L120 PSU OC       | PS                       | IP20                    |
| 911401511132 | RC160V LED39/840 W30L120 PSU OC       | PS                       | IP20                    |
| 911401511232 | RC160V LED39/865 W30L120 PSU OC       | PS                       | IP20                    |
| 911401511932 | RC160V LED27/830 W30L120 PSU 16       | Polycarbonate bowl/cover | IP20                    |
| 911401512032 | RC160V LED29/840 W30L120 PSU 16       | Polycarbonate bowl/cover | IP20                    |
| 911401512132 | RC160V LED29/865 W30L120 PSU 16       | Polycarbonate bowl/cover | IP20                    |
| 911401512832 | RC160V LED37/830 W30L120 PSU 54       | PS                       | IP54/20                 |
| 911401512932 | RC160V LED39/840 W30L120 PSU 54       | PS                       | IP54/20                 |
| 911401513032 | RC160V LED39/865 W30L120 PSU 54       | PS                       | IP54/20                 |
| 911401513732 | RC160V LED37/830 W30L120 PSU OC 54    | PS                       | IP54/20                 |
| 911401513832 | RC160V LED39/840 W30L120 PSU OC 54    | PS                       | IP54/20                 |

| Order Code   | Full Product Name                      | Optical cover type       | Ingress protection code |
|--------------|--|--------------------------|-------------------------|
| 911401513932 | RC160V LED39/865 W30L120 PSU OC 54     | PS                       | IP54/20                 |
| 911401514632 | RC160V LED27/830 W30L120 PSU 16 54     | Polycarbonate bowl/cover | IP54/20                 |
| 911401514732 | RC160V LED29/840 W30L120 PSU 16 54     | Polycarbonate bowl/cover | IP54/20                 |
| 911401514832 | RC160V LED29/865 W30L120 PSU 16 54     | Polycarbonate bowl/cover | IP54/20                 |
| 911401516432 | RC160V LED37/830 W30L120 PSU OC CPC    | PS                       | IP20                    |
| 911401516532 | RC160V LED39/840 W30L120 PSU OC CPC    | PS                       | IP20                    |
| 911401516632 | RC160V LED39/865 W30L120 PSU OC CPC    | PS                       | IP20                    |
| 911401519132 | RC160V LED37/830 W30L120 PSU OC 54 CPC | PS                       | IP54/20                 |
| 911401519232 | RC160V LED39/840 W30L120 PSU OC 54 CPC | PS                       | IP54/20                 |
| 911401519332 | RC160V LED39/865 W30L120 PSU OC 54 CPC | PS                       | IP54/20                 |
| 911401520932 | RC160V LED37/830 W30L120 PSD           | PS                       | IP20                    |
| 911401521032 | RC160V LED39/840 W30L120 PSD           | PS                       | IP20                    |
| 911401521132 | RC160V LED39/865 W30L120 PSD           | PS                       | IP20                    |
| 911401521832 | RC160V LED37/830 W30L120 PSD OC        | PS                       | IP20                    |
| 911401521932 | RC160V LED39/840 W30L120 PSD OC        | PS                       | IP20                    |
| 911401522032 | RC160V LED39/865 W30L120 PSD OC        | PS                       | IP20                    |

# RC160V

| Order Code   | Full Product Name                   | Optical cover type       | Ingress protection code |
|--------------|-------------------------------------|--------------------------|-------------------------|
| 911401522732 | RC160V LED27/830 W30L120 PSD 16     | Polycarbonate bowl/cover | IP20                    |
| 911401522832 | RC160V LED29/840 W30L120 PSD 16     | Polycarbonate bowl/cover | IP20                    |
| 911401522932 | RC160V LED29/865 W30L120 PSD 16     | Polycarbonate bowl/cover | IP20                    |
| 911401523632 | RC160X LED37/830 W30L120 WIA        | PS                       | IP20                    |
| 911401523732 | RC160X LED39/840 W30L120 WIA        | PS                       | IP20                    |
| 911401523832 | RC160X LED39/865 W30L120 WIA        | PS                       | IP20                    |
| 911401524832 | RC160X LED37/830 W30L120 SIA        | PS                       | IP20                    |
| 911401524932 | RC160X LED39/840 W30L120 SIA        | PS                       | IP20                    |
| 911401525032 | RC160X LED39/865 W30L120 SIA        | PS                       | IP20                    |
| 911401525532 | RC160V LED38/8TW W30L120            | PS                       | IP20                    |
| 911401526032 | RC160V LED37/830 W30L120 PSU CAU    | PS                       | IP20                    |
| 911401526132 | RC160V LED39/840 W30L120 PSU CAU    | PS                       | IP20                    |
| 911401526232 | RC160V LED39/865 W30L120 PSU CAU    | PS                       | IP20                    |
| 911401526932 | RC160V LED37/830 W30L120 PSD CAU    | PS                       | IP20                    |
| 911401527032 | RC160V LED39/840 W30L120 PSD CAU    | PS                       | IP20                    |
| 911401527132 | RC160V LED39/865 W30L120 PSD CAU    | PS                       | IP20                    |
| 911401527832 | RC160X LED37/830 W30L120 WIA CAU    | PS                       | IP20                    |
| 911401527932 | RC160X LED39/840 W30L120 WIA CAU    | PS                       | IP20                    |
| 911401528032 | RC160X LED39/865 W30L120 WIA CAU    | PS                       | IP20                    |
| 911401528432 | RC160X LED37/830 W30L120 SIA CAU    | PS                       | IP20                    |
| 911401528532 | RC160X LED39/840 W30L120 SIA CAU    | PS                       | IP20                    |
| 911401528632 | RC160X LED39/865 W30L120 SIA CAU    | PS                       | IP20                    |
| 911401529332 | RC160V LED37/830 W30L120 PSU OC CAU | PS                       | IP20                    |
| 911401529432 | RC160V LED39/840 W30L120 PSU OC CAU | PS                       | IP20                    |
| 911401529532 | RC160V LED39/865 W30L120 PSU OC CAU | PS                       | IP20                    |
| 911401530232 | RC160V LED37/830 W30L120 PSD OC CAU | PS                       | IP20                    |
| 911401530332 | RC160V LED39/840 W30L120 PSD OC CAU | PS                       | IP20                    |
| 911401530432 | RC160V LED39/865 W30L120 PSD OC CAU | PS                       | IP20                    |

| Order Code   | Full Product Name                      | Optical cover type       | Ingress protection code |
|--------------|--|--------------------------|-------------------------|
| 911401531432 | RC160V LED27/830 W30L120 PSU 16 CAU    | Polycarbonate bowl/cover | IP20                    |
| 911401531532 | RC160V LED29/840 W30L120 PSU 16 CAU    | Polycarbonate bowl/cover | IP20                    |
| 911401531632 | RC160V LED29/865 W30L120 PSU 16 CAU    | Polycarbonate bowl/cover | IP20                    |
| 911401532332 | RC160V LED27/830 W30L120 PSD 16 CAU    | Polycarbonate bowl/cover | IP20                    |
| 911401532432 | RC160V LED29/840 W30L120 PSD 16 CAU    | Polycarbonate bowl/cover | IP20                    |
| 911401532532 | RC160V LED29/865 W30L120 PSD 16 CAU    | Polycarbonate bowl/cover | IP20                    |
| 911401533532 | RC160V LED37/830 W30L120 PSU 54 CAU    | PS                       | IP54/20                 |
| 911401533632 | RC160V LED39/840 W30L120 PSU 54 CAU    | PS                       | IP54/20                 |
| 911401533732 | RC160V LED39/865 W30L120 PSU 54 CAU    | PS                       | IP54/20                 |
| 911401534432 | RC160V LED37/830 W30L120 PSU OC 54 CAU | PS                       | IP54/20                 |
| 911401534532 | RC160V LED39/840 W30L120 PSU OC 54 CAU | PS                       | IP54/20                 |
| 911401534632 | RC160V LED39/865 W30L120 PSU OC 54 CAU | PS                       | IP54/20                 |
| 911401535332 | RC160V LED27/830 W30L120 PSU 16 54 CAU | Polycarbonate bowl/cover | IP54/20                 |
| 911401535432 | RC160V LED29/840 W30L120 PSU 16 54 CAU | Polycarbonate bowl/cover | IP54/20                 |
| 911401535532 | RC160V LED29/865 W30L120 PSU 16 54 CAU | Polycarbonate bowl/cover | IP54/20                 |
| 911401536232 | RC160V LED37/830 W30L1210 PSU UVG      | PS                       | IP20                    |
| 911401536332 | RC160V LED39/840 W30L1210 PSU UVG      | PS                       | IP20                    |
| 911401536432 | RC160V LED39/865 W30L1210 PSU UVG      | PS                       | IP20                    |
| 911401536832 | RC160V LED35/930 W30L120 PSU           | PS                       | IP20                    |
| 911401536932 | RC160V LED37/940 W30L120 PSU           | PS                       | IP20                    |
| 911401537032 | RC160V LED37/965 W30L120 PSU           | PS                       | IP20                    |
| 911401537732 | RC160V LED35/930 W30L120 PSU 54        | PS                       | IP54/20                 |
| 911401537832 | RC160V LED37/940 W30L120 PSU 54        | PS                       | IP54/20                 |
| 911401537932 | RC160V LED37/965 W30L120 PSU 54        | PS                       | IP54/20                 |
| 911401538632 | RC160V LED35/930 W30L120 PSD           | PS                       | IP20                    |

# RC160V

| Order Code   | Full Product Name                     | Optical cover type | Ingress protection code |
|--------------|---------------------------------------|--------------------|-------------------------|
| 911401538732 | RC160V LED37/940 W30L120 PSD          | PS                 | IP20                    |
| 911401538832 | RC160V LED37/965 W30L120 PSD          | PS                 | IP20                    |
| 911401539532 | RC160X LED35/930 W30L120 WIA          | PS                 | IP20                    |
| 911401539632 | RC160X LED37/940 W30L120 WIA          | PS                 | IP20                    |
| 911401539732 | RC160X LED37/965 W30L120 WIA          | PS                 | IP20                    |
| 911401540132 | RC160X LED35/930 W30L120 SIA          | PS                 | IP20                    |
| 911401540232 | RC160X LED37/940 W30L120 SIA          | PS                 | IP20                    |
| 911401540332 | RC160X LED37/965 W30L120 SIA          | PS                 | IP20                    |
| 911401541032 | RC160V LED35/930 W30L120 PSU CAU      | PS                 | IP20                    |
| 911401541132 | RC160V LED37/940 W30L120 PSU CAU      | PS                 | IP20                    |
| 911401541232 | RC160V LED37/965 W30L120 PSU CAU      | PS                 | IP20                    |
| 911401541932 | RC160V LED35/930 W30L120 PSD CAU      | PS                 | IP20                    |
| 911401542032 | RC160V LED37/940 W30L120 PSD CAU      | PS                 | IP20                    |
| 911401542132 | RC160V LED37/965 W30L120 PSD CAU      | PS                 | IP20                    |
| 911401542832 | RC160X LED35/930 W30L120 WIA CAU      | PS                 | IP20                    |
| 911401542932 | RC160X LED37/940 W30L120 WIA CAU      | PS                 | IP20                    |
| 911401543032 | RC160X LED37/965 W30L120 WIA CAU      | PS                 | IP20                    |
| 911401543432 | RC160X LED35/930 W30L120 SIA CAU      | PS                 | IP20                    |
| 911401543532 | RC160X LED37/940 W30L120 SIA CAU      | PS                 | IP20                    |
| 911401543632 | RC160X LED37/965 W30L120 SIA CAU      | PS                 | IP20                    |
| 911401544332 | RC160V LED35/930 W30L120 PSU 54 CAU   | PS                 | IP54/20                 |
| 911401544432 | RC160V LED37/940 W30L120 PSU 54 CAU   | PS                 | IP54/20                 |
| 911401544532 | RC160V LED37/965 W30L120 PSU 54 CAU   | PS                 | IP54/20                 |
| 911401545632 | RC160V LED37/9TW W30L120              | PS                 | IP20                    |
| 911401545932 | RC160V LED37/9TW W30L120 54           | PS                 | IP54/20                 |
| 911401546232 | RC160V LED37/9TW W30L120 CAU          | PS                 | IP20                    |
| 911401546532 | RC160V LED37/9TW W30L120 54 CAU       | PS                 | IP54/20                 |
| 911401578942 | RC160V LED37/830 W303L1210 PSU OC UVG | PS                 | IP20                    |
| 911401579042 | RC160V LED39/840 W303L1210 PSU OC UVG | PS                 | IP20                    |

| Order Code   | Full Product Name                     | Optical cover type       | Ingress protection code |
|--------------|---------------------------------------|--------------------------|-------------------------|
| 911401579142 | RC160V LED39/865 W303L1210 PSU OC UVG | PS                       | IP20                    |
| 911401510432 | RC160V LED57/830 W60L120 PSU          | PS                       | IP20                    |
| 911401510532 | RC160V LED60/840 W60L120 PSU          | PS                       | IP20                    |
| 911401510632 | RC160V LED60/865 W60L120 PSU          | PS                       | IP20                    |
| 911401511332 | RC160V LED57/830 W60L120 PSU OC       | PS                       | IP20                    |
| 911401511432 | RC160V LED60/840 W60L120 PSU OC       | PS                       | IP20                    |
| 911401511532 | RC160V LED60/865 W60L120 PSU OC       | PS                       | IP20                    |
| 911401512232 | RC160V LED54/830 W60L120 PSU 16       | Polycarbonate bowl/cover | IP20                    |
| 911401512332 | RC160V LED58/840 W60L120 PSU 16       | Polycarbonate bowl/cover | IP20                    |
| 911401512432 | RC160V LED58/865 W60L120 PSU 16       | Polycarbonate bowl/cover | IP20                    |
| 911401513132 | RC160V LED57/830 W60L120 PSU 54       | PS                       | IP54/20                 |
| 911401513232 | RC160V LED60/840 W60L120 PSU 54       | PS                       | IP54/20                 |
| 911401513332 | RC160V LED60/865 W60L120 PSU 54       | PS                       | IP54/20                 |
| 911401514032 | RC160V LED57/830 W60L120 PSU OC 54    | PS                       | IP54/20                 |
| 911401514132 | RC160V LED60/840 W60L120 PSU OC 54    | PS                       | IP54/20                 |
| 911401514232 | RC160V LED60/865 W60L120 PSU OC 54    | PS                       | IP54/20                 |
| 911401514932 | RC160V LED54/830 W60L120 PSU 16 54    | Polycarbonate bowl/cover | IP54/20                 |
| 911401515032 | RC160V LED58/840 W60L120 PSU 16 54    | Polycarbonate bowl/cover | IP54/20                 |
| 911401515132 | RC160V LED58/865 W60L120 PSU 16 54    | Polycarbonate bowl/cover | IP54/20                 |
| 911401521232 | RC160V LED57/830 W60L120 PSD          | PS                       | IP20                    |
| 911401521332 | RC160V LED60/840 W60L120 PSD          | PS                       | IP20                    |
| 911401521432 | RC160V LED60/865 W60L120 PSD          | PS                       | IP20                    |
| 911401522132 | RC160V LED57/830 W60L120 PSD OC       | PS                       | IP20                    |
| 911401522232 | RC160V LED60/840 W60L120 PSD OC       | PS                       | IP20                    |
| 911401522332 | RC160V LED60/865 W60L120 PSD OC       | PS                       | IP20                    |

# RC160V

| Order Code   | Full Product Name                      | Optical cover type          | Ingress protection code |
|--------------|--|-----------------------------|-------------------------|
| 911401523032 | RC160V LED54/830 W60L120<br>PSD 16     | Polycarbonate<br>bowl/cover | IP20                    |
| 911401523132 | RC160V LED58/840 W60L120<br>PSD 16     | Polycarbonate<br>bowl/cover | IP20                    |
| 911401523232 | RC160V LED58/865 W60L120<br>PSD 16     | Polycarbonate<br>bowl/cover | IP20                    |
| 911401525132 | RC160X LED57/830 W60L120 SIA           | PS                          | IP20                    |
| 911401525232 | RC160X LED60/840 W60L120 SIA           | PS                          | IP20                    |
| 911401525332 | RC160X LED60/865 W60L120 SIA           | PS                          | IP20                    |
| 911401526332 | RC160V LED57/830 W60L120<br>PSU CAU    | PS                          | IP20                    |
| 911401526432 | RC160V LED60/840 W60L120<br>PSU CAU    | PS                          | IP20                    |
| 911401526532 | RC160V LED60/865 W60L120<br>PSU CAU    | PS                          | IP20                    |
| 911401527232 | RC160V LED57/830 W60L120<br>PSD CAU    | PS                          | IP20                    |
| 911401527332 | RC160V LED60/840 W60L120<br>PSD CAU    | PS                          | IP20                    |
| 911401527432 | RC160V LED60/865 W60L120<br>PSD CAU    | PS                          | IP20                    |
| 911401528732 | RC160X LED57/830 W60L120 SIA<br>CAU    | PS                          | IP20                    |
| 911401528832 | RC160X LED60/840 W60L120 SIA<br>CAU    | PS                          | IP20                    |
| 911401528932 | RC160X LED60/865 W60L120 SIA<br>CAU    | PS                          | IP20                    |
| 911401529632 | RC160V LED57/830 W60L120<br>PSU OC CAU | PS                          | IP20                    |
| 911401529732 | RC160V LED60/840 W60L120<br>PSU OC CAU | PS                          | IP20                    |
| 911401529832 | RC160V LED60/865 W60L120<br>PSU OC CAU | PS                          | IP20                    |
| 911401530532 | RC160V LED57/830 W60L120<br>PSD OC CAU | PS                          | IP20                    |
| 911401530632 | RC160V LED60/840 W60L120<br>PSD OC CAU | PS                          | IP20                    |
| 911401530732 | RC160V LED60/865 W60L120<br>PSD OC CAU | PS                          | IP20                    |
| 911401531732 | RC160V LED54/830 W60L120<br>PSU 16 CAU | Polycarbonate<br>bowl/cover | IP20                    |
| 911401531832 | RC160V LED58/840 W60L120<br>PSU 16 CAU | Polycarbonate<br>bowl/cover | IP20                    |
| 911401531932 | RC160V LED58/865 W60L120<br>PSU 16 CAU | Polycarbonate<br>bowl/cover | IP20                    |
| 911401532632 | RC160V LED54/830 W60L120<br>PSD 16 CAU | Polycarbonate<br>bowl/cover | IP20                    |
| 911401532732 | RC160V LED58/840 W60L120<br>PSD 16 CAU | Polycarbonate<br>bowl/cover | IP20                    |

| Order Code   | Full Product Name                         | Optical cover type          | Ingress protection code |
|--------------|---|-----------------------------|-------------------------|
| 911401532832 | RC160V LED58/865 W60L120<br>PSD 16 CAU    | Polycarbonate<br>bowl/cover | IP20                    |
| 911401533832 | RC160V LED57/830 W60L120<br>PSU 54 CAU    | PS                          | IP54/20                 |
| 911401533932 | RC160V LED60/840 W60L120<br>PSU 54 CAU    | PS                          | IP54/20                 |
| 911401534032 | RC160V LED60/865 W60L120<br>PSU 54 CAU    | PS                          | IP54/20                 |
| 911401534732 | RC160V LED57/830 W60L120<br>PSU OC 54 CAU | PS                          | IP54/20                 |
| 911401534832 | RC160V LED60/840 W60L120<br>PSU OC 54 CAU | PS                          | IP54/20                 |
| 911401534932 | RC160V LED60/865 W60L120<br>PSU OC 54 CAU | PS                          | IP54/20                 |
| 911401535632 | RC160V LED54/830 W60L120<br>PSU 16 54 CAU | Polycarbonate<br>bowl/cover | IP54/20                 |
| 911401535732 | RC160V LED58/840 W60L120<br>PSU 16 54 CAU | Polycarbonate<br>bowl/cover | IP54/20                 |
| 911401535832 | RC160V LED58/865 W60L120<br>PSU 16 54 CAU | Polycarbonate<br>bowl/cover | IP54/20                 |
| 911401537132 | RC160V LED54/930 W60L120<br>PSU           | PS                          | IP20                    |
| 911401537232 | RC160V LED58/940 W60L120<br>PSU           | PS                          | IP20                    |
| 911401537332 | RC160V LED58/965 W60L120<br>PSU           | PS                          | IP20                    |
| 911401538032 | RC160V LED54/930 W60L120<br>PSU 54        | PS                          | IP54/20                 |
| 911401538132 | RC160V LED58/940 W60L120<br>PSU 54        | PS                          | IP54/20                 |
| 911401538232 | RC160V LED58/965 W60L120<br>PSU 54        | PS                          | IP54/20                 |
| 911401538932 | RC160V LED54/930 W60L120<br>PSD           | PS                          | IP20                    |
| 911401539032 | RC160V LED58/940 W60L120<br>PSD           | PS                          | IP20                    |
| 911401539132 | RC160V LED58/965 W60L120<br>PSD           | PS                          | IP20                    |
| 911401540432 | RC160X LED54/930 W60L120 SIA              | PS                          | IP20                    |
| 911401540532 | RC160X LED58/940 W60L120 SIA              | PS                          | IP20                    |
| 911401540632 | RC160X LED58/965 W60L120 SIA              | PS                          | IP20                    |
| 911401541332 | RC160V LED54/930 W60L120<br>PSU CAU       | PS                          | IP20                    |
| 911401541432 | RC160V LED58/940 W60L120<br>PSU CAU       | PS                          | IP20                    |
| 911401541532 | RC160V LED58/965 W60L120<br>PSU CAU       | PS                          | IP20                    |
| 911401542232 | RC160V LED54/930 W60L120<br>PSD CAU       | PS                          | IP20                    |

# RC160V

| Order Code   | Full Product Name                    | Optical cover type       | Ingress protection code |
|--------------|--------------------------------------|--------------------------|-------------------------|
| 911401542332 | RC160V LED58/940 W60L120 PSD CAU     | PS                       | IP20                    |
| 911401542432 | RC160V LED58/965 W60L120 PSD CAU     | PS                       | IP20                    |
| 911401543732 | RC160X LED54/930 W60L120 SIA CAU     | PS                       | IP20                    |
| 911401543832 | RC160X LED58/940 W60L120 SIA CAU     | PS                       | IP20                    |
| 911401543932 | RC160X LED58/965 W60L120 SIA CAU     | PS                       | IP20                    |
| 911401544632 | RC160V LED54/930 W60L120 PSU 54 CAU  | PS                       | IP54/20                 |
| 911401544732 | RC160V LED58/940 W60L120 PSU 54 CAU  | PS                       | IP54/20                 |
| 911401544832 | RC160V LED58/965 W60L120 PSU 54 CAU  | PS                       | IP54/20                 |
| 911401544932 | RC160X LED48/930 W60L120 WIA         | PS                       | IP20                    |
| 911401545032 | RC160X LED51/940 W60L120 WIA         | PS                       | IP20                    |
| 911401545132 | RC160X LED51/965 W60L120 WIA         | PS                       | IP20                    |
| 911401545232 | RC160X LED48/930 W60L120 WIA CAU     | PS                       | IP20                    |
| 911401545332 | RC160X LED51/940 W60L120 WIA CAU     | PS                       | IP20                    |
| 911401545432 | RC160X LED51/965 W60L120 WIA CAU     | PS                       | IP20                    |
| 911401505343 | RC160V LED37/940 W603L603 PSU OC UVG | PS                       | IP20                    |
| 911401505443 | RC160V LED37/965 W603L603 PSU OC UVG | PS                       | IP20                    |
| 911401509832 | RC160V LED37/830 W60L60 PSU 2        | PS                       | IP20                    |
| 911401509932 | RC160V LED39/840 W60L60 PSU 2        | PS                       | IP20                    |
| 911401510032 | RC160V LED39/865 W60L60 PSU          | PS                       | IP20                    |
| 911401510732 | RC160V LED37/830 W60L60 PSU OC       | PS                       | IP20                    |
| 911401510832 | RC160V LED39/840 W60L60 PSU OC       | PS                       | IP20                    |
| 911401510932 | RC160V LED39/865 W60L60 PSU OC       | PS                       | IP20                    |
| 911401511632 | RC160V LED27/830 W60L60 PSU 16       | Polycarbonate bowl/cover | IP20                    |
| 911401511732 | RC160V LED29/840 W60L60 PSU 16       | Polycarbonate bowl/cover | IP20                    |
| 911401511832 | RC160V LED29/865 W60L60 PSU 16       | Polycarbonate bowl/cover | IP20                    |
| 911401512532 | RC160V LED37/830 W60L60 PSU 54       | PS                       | IP54/20                 |

| Order Code   | Full Product Name                     | Optical cover type       | Ingress protection code |
|--------------|---------------------------------------|--------------------------|-------------------------|
| 911401512632 | RC160V LED39/840 W60L60 PSU 54        | PS                       | IP54/20                 |
| 911401512732 | RC160V LED39/865 W60L60 PSU 54        | PS                       | IP54/20                 |
| 911401513432 | RC160V LED37/830 W60L60 PSU OC 54     | PS                       | IP54/20                 |
| 911401513532 | RC160V LED39/840 W60L60 PSU OC 54     | PS                       | IP54/20                 |
| 911401513632 | RC160V LED39/865 W60L60 PSU OC 54     | PS                       | IP54/20                 |
| 911401514332 | RC160V LED27/830 W60L60 PSU 16 54     | Polycarbonate bowl/cover | IP54/20                 |
| 911401514432 | RC160V LED29/840 W60L60 PSU 16 54     | Polycarbonate bowl/cover | IP54/20                 |
| 911401514532 | RC160V LED29/865 W60L60 PSU 16 54     | Polycarbonate bowl/cover | IP54/20                 |
| 911401516132 | RC160V LED37/830 W60L60 PSU OC CPC    | PS                       | IP20                    |
| 911401516232 | RC160V LED39/840 W60L60 PSU OC CPC    | PS                       | IP20                    |
| 911401516332 | RC160V LED39/865 W60L60 PSU OC CPC    | PS                       | IP20                    |
| 911401518832 | RC160V LED37/830 W60L60 PSU OC 54 CPC | PS                       | IP54/20                 |
| 911401518932 | RC160V LED39/840 W60L60 PSU OC 54 CPC | PS                       | IP54/20                 |
| 911401519032 | RC160V LED39/865 W60L60 PSU OC 54 CPC | PS                       | IP54/20                 |
| 911401520632 | RC160V LED37/830 W60L60 PSD           | PS                       | IP20                    |
| 911401520732 | RC160V LED39/840 W60L60 PSD           | PS                       | IP20                    |
| 911401520832 | RC160V LED39/865 W60L60 PSD           | PS                       | IP20                    |
| 911401521532 | RC160V LED37/830 W60L60 PSD OC        | PS                       | IP20                    |
| 911401521632 | RC160V LED39/840 W60L60 PSD OC        | PS                       | IP20                    |
| 911401521732 | RC160V LED39/865 W60L60 PSD OC        | PS                       | IP20                    |
| 911401522432 | RC160V LED27/830 W60L60 PSD 16        | Polycarbonate bowl/cover | IP20                    |
| 911401522532 | RC160V LED29/840 W60L60 PSD 16        | Polycarbonate bowl/cover | IP20                    |
| 911401522632 | RC160V LED29/865 W60L60 PSD 16        | Polycarbonate bowl/cover | IP20                    |
| 911401523332 | RC160X LED37/830 W60L60 WIA           | PS                       | IP20                    |
| 911401523432 | RC160X LED39/840 W60L60 WIA           | PS                       | IP20                    |
| 911401523532 | RC160X LED39/865 W60L60 WIA           | PS                       | IP20                    |
| 911401523932 | RC160X LED37/830 W60L60 WIA OC        | PS                       | IP20                    |
| 911401524032 | RC160X LED39/840 W60L60 WIA OC        | PS                       | IP20                    |

# RC160V

| Order Code   | Full Product Name                     | Optical cover type          | Ingress protection code |
|--------------|---------------------------------------|-----------------------------|-------------------------|
| 911401524132 | RC160X LED39/865 W60L60 WIA<br>OC     | PS                          | IP20                    |
| 911401524232 | RC160X LED27/830 W60L60 WIA<br>16     | Polycarbonate<br>bowl/cover | IP20                    |
| 911401524332 | RC160X LED29/840 W60L60 WIA<br>16     | Polycarbonate<br>bowl/cover | IP20                    |
| 911401524432 | RC160X LED29/865 W60L60 WIA<br>16     | Polycarbonate<br>bowl/cover | IP20                    |
| 911401524532 | RC160X LED37/830 W60L60 SIA           | PS                          | IP20                    |
| 911401524632 | RC160X LED39/840 W60L60 SIA           | PS                          | IP20                    |
| 911401524732 | RC160X LED39/865 W60L60 SIA           | PS                          | IP20                    |
| 911401525432 | RC160V LED37/8TW W60L60               | PS                          | IP20                    |
| 911401525732 | RC160V LED37/830 W60L60 PSU<br>CAU    | PS                          | IP20                    |
| 911401525832 | RC160V LED39/840 W60L60 PSU<br>CAU    | PS                          | IP20                    |
| 911401525932 | RC160V LED39/865 W60L60 PSU<br>CAU    | PS                          | IP20                    |
| 911401526632 | RC160V LED37/830 W60L60 PSD<br>CAU    | PS                          | IP20                    |
| 911401526732 | RC160V LED39/840 W60L60 PSD<br>CAU    | PS                          | IP20                    |
| 911401526832 | RC160V LED39/865 W60L60 PSD<br>CAU    | PS                          | IP20                    |
| 911401527532 | RC160X LED37/830 W60L60 WIA<br>CAU    | PS                          | IP20                    |
| 911401527632 | RC160X LED39/840 W60L60 WIA<br>CAU    | PS                          | IP20                    |
| 911401527732 | RC160X LED39/865 W60L60 WIA<br>CAU    | PS                          | IP20                    |
| 911401528132 | RC160X LED37/830 W60L60 SIA<br>CAU    | PS                          | IP20                    |
| 911401528232 | RC160X LED39/840 W60L60 SIA<br>CAU    | PS                          | IP20                    |
| 911401528332 | RC160X LED39/865 W60L60 SIA<br>CAU    | PS                          | IP20                    |
| 911401529032 | RC160V LED37/830 W60L60 PSU<br>OC CAU | PS                          | IP20                    |
| 911401529132 | RC160V LED39/840 W60L60 PSU<br>OC CAU | PS                          | IP20                    |
| 911401529232 | RC160V LED39/865 W60L60 PSU<br>OC CAU | PS                          | IP20                    |
| 911401529932 | RC160V LED37/830 W60L60 PSD<br>OC CAU | PS                          | IP20                    |
| 911401530032 | RC160V LED39/840 W60L60 PSD<br>OC CAU | PS                          | IP20                    |
| 911401530132 | RC160V LED39/865 W60L60 PSD<br>OC CAU | PS                          | IP20                    |
| 911401530832 | RC160X LED37/830 W60L60 WIA<br>OC CAU | PS                          | IP20                    |

| Order Code   | Full Product Name                        | Optical cover type          | Ingress protection code |
|--------------|--|-----------------------------|-------------------------|
| 911401530932 | RC160X LED39/840 W60L60 WIA<br>OC CAU    | PS                          | IP20                    |
| 911401531032 | RC160X LED39/865 W60L60 WIA<br>OC CAU    | PS                          | IP20                    |
| 911401531132 | RC160V LED27/830 W60L60 PSU<br>16 CAU    | Polycarbonate<br>bowl/cover | IP20                    |
| 911401531232 | RC160V LED29/840 W60L60 PSU<br>16 CAU    | Polycarbonate<br>bowl/cover | IP20                    |
| 911401531332 | RC160V LED29/865 W60L60 PSU<br>16 CAU    | Polycarbonate<br>bowl/cover | IP20                    |
| 911401532032 | RC160V LED27/830 W60L60 PSD<br>16 CAU    | Polycarbonate<br>bowl/cover | IP20                    |
| 911401532132 | RC160V LED29/840 W60L60 PSD<br>16 CAU    | Polycarbonate<br>bowl/cover | IP20                    |
| 911401532232 | RC160V LED29/865 W60L60 PSD<br>16 CAU    | Polycarbonate<br>bowl/cover | IP20                    |
| 911401532932 | RC160X LED27/830 W60L60 WIA<br>16 CAU    | Polycarbonate<br>bowl/cover | IP20                    |
| 911401533032 | RC160X LED29/840 W60L60 WIA<br>16 CAU    | Polycarbonate<br>bowl/cover | IP20                    |
| 911401533132 | RC160X LED29/865 W60L60 WIA<br>16 CAU    | Polycarbonate<br>bowl/cover | IP20                    |
| 911401533232 | RC160V LED37/830 W60L60 PSU<br>54 CAU    | PS                          | IP54/20                 |
| 911401533332 | RC160V LED39/840 W60L60 PSU<br>54 CAU    | PS                          | IP54/20                 |
| 911401533432 | RC160V LED39/865 W60L60 PSU<br>54 CAU    | PS                          | IP54/20                 |
| 911401534132 | RC160V LED37/830 W60L60 PSU<br>OC 54 CAU | PS                          | IP54/20                 |
| 911401534232 | RC160V LED39/840 W60L60 PSU<br>OC 54 CAU | PS                          | IP54/20                 |
| 911401534332 | RC160V LED39/865 W60L60 PSU<br>OC 54 CAU | PS                          | IP54/20                 |
| 911401535032 | RC160V LED27/830 W60L60 PSU<br>16 54 CAU | Polycarbonate<br>bowl/cover | IP54/20                 |
| 911401535132 | RC160V LED29/840 W60L60 PSU<br>16 54 CAU | Polycarbonate<br>bowl/cover | IP54/20                 |
| 911401535232 | RC160V LED29/865 W60L60 PSU<br>16 54 CAU | Polycarbonate<br>bowl/cover | IP54/20                 |
| 911401535932 | RC160V LED37/830 W603L603<br>PSU UVG     | PS                          | IP20                    |
| 911401536032 | RC160V LED39/840 W603L603<br>PSU UVG     | PS                          | IP20                    |
| 911401536132 | RC160V LED39/865 W603L603<br>PSU UVG     | PS                          | IP20                    |
| 911401536532 | RC160V LED35/930 W60L60 PSU              | PS                          | IP20                    |
| 911401536632 | RC160V LED37/940 W60L60 PSU              | PS                          | IP20                    |
| 911401536732 | RC160V LED37/965 W60L60 PSU              | PS                          | IP20                    |

# RC160V

| Order Code   | Full Product Name                       | Optical cover type | Ingress protection code |
|--------------|---|--------------------|-------------------------|
| 911401537432 | RC160V LED35/930 W60L60 PSU<br>54       | PS                 | IP54/20                 |
| 911401537532 | RC160V LED37/940 W60L60 PSU<br>54       | PS                 | IP54/20                 |
| 911401537632 | RC160V LED37/965 W60L60 PSU<br>54       | PS                 | IP54/20                 |
| 911401538332 | RC160V LED35/930 W60L60 PSD             | PS                 | IP20                    |
| 911401538432 | RC160V LED37/940 W60L60 PSD             | PS                 | IP20                    |
| 911401538532 | RC160V LED37/965 W60L60 PSD             | PS                 | IP20                    |
| 911401539232 | RC160X LED35/930 W60L60 WIA             | PS                 | IP20                    |
| 911401539332 | RC160X LED37/940 W60L60 WIA             | PS                 | IP20                    |
| 911401539432 | RC160X LED37/965 W60L60 WIA             | PS                 | IP20                    |
| 911401539832 | RC160X LED35/930 W60L60 SIA             | PS                 | IP20                    |
| 911401539932 | RC160X LED37/940 W60L60 SIA             | PS                 | IP20                    |
| 911401540032 | RC160X LED37/965 W60L60 SIA<br>2        | PS                 | IP20                    |
| 911401540732 | RC160V LED35/930 W60L60 PSU<br>CAU      | PS                 | IP20                    |
| 911401540832 | RC160V LED37/940 W60L60 PSU<br>CAU      | PS                 | IP20                    |
| 911401540932 | RC160V LED37/965 W60L60 PSU<br>2<br>CAU | PS                 | IP20                    |
| 911401541632 | RC160V LED35/930 W60L60 PSD<br>CAU      | PS                 | IP20                    |
| 911401541732 | RC160V LED37/940 W60L60 PSD<br>CAU      | PS                 | IP20                    |
| 911401541832 | RC160V LED37/965 W60L60 PSD<br>CAU      | PS                 | IP20                    |
| 911401542532 | RC160X LED35/930 W60L60 WIA<br>CAU      | PS                 | IP20                    |

| Order Code   | Full Product Name                       | Optical cover type | Ingress protection code |
|--------------|---|--------------------|-------------------------|
| 911401542632 | RC160X LED37/940 W60L60 WIA<br>CAU      | PS                 | IP20                    |
| 911401542732 | RC160X LED37/965 W60L60 WIA<br>CAU      | PS                 | IP20                    |
| 911401543132 | RC160X LED35/930 W60L60 SIA<br>CAU      | PS                 | IP20                    |
| 911401543232 | RC160X LED37/940 W60L60 SIA<br>CAU      | PS                 | IP20                    |
| 911401543332 | RC160X LED37/965 W60L60 SIA<br>CAU      | PS                 | IP20                    |
| 911401544032 | RC160V LED35/930 W60L60 PSU<br>54 CAU   | PS                 | IP54/20                 |
| 911401544132 | RC160V LED37/940 W60L60 PSU<br>54 CAU   | PS                 | IP54/20                 |
| 911401544232 | RC160V LED37/965 W60L60 PSU<br>54 CAU   | PS                 | IP54/20                 |
| 911401545532 | RC160V LED36/9TW W60L60                 | PS                 | IP20                    |
| 911401545832 | RC160V LED36/9TW W60L60 54              | PS                 | IP54/20                 |
| 911401546132 | RC160V LED36/9TW W60L60<br>CAU          | PS                 | IP20                    |
| 911401546432 | RC160V LED36/9TW W60L60 54<br>CAU       | PS                 | IP54/20                 |
| 911401578642 | RC160V LED37/830 W603L603<br>PSU OC UVG | PS                 | IP20                    |
| 911401578742 | RC160V LED39/840 W603L603<br>PSU OC UVG | PS                 | IP20                    |
| 911401578842 | RC160V LED39/865 W603L603<br>PSU OC UVG | PS                 | IP20                    |

