

# Philips TrueLine Surface: True line of light

## TrueLine, surface mounted

Architects need a lighting solution that matches the interior architecture of the space they are enhancing. They want a light line with elegant proportions and high light levels that offers maximum design freedom. Philips TrueLine is a flexible linear luminaire for indoor office applications that offers excellent quality with the promise of future-proof upgrades. Specifiers need luminaires that save energy, at the same time as providing the right level of light. TrueLine recessed meets both these sets of requirements. Not only is it compliant with the WELL Building Standard for Light, TrueLine surface is rated UGR<19, which is compliant with all office norms (OC). TrueLine also comes in suspended and recess-mounted versions. All the luminaires in the family are available in different lengths, shapes, colors and light outputs. This offers the ultimate design flexibility and unlimited possibilities. TrueLine luminaires are also a sustainable, future-proof choice with high efficiency up to 140 lm/W and the option to upgrade to wireless connectivity and control.

### Benefits

- Extremely high efficacy for a line luminaire
- Office compliant lighting
- Future-ready, scalable smart office capabilities
- Compatible with the Interact connected lighting system
- Supports sustainable building design and energy-saving subsidy criteria

# TrueLine, surface mounted

## Features

- Highly-uniform lighting with excellent glare control (UGR<19, L65<3000cd/m2)
- Best-in-class efficacy up to 140 lm/W
- 3000K, 4000K, and Tunable White versions, all CRI>90
- Long lifetime L90@50,000 hours
- Integrated sensors/wireless drivers for data collection, occupancy, daylight regulation and wayfinding
- Environmental Product Declaration (EPD)
- Recessed, suspended and surface mounted options, including all accessories

## Application

- Offices
- Education
- Retail

## Warnings and Safety

- The product is IPX0 and, as such, is not protected against water ingress. Therefore, we strongly recommend that the environment in which the luminaire is to be installed is suitably checked.
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure and the product warranty will become void.

## Versions



# TrueLine, surface mounted

## Versions

TrueLine-SM530 L570 BK





TrueLine SM-U3



TrueLine-SM530 L2810 WH




## Dimensional drawing



# TrueLine, surface mounted

## Dimensional drawing



# TrueLine, surface mounted

## Product details



TrueLine-SP534\_SM534P-DPP.tif



TrueLine-RC534B\_SM534C\_SP534P-DPP.tif




TrueLine\_SM-line-U3



TrueLine Surface Mounted black housing



TrueLine\_SM\_SP-line-coupling-piece-side-view



TrueLine\_SM\_SP-line-connection-top-view-2



TrueLine\_Surface-Mounted-line-side-view



SP530P U4 BK DPP

## TrueLine, surface mounted

### Product details



TrueLine\_SM\_SP-line-connectio-  
side-view-2

## TrueLine, surface mounted

General Information	
Driver included	Yes
Number of gear units	1 unit
Light Technical	
Beam angle of light source	120 degree(s)
Color rendering index (CRI)	>90
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Temperature	
Ambient temperature range	+10 to +40 °C
Controls and Dimming	
Dimmable	Yes
Approval and Application	
CE mark	Yes
Protection class IEC	Safety class I
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Mech. impact protection code	IK02
Ingress protection code	IP20
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Application Conditions	
Maximum dim level	1%

## General Information

Order Code	Full Product Name	Embedded control	Light source replaceable	Product family code
910505103218	SM530C LED40S/940 PSD PI5 L1130 ALU	-	No	SM530C
910505103219	SM530C LED34S/940 PSD PI5 L1130 ALU	-	No	SM530C
910505103220	SM530C LED19S/940 PSD PI5 L1410 ALU	-	No	SM530C
910505103223	SM531C LED19S/940 PSD PI5 L1410 ALU	-	No	SM531C
910505103224	SM531C LED19S/930 PSD PI5 L1410 ALU	-	No	SM531C
910505103227	SM530C LED43S/940 PSD PI5 L1410 ALU	-	No	SM530C
910505103228	SM530C LED34S/930 PSD PI5 L1130 ALU	-	No	SM530C
910505103229	SM530C LED31S/940 PSD PI5 L1410 ALU	-	No	SM530C
910505103233	SM530C LED50S/940 PSD PI5 L1410 ALU	-	No	SM530C
910505103275	SM530C LED40S/TW9 DIA PI5 L1130 ALU	-	No	SM530C
910505103221	SM534C LED40S/940 PSD PI5 L1130 ALU	-	No	SM534C
910505103222	SM534C LED50S/940 PSD PI5 L1410 ALU	-	No	SM534C
910505103217	SM530C LED19S/940 PSD PI5 L1410 WH	-	No	SM530C
910505103225	SM530C LED43S/940 PSD PI5 L1410 WH	-	No	SM530C
910505103226	SM530C LED50S/940 PSD PI5 L1410 WH	-	No	SM530C
910505103230	SM530C LED31S/940 PSD PI5 L1410 WH	-	No	SM530C
910505103231	SM531C LED19S/930 PSD PI5 L1410 WH	-	No	SM531C
910505103232	SM531C LED19S/940 PSD PI5 L1410 WH	-	No	SM531C
910505103277	SM531C LED31S/TW9 DIA PI5 L1410 WH	-	No	SM531C
910505103242	SM531C LED12S/940 PSD LE2 PI5 L570 WH	-	No	SM531C
910505103250	SM530C LED30S/940 PSD PI5 L2250 ALU	-	No	SM530C
910505103253	SM530C LED50S/930 PSD PI5 L2250 ALU	-	No	SM530C
910505103254	SM530C LED30S/940 PSD LF1 PI5 L2250 ALU	-	No	SM530C
910505103255	SM530C LED68S/940 PSD PI5 L2250 ALU	-	No	SM530C
910505103264	SM530C LED62S/930 PSD PI5 L2810 ALU	-	No	SM530C
910505103267	SM530C LED38S/940 PSD LF1 PI5 L2810 ALU	-	No	SM530C
910505103252	SM530C LED50S/940 SRD U4 PI3 L2290 BK	-	No	SM530C
910505103236	SM530C LED31S/940 PSD PI5 L1410 BK	-	No	SM530C
910505103276	SM530C LED34S/TW9 DIA PI5 L1130 BK	-	No	SM530C
910505103241	SM530C LED12S/940 PSD LE2 PI5 L570 ALU	-	No	SM530C
910505103251	SM531C LED30S/940 PSD PI5 L2250 BK	-	No	SM531C
910505103265	SM530C LED62S/940 PSD PI5 L2810 BK	-	No	SM530C
910505103268	SM530C LED86S/940 SRD U4LF1 PI3 L2850ALU	-	No	SM530C
910505103243	SM530C LED17S/940 PSD LE2 PI5 L570 BK	-	No	SM530C
910505103237	SM530C LED40S/940 SRD U4 PI3 L1170 ALU	-	No	SM530C
910505103238	SM530C LED34S/930 SRD U4 PI3 L1170 ALU	-	No	SM530C
910505103239	SM530C LED43S/940 SRD U4 PI3 L1450 ALU	-	No	SM530C
910505103240	SM530C LED31S/940 SRD U4 PI3 L1450 ALU	-	No	SM530C
910505103278	SM530C LED43S/TW9 SIA U4 L1450 ALU	-	No	SM530C

## TrueLine, surface mounted

Order Code	Full Product Name	Embedded control	Light source replaceable	Product family code
910505105667	SM530C LED50S/TW9 SIA U4 L1450 ALU	Upgradable sensor slot with SNS210 sensor	-	SM530C
910505105668	SM531C LED31S/TW9 SIA U4 L1450 ALU	Upgradable sensor slot with SNS210 sensor	-	SM531C
910505105675	SM530C LED40S/TW9 SIA U4 L1170 ALU	Upgradable sensor slot with SNS210 sensor	-	SM530C
910505105676	SM531C LED25S/TW9 SIA U4 L1170 ALU	Upgradable sensor slot with SNS210 sensor	-	SM531C
910505103266	SM531C LED62S/940 PSD PI5 L2810 WH	-	No	SM531C

### Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
		(K)	(lm/W)	(lm)	
910505103218	SM530C LED40S/940 PSD PI5 L1130 ALU	4000 K	138 lm/W	4,000 lm	Wide beam
910505103219	SM530C LED34S/940 PSD PI5 L1130 ALU	4000 K	143 lm/W	3,400 lm	Wide beam
910505103220	SM530C LED19S/940 PSD PI5 L1410 ALU	4000 K	139 lm/W	1,900 lm	Wide beam
910505103223	SM531C LED19S/940 PSD PI5 L1410 ALU	4000 K	110 lm/W	1,900 lm	Wide beam
910505103224	SM531C LED19S/930 PSD PI5 L1410 ALU	3000 K	104 lm/W	1,900 lm	Wide beam
910505103227	SM530C LED43S/940 PSD PI5 L1410 ALU	4000 K	144 lm/W	4,300 lm	Wide beam
910505103228	SM530C LED34S/930 PSD PI5 L1130 ALU	3000 K	133 lm/W	3,400 lm	Wide beam
910505103229	SM530C LED31S/940	4000 K	148 lm/W	3,100 lm	Wide beam

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
		(K)	(lm/W)	(lm)	
910505103233	SM530C LED50S/940 PSD PI5 L1410 ALU	4000 K	142 lm/W	5,000 lm	Wide beam
910505103275	SM530C LED40S/TW9 DIA PI5 L1130 ALU	Tunable white 2700-6500 K	121 lm/W	4,000 lm	Wide beam
910505103221	SM534C LED40S/940 PSD PI5 L1130 ALU	4000 K	130 lm/W	4,000 lm	Asymmetrical mirror
910505103222	SM534C LED50S/940 PSD PI5 L1410 ALU	4000 K	132 lm/W	5,000 lm	Asymmetrical mirror
910505103217	SM530C LED19S/940 PSD PI5 L1410 WH	4000 K	139 lm/W	1,900 lm	Wide beam
910505103225	SM530C LED43S/940 PSD PI5 L1410 WH	4000 K	144 lm/W	4,300 lm	Wide beam
910505103226	SM530C LED50S/940 PSD PI5 L1410 WH	4000 K	142 lm/W	5,000 lm	Wide beam



## TrueLine, surface mounted

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous	
		Temperature (Nom)	(rated) (Nom)	Flux	Optic type
910505103230	SM530C LED31S/940 PSD PI5 L1410 WH	4000 K	148 lm/W	3,100 lm	Wide beam
910505103231	SM531C LED19S/930 PSD PI5 L1410 WH	3000 K	104 lm/W	1,900 lm	Wide beam
910505103232	SM531C LED19S/940 PSD PI5 L1410 WH	4000 K	110 lm/W	1,900 lm	Wide beam
910505103277	SM531C LED31S/TW9 DIA PI5 L1410 WH	Tunable white 2700-6500 K	91 lm/W	3,100 lm	Wide beam
910505103242	SM531C LED12S/940 PSD LE2 PI5 L570 WH	4000 K	102 lm/W	1,250 lm	Wide beam
910505103250	SM530C LED30S/940 PSD PI5 L2250 ALU	4000 K	151 lm/W	3,000 lm	Wide beam
910505103253	SM530C LED50S/930 PSD PI5 L2250 ALU	3000 K	141 lm/W	5,000 lm	Wide beam
910505103254	SM530C LED30S/940 PSD LF1 PI5 L2250 ALU	4000 K	151 lm/W	3,000 lm	Wide beam
910505103255	SM530C LED68S/940 PSD PI5 L2250 ALU	4000 K	146 lm/W	6,800 lm	Wide beam
910505103264	SM530C LED62S/930 PSD PI5 L2810 ALU	3000 K	140 lm/W	6,200 lm	Wide beam
910505103267	SM530C LED38S/940 PSD LF1 PI5 L2810 ALU	4000 K	153 lm/W	3,800 lm	Wide beam
910505103252	SM530C LED50S/940 SRD U4 PI3 L2290 BK	4000 K	155 lm/W	5,000 lm	Wide beam

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous	
		Temperature (Nom)	(rated) (Nom)	Flux	Optic type
910505103236	SM530C LED31S/940 PSD PI5 L1410 BK	4000 K	148 lm/W	3,100 lm	Wide beam
910505103276	SM530C LED34S/TW9 DIA PI5 L1130 BK	Tunable white 2700-6500 K	124 lm/W	3,400 lm	Wide beam
910505103241	SM530C LED12S/940 PSD LE2 PI5 L570 ALU	4000 K	143 lm/W	1,250 lm	Wide beam
910505103251	SM531C LED30S/940 PSD PI5 L2250 BK	4000 K	115 lm/W	3,000 lm	Wide beam
910505103265	SM530C LED62S/940 PSD PI5 L2810 BK	4000 K	150 lm/W	6,200 lm	Wide beam
910505103268	SM530C LED86S/940 SRD U4LF1 PI3 L2850ALU	4000 K	154 lm/W	8,600 lm	Wide beam
910505103243	SM530C LED17S/940 PSD LE2 PI5 L570 BK	4000 K	143 lm/W	1,700 lm	Wide beam
910505103237	SM530C LED40S/940 SRD U4 PI3 L1170 ALU	4000 K	143 lm/W	4,000 lm	Wide beam
910505103238	SM530C LED34S/930 SRD U4 PI3 L1170 ALU	3000 K	138 lm/W	3,400 lm	Wide beam
910505103239	SM530C LED43S/940 SRD U4 PI3 L1450 ALU	4000 K	149 lm/W	4,300 lm	Wide beam
910505103240	SM530C LED31S/940 SRD U4 PI3 L1450 ALU	4000 K	144 lm/W	3,100 lm	Wide beam
910505103278	SM530C LED43S/TW9 SIA U4 L1450 ALU	Tunable white 2700-6500 K	121 lm/W	4,300 lm	Wide beam

## TrueLine, surface mounted

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous Flux	Optic type
		Temperature (Nom)	(rated) (Nom)		
910505105667	SM530C	Tunable white	121 lm/W	5,000 lm	Wide beam office compliant
	LED50S/TW9	2700-6500 K			
	SIA U4 L1450				
	ALU				
910505105668	SM531C	Tunable white	91 lm/W	3,100 lm	Wide beam
	LED31S/TW9	2700-6500 K			
	SIA U4 L1450				
	ALU				
910505105675	SM530C	Tunable white	121 lm/W	4,000 lm	Wide beam office compliant
	LED40S/TW9	2700-6500 K			
	SIA U4 L1170				
	ALU				

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous Flux	Optic type
		Temperature (Nom)	(rated) (Nom)		
910505105676	SM531C	Tunable white	93 lm/W	2,500 lm	Wide beam
	LED25S/TW9	2700-6500 K			
	SIA U4 L1170				
	ALU				
910505103266	SM531C	4000 K	111 lm/W	6,200 lm	Wide beam
	LED62S/940				
	PSD P15				
	L2810 WH				

### Operating and Electrical

Order Code	Full Product Name	Power Consumption
910505103218	SM530C LED40S/940 PSD P15 L1130 ALU	28.5 W
910505103219	SM530C LED34S/940 PSD P15 L1130 ALU	24.5 W
910505103220	SM530C LED19S/940 PSD P15 L1410 ALU	14 W
910505103223	SM531C LED19S/940 PSD P15 L1410 ALU	17.8 W
910505103224	SM531C LED19S/930 PSD P15 L1410 ALU	18.6 W
910505103227	SM530C LED43S/940 PSD P15 L1410 ALU	30.5 W
910505103228	SM530C LED34S/930 PSD P15 L1130 ALU	26 W
910505103229	SM530C LED31S/940 PSD P15 L1410 ALU	22 W
910505103233	SM530C LED50S/940 PSD P15 L1410 ALU	36 W
910505103275	SM530C LED40S/TW9 DIA P15 L1130 ALU	33 W
910505103221	SM534C LED40S/940 PSD P15 L1130 ALU	28.5 W
910505103222	SM534C LED50S/940 PSD P15 L1410 ALU	38.5 W
910505103217	SM530C LED19S/940 PSD P15 L1410 WH	14 W
910505103225	SM530C LED43S/940 PSD P15 L1410 WH	30.5 W
910505103226	SM530C LED50S/940 PSD P15 L1410 WH	36 W
910505103230	SM530C LED31S/940 PSD P15 L1410 WH	22 W
910505103231	SM531C LED19S/930 PSD P15 L1410 WH	18.6 W
910505103232	SM531C LED19S/940 PSD P15 L1410 WH	17.8 W
910505103277	SM531C LED31S/TW9 DIA P15 L1410 WH	34 W
910505103242	SM531C LED12S/940 PSD LE2 P15 L570 WH	11.8 W
910505103250	SM530C LED30S/940 PSD P15 L2250 ALU	22 W
910505103253	SM530C LED50S/930 PSD P15 L2250 ALU	37.5 W

Order Code	Full Product Name	Power Consumption
910505103254	SM530C LED30S/940 PSD LF1 P15 L2250 ALU	22 W
910505103255	SM530C LED68S/940 PSD P15 L2250 ALU	48.5 W
910505103264	SM530C LED62S/930 PSD P15 L2810 ALU	46 W
910505103267	SM530C LED38S/940 PSD LF1 P15 L2810 ALU	27 W
910505103252	SM530C LED50S/940 SRD U4 P13 L2290 BK	35.5 W
910505103236	SM530C LED31S/940 PSD P15 L1410 BK	22 W
910505103276	SM530C LED34S/TW9 DIA P15 L1130 BK	27.5 W
910505103241	SM530C LED12S/940 PSD LE2 P15 L570 ALU	9.1 W
910505103251	SM531C LED30S/940 PSD P15 L2250 BK	26.5 W
910505103265	SM530C LED62S/940 PSD P15 L2810 BK	44 W
910505103268	SM530C LED86S/940 SRD U4LF1 P13 L2850ALU	61 W
910505103243	SM530C LED17S/940 PSD LE2 P15 L570 BK	12.2 W
910505103237	SM530C LED40S/940 SRD U4 P13 L1170 ALU	28.5 W
910505103238	SM530C LED34S/930 SRD U4 P13 L1170 ALU	25.5 W
910505103239	SM530C LED43S/940 SRD U4 P13 L1450 ALU	30.5 W
910505103240	SM530C LED31S/940 SRD U4 P13 L1450 ALU	21.5 W
910505103278	SM530C LED43S/TW9 SIA U4 L1450 ALU	35.5 W
910505105667	SM530C LED50S/TW9 SIA U4 L1450 ALU	41.5 W
910505105668	SM531C LED31S/TW9 SIA U4 L1450 ALU	34 W
910505105675	SM530C LED40S/TW9 SIA U4 L1170 ALU	33 W
910505105676	SM531C LED25S/TW9 SIA U4 L1170 ALU	27 W
910505103266	SM531C LED62S/940 PSD P15 L2810 WH	56 W

### Mechanical and Housing

Order Code	Full Product Name	Housing Color
910505103218	SM530C LED40S/940 PSD P15 L1130 ALU	Aluminum
910505103219	SM530C LED34S/940 PSD P15 L1130 ALU	Aluminum
910505103220	SM530C LED19S/940 PSD P15 L1410 ALU	Aluminum
910505103223	SM531C LED19S/940 PSD P15 L1410 ALU	Aluminum
910505103224	SM531C LED19S/930 PSD P15 L1410 ALU	Aluminum
910505103227	SM530C LED43S/940 PSD P15 L1410 ALU	Aluminum

Order Code	Full Product Name	Housing Color
910505103228	SM530C LED34S/930 PSD P15 L1130 ALU	Aluminum
910505103229	SM530C LED31S/940 PSD P15 L1410 ALU	Aluminum
910505103233	SM530C LED50S/940 PSD P15 L1410 ALU	Aluminum
910505103275	SM530C LED40S/TW9 DIA P15 L1130 ALU	Aluminum
910505103221	SM534C LED40S/940 PSD P15 L1130 ALU	Aluminum
910505103222	SM534C LED50S/940 PSD P15 L1410 ALU	Aluminum

## TrueLine, surface mounted

Order Code	Full Product Name	Housing Color
910505103217	SM530C LED19S/940 PSD P15 L1410 WH	White
910505103225	SM530C LED43S/940 PSD P15 L1410 WH	White
910505103226	SM530C LED50S/940 PSD P15 L1410 WH	White
910505103230	SM530C LED31S/940 PSD P15 L1410 WH	White
910505103231	SM531C LED19S/930 PSD P15 L1410 WH	White
910505103232	SM531C LED19S/940 PSD P15 L1410 WH	White
910505103277	SM531C LED31S/TW9 DIA P15 L1410 WH	White
910505103242	SM531C LED12S/940 PSD LE2 P15 L570 WH	White
910505103250	SM530C LED30S/940 PSD P15 L2250 ALU	Aluminum
910505103253	SM530C LED50S/930 PSD P15 L2250 ALU	Aluminum
910505103254	SM530C LED30S/940 PSD LF1 P15 L2250 ALU	Aluminum
910505103255	SM530C LED68S/940 PSD P15 L2250 ALU	Aluminum
910505103264	SM530C LED62S/930 PSD P15 L2810 ALU	Aluminum
910505103267	SM530C LED38S/940 PSD LF1 P15 L2810 ALU	Aluminum
910505103252	SM530C LED50S/940 SRD U4 P13 L2290 BK	Black
910505103236	SM530C LED31S/940 PSD P15 L1410 BK	Black

Order Code	Full Product Name	Housing Color
910505103276	SM530C LED34S/TW9 DIA P15 L1130 BK	Black
910505103241	SM530C LED12S/940 PSD LE2 P15 L570 ALU	Aluminum
910505103251	SM531C LED30S/940 PSD P15 L2250 BK	Black
910505103265	SM530C LED62S/940 PSD P15 L2810 BK	Black
910505103268	SM530C LED86S/940 SRD U4LF1 P13 L2850ALU	Aluminum
910505103243	SM530C LED17S/940 PSD LE2 P15 L570 BK	Black
910505103237	SM530C LED40S/940 SRD U4 P13 L1170 ALU	Aluminum
910505103238	SM530C LED34S/930 SRD U4 P13 L1170 ALU	Aluminum
910505103239	SM530C LED43S/940 SRD U4 P13 L1450 ALU	Aluminum
910505103240	SM530C LED31S/940 SRD U4 P13 L1450 ALU	Aluminum
910505103278	SM530C LED43S/TW9 SIA U4 L1450 ALU	Aluminum
910505105667	SM530C LED50S/TW9 SIA U4 L1450 ALU	Aluminum
910505105668	SM531C LED31S/TW9 SIA U4 L1450 ALU	Aluminum
910505105675	SM530C LED40S/TW9 SIA U4 L1170 ALU	Aluminum
910505105676	SM531C LED25S/TW9 SIA U4 L1170 ALU	Aluminum
910505103266	SM531C LED62S/940 PSD P15 L2810 WH	White

### Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
910505103218	SM530C LED40S/940 PSD P15 L1130 ALU	(0.38, 0.38) SDCM <3
910505103219	SM530C LED34S/940 PSD P15 L1130 ALU	(0.38, 0.38) SDCM <3
910505103220	SM530C LED19S/940 PSD P15 L1410 ALU	(0.38, 0.38) SDCM <3
910505103223	SM531C LED19S/940 PSD P15 L1410 ALU	(0.38, 0.38) SDCM <3
910505103224	SM531C LED19S/930 PSD P15 L1410 ALU	(0.38, 0.38) SDCM <3
910505103227	SM530C LED43S/940 PSD P15 L1410 ALU	(0.38, 0.38) SDCM <3
910505103228	SM530C LED34S/930 PSD P15 L1130 ALU	(0.38, 0.38) SDCM <3
910505103229	SM530C LED31S/940 PSD P15 L1410 ALU	(0.38, 0.38) SDCM <3
910505103233	SM530C LED50S/940 PSD P15 L1410 ALU	(0.38, 0.38) SDCM <3
910505103275	SM530C LED40S/TW9 DIA P15 L1130 ALU	(0.38, 0.38) SDCM <3
910505103221	SM534C LED40S/940 PSD P15 L1130 ALU	(0.38, 0.38) SDCM <3
910505103222	SM534C LED50S/940 PSD P15 L1410 ALU	(0.38, 0.38) SDCM <3
910505103217	SM530C LED19S/940 PSD P15 L1410 WH	(0.38, 0.38) SDCM <3
910505103225	SM530C LED43S/940 PSD P15 L1410 WH	(0.38, 0.38) SDCM <3
910505103226	SM530C LED50S/940 PSD P15 L1410 WH	(0.38, 0.38) SDCM <3
910505103230	SM530C LED31S/940 PSD P15 L1410 WH	(0.38, 0.38) SDCM <3
910505103231	SM531C LED19S/930 PSD P15 L1410 WH	(0.38, 0.38) SDCM <3
910505103232	SM531C LED19S/940 PSD P15 L1410 WH	(0.38, 0.38) SDCM <3
910505103277	SM531C LED31S/TW9 DIA P15 L1410 WH	(0.38, 0.38) SDCM <3
910505103242	SM531C LED12S/940 PSD LE2 P15 L570 WH	(0.38, 0.38) SDCM <3
910505103250	SM530C LED30S/940 PSD P15 L2250 ALU	(0.38, 0.38) SDCM <3
910505103253	SM530C LED50S/930 PSD P15 L2250 ALU	(0.38, 0.38) SDCM <3

Order Code	Full Product Name	Initial chromaticity
910505103254	SM530C LED30S/940 PSD LF1 P15 L2250 ALU	(0.38, 0.38) SDCM <3
910505103255	SM530C LED68S/940 PSD P15 L2250 ALU	(0.38, 0.38) SDCM <3
910505103264	SM530C LED62S/930 PSD P15 L2810 ALU	(0.38, 0.38) SDCM <3
910505103267	SM530C LED38S/940 PSD LF1 P15 L2810 ALU	(0.38, 0.38) SDCM <3
910505103252	SM530C LED50S/940 SRD U4 P13 L2290 BK	(0.38, 0.38) SDCM <3
910505103236	SM530C LED31S/940 PSD P15 L1410 BK	(0.38, 0.38) SDCM <3
910505103276	SM530C LED34S/TW9 DIA P15 L1130 BK	(0.38, 0.38) SDCM <3
910505103241	SM530C LED12S/940 PSD LE2 P15 L570 ALU	(0.38, 0.38) SDCM <3
910505103251	SM531C LED30S/940 PSD P15 L2250 BK	(0.38, 0.38) SDCM <3
910505103265	SM530C LED62S/940 PSD P15 L2810 BK	(0.38, 0.38) SDCM <3
910505103268	SM530C LED86S/940 SRD U4LF1 P13 L2850ALU	(0.38, 0.38) SDCM <3
910505103243	SM530C LED17S/940 PSD LE2 P15 L570 BK	(0.38, 0.38) SDCM <3
910505103237	SM530C LED40S/940 SRD U4 P13 L1170 ALU	(0.38, 0.38) SDCM <3
910505103238	SM530C LED34S/930 SRD U4 P13 L1170 ALU	(0.38, 0.38) SDCM <3
910505103239	SM530C LED43S/940 SRD U4 P13 L1450 ALU	(0.38, 0.38) SDCM <3
910505103240	SM530C LED31S/940 SRD U4 P13 L1450 ALU	(0.38, 0.38) SDCM <3
910505103278	SM530C LED43S/TW9 SIA U4 L1450 ALU	(0.38, 0.38) SDCM <3
910505105667	SM530C LED50S/TW9 SIA U4 L1450 ALU	Tunable, SDCM ≤3
910505105668	SM531C LED31S/TW9 SIA U4 L1450 ALU	Tunable, SDCM ≤3
910505105675	SM530C LED40S/TW9 SIA U4 L1170 ALU	Tunable, SDCM ≤3
910505105676	SM531C LED25S/TW9 SIA U4 L1170 ALU	Tunable, SDCM ≤3
910505103266	SM531C LED62S/940 PSD P15 L2810 WH	(0.38, 0.38) SDCM <3

### Application Conditions

Order Code	Full Product Name	Suitable for random switching
910505103218	SM530C LED40S/940 PSD P15 L1130 ALU	No
910505103219	SM530C LED34S/940 PSD P15 L1130 ALU	No
910505103220	SM530C LED19S/940 PSD P15 L1410 ALU	No
910505103223	SM531C LED19S/940 PSD P15 L1410 ALU	No


Order Code	Full Product Name	Suitable for random switching
910505103224	SM531C LED19S/930 PSD P15 L1410 ALU	No
910505103227	SM530C LED43S/940 PSD P15 L1410 ALU	No
910505103228	SM530C LED34S/930 PSD P15 L1130 ALU	No
910505103229	SM530C LED31S/940 PSD P15 L1410 ALU	No

## TrueLine, surface mounted


Order Code	Full Product Name	Suitable for random switching
910505103233	SM530C LED50S/940 PSD PI5 L1410 ALU	No
910505103275	SM530C LED40S/TW9 DIA PI5 L1130 ALU	No
910505103221	SM534C LED40S/940 PSD PI5 L1130 ALU	No
910505103222	SM534C LED50S/940 PSD PI5 L1410 ALU	No
910505103217	SM530C LED19S/940 PSD PI5 L1410 WH	No
910505103225	SM530C LED43S/940 PSD PI5 L1410 WH	No
910505103226	SM530C LED50S/940 PSD PI5 L1410 WH	No
910505103230	SM530C LED31S/940 PSD PI5 L1410 WH	No
910505103231	SM531C LED19S/930 PSD PI5 L1410 WH	No
910505103232	SM531C LED19S/940 PSD PI5 L1410 WH	No
910505103277	SM531C LED31S/TW9 DIA PI5 L1410 WH	No
910505103242	SM531C LED12S/940 PSD LE2 PI5 L570 WH	No
910505103250	SM530C LED30S/940 PSD PI5 L2250 ALU	No
910505103253	SM530C LED50S/930 PSD PI5 L2250 ALU	No
910505103254	SM530C LED30S/940 PSD LF1 PI5 L2250 ALU	No
910505103255	SM530C LED68S/940 PSD PI5 L2250 ALU	No
910505103264	SM530C LED62S/930 PSD PI5 L2810 ALU	No
910505103267	SM530C LED38S/940 PSD LF1 PI5 L2810 ALU	No
910505103252	SM530C LED50S/940 SRD U4 PI3 L2290 BK	No
910505103236	SM530C LED31S/940 PSD PI5 L1410 BK	No
910505103276	SM530C LED34S/TW9 DIA PI5 L1130 BK	No
910505103241	SM530C LED12S/940 PSD LE2 PI5 L570 ALU	No
910505103251	SM531C LED30S/940 PSD PI5 L2250 BK	No
910505103265	SM530C LED62S/940 PSD PI5 L2810 BK	No

Order Code	Full Product Name	Suitable for random switching
910505103268	SM530C LED86S/940 SRD U4LF1 PI3 L2850ALU	No
910505103243	SM530C LED17S/940 PSD LE2 PI5 L570 BK	No
910505103237	SM530C LED40S/940 SRD U4 PI3 L1170 ALU	No
910505103238	SM530C LED34S/930 SRD U4 PI3 L1170 ALU	No
910505103239	SM530C LED43S/940 SRD U4 PI3 L1450 ALU	No
910505103240	SM530C LED31S/940 SRD U4 PI3 L1450 ALU	No
910505103278	SM530C LED43S/TW9 SIA U4 L1450 ALU	No
910505105667	SM530C LED50S/TW9 SIA U4 L1450 ALU	Yes (relates to presence/ movement detection and daylight harvesting)
910505105668	SM531C LED31S/TW9 SIA U4 L1450 ALU	Yes (relates to presence/ movement detection and daylight harvesting)
910505105675	SM530C LED40S/TW9 SIA U4 L1170 ALU	Yes (relates to presence/ movement detection and daylight harvesting)
910505105676	SM531C LED25S/TW9 SIA U4 L1170 ALU	Yes (relates to presence/ movement detection and daylight harvesting)
910505103266	SM531C LED62S/940 PSD PI5 L2810 WH	No


## Polar Wide Diagrams



Polar Normal (separate) - SM530CI - 910505103239




Polar Normal (separate) - SM530CI - 910505103223




Polar Normal (separate) - SM530CI - 910505103224


Polar Wide Diagrams




Polar Normal (separate) - SM530CI - 910505103237




Polar Normal (separate) - SM530CI - 910505103228




Polar Normal (separate) - SM530CI - 910505103278




Polar Normal (separate) - SM530CI - 910505103251




Polar Normal (separate) - SM530CI - 910505103229




Polar Normal (separate) - SM530CI - 910505103267



Polar Normal (separate) - SM530CI - 910505103264




Polar Normal (separate) - SM530CI - 910505103255




Polar Normal (separate) - SM530CI - 910505103226


Polar Wide Diagrams




Polar Normal (separate) - SM530CI - 910505103217




Polar Normal (separate) - SM530CI - 910505103230




Polar Normal (separate) - SM530CI - 910505103232




Polar Normal (separate) - SM530CI - 910505103222




Polar Normal (separate) - SM530CI - 910505103238




Polar Normal (separate) - SM530CI - 910505103221



Polar Normal (separate) - SM530CI - 910505103250






Polar Normal (separate) - SM530CI - 910505103227



Polar Normal (separate) - SM530CI - 910505103218




Polar Wide Diagrams



Polar Normal (separate) - SM530CI - 910505103225

Polar Normal (separate) - SM530CI - 910505103275




Polar Normal (separate) - SM530CI - 910505103254



Polar Normal (separate) - SM530CI - 910505103243

Polar Normal (separate) - SM530CI - 910505103252

Polar Normal (separate) - SM530CI - 910505103277




Polar Normal (separate) - SM530CI - 910505103276


Polar Normal (separate) - SM530CI - 910505103240

Polar Normal (separate) - SM530CI - 910505103266


Polar Wide Diagrams




Polar Normal (separate) - SM530CI - 910505103268




Polar Normal (separate) - SM530CI - 910505103242




Polar Normal (separate) - SM530CI - 910505103231




Polar Normal (separate) - SM530CI - 910505103253




Polar Normal (separate) - SM530CI - 910505103233




Polar Normal (separate) - SM530CI - 910505103265



Polar Normal (separate) - SM530CI - 910505103219



Polar Normal (separate) - SM530CI - 910505103241




Polar Normal (separate) - SM530CI - 910505103220




# TrueLine, surface mounted


## Polar Wide Diagrams




Polar Normal (separate) - SM530CI -  
910505103236




Polar Normal (separate) - SM530CI -  
910505105667



Polar Normal (separate) - SM530CI -  
910505105668



Polar Normal (separate) - SM530CI -  
910505105676



Polar Normal (separate) - SM530CI -  
910505105675

