





Philips Zadora LED RS049B



	LEDs	V	P(W)	 Ø mm	 kg
RS049 adjustable	MASTER LEDspot	220-240V	5.0-50	75	0.55
RS049 adjustable	CorePro LEDspot	220-240V	5.0-50	75	0.55
RS049 adjustable	CLASSIC LEDspot	220-240V	4.6-50	75	0.55

The luminaire shall be installed by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements.



Dimensions in mm

For complete and updated list of advised dimmers, please check the Zadora LED page on the Philips Lighting eCatalog: <http://www.ecat.lighting.philips.com>

