



A flexible and affordable fixed downlight for retail stores

GreenSpace Accent Fixed

Thanks to the GreenSpace Accent family, retailers and building operators can now make the switch from CDM to LED lighting and enjoy significant energy savings for a reasonable initial investment. This GreenSpace Accent downlight has regular cut-out and specific lumen packages to make retrofit installation quick and easy.

Furthermore, the fixed downlights offer multiple system integration and dimming options, including wired as well as wireless. For fashion and food retailers, every GreenSpace Accent downlight is available with special LED flavors and fresh food LED lighting recipes to show the merchandise in the very best light. Check out our Fashion and Food catalog pages to find out more about PremiumWhite, PremiumColor, Fresh Meat, Rosé, Frost and Champagne.

Benefits

- Blends into ceilings with a clean and simple design
- Easy to design in thanks to CDM retrofit dimensions
- Reduce your carbon footprint with energy-saving LED lighting

Features

- Retrofit dimensions with CDM luminaires
- Retail LED flavors and fresh food LED lighting recipes included
- RS340B available for normal mains (PSU), simple DALI dimming (PSD), Interact compatible DALI (DIA), Indoor positioning (DIA-VLC) or wireless Interact (WIA)

GreenSpace Accent Fixed


Application

- Supermarkets
- Hypermarkets
- Large format retail
- Fashion stores

Warnings and Safety

- During maintenance, the product must be switched off and cooled down
- The product must be installed out of arm's reach. Manipulating the product when hot is only possible with an insulated glove

Dimensional drawing



Product details



GreenSpace_Accent_Fixed-
RS340B-DP01.tif



GreenSpace_Accent_Fixed-
RS340B-DP02.tif

GreenSpace Accent Fixed

Product details

GreenSpace_Accent_Fixed-
RS340B-DP03.tif



General Information	
CE mark	Yes
Driver included	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Light source replaceable	No
Number of gear units	1 unit
Product family code	RS340B
Light Technical	
Beam angle of light source	120 degree(s)
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Mechanical and Housing	
Housing Color	White
Approval and Application	
Protection class IEC	Safety class II
Mech. impact protection code	IK02
Ingress protection code	IP20
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Application Conditions	
Suitable for random switching	Yes

Light Technical (1/2)

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505101448	RS340B 19S/FMT PSU-E WB CP WH	3000 K	>90	86 lm/W	1,900 lm
910505101449	RS340B 27S/830 DIA-VLC-E VWB CP WH	3000 K	≥80	115 lm/W	2,700 lm
910505101450	RS340B 27S/830 PSU-E VWB CP WH	3000 K	≥80	115 lm/W	2,700 lm
910505101451	RS340B 27S/830 PSU-E WB CP WH	3000 K	≥80	115 lm/W	2,700 lm
910505101452	RS340B 27S/840 PSU-E WB CP WH	4000 K	≥80	120 lm/W	2,700 lm
910505101453	RS340B 27S/CH PSU-E WB CP WH	2700 K	≥80	115 lm/W	2,700 lm
910505101454	RS340B 27S/FMT PSU-E MB CP WH	3000 K	>90	77 lm/W	2,700 lm
910505101455	RS340B 27S/PW930 PSU-E WB CP WH	3000 K	≥90	121 lm/W	2,850 lm
910505101456	RS340B 39S/827 PSU-E WB CP WH	2700 K	≥80	119 lm/W	3,900 lm
910505101457	RS340B 39S/830 DIA-VLC-E VWB CP WH	3000 K	≥80	123 lm/W	3,900 lm
910505101458	RS340B 39S/830 PSU-E WB CP WH	3000 K	≥80	123 lm/W	3,900 lm
910505101459	RS340B 39S/840 DIA-VLC-E WB CP WH	4000 K	≥80	142 lm/W	4,000 lm
910505101460	RS340B 39S/840 PSU-E WB CP WH	4000 K	≥80	142 lm/W	4,000 lm
910505101461	RS340B 39S/840 PSU-E VWB CP WH	4000 K	≥80	142 lm/W	4,000 lm
910505101462	RS340B 39S/PW930 PSU-E WB CP WH	3000 K	≥90	124 lm/W	3,850 lm
910505102308	RS340B 27S/PW930 WIA-E WB CP WH	3000 K	≥90	103 lm/W	2,700 lm

Light Technical (2/2)

GreenSpace Accent Fixed

Order Code	Full Product Name	Optic type
910505101448	RS340B 19S/FMT PSU-E WB CP WH	Wide beam
910505101449	RS340B 27S/830 DIA-VLC-E VWB CP WH	Very wide beam
910505101450	RS340B 27S/830 PSU-E VWB CP WH	Very wide beam
910505101451	RS340B 27S/830 PSU-E WB CP WH	Wide beam
910505101452	RS340B 27S/840 PSU-E WB CP WH	Wide beam
910505101453	RS340B 27S/CH PSU-E WB CP WH	Wide beam
910505101454	RS340B 27S/FMT PSU-E MB CP WH	Medium beam
910505101455	RS340B 27S/PW930 PSU-E WB CP WH	Wide beam

Order Code	Full Product Name	Optic type
910505101456	RS340B 39S/827 PSU-E WB CP WH	Wide beam
910505101457	RS340B 39S/830 DIA-VLC-E VWB CP WH	Very wide beam
910505101458	RS340B 39S/830 PSU-E WB CP WH	Wide beam
910505101459	RS340B 39S/840 DIA-VLC-E WB CP WH	Wide beam
910505101460	RS340B 39S/840 PSU-E WB CP WH	Wide beam
910505101461	RS340B 39S/840 PSU-E VWB CP WH	Very wide beam
910505101462	RS340B 39S/PW930 PSU-E WB CP WH	Wide beam
910505102308	RS340B 27S/PW930 WIA-E WB CP WH	Wide beam

Operating and Electrical

Order Code	Full Product Name	Power Consumption
910505101448	RS340B 19S/FMT PSU-E WB CP WH	22 W
910505101449	RS340B 27S/830 DIA-VLC-E VWB CP WH	23.5 W
910505101450	RS340B 27S/830 PSU-E VWB CP WH	23.5 W
910505101451	RS340B 27S/830 PSU-E WB CP WH	23.5 W
910505101452	RS340B 27S/840 PSU-E WB CP WH	23.5 W
910505101453	RS340B 27S/CH PSU-E WB CP WH	23.5 W
910505101454	RS340B 27S/FMT PSU-E MB CP WH	35 W
910505101455	RS340B 27S/PW930 PSU-E WB CP WH	26 W

Order Code	Full Product Name	Power Consumption
910505101456	RS340B 39S/827 PSU-E WB CP WH	31.5 W
910505101457	RS340B 39S/830 DIA-VLC-E VWB CP WH	31.5 W
910505101458	RS340B 39S/830 PSU-E WB CP WH	31.5 W
910505101459	RS340B 39S/840 DIA-VLC-E WB CP WH	28 W
910505101460	RS340B 39S/840 PSU-E WB CP WH	28 W
910505101461	RS340B 39S/840 PSU-E VWB CP WH	28 W
910505101462	RS340B 39S/PW930 PSU-E WB CP WH	36 W
910505102308	RS340B 27S/PW930 WIA-E WB CP WH	26 W

Temperature

Order Code	Full Product Name	Ambient temperature range
910505101448	RS340B 19S/FMT PSU-E WB CP WH	+10 to +25 °C
910505101449	RS340B 27S/830 DIA-VLC-E VWB CP WH	+10 to +25 °C
910505101450	RS340B 27S/830 PSU-E VWB CP WH	+10 to +25 °C
910505101451	RS340B 27S/830 PSU-E WB CP WH	+10 to +25 °C
910505101452	RS340B 27S/840 PSU-E WB CP WH	+10 to +25 °C
910505101453	RS340B 27S/CH PSU-E WB CP WH	+10 to +25 °C
910505101454	RS340B 27S/FMT PSU-E MB CP WH	+10 to +25 °C
910505101455	RS340B 27S/PW930 PSU-E WB CP WH	+10 to +35 °C

Order Code	Full Product Name	Ambient temperature range
910505101456	RS340B 39S/827 PSU-E WB CP WH	+10 to +25 °C
910505101457	RS340B 39S/830 DIA-VLC-E VWB CP WH	+10 to +25 °C
910505101458	RS340B 39S/830 PSU-E WB CP WH	+10 to +25 °C
910505101459	RS340B 39S/840 DIA-VLC-E WB CP WH	+10 to +25 °C
910505101460	RS340B 39S/840 PSU-E WB CP WH	+10 to +25 °C
910505101461	RS340B 39S/840 PSU-E VWB CP WH	+10 to +25 °C
910505101462	RS340B 39S/PW930 PSU-E WB CP WH	+10 to +35 °C
910505102308	RS340B 27S/PW930 WIA-E WB CP WH	+10 to +35 °C

Controls and Dimming

Order Code	Full Product Name	Dimmable
910505101448	RS340B 19S/FMT PSU-E WB CP WH	No
910505101449	RS340B 27S/830 DIA-VLC-E VWB CP WH	Yes
910505101450	RS340B 27S/830 PSU-E VWB CP WH	No
910505101451	RS340B 27S/830 PSU-E WB CP WH	No
910505101452	RS340B 27S/840 PSU-E WB CP WH	No
910505101453	RS340B 27S/CH PSU-E WB CP WH	No
910505101454	RS340B 27S/FMT PSU-E MB CP WH	No
910505101455	RS340B 27S/PW930 PSU-E WB CP WH	No

Order Code	Full Product Name	Dimmable
910505101456	RS340B 39S/827 PSU-E WB CP WH	No
910505101457	RS340B 39S/830 DIA-VLC-E VWB CP WH	Yes
910505101458	RS340B 39S/830 PSU-E WB CP WH	No
910505101459	RS340B 39S/840 DIA-VLC-E WB CP WH	Yes
910505101460	RS340B 39S/840 PSU-E WB CP WH	No
910505101461	RS340B 39S/840 PSU-E VWB CP WH	No
910505101462	RS340B 39S/PW930 PSU-E WB CP WH	No
910505102308	RS340B 27S/PW930 WIA-E WB CP WH	Yes

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
910505101448	RS340B 19S/FMT PSU-E WB CP WH	(0.406, 0.350) SDCM<3
910505101449	RS340B 27S/830 DIA-VLC-E VWB CP WH	(0.434, 0.403) SDCM <3
910505101450	RS340B 27S/830 PSU-E VWB CP WH	(0.434, 0.403) SDCM <3

Order Code	Full Product Name	Initial chromaticity
910505101451	RS340B 27S/830 PSU-E WB CP WH	(0.434, 0.403) SDCM <3
910505101452	RS340B 27S/840 PSU-E WB CP WH	(0.382, 0.380) SDCM <3
910505101453	RS340B 27S/CH PSU-E WB CP WH	(0.458, 0.410) SDCM <3

GreenSpace Accent Fixed

Order Code	Full Product Name	Initial chromaticity
910505101454	RS340B 27S/FMT PSU-E MB CP WH	(0.406, 0.350) SDCM<3
910505101455	RS340B 27S/PW930 PSU-E WB CP WH	(0.422, 0.386) SDCM <2
910505101456	RS340B 39S/827 PSU-E WB CP WH	(0.458, 0.410) SDCM <3
910505101457	RS340B 39S/830 DIA-VLC-E VWB CP WH	(0.434, 0.403) SDCM <3
910505101458	RS340B 39S/830 PSU-E WB CP WH	(0.434, 0.403) SDCM <3

Order Code	Full Product Name	Initial chromaticity
910505101459	RS340B 39S/840 DIA-VLC-E WB CP WH	(0.382, 0.380) SDCM <3
910505101460	RS340B 39S/840 PSU-E WB CP WH	(0.382, 0.380) SDCM <3
910505101461	RS340B 39S/840 PSU-E VWB CP WH	(0.382, 0.380) SDCM <3
910505101462	RS340B 39S/PW930 PSU-E WB CP WH	(0.422, 0.386) SDCM <2
910505102308	RS340B 27S/PW930 WIA-E WB CP WH	(0.422, 0.386) SDCM <2

Application Conditions

Order Code	Full Product Name	Maximum dim level
910505101448	RS340B 19S/FMT PSU-E WB CP WH	Not applicable
910505101449	RS340B 27S/830 DIA-VLC-E VWB CP WH	1%
910505101450	RS340B 27S/830 PSU-E VWB CP WH	Not applicable
910505101451	RS340B 27S/830 PSU-E WB CP WH	Not applicable
910505101452	RS340B 27S/840 PSU-E WB CP WH	Not applicable
910505101453	RS340B 27S/CH PSU-E WB CP WH	Not applicable
910505101454	RS340B 27S/FMT PSU-E MB CP WH	Not applicable
910505101455	RS340B 27S/PW930 PSU-E WB CP WH	Not applicable

Order Code	Full Product Name	Maximum dim level
910505101456	RS340B 39S/827 PSU-E WB CP WH	Not applicable
910505101457	RS340B 39S/830 DIA-VLC-E VWB CP WH	1%
910505101458	RS340B 39S/830 PSU-E WB CP WH	Not applicable
910505101459	RS340B 39S/840 DIA-VLC-E WB CP WH	1%
910505101460	RS340B 39S/840 PSU-E WB CP WH	Not applicable
910505101461	RS340B 39S/840 PSU-E VWB CP WH	Not applicable
910505101462	RS340B 39S/PW930 PSU-E WB CP WH	Not applicable
910505102308	RS340B 27S/PW930 WIA-E WB CP WH	Not applicable

