



When light really matters

GreenPerform Direct LED Panel

GreenPerform RC099V G2 direct Panel is an affordable LED panel delivering comfortable light with excellent uniformity. It offers 3 types, 600x600, 300x1200, and 600x1200mm with max: 110lm/w system efficacy. Its UGR19 version brings more visual comfort to the office. By means of its compact design, the housing height (without driver) reaches only 35mm which gives more flexibility for recessed installation.

Benefits

- Full range offer from 600x600, 300x1200 to 600x1200mm to cover key applications
- Low glare UGR19 to provide more comfortable lighting environment
- 35mm product housing height (without driver) for critical ceiling installation

Features


- System efficiency 110lm/W (UGR22)
- CRI 80 with 4000K, 5000K and 6500K CCT available
- Lifetime: 50K hours (L70@Ta25deg)

Application


- Open plan office
- Meeting/Training room

GreenPerform Direct LED Panel

Versions



GreenPerform Direct LED Panel




GreenPerform Direct LED Panel



GreenPerform Direct LED Panel

Product details



GreenPerform Direct LED panel

Application conditions	
Ambient temperature range	-20 to +40 °C
Approval and application	
Ingress protection code	IP20
General information	
CE mark	CE mark
Protection class IEC	Safety class II
Initial performance (IEC compliant)	
Init. Color Rendering Index	>80
Luminous flux tolerance	+/-10%
Mechanical and housing	
Color	White RAL 9003

Approval and application

Order Code	Full Product Name	Mech. impact protection code
911401504581	RC099V G2 LED29/840 PSD W60L60 OC CAU	IK02
911401504681	RC099V G2 LED29/850 PSD W60L60 OC CAU	IK02

Order Code	Full Product Name	Mech. impact protection code
911401504781	RC099V G2 LED29/865 PSD W60L60 OC CAU	IK02
911401505181	RC099V G2 LED32/840 PSD W60L60 OC CAU	IK02

GreenPerform Direct LED Panel

Order Code	Full Product Name	Mech. impact protection code
911401505281	RC099V G2 LED32/850 PSD W60L60 OC CAU	IK02
911401505381	RC099V G2 LED32/865 PSD W60L60 OC CAU	IK02
911401505781	RC099V G2 LED34/840 PSU W60L60 OC CAU	IK02
911401505881	RC099V G2 LED34/850 PSU W60L60 OC CAU	IK02
911401505981	RC099V G2 LED34/865 PSU W60L60 OC CAU	IK02
911401506681	RC099V G2 LED34/840 PSU W60L60 OC NZ	IK02
911401506781	RC099V G2 LED34/850 PSU W60L60 OC NZ	IK02
911401506881	RC099V G2 LED34/865 PSU W60L60 OC NZ	IK02
911401700643	RC099V G2 LED38/840 PSU W60L60 NZ	IK02
911401700653	RC099V G2 LED38/850 PSU W60L60 NZ	IK02
911401700663	RC099V G2 LED38/865 PSU W60L60 NZ	IK02
911401700733	RC099V G2 LED38/840 PSU W60L60	-
911401700743	RC099V G2 LED38/850 PSU W60L60	-
911401700753	RC099V G2 LED38/865 PSU W60L60	-
911401700823	RC099V G2 LED36/840 PSU W60L60 OC	-
911401700833	RC099V G2 LED36/850 PSU W60L60 OC	-
911401700843	RC099V G2 LED36/865 PSU W60L60 OC	-
911401504881	RC099V G2 LED29/840 PSD W30L120 OC CAU	IK02
911401504981	RC099V G2 LED29/850 PSD W30L120 OC CAU	IK02
911401505081	RC099V G2 LED29/865 PSD W30L120 OC CAU	IK02
911401505481	RC099V G2 LED32/840 PSD W30L120 OC CAU	IK02
911401505581	RC099V G2 LED32/850 PSD W30L120 OC CAU	IK02
911401505681	RC099V G2 LED32/865 PSD W30L120 OC CAU	IK02
911401506081	RC099V G2 LED34/840 PSU W30L120 OC CAU	IK02
911401506181	RC099V G2 LED34/850 PSU W30L120 OC CAU	IK02
911401506281	RC099V G2 LED34/865 PSU W30L120 OC CAU	IK02
911401506981	RC099V G2 LED34/840 PSU W30L120 OC NZ	IK02
911401507081	RC099V G2 LED34/850 PSU W30L120 OC NZ	IK02

Order Code	Full Product Name	Mech. impact protection code
911401507181	RC099V G2 LED34/865 PSU W30L120 OC NZ	IK02
911401700673	RC099V G2 LED38/840 PSU W30L120 NZ	IK02
911401700683	RC099V G2 LED38/850 PSU W30L120 NZ	IK02
911401700693	RC099V G2 LED38/865 PSU W30L120 NZ	IK02
911401700763	RC099V G2 LED38/840 PSU W30L120	-
911401700773	RC099V G2 LED38/850 PSU W30L120	-
911401700783	RC099V G2 LED38/865 PSU W30L120	-
911401700853	RC099V G2 LED36/840 PSU W30L120 OC	-
911401700863	RC099V G2 LED36/850 PSU W30L120 OC	-
911401700873	RC099V G2 LED36/865 PSU W30L120 OC	-
911401506381	RC099V G2 LED50/840 PSU W60L120 OC CAU	IK02
911401506481	RC099V G2 LED50/850 PSU W60L120 OC CAU	IK02
911401506581	RC099V G2 LED50/865 PSU W60L120 OC CAU	IK02
911401507281	RC099V G2 LED50/840 PSU W60L120 OC NZ	IK02
911401507381	RC099V G2 LED50/850 PSU W60L120 OC NZ	IK02
911401507481	RC099V G2 LED50/865 PSU W60L120 OC NZ	IK02
911401587171	RC099V G2 LED50/840 PSD W60L120 OC CAU	IK02
911401587271	RC099V G2 LED50/850 PSD W60L120 OC CAU	IK02
911401587371	RC099V G2 LED50/865 PSD W60L120 OC CAU	IK02
911401700703	RC099V G2 LED54/840 PSU W60L120 NZ	IK02
911401700713	RC099V G2 LED54/850 PSU W60L120 NZ	IK02
911401700723	RC099V G2 LED54/865 PSU W60L120 NZ	IK02
911401700793	RC099V G2 LED54/840 PSU W60L120	-
911401700803	RC099V G2 LED54/850 PSU W60L120	-
911401700813	RC099V G2 LED54/865 PSU W60L120	-
911401700883	RC099V G2 LED50/840 PSU W60L120 OC	-
911401700893	RC099V G2 LED50/850 PSU W60L120 OC	-
911401700903	RC099V G2 LED50/865 PSU W60L120 OC	-

Controls and dimming

Order Code	Full Product Name	Dimmable
911401504581	RC099V G2 LED29/840 PSD W60L60 OC CAU	Yes
911401504681	RC099V G2 LED29/850 PSD W60L60 OC CAU	Yes
911401504781	RC099V G2 LED29/865 PSD W60L60 OC CAU	Yes
911401505181	RC099V G2 LED32/840 PSD W60L60 OC CAU	Yes
911401505281	RC099V G2 LED32/850 PSD W60L60 OC CAU	Yes
911401505381	RC099V G2 LED32/865 PSD W60L60 OC CAU	Yes
911401505781	RC099V G2 LED34/840 PSU W60L60 OC CAU	No
911401505881	RC099V G2 LED34/850 PSU W60L60 OC CAU	No
911401505981	RC099V G2 LED34/865 PSU W60L60 OC CAU	No
911401506681	RC099V G2 LED34/840 PSU W60L60 OC NZ	No
911401506781	RC099V G2 LED34/850 PSU W60L60 OC NZ	No
911401506881	RC099V G2 LED34/865 PSU W60L60 OC NZ	No
911401700643	RC099V G2 LED38/840 PSU W60L60 NZ	No
911401700653	RC099V G2 LED38/850 PSU W60L60 NZ	No
911401700663	RC099V G2 LED38/865 PSU W60L60 NZ	No
911401700733	RC099V G2 LED38/840 PSU W60L60	No
911401700743	RC099V G2 LED38/850 PSU W60L60	No
911401700753	RC099V G2 LED38/865 PSU W60L60	No
911401700823	RC099V G2 LED36/840 PSU W60L60 OC	No

Order Code	Full Product Name	Dimmable
911401700833	RC099V G2 LED36/850 PSU W60L60 OC	No
911401700843	RC099V G2 LED36/865 PSU W60L60 OC	No
911401504881	RC099V G2 LED29/840 PSD W30L120 OC CAU	Yes
911401504981	RC099V G2 LED29/850 PSD W30L120 OC CAU	Yes
911401505081	RC099V G2 LED29/865 PSD W30L120 OC CAU	Yes
911401505481	RC099V G2 LED32/840 PSD W30L120 OC CAU	Yes
911401505581	RC099V G2 LED32/850 PSD W30L120 OC CAU	Yes
911401505681	RC099V G2 LED32/865 PSD W30L120 OC CAU	Yes
911401506081	RC099V G2 LED34/840 PSU W30L120 OC CAU	No
911401506181	RC099V G2 LED34/850 PSU W30L120 OC CAU	No
911401506281	RC099V G2 LED34/865 PSU W30L120 OC CAU	No
911401506981	RC099V G2 LED34/840 PSU W30L120 OC NZ	No
911401507081	RC099V G2 LED34/850 PSU W30L120 OC NZ	No
911401507181	RC099V G2 LED34/865 PSU W30L120 OC NZ	No
911401700673	RC099V G2 LED38/840 PSU W30L120 NZ	No
911401700683	RC099V G2 LED38/850 PSU W30L120 NZ	No
911401700693	RC099V G2 LED38/865 PSU W30L120 NZ	No
911401700763	RC099V G2 LED38/840 PSU W30L120	No
911401700773	RC099V G2 LED38/850 PSU W30L120	No

GreenPerform Direct LED Panel

Order Code	Full Product Name	Dimmable
911401700783	RC099V G2 LED38/865 PSU W30L120	No
911401700853	RC099V G2 LED36/840 PSU W30L120 OC	No
911401700863	RC099V G2 LED36/850 PSU W30L120 OC	No
911401700873	RC099V G2 LED36/865 PSU W30L120 OC	No
911401506381	RC099V G2 LED50/840 PSU W60L120 OC CAU	No
911401506481	RC099V G2 LED50/850 PSU W60L120 OC CAU	No
911401506581	RC099V G2 LED50/865 PSU W60L120 OC CAU	No
911401507281	RC099V G2 LED50/840 PSU W60L120 OC NZ	No
911401507381	RC099V G2 LED50/850 PSU W60L120 OC NZ	No
911401507481	RC099V G2 LED50/865 PSU W60L120 OC NZ	No
911401587171	RC099V G2 LED50/840 PSD W60L120 OC CAU	Yes

Order Code	Full Product Name	Dimmable
911401587271	RC099V G2 LED50/850 PSD W60L120 OC CAU	Yes
911401587371	RC099V G2 LED50/865 PSD W60L120 OC CAU	Yes
911401700703	RC099V G2 LED54/840 PSU W60L120 NZ	No
911401700713	RC099V G2 LED54/850 PSU W60L120 NZ	No
911401700723	RC099V G2 LED54/865 PSU W60L120 NZ	No
911401700793	RC099V G2 LED54/840 PSU W60L120	No
911401700803	RC099V G2 LED54/850 PSU W60L120	No
911401700813	RC099V G2 LED54/865 PSU W60L120	No
911401700883	RC099V G2 LED50/840 PSU W60L120 OC	No
911401700893	RC099V G2 LED50/850 PSU W60L120 OC	No
911401700903	RC099V G2 LED50/865 PSU W60L120 OC	No

Operating and electrical

Order Code	Full Product Name	Input Voltage
911401504581	RC099V G2 LED29/840 PSD W60L60 OC CAU	220-240 V
911401504681	RC099V G2 LED29/850 PSD W60L60 OC CAU	220-240 V
911401504781	RC099V G2 LED29/865 PSD W60L60 OC CAU	220-240 V
911401505181	RC099V G2 LED32/840 PSD W60L60 OC CAU	220-240 V
911401505281	RC099V G2 LED32/850 PSD W60L60 OC CAU	220-240 V
911401505381	RC099V G2 LED32/865 PSD W60L60 OC CAU	220-240 V
911401505781	RC099V G2 LED34/840 PSU W60L60 OC CAU	220-240 V
911401505881	RC099V G2 LED34/850 PSU W60L60 OC CAU	220-240 V
911401505981	RC099V G2 LED34/865 PSU W60L60 OC CAU	220-240 V
911401506681	RC099V G2 LED34/840 PSU W60L60 OC NZ	220-240 V
911401506781	RC099V G2 LED34/850 PSU W60L60 OC NZ	220-240 V
911401506881	RC099V G2 LED34/865 PSU W60L60 OC NZ	220-240 V
911401700643	RC099V G2 LED38/840 PSU W60L60 NZ	220-240 V
911401700653	RC099V G2 LED38/850 PSU W60L60 NZ	220-240 V
911401700663	RC099V G2 LED38/865 PSU W60L60 NZ	220-240 V
911401700733	RC099V G2 LED38/840 PSU W60L60	220 to 240 V
911401700743	RC099V G2 LED38/850 PSU W60L60	220 to 240 V
911401700753	RC099V G2 LED38/865 PSU W60L60	220 to 240 V
911401700823	RC099V G2 LED36/840 PSU W60L60 OC	220 to 240 V
911401700833	RC099V G2 LED36/850 PSU W60L60 OC	220 to 240 V
911401700843	RC099V G2 LED36/865 PSU W60L60 OC	220 to 240 V
911401504881	RC099V G2 LED29/840 PSD W30L120 OC CAU	220-240 V
911401504981	RC099V G2 LED29/850 PSD W30L120 OC CAU	220-240 V
911401505081	RC099V G2 LED29/865 PSD W30L120 OC CAU	220-240 V
911401505481	RC099V G2 LED32/840 PSD W30L120 OC CAU	220-240 V
911401505581	RC099V G2 LED32/850 PSD W30L120 OC CAU	220-240 V
911401505681	RC099V G2 LED32/865 PSD W30L120 OC CAU	220-240 V
911401506081	RC099V G2 LED34/840 PSU W30L120 OC CAU	220-240 V
911401506181	RC099V G2 LED34/850 PSU W30L120 OC CAU	220-240 V
911401506281	RC099V G2 LED34/865 PSU W30L120 OC CAU	220-240 V

Order Code	Full Product Name	Input Voltage
911401506981	RC099V G2 LED34/840 PSU W30L120 OC NZ	220-240 V
911401507081	RC099V G2 LED34/850 PSU W30L120 OC NZ	220-240 V
911401507181	RC099V G2 LED34/865 PSU W30L120 OC NZ	220-240 V
911401700673	RC099V G2 LED38/840 PSU W30L120 NZ	220-240 V
911401700683	RC099V G2 LED38/850 PSU W30L120 NZ	220-240 V
911401700693	RC099V G2 LED38/865 PSU W30L120 NZ	220-240 V
911401700763	RC099V G2 LED38/840 PSU W30L120	220 to 240 V
911401700773	RC099V G2 LED38/850 PSU W30L120	220 to 240 V
911401700783	RC099V G2 LED38/865 PSU W30L120	220 to 240 V
911401700853	RC099V G2 LED36/840 PSU W30L120 OC	220 to 240 V
911401700863	RC099V G2 LED36/850 PSU W30L120 OC	220 to 240 V
911401700873	RC099V G2 LED36/865 PSU W30L120 OC	220 to 240 V
911401506381	RC099V G2 LED50/840 PSU W60L120 OC CAU	220-240 V
911401506481	RC099V G2 LED50/850 PSU W60L120 OC CAU	220-240 V
911401506581	RC099V G2 LED50/865 PSU W60L120 OC CAU	220-240 V
911401507281	RC099V G2 LED50/840 PSU W60L120 OC NZ	220-240 V
911401507381	RC099V G2 LED50/850 PSU W60L120 OC NZ	220-240 V
911401507481	RC099V G2 LED50/865 PSU W60L120 OC NZ	220-240 V
911401587171	RC099V G2 LED50/840 PSD W60L120 OC CAU	220-240 V
911401587271	RC099V G2 LED50/850 PSD W60L120 OC CAU	220-240 V
911401587371	RC099V G2 LED50/865 PSD W60L120 OC CAU	220-240 V
911401700703	RC099V G2 LED54/840 PSU W60L120 NZ	220-240 V
911401700713	RC099V G2 LED54/850 PSU W60L120 NZ	220-240 V
911401700723	RC099V G2 LED54/865 PSU W60L120 NZ	220-240 V
911401700793	RC099V G2 LED54/840 PSU W60L120	220 to 240 V
911401700803	RC099V G2 LED54/850 PSU W60L120	220 to 240 V
911401700813	RC099V G2 LED54/865 PSU W60L120	220 to 240 V
911401700883	RC099V G2 LED50/840 PSU W60L120 OC	220 to 240 V
911401700893	RC099V G2 LED50/850 PSU W60L120 OC	220 to 240 V
911401700903	RC099V G2 LED50/865 PSU W60L120 OC	220 to 240 V

General information

GreenPerform Direct LED Panel

Order Code	Full Product Name	Optical cover/lens type	Flammability mark
911401504581	RC099V G2 LED29/840 PSD W60L60 OC CAU	Acrylic bowl/cover clear	For mounting on normally flammable surfaces
911401504681	RC099V G2 LED29/850 PSD W60L60 OC CAU	Acrylic bowl/cover clear	For mounting on normally flammable surfaces
911401504781	RC099V G2 LED29/865 PSD W60L60 OC CAU	Acrylic bowl/cover clear	For mounting on normally flammable surfaces
911401505181	RC099V G2 LED32/840 PSD W60L60 OC CAU	Acrylic bowl/cover clear	For mounting on normally flammable surfaces
911401505281	RC099V G2 LED32/850 PSD W60L60 OC CAU	Acrylic bowl/cover clear	For mounting on normally flammable surfaces
911401505381	RC099V G2 LED32/865 PSD W60L60 OC CAU	Acrylic bowl/cover clear	For mounting on normally flammable surfaces
911401505781	RC099V G2 LED34/840 PSU W60L60 OC CAU	Acrylic bowl/cover clear	For mounting on normally flammable surfaces
911401505881	RC099V G2 LED34/850 PSU W60L60 OC CAU	Acrylic bowl/cover clear	For mounting on normally flammable surfaces
911401505981	RC099V G2 LED34/865 PSU W60L60 OC CAU	Acrylic bowl/cover clear	For mounting on normally flammable surfaces
911401506681	RC099V G2 LED34/840 PSU W60L60 OC NZ	Acrylic bowl/cover clear	For mounting on normally flammable surfaces
911401506781	RC099V G2 LED34/850 PSU W60L60 OC NZ	Acrylic bowl/cover clear	For mounting on normally flammable surfaces
911401506881	RC099V G2 LED34/865 PSU W60L60 OC NZ	Acrylic bowl/cover clear	For mounting on normally flammable surfaces
911401700643	RC099V G2 LED38/840 PSU W60L60 NZ	Acrylic bowl/cover clear	For mounting on normally flammable surfaces
911401700653	RC099V G2 LED38/850 PSU W60L60 NZ	Acrylic bowl/cover clear	For mounting on normally flammable surfaces
911401700663	RC099V G2 LED38/865 PSU W60L60 NZ	Acrylic bowl/cover clear	For mounting on normally flammable surfaces
911401700733	RC099V G2 LED38/840 PSU W60L60	Polystyrene bowl/cover prismatic	-
911401700743	RC099V G2 LED38/850 PSU W60L60	Polystyrene bowl/cover prismatic	-
911401700753	RC099V G2 LED38/865 PSU W60L60	Polystyrene bowl/cover prismatic	-

Order Code	Full Product Name	Optical cover/lens type	Flammability mark
911401700823	RC099V G2 LED36/840 PSU W60L60 OC	Polystyrene bowl/cover prismatic	-
911401700833	RC099V G2 LED36/850 PSU W60L60 OC	Polystyrene bowl/cover prismatic	-
911401700843	RC099V G2 LED36/865 PSU W60L60 OC	Polystyrene bowl/cover prismatic	-
911401504881	RC099V G2 LED29/840 PSD W30L120 OC CAU	Acrylic bowl/cover clear	For mounting on normally flammable surfaces
911401504981	RC099V G2 LED29/850 PSD W30L120 OC CAU	Acrylic bowl/cover clear	For mounting on normally flammable surfaces
911401505081	RC099V G2 LED29/865 PSD W30L120 OC CAU	Acrylic bowl/cover clear	For mounting on normally flammable surfaces
911401505481	RC099V G2 LED32/840 PSD W30L120 OC CAU	Acrylic bowl/cover clear	For mounting on normally flammable surfaces
911401505581	RC099V G2 LED32/850 PSD W30L120 OC CAU	Acrylic bowl/cover clear	For mounting on normally flammable surfaces
911401505681	RC099V G2 LED32/865 PSD W30L120 OC CAU	Acrylic bowl/cover clear	For mounting on normally flammable surfaces
911401506081	RC099V G2 LED34/840 PSU W30L120 OC CAU	Acrylic bowl/cover clear	For mounting on normally flammable surfaces
911401506181	RC099V G2 LED34/850 PSU W30L120 OC CAU	Acrylic bowl/cover clear	For mounting on normally flammable surfaces
911401506281	RC099V G2 LED34/865 PSU W30L120 OC CAU	Acrylic bowl/cover clear	For mounting on normally flammable surfaces
911401506981	RC099V G2 LED34/840 PSU W30L120 OC NZ	Acrylic bowl/cover clear	For mounting on normally flammable surfaces
911401507081	RC099V G2 LED34/850 PSU W30L120 OC NZ	Acrylic bowl/cover clear	For mounting on normally flammable surfaces
911401507181	RC099V G2 LED34/865 PSU W30L120 OC NZ	Acrylic bowl/cover clear	For mounting on normally flammable surfaces
911401700673	RC099V G2 LED38/840 PSU W30L120 NZ	Acrylic bowl/cover clear	For mounting on normally flammable surfaces
911401700683	RC099V G2 LED38/850 PSU W30L120 NZ	Acrylic bowl/cover clear	For mounting on normally flammable surfaces
911401700693	RC099V G2 LED38/865 PSU W30L120 NZ	Acrylic bowl/cover clear	For mounting on normally flammable surfaces

GreenPerform Direct LED Panel

Order Code	Full Product Name	Optical cover/lens type	Flammability mark
911401700763	RC099V G2 LED38/840 PSU W30L120	Polystyrene bowl/cover prismatic	-
911401700773	RC099V G2 LED38/850 PSU W30L120	Polystyrene bowl/cover prismatic	-
911401700783	RC099V G2 LED38/865 PSU W30L120	Polystyrene bowl/cover prismatic	-
911401700853	RC099V G2 LED36/840 PSU W30L120 OC	Polystyrene bowl/cover prismatic	-
911401700863	RC099V G2 LED36/850 PSU W30L120 OC	Polystyrene bowl/cover prismatic	-
911401700873	RC099V G2 LED36/865 PSU W30L120 OC	Polystyrene bowl/cover prismatic	-
911401506381	RC099V G2 LED50/840 PSU W60L120 OC CAU	Acrylic bowl/cover clear	For mounting on normally flammable surfaces
911401506481	RC099V G2 LED50/850 PSU W60L120 OC CAU	Acrylic bowl/cover clear	For mounting on normally flammable surfaces
911401506581	RC099V G2 LED50/865 PSU W60L120 OC CAU	Acrylic bowl/cover clear	For mounting on normally flammable surfaces
911401507281	RC099V G2 LED50/840 PSU W60L120 OC NZ	Acrylic bowl/cover clear	For mounting on normally flammable surfaces
911401507381	RC099V G2 LED50/850 PSU W60L120 OC NZ	Acrylic bowl/cover clear	For mounting on normally flammable surfaces
911401507481	RC099V G2 LED50/865 PSU W60L120 OC NZ	Acrylic bowl/cover clear	For mounting on normally flammable surfaces

Order Code	Full Product Name	Optical cover/lens type	Flammability mark
911401587171	RC099V G2 LED50/840 PSD W60L120 OC CAU	Acrylic bowl/cover clear	For mounting on normally flammable surfaces
911401587271	RC099V G2 LED50/850 PSD W60L120 OC CAU	Acrylic bowl/cover clear	For mounting on normally flammable surfaces
911401587371	RC099V G2 LED50/865 PSD W60L120 OC CAU	Acrylic bowl/cover clear	For mounting on normally flammable surfaces
911401700703	RC099V G2 LED54/840 PSU W60L120 NZ	Acrylic bowl/cover clear	For mounting on normally flammable surfaces
911401700713	RC099V G2 LED54/850 PSU W60L120 NZ	Acrylic bowl/cover clear	For mounting on normally flammable surfaces
911401700723	RC099V G2 LED54/865 PSU W60L120 NZ	Acrylic bowl/cover clear	For mounting on normally flammable surfaces
911401700793	RC099V G2 LED54/840 PSU W60L120	Polystyrene bowl/cover prismatic	-
911401700803	RC099V G2 LED54/850 PSU W60L120	Polystyrene bowl/cover prismatic	-
911401700813	RC099V G2 LED54/865 PSU W60L120	Polystyrene bowl/cover prismatic	-
911401700883	RC099V G2 LED50/840 PSU W60L120 OC	Polystyrene bowl/cover prismatic	-
911401700893	RC099V G2 LED50/850 PSU W60L120 OC	Polystyrene bowl/cover prismatic	-
911401700903	RC099V G2 LED50/865 PSU W60L120 OC	Polystyrene bowl/cover prismatic	-

Initial performance (IEC compliant)

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
911401504581	RC099V G2 LED29/840 PSD W60L60 OC CAU	(0.38, 0.38) SDCM 4	4000 K	100 lm/W	2900 lm	30 W
911401504681	RC099V G2 LED29/850 PSD W60L60 OC CAU	(0.346, 0.359) SDCM 4	5000 K	100 lm/W	2900 lm	30 W
911401504781	RC099V G2 LED29/865 PSD W60L60 OC CAU	(0.313, 0.337) SDCM 4	6500 K	100 lm/W	2900 lm	30 W
911401505181	RC099V G2 LED32/840 PSD W60L60 OC CAU	(0.38, 0.38) SDCM 4	4000 K	100 lm/W	3200 lm	33 W
911401505281	RC099V G2 LED32/850 PSD W60L60 OC CAU	(0.346, 0.359) SDCM 4	5000 K	100 lm/W	3200 lm	33 W
911401505381	RC099V G2 LED32/865 PSD W60L60 OC CAU	(0.313, 0.337) SDCM 4	6500 K	100 lm/W	3200 lm	33 W
911401505781	RC099V G2 LED34/840 PSU W60L60 OC CAU	(0.38, 0.38) SDCM 4	4000 K	100 lm/W	3400 lm	35 W
911401505881	RC099V G2 LED34/850 PSU W60L60 OC CAU	(0.346, 0.359) SDCM 4	5000 K	100 lm/W	3400 lm	35 W
911401505981	RC099V G2 LED34/865 PSU W60L60 OC CAU	(0.313, 0.337) SDCM 4	6500 K	100 lm/W	3400 lm	35 W
911401506681	RC099V G2 LED34/840 PSU W60L60 OC NZ	(0.38, 0.38) SDCM 4	4000 K	100 lm/W	3400 lm	35 W
911401506781	RC099V G2 LED34/850 PSU W60L60 OC NZ	(0.346, 0.359) SDCM 4	5000 K	100 lm/W	3400 lm	35 W
911401506881	RC099V G2 LED34/865 PSU W60L60 OC NZ	(0.313, 0.337) SDCM 4	6500 K	100 lm/W	3400 lm	35 W
911401700643	RC099V G2 LED38/840 PSU W60L60 NZ	(0.38, 0.38) SDCM 4	4000 K	110 lm/W	3800 lm	35 W
911401700653	RC099V G2 LED38/850 PSU W60L60 NZ	(0.346, 0.359) SDCM 4	5000 K	110 lm/W	3800 lm	35 W
911401700663	RC099V G2 LED38/865 PSU W60L60 NZ	(0.313, 0.337) SDCM 4	6500 K	110 lm/W	3800 lm	35 W
911401700733	RC099V G2 LED38/840 PSU W60L60	-	4000 K	110 lm/W	3800 lm	35 W

GreenPerform Direct LED Panel

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
911401700743	RC099V G2 LED38/850 PSU W60L60	-	5000 K	110 lm/W	3800 lm	35 W
911401700753	RC099V G2 LED38/865 PSU W60L60	-	6500 K	110 lm/W	3800 lm	35 W
911401700823	RC099V G2 LED36/840 PSU W60L60 OC	-	4000 K	100 lm/W	3600 lm	35 W
911401700833	RC099V G2 LED36/850 PSU W60L60 OC	-	5000 K	100 lm/W	3600 lm	35 W
911401700843	RC099V G2 LED36/865 PSU W60L60 OC	-	6500 K	100 lm/W	3600 lm	35 W
911401504881	RC099V G2 LED29/840 PSD W30L120 OC CAU	(0.38, 0.38) SDCM 4	4000 K	100 lm/W	2900 lm	30 W
911401504981	RC099V G2 LED29/850 PSD W30L120 OC CAU	(0.346, 0.359) SDCM 4	5000 K	100 lm/W	2900 lm	30 W
911401505081	RC099V G2 LED29/865 PSD W30L120 OC CAU	(0.313, 0.337) SDCM 4	6500 K	100 lm/W	2900 lm	30 W
911401505481	RC099V G2 LED32/840 PSD W30L120 OC CAU	(0.38, 0.38) SDCM 4	4000 K	100 lm/W	3200 lm	33 W
911401505581	RC099V G2 LED32/850 PSD W30L120 OC CAU	(0.346, 0.359) SDCM 4	5000 K	100 lm/W	3200 lm	33 W
911401505681	RC099V G2 LED32/865 PSD W30L120 OC CAU	(0.313, 0.337) SDCM 4	6500 K	100 lm/W	3200 lm	33 W
911401506081	RC099V G2 LED34/840 PSU W30L120 OC CAU	(0.38, 0.38) SDCM 4	4000 K	100 lm/W	3400 lm	35 W
911401506181	RC099V G2 LED34/850 PSU W30L120 OC CAU	(0.346, 0.359) SDCM 4	5000 K	100 lm/W	3400 lm	35 W
911401506281	RC099V G2 LED34/865 PSU W30L120 OC CAU	(0.313, 0.337) SDCM 4	6500 K	100 lm/W	3400 lm	35 W
911401506981	RC099V G2 LED34/840 PSU W30L120 OC NZ	(0.38, 0.38) SDCM 4	4000 K	100 lm/W	3400 lm	35 W
911401507081	RC099V G2 LED34/850 PSU W30L120 OC NZ	(0.346, 0.359) SDCM 4	5000 K	100 lm/W	3400 lm	35 W
911401507181	RC099V G2 LED34/865 PSU W30L120 OC NZ	(0.313, 0.337) SDCM 4	6500 K	100 lm/W	3400 lm	35 W
911401700673	RC099V G2 LED38/840 PSU W30L120 NZ	(0.38, 0.38) SDCM 4	4000 K	110 lm/W	3800 lm	35 W
911401700683	RC099V G2 LED38/850 PSU W30L120 NZ	(0.346, 0.359) SDCM 4	5000 K	110 lm/W	3800 lm	35 W
911401700693	RC099V G2 LED38/865 PSU W30L120 NZ	(0.313, 0.337) SDCM 4	6500 K	110 lm/W	3800 lm	35 W
911401700763	RC099V G2 LED38/840 PSU W30L120	-	4000 K	110 lm/W	3800 lm	35 W
911401700773	RC099V G2 LED38/850 PSU W30L120	-	5000 K	110 lm/W	3800 lm	35 W
911401700783	RC099V G2 LED38/865 PSU W30L120	-	6500 K	110 lm/W	3800 lm	35 W
911401700853	RC099V G2 LED36/840 PSU W30L120 OC	-	4000 K	100 lm/W	3600 lm	35 W
911401700863	RC099V G2 LED36/850 PSU W30L120 OC	-	5000 K	100 lm/W	3600 lm	35 W
911401700873	RC099V G2 LED36/865 PSU W30L120 OC	-	6500 K	100 lm/W	3600 lm	35 W
911401506381	RC099V G2 LED50/840 PSU W60L120 OC CAU	(0.38, 0.38) SDCM 4	4000 K	110 lm/W	5000 lm	45 W
911401506481	RC099V G2 LED50/850 PSU W60L120 OC CAU	(0.346, 0.359) SDCM 4	5000 K	110 lm/W	5000 lm	45 W
911401506581	RC099V G2 LED50/865 PSU W60L120 OC CAU	(0.313, 0.337) SDCM 4	6500 K	110 lm/W	5000 lm	45 W
911401507281	RC099V G2 LED50/840 PSU W60L120 OC NZ	(0.38, 0.38) SDCM 4	4000 K	110 lm/W	5000 lm	45 W
911401507381	RC099V G2 LED50/850 PSU W60L120 OC NZ	(0.346, 0.359) SDCM 4	5000 K	110 lm/W	5000 lm	45 W
911401507481	RC099V G2 LED50/865 PSU W60L120 OC NZ	(0.313, 0.337) SDCM 4	6500 K	110 lm/W	5000 lm	45 W
911401587171	RC099V G2 LED50/840 PSD W60L120 OC CAU	(0.38, 0.38) SDCM 4	4000 K	110 lm/W	5000 lm	45 W
911401587271	RC099V G2 LED50/850 PSD W60L120 OC CAU	(0.346, 0.359) SDCM 4	5000 K	110 lm/W	5000 lm	45 W
911401587371	RC099V G2 LED50/865 PSD W60L120 OC CAU	(0.313, 0.337) SDCM 4	6500 K	110 lm/W	5000 lm	45 W
911401700703	RC099V G2 LED54/840 PSU W60L120 NZ	(0.38, 0.38) SDCM 4	4000 K	120 lm/W	5400 lm	45 W
911401700713	RC099V G2 LED54/850 PSU W60L120 NZ	(0.346, 0.359) SDCM 4	5000 K	120 lm/W	5400 lm	45 W
911401700723	RC099V G2 LED54/865 PSU W60L120 NZ	(0.313, 0.337) SDCM 4	6500 K	120 lm/W	5400 lm	45 W
911401700793	RC099V G2 LED54/840 PSU W60L120	-	4000 K	120 lm/W	5400 lm	45 W
911401700803	RC099V G2 LED54/850 PSU W60L120	-	5000 K	120 lm/W	5400 lm	45 W
911401700813	RC099V G2 LED54/865 PSU W60L120	-	6500 K	120 lm/W	5400 lm	45 W
911401700883	RC099V G2 LED50/840 PSU W60L120 OC	-	4000 K	110 lm/W	5000 lm	45 W
911401700893	RC099V G2 LED50/850 PSU W60L120 OC	-	5000 K	110 lm/W	5000 lm	45 W
911401700903	RC099V G2 LED50/865 PSU W60L120 OC	-	6500 K	110 lm/W	5000 lm	45 W

GreenPerform Direct LED Panel

