



The highest efficacy with long lasting reliability.

RoadForce

With an extremely high measured efficacy of up to 190 lm/W, excellent optical gear and great installation flexibility with an integrated angle adjustment system, the RoadForce family ensures a high-quality luminous result compliant with local application standards. Designed with robust components, the RoadForce luminaire complies with the highest quality standards while reducing the maintenance costs.

Benefits

- Presenting great optical performance and high measured efficacy (of up to 190 lm/W) combined with its installation versatility, with an embedded tilt angle adjustment system (-5° / 0° / +5°), RoadForce achieves energy savings of 70% versus conventional lighting alternatives, with an additional savings potential when combined with control and tele management systems (Interact City). The broadest and most diverse product family in its category, with 24 lumen output options, allowing for the optimisation of lighting projects according to their actual specifications. Achieve maintenance cost reductions: RoadForce incorporates long lasting LED technologies and other high-quality components ensuring a system lifetime of 78.000 hours (@L70B50) at 35 °C.

Features

- Die cast aluminium body, Grey Munsel N6.5 painting with high resistance to corrosion, tested for 1.000 hours salt spray and sealing with silicon gasket.
- Two colour temperature options available (4000K and 5000K) and two light distribution options available (DML and DWL).
- Standard surge protection: 10kV/10kA. Optional version available: 10kV/12kA.
- CISPR15 compliant dimmable driver.
- High transparency UV resistant polycarbonate (PC) lenses.
- Easy connection to tele management systems such as Interact City, with a standard 7-pin NEMA socket, allowing for remote lighting management.

Application

- Traffic routes: highways, streets, and avenues.
- Urban areas: parks and plazas, pedestrian crossings, bike paths, parking areas.
- Large open areas: industrial yards, harbours, airports, canals, railway terminals.

Warnings and Safety

- Follow the mounting instructions provided by the manufacturer.

Versions



RoadForce



RoadForce



RoadForce



RoadForce




RoadForce



RoadForce

Product details



RoadForce



RoadForce



RoadForce

Application Conditions

Ambient temperature range	-5 to +50 °C
---------------------------	--------------

Approval and Application

Mech. impact protection code	IK08
Ingress protection code	IP66
Surge Protection (Common/ Differential)	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode

Controls and Dimming

Dimmable	Yes
----------	-----

General Information

Luminaire light beam spread	-
Driver included	Yes
Lamp family code	LED-HP
Light source replaceable	Yes

Initial Performance (IEC Compliant)

Init. Color Rendering Index	>70
-----------------------------	-----

Light Technical

Standard tilt angle side entry	0°
Standard tilt angle posttop	-

Mechanical and Housing

Color	Gray
Overall height	126 mm

General Information

Order Code	Full Product Name	Number of light sources
919306031971	BRP481 LED43 NW 24W DWL P7 0-10	1 pc
919306031981	BRP481 LED51 NW 27W DWL P7 0-10	1 pc
919306031991	BRP481 LED60 NW 33W DWL P7 0-10	1 pc
919306032001	BRP481 LED73 NW 41W DWL P7 0-10	1 pc
919306032011	BRP481 LED85 NW 48W DWL P7 0-10	1 pc
919306032021	BRP481 LED96 NW 55W DWL P7 0-10	1 pc
919306032031	BRP481 LED43 CW 24W DWL P7 0-10	1 pc
919306032051	BRP481 LED60 CW 33W DWL P7 0-10	1 pc
919306032061	BRP481 LED73 CW 41W DWL P7 0-10	1 pc
919306032071	BRP481 LED85 CW 48W DWL P7 0-10	1 pc
919306032081	BRP481 LED96 CW 55W DWL P7 0-10	1 pc
919306032091	BRP481 LED43 NW 24W DML P7 0-10	1 pc
919306032101	BRP481 LED51 NW 27W DML P7 0-10	1 pc
919306032111	BRP481 LED60 NW 33W DML P7 0-10	1 pc
919306032121	BRP481 LED73 NW 41W DML P7 0-10	1 pc
919306032131	BRP481 LED85 NW 48W DML P7 0-10	1 pc
919306032141	BRP481 LED96 NW 55W DML P7 0-10	1 pc
919306032151	BRP481 LED43 CW 24W DML P7 0-10	1 pc
919306032161	BRP481 LED51 CW 27W DML P7 0-10	1 pc
919306032171	BRP481 LED60 CW 33W DML P7 0-10	1 pc
919306032181	BRP481 LED73 CW 41W DML P7 0-10	1 pc
919306032191	BRP481 LED85 CW 48W DML P7 0-10	1 pc
919306032201	BRP481 LED96 CW 55W DML P7 0-10	1 pc
919306032211	BRP482 LED104 NW 56W DWL P7 0-10	2 pcs
919306032221	BRP482 LED113 NW 61W DWL P7 0-10	2 pcs
919306032231	BRP482 LED126 NW 70W DWL P7 0-10	2 pcs
919306032241	BRP482 LED136 NW 76W DWL P7 0-10	2 pcs
919306032251	BRP482 LED147 NW 83W DWL P7 0-10	2 pcs
919306032261	BRP482 LED160 NW 92W DWL P7 0-10	2 pcs
919306032271	BRP482 LED172 NW 100W DWL P7 0-10	2 pcs

Order Code	Full Product Name	Number of light sources
919306032281	BRP482 LED179 NW 105W DWL P7 0-10	2 pcs
919306032291	BRP482 LED186 NW 110W DWL P7 0-10	2 pcs
919306032311	BRP482 LED113 CW 61W DWL P7 0-10	2 pcs
919306032331	BRP482 LED136 CW 76W DWL P7 0-10	2 pcs
919306032361	BRP482 LED172 CW 100W DWL P7 0-10	2 pcs
919306032381	BRP482 LED186 CW 110W DWL P7 0-10	2 pcs
919306032391	BRP482 LED104 NW 56W DML P7 0-10	2 pcs
919306032401	BRP482 LED113 NW 61W DML P7 0-10	2 pcs
919306032411	BRP482 LED126 NW 70W DML P7 0-10	2 pcs
919306032421	BRP482 LED136 NW 76W DML P7 0-10	2 pcs
919306032431	BRP482 LED147 NW 83W DML P7 0-10	2 pcs
919306032441	BRP482 LED160 NW 92W DML P7 0-10	2 pcs
919306032451	BRP482 LED172 NW 100W DML P7 0-10	2 pcs
919306032461	BRP482 LED179 NW 105W DML P7 0-10	2 pcs
919306032471	BRP482 LED186 NW 110W DML P7 0-10	2 pcs
919306032481	BRP482 LED104 CW 56W DML P7 0-10	2 pcs
919306032491	BRP482 LED113 CW 61W DML P7 0-10	2 pcs
919306032501	BRP482 LED126 CW 70W DML P7 0-10	2 pcs
919306032511	BRP482 LED136 CW 76W DML P7 0-10	2 pcs
919306032521	BRP482 LED147 CW 83W DML P7 0-10	2 pcs
919306032531	BRP482 LED160 CW 92W DML P7 0-10	2 pcs
919306032541	BRP482 LED172 CW 100W DML P7 0-10	2 pcs
919306032551	BRP482 LED179 CW 105W DML P7 0-10	2 pcs
919306032561	BRP482 LED186 CW 110W DML P7 0-10	2 pcs
919306032571	BRP483 LED202 NW 113W DWL P7 0-10	3 pcs
919306032581	BRP483 LED216 NW 122W DWL P7 0-10	3 pcs
919306032591	BRP483 LED236 NW 136W DWL P7 0-10	3 pcs
919306032601	BRP483 LED255 NW 150W DWL P7 0-10	3 pcs
919306032611	BRP483 LED274 NW 165W DWL P7 0-10	3 pcs
919306032621	BRP483 LED202 NW 113W DML P7 0-10	3 pcs
919306032631	BRP483 LED216 NW 122W DML P7 0-10	3 pcs
919306032641	BRP483 LED236 NW 136W DML P7 0-10	3 pcs
919306032651	BRP483 LED255 NW 150W DML P7 0-10	3 pcs
919306032661	BRP483 LED274 NW 165W DML P7 0-10	3 pcs
919306032681	BRP483 LED216 CW 122W DWL P7 0-10	3 pcs
919306032701	BRP483 LED255 CW 150W DWL P7 0-10	3 pcs
919306032711	BRP483 LED274 CW 165W DWL P7 0-10	3 pcs
919306032721	BRP483 LED202 CW 113W DML P7 0-10	3 pcs
919306032731	BRP483 LED216 CW 122W DML P7 0-10	3 pcs
919306032741	BRP483 LED236 CW 136W DML P7 0-10	3 pcs
919306032751	BRP483 LED255 CW 150W DML P7 0-10	3 pcs
919306032761	BRP483 LED274 CW 165W DML P7 0-10	3 pcs
919306032771	BRP484 LED292 NW 169W DWL P7 0-10	4 pcs
919306032781	BRP484 LED307 NW 179W DWL P7 0-10	4 pcs
919306032791	BRP484 LED292 NW 169W DML P7 0-10	4 pcs
919306032801	BRP484 LED307 NW 179W DML P7 0-10	4 pcs
919306032811	BRP484 LED292 CW 169W DWL P7 0-10	4 pcs
919306032821	BRP484 LED307 CW 179W DWL P7 0-10	4 pcs
919306032831	BRP484 LED292 CW 169W DML P7 0-10	4 pcs
919306032841	BRP484 LED307 CW 179W DML P7 0-10	4 pcs
919306032851	BRP485 LED328 NW 185W DWL P7 0-10	5 pcs
919306032861	BRP485 LED328 NW 185W DML P7 0-10	5 pcs

Order Code	Full Product Name	Number of light sources
919306032871	BRP485 LED328 CW 185W DWL P7 0-10	5 pcs
919306032881	BRP485 LED328 CW 185W DML P7 0-10	5 pcs
919306032891	BRP486 LED351 NW 195W DWL P7 0-10	6 pcs
919306032901	BRP486 LED351 NW 195W DML P7 0-10	6 pcs
919306032911	BRP486 LED351 CW 195W DWL P7 0-10	6 pcs
919306032921	BRP486 LED351 CW 195W DML P7 0-10	6 pcs

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial luminous flux	System Power	Order Code	Full Product Name	Init. Corr. Color Temperature	Initial luminous flux	System Power
919306031971	BRP481 LED43 NW 24W DWL P7 0-10	4000 K	4500 lm	25.36 W	919306032181	BRP481 LED73 CW 41W DML P7 0-10	5000 K	7300 lm	41.57 W
919306031981	BRP481 LED51 NW 27W DWL P7 0-10	4000 K	5100 lm	27.81 W	919306032191	BRP481 LED85 CW 48W DML P7 0-10	5000 K	8500 lm	48.99 W
919306031991	BRP481 LED60 NW 33W DWL P7 0-10	4000 K	6100 lm	33.73 W	919306032201	BRP481 LED96 CW 55W DML P7 0-10	5000 K	9600 lm	56.37 W
919306032001	BRP481 LED73 NW 41W DWL P7 0-10	4000 K	7300 lm	41.57 W	919306032211	BRP482 LED104 NW 56W DWL P7 0-10	4000 K	10400 lm	55.88 W
919306032011	BRP481 LED85 NW 48W DWL P7 0-10	4000 K	8500 lm	48.99 W	919306032221	BRP482 LED113 NW 61W DWL P7 0-10	4000 K	11300 lm	60.74 W
919306032021	BRP481 LED96 NW 55W DWL P7 0-10	4000 K	9600 lm	56.37 W	919306032231	BRP482 LED126 NW 70W DWL P7 0-10	4000 K	12600 lm	68.97 W
919306032031	BRP481 LED43 CW 24W DWL P7 0-10	5000 K	4500 lm	25.36 W	919306032241	BRP482 LED136 NW 76W DWL P7 0-10	4000 K	13600 lm	75.28 W
919306032051	BRP481 LED60 CW 33W DWL P7 0-10	5000 K	6100 lm	33.73 W	919306032251	BRP482 LED147 NW 83W DWL P7 0-10	4000 K	14700 lm	82.77 W
919306032061	BRP481 LED73 CW 41W DWL P7 0-10	5000 K	7300 lm	41.57 W	919306032261	BRP482 LED160 NW 92W DWL P7 0-10	4000 K	16000 lm	91.3 W
919306032071	BRP481 LED85 CW 48W DWL P7 0-10	5000 K	8500 lm	48.99 W	919306032271	BRP482 LED172 NW 100W DWL P7 0-10	4000 K	17200 lm	99.99 W
919306032081	BRP481 LED96 CW 55W DWL P7 0-10	5000 K	9600 lm	56.37 W	919306032281	BRP482 LED179 NW 105W DWL P7 0-10	4000 K	17900 lm	105.44 W
919306032091	BRP481 LED43 NW 24W DML P7 0-10	4000 K	4500 lm	25.36 W	919306032291	BRP482 LED186 NW 110W DWL P7 0-10	4000 K	18600 lm	110.75 W
919306032101	BRP481 LED51 NW 27W DML P7 0-10	4000 K	5100 lm	27.81 W	919306032311	BRP482 LED113 CW 61W DWL P7 0-10	5000 K	11300 lm	60.74 W
919306032111	BRP481 LED60 NW 33W DML P7 0-10	4000 K	6100 lm	33.73 W	919306032331	BRP482 LED136 CW 76W DWL P7 0-10	5000 K	13600 lm	75.28 W
919306032121	BRP481 LED73 NW 41W DML P7 0-10	4000 K	7300 lm	41.57 W	919306032361	BRP482 LED172 CW 100W DWL P7 0-10	5000 K	17200 lm	99.99 W
919306032131	BRP481 LED85 NW 48W DML P7 0-10	4000 K	8500 lm	48.99 W	919306032381	BRP482 LED186 CW 110W DWL P7 0-10	5000 K	18600 lm	110.75 W
919306032141	BRP481 LED96 NW 55W DML P7 0-10	4000 K	9600 lm	56.37 W	919306032391	BRP482 LED104 NW 56W DML P7 0-10	4000 K	10400 lm	55.88 W
919306032151	BRP481 LED43 CW 24W DML P7 0-10	5000 K	4500 lm	25.36 W	919306032401	BRP482 LED113 NW 61W DML P7 0-10	4000 K	11300 lm	60.74 W
919306032161	BRP481 LED51 CW 27W DML P7 0-10	5000 K	5100 lm	27.81 W	919306032411	BRP482 LED126 NW 70W DML P7 0-10	4000 K	12600 lm	68.97 W
919306032171	BRP481 LED60 CW 33W DML P7 0-10	5000 K	6100 lm	33.73 W	919306032421	BRP482 LED136 NW 76W DML P7 0-10	4000 K	13600 lm	75.28 W

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial luminous flux	System Power
919306032431	BRP482 LED147 NW 83W DML P7 0-10	4000 K	14700 lm	82.77 W
919306032441	BRP482 LED160 NW 92W DML P7 0-10	4000 K	16000 lm	91.3 W
919306032451	BRP482 LED172 NW 100W DML P7 0-10	4000 K	17200 lm	99.99 W
919306032461	BRP482 LED179 NW 105W DML P7 0-10	4000 K	17900 lm	105.44 W
919306032471	BRP482 LED186 NW 110W DML P7 0-10	4000 K	18600 lm	110.75 W
919306032481	BRP482 LED104 CW 56W DML P7 0-10	5000 K	10400 lm	55.88 W
919306032491	BRP482 LED113 CW 61W DML P7 0-10	5000 K	11300 lm	60.74 W
919306032501	BRP482 LED126 CW 70W DML P7 0-10	5000 K	12600 lm	68.97 W
919306032511	BRP482 LED136 CW 76W DML P7 0-10	5000 K	13600 lm	75.28 W
919306032521	BRP482 LED147 CW 83W DML P7 0-10	5000 K	14700 lm	82.77 W
919306032531	BRP482 LED160 CW 92W DML P7 0-10	5000 K	16000 lm	91.3 W
919306032541	BRP482 LED172 CW 100W DML P7 0-10	5000 K	17200 lm	99.99 W
919306032551	BRP482 LED179 CW 105W DML P7 0-10	5000 K	17900 lm	105.44 W
919306032561	BRP482 LED186 CW 110W DML P7 0-10	5000 K	18600 lm	110.75 W
919306032571	BRP483 LED202 NW 113W DWL P7 0-10	4000 K	20200 lm	111.4 W
919306032581	BRP483 LED216 NW 122W DWL P7 0-10	4000 K	21600 lm	120.96 W
919306032591	BRP483 LED236 NW 136W DWL P7 0-10	4000 K	23600 lm	134.89 W
919306032601	BRP483 LED255 NW 150W DWL P7 0-10	4000 K	25500 lm	148.46 W
919306032611	BRP483 LED274 NW 165W DWL P7 0-10	4000 K	27400 lm	164.31 W
919306032621	BRP483 LED202 NW 113W DML P7 0-10	4000 K	20200 lm	111.4 W
919306032631	BRP483 LED216 NW 122W DML P7 0-10	4000 K	21600 lm	120.96 W
919306032641	BRP483 LED236 NW 136W DML P7 0-10	4000 K	23600 lm	134.89 W
919306032651	BRP483 LED255 NW 150W DML P7 0-10	4000 K	25500 lm	148.46 W
919306032661	BRP483 LED274 NW 165W DML P7 0-10	4000 K	27400 lm	164.31 W

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial luminous flux	System Power
919306032681	BRP483 LED216 CW 122W DWL P7 0-10	5000 K	21600 lm	120.96 W
919306032701	BRP483 LED255 CW 150W DWL P7 0-10	5000 K	25500 lm	148.46 W
919306032711	BRP483 LED274 CW 165W DWL P7 0-10	5000 K	27400 lm	164.31 W
919306032721	BRP483 LED202 CW 113W DML P7 0-10	5000 K	20200 lm	111.4 W
919306032731	BRP483 LED216 CW 122W DML P7 0-10	5000 K	21600 lm	120.96 W
919306032741	BRP483 LED236 CW 136W DML P7 0-10	5000 K	23600 lm	134.89 W
919306032751	BRP483 LED255 CW 150W DML P7 0-10	5000 K	25500 lm	148.46 W
919306032761	BRP483 LED274 CW 165W DML P7 0-10	5000 K	27400 lm	164.31 W
919306032771	BRP484 LED292 NW 169W DWL P7 0-10	4000 K	29200 lm	166.56 W
919306032781	BRP484 LED307 NW 179W DWL P7 0-10	4000 K	30700 lm	176.68 W
919306032791	BRP484 LED292 NW 169W DML P7 0-10	4000 K	29200 lm	166.56 W
919306032801	BRP484 LED307 NW 179W DML P7 0-10	4000 K	30700 lm	176.68 W
919306032811	BRP484 LED292 CW 169W DWL P7 0-10	5000 K	29200 lm	166.56 W
919306032821	BRP484 LED307 CW 179W DWL P7 0-10	5000 K	30700 lm	176.68 W
919306032831	BRP484 LED292 CW 169W DML P7 0-10	5000 K	29200 lm	166.56 W
919306032841	BRP484 LED307 CW 179W DML P7 0-10	5000 K	30700 lm	176.68 W
919306032851	BRP485 LED328 NW 185W DWL P7 0-10	4000 K	32800 lm	181.44 W
919306032861	BRP485 LED328 NW 185W DML P7 0-10	4000 K	32800 lm	181.44 W
919306032871	BRP485 LED328 CW 185W DWL P7 0-10	5000 K	32800 lm	181.44 W
919306032881	BRP485 LED328 CW 185W DML P7 0-10	5000 K	32800 lm	181.44 W
919306032891	BRP486 LED351 NW 195W DWL P7 0-10	4000 K	35100 lm	190.25 W
919306032901	BRP486 LED351 NW 195W DML P7 0-10	4000 K	35100 lm	190.25 W
919306032911	BRP486 LED351 CW 195W DWL P7 0-10	5000 K	35100 lm	190.25 W
919306032921	BRP486 LED351 CW 195W DML P7 0-10	5000 K	35100 lm	190.25 W

Mechanical and Housing

Order Code	Full Product Name	Overall length	Overall width	Order Code	Full Product Name	Overall length	Overall width
919306031971	BRP481 LED43 NW 24W DWL P7 0-10	420 mm	180 mm	919306032471	BRP482 LED186 NW 110W DML P7 0-10	430 mm	203 mm
919306031981	BRP481 LED51 NW 27W DWL P7 0-10	420 mm	180 mm	919306032481	BRP482 LED104 CW 56W DML P7 0-10	430 mm	203 mm
919306031991	BRP481 LED60 NW 33W DWL P7 0-10	420 mm	180 mm	919306032491	BRP482 LED113 CW 61W DML P7 0-10	430 mm	203 mm
919306032001	BRP481 LED73 NW 41W DWL P7 0-10	420 mm	180 mm	919306032501	BRP482 LED126 CW 70W DML P7 0-10	430 mm	203 mm
919306032011	BRP481 LED85 NW 48W DWL P7 0-10	420 mm	180 mm	919306032511	BRP482 LED136 CW 76W DML P7 0-10	430 mm	203 mm
919306032021	BRP481 LED96 NW 55W DWL P7 0-10	420 mm	180 mm	919306032521	BRP482 LED147 CW 83W DML P7 0-10	430 mm	203 mm
919306032031	BRP481 LED43 CW 24W DWL P7 0-10	420 mm	180 mm	919306032531	BRP482 LED160 CW 92W DML P7 0-10	430 mm	203 mm
919306032051	BRP481 LED60 CW 33W DWL P7 0-10	420 mm	180 mm	919306032541	BRP482 LED172 CW 100W DML P7 0-10	430 mm	203 mm
919306032061	BRP481 LED73 CW 41W DWL P7 0-10	420 mm	180 mm	919306032551	BRP482 LED179 CW 105W DML P7 0-10	430 mm	203 mm
919306032071	BRP481 LED85 CW 48W DWL P7 0-10	420 mm	180 mm	919306032561	BRP482 LED186 CW 110W DML P7 0-10	430 mm	203 mm
919306032081	BRP481 LED96 CW 55W DWL P7 0-10	420 mm	180 mm	919306032571	BRP483 LED202 NW 113W DWL P7 0-10	420 mm	220 mm
919306032091	BRP481 LED43 NW 24W DML P7 0-10	420 mm	180 mm	919306032581	BRP483 LED216 NW 122W DWL P7 0-10	420 mm	220 mm
919306032101	BRP481 LED51 NW 27W DML P7 0-10	420 mm	180 mm	919306032591	BRP483 LED236 NW 136W DWL P7 0-10	420 mm	220 mm
919306032111	BRP481 LED60 NW 33W DML P7 0-10	420 mm	180 mm	919306032601	BRP483 LED255 NW 150W DWL P7 0-10	420 mm	220 mm
919306032121	BRP481 LED73 NW 41W DML P7 0-10	420 mm	180 mm	919306032611	BRP483 LED274 NW 165W DWL P7 0-10	420 mm	220 mm
919306032131	BRP481 LED85 NW 48W DML P7 0-10	420 mm	180 mm	919306032621	BRP483 LED202 NW 113W DML P7 0-10	420 mm	220 mm
919306032141	BRP481 LED96 NW 55W DML P7 0-10	420 mm	180 mm	919306032631	BRP483 LED216 NW 122W DML P7 0-10	420 mm	220 mm
919306032151	BRP481 LED43 CW 24W DML P7 0-10	420 mm	180 mm	919306032641	BRP483 LED236 NW 136W DML P7 0-10	420 mm	220 mm
919306032161	BRP481 LED51 CW 27W DML P7 0-10	420 mm	180 mm	919306032651	BRP483 LED255 NW 150W DML P7 0-10	420 mm	220 mm
919306032171	BRP481 LED60 CW 33W DML P7 0-10	420 mm	180 mm	919306032661	BRP483 LED274 NW 165W DML P7 0-10	420 mm	220 mm
919306032181	BRP481 LED73 CW 41W DML P7 0-10	420 mm	180 mm	919306032681	BRP483 LED216 CW 122W DWL P7 0-10	420 mm	220 mm
919306032191	BRP481 LED85 CW 48W DML P7 0-10	420 mm	180 mm	919306032701	BRP483 LED255 CW 150W DWL P7 0-10	420 mm	220 mm
919306032201	BRP481 LED96 CW 55W DML P7 0-10	420 mm	180 mm	919306032711	BRP483 LED274 CW 165W DWL P7 0-10	420 mm	220 mm
919306032211	BRP482 LED104 NW 56W DWL P7 0-10	430 mm	203 mm	919306032721	BRP483 LED202 CW 113W DML P7 0-10	420 mm	220 mm
919306032221	BRP482 LED113 NW 61W DWL P7 0-10	430 mm	203 mm	919306032731	BRP483 LED216 CW 122W DML P7 0-10	420 mm	220 mm
919306032231	BRP482 LED126 NW 70W DWL P7 0-10	430 mm	203 mm	919306032741	BRP483 LED236 CW 136W DML P7 0-10	420 mm	220 mm
919306032241	BRP482 LED136 NW 76W DWL P7 0-10	430 mm	203 mm	919306032751	BRP483 LED255 CW 150W DML P7 0-10	420 mm	220 mm
919306032251	BRP482 LED147 NW 83W DWL P7 0-10	430 mm	203 mm	919306032761	BRP483 LED274 CW 165W DML P7 0-10	420 mm	220 mm
919306032261	BRP482 LED160 NW 92W DWL P7 0-10	430 mm	203 mm	919306032771	BRP484 LED292 NW 169W DWL P7 0-10	670 mm	200 mm
919306032271	BRP482 LED172 NW 100W DWL P7 0-10	430 mm	203 mm	919306032781	BRP484 LED307 NW 179W DWL P7 0-10	670 mm	200 mm
919306032281	BRP482 LED179 NW 105W DWL P7 0-10	430 mm	203 mm	919306032791	BRP484 LED292 NW 169W DML P7 0-10	670 mm	200 mm
919306032291	BRP482 LED186 NW 110W DWL P7 0-10	430 mm	203 mm	919306032801	BRP484 LED307 NW 179W DML P7 0-10	670 mm	200 mm
919306032311	BRP482 LED113 CW 61W DWL P7 0-10	430 mm	203 mm	919306032811	BRP484 LED292 CW 169W DWL P7 0-10	670 mm	200 mm
919306032331	BRP482 LED136 CW 76W DWL P7 0-10	430 mm	203 mm	919306032821	BRP484 LED307 CW 179W DWL P7 0-10	670 mm	200 mm
919306032361	BRP482 LED172 CW 100W DWL P7 0-10	430 mm	203 mm	919306032831	BRP484 LED292 CW 169W DML P7 0-10	670 mm	200 mm
919306032381	BRP482 LED186 CW 110W DWL P7 0-10	430 mm	203 mm	919306032841	BRP484 LED307 CW 179W DML P7 0-10	670 mm	200 mm
919306032391	BRP482 LED104 NW 56W DML P7 0-10	430 mm	203 mm	919306032851	BRP485 LED328 NW 185W DWL P7 0-10	670 mm	280 mm
919306032401	BRP482 LED113 NW 61W DML P7 0-10	430 mm	203 mm	919306032861	BRP485 LED328 NW 185W DML P7 0-10	670 mm	280 mm
919306032411	BRP482 LED126 NW 70W DML P7 0-10	430 mm	203 mm	919306032871	BRP485 LED328 CW 185W DWL P7 0-10	670 mm	280 mm
919306032421	BRP482 LED136 NW 76W DML P7 0-10	430 mm	203 mm	919306032881	BRP485 LED328 CW 185W DML P7 0-10	670 mm	280 mm
919306032431	BRP482 LED147 NW 83W DML P7 0-10	430 mm	203 mm	919306032891	BRP486 LED351 NW 195W DWL P7 0-10	670 mm	280 mm
919306032441	BRP482 LED160 NW 92W DML P7 0-10	430 mm	203 mm	919306032901	BRP486 LED351 NW 195W DML P7 0-10	670 mm	280 mm
919306032451	BRP482 LED172 NW 100W DML P7 0-10	430 mm	203 mm	919306032911	BRP486 LED351 CW 195W DWL P7 0-10	670 mm	280 mm
919306032461	BRP482 LED179 NW 105W DML P7 0-10	430 mm	203 mm	919306032921	BRP486 LED351 CW 195W DML P7 0-10	670 mm	280 mm

