



The highest efficacy with long lasting reliability.

RoadForce

With an extremely high measured efficacy of up to 190 lm/W, excellent optical gear and great installation flexibility with an integrated angle adjustment system, the RoadForce family ensures a high-quality luminous result compliant with local application standards. Designed with robust components, the RoadForce luminaire complies with the highest quality standards while reducing the maintenance costs.

Benefits

- Presenting great optical performance and high measured efficacy (of up to 190 lm/W) combined with its installation versatility, with an embedded tilt angle adjustment system (-5° / 0° / +5°), RoadForce achieves energy savings of 70% versus conventional lighting alternatives, with an additional savings potential when combined with control and tele management systems (Interact City).
- The broadest and most diverse product family in its category, with 24 lumen output options, allowing for the optimisation of lighting projects according to their actual specifications.
- Achieve maintenance cost reductions: RoadForce incorporates long lasting LED technologies and other high-quality components ensuring a system lifetime of 78.000 hours (@L70B50) at 35 °C.

RoadForce

Features

- Die cast aluminium body, Grey Munsel N6.5 painting with high resistance to corrosion, tested for 1.000 hours salt spray and sealing with silicon gasket.
- Two colour temperature options available (4000K and 5000K) and two light distribution options available (DML and DWL).
- Standard surge protection: 10kV/10kA. Optional version available: 10kV/12kA.
- CISPR15 compliant dimmable driver.
- High transparency UV resistant polycarbonate (PC) lenses.
- Easy connection to tele management systems such as Interact City, with a standard 7-pin NEMA socket, allowing for remote lighting management.

Application

- Traffic routes: highways, streets, and avenues.
- Urban areas: parks and plazas, pedestrian crossings, bike paths, parking areas.
- Large open areas: industrial yards, harbours, airports, canals, railway terminals.

Warnings and Safety

- Follow the mounting instructions provided by the manufacturer.

Versions




RoadForce

Product details



RoadForce



Roadforce

Product details



RoadForce



Roadforce



RoadForce

General Information

| | |
|--------------------------|-----|
| Driver included | Yes |
| Light source replaceable | Yes |

Light Technical

| | |
|-----------------------------|---|
| Luminaire light beam spread | - |
| Standard tilt angle posttop | - |

Mechanical and Housing

| | |
|----------------|--------|
| Housing Color | Gray |
| Overall height | 126 mm |

Approval and Application

| | |
|-------------------------|------|
| Ingress protection code | IP66 |
|-------------------------|------|

General Information

| Order Code | Full Product Name | Lamp family code |
|--------------|--|------------------|
| 919306032771 | BRP484 LED292 NW 169W DWL P7 0-10 | LED-HP |
| 919306032781 | BRP484 LED307 NW 179W DWL P7 0-10 | LED-HP |
| 919306032791 | BRP484 LED292 NW 169W DML P7 0-10 | LED-HP |
| 919306032801 | BRP484 LED307 NW 179W DML P7 0-10 | LED-HP |
| 919306032811 | BRP484 LED292 CW 169W DWL P7 0-10 | LED-HP |
| 919306032821 | BRP484 LED307 CW 179W DWL P7 0-10 | LED-HP |
| 919306032831 | BRP484 LED292 CW 169W DML P7 0-10 | LED-HP |
| 919306032841 | BRP484 LED307 CW 179W DML P7 0-10 | LED-HP |
| 919306035351 | BRP484 LED292-2S NW 169W DML P7 0-10 | - |
| 919306035361 | BRP484 LED292-2S NW 169W DML P7 0-10 M | - |
| 919306035371 | BRP484 LED292-2S NW 169W DWL P7 0-10 | - |
| 919306035381 | BRP484 LED292-2S NW 169W DWL P7 0-10 M | - |
| 919306035411 | BRP484 LED307-2S NW 179W DML P7 0-10 | - |
| 919306035421 | BRP484 LED307-2S NW 179W DML P7 0-10 M | - |

| Order Code | Full Product Name | Lamp family code |
|--------------|---|------------------|
| 919306035431 | BRP484 LED307-2S NW 179W DWL P7 0-10 | - |
| 919306035441 | BRP484 LED307-2S NW 179W DWL P7 0-10 M | - |
| 919306035451 | BRP484 LED328-2S NW 182W DWL-S P7 0-10 | - |
| 919306035461 | BRP484 LED351-2S NW 196W DWL-S P7 0-10 | - |
| 919306035721 | BRP484 LED266/NW 176W II DML PSR P7 EXP | LED-HP |
| 919306035731 | BRP484 LED290/NW 191W II DML PSR P7 EXP | LED-HP |
| 919306035781 | BRP484 LED266/NW 176W II DWL PSR P7 EXP | LED-HP |
| 919306035791 | BRP484 LED290/NW 191W II DWL PSR P7 EXP | LED-HP |
| 919306032891 | BRP486 LED351 NW 195W DWL P7 0-10 | LED-HP |
| 919306032901 | BRP486 LED351 NW 195W DML P7 0-10 | LED-HP |
| 919306032911 | BRP486 LED351 CW 195W DWL P7 0-10 | LED-HP |
| 919306032921 | BRP486 LED351 CW 195W DML P7 0-10 | LED-HP |
| 919306035551 | BRP486 LED351-2S NW 195W DML P7 0-10 | - |
| 919306035561 | BRP486 LED351-2S NW 195W DML P7 0-10 M | - |

| Order Code | Full Product Name | Lamp family code | Order Code | Full Product Name | Lamp family code |
|--------------|---|------------------|--------------|---|------------------|
| 919306035571 | BRP486 LED351-2S NW 195W DWL P7 0-10 | - | 919306034651 | BRP482 LED136-2S NW 76W DML P7 0-10 | - |
| 919306035581 | BRP486 LED351-2S NW 195W DWL P7 0-10 M | - | 919306034661 | BRP482 LED136-2S NW 76W DML P7 0-10 M | - |
| 919306035741 | BRP486 LED330/NW 213W II DML PSR P7 EXP | LED-HP | 919306034671 | BRP482 LED136-2S NW 76W DWL P7 0-10 | - |
| 919306035801 | BRP486 LED330/NW 213W II DWL PSR P7 EXP | LED-HP | 919306034681 | BRP482 LED136-2S NW 76W DWL P7 0-10 M | - |
| 820619285181 | BRP482 LED160-2S NW 92W DML P7 0-10 MX4 | - | 919306034711 | BRP482 LED147-2S NW 83W DML P7 0-10 | - |
| 919306032211 | BRP482 LED104 NW 56W DWL P7 0-10 | LED-HP | 919306034721 | BRP482 LED147-2S NW 83W DML P7 0-10 M | - |
| 919306032221 | BRP482 LED113 NW 61W DWL P7 0-10 | LED-HP | 919306034731 | BRP482 LED147-2S NW 83W DWL P7 0-10 | - |
| 919306032231 | BRP482 LED126 NW 70W DWL P7 0-10 | LED-HP | 919306034741 | BRP482 LED147-2S NW 83W DWL P7 0-10 M | - |
| 919306032241 | BRP482 LED136 NW 76W DWL P7 0-10 | LED-HP | 919306034771 | BRP482 LED160-2S NW 92W DML P7 0-10 | - |
| 919306032251 | BRP482 LED147 NW 83W DWL P7 0-10 | LED-HP | 919306034781 | BRP482 LED160-2S NW 92W DML P7 0-10 M | - |
| 919306032261 | BRP482 LED160 NW 92W DWL P7 0-10 | LED-HP | 919306034791 | BRP482 LED160-2S NW 92W DWL P7 0-10 | - |
| 919306032271 | BRP482 LED172 NW 100W DWL P7 0-10 | LED-HP | 919306034801 | BRP482 LED160-2S NW 92W DWL P7 0-10 M | - |
| 919306032281 | BRP482 LED179 NW 105W DWL P7 0-10 | LED-HP | 919306034831 | BRP482 LED172-2S NW 100W DML P7 0-10 | - |
| 919306032291 | BRP482 LED186 NW 110W DWL P7 0-10 | LED-HP | 919306034841 | BRP482 LED172-2S NW 100W DML P7 0-10 M | - |
| 919306032301 | BRP482 LED104 CW 56W DWL P7 0-10 | LED-HP | 919306034851 | BRP482 LED172-2S NW 100W DWL P7 0-10 | - |
| 919306032311 | BRP482 LED113 CW 61W DWL P7 0-10 | LED-HP | 919306034861 | BRP482 LED172-2S NW 100W DWL P7 0-10 M | - |
| 919306032321 | BRP482 LED126 CW 70W DWL P7 0-10 | LED-HP | 919306034891 | BRP482 LED179-2S NW 105W DML P7 0-10 | - |
| 919306032331 | BRP482 LED136 CW 76W DWL P7 0-10 | LED-HP | 919306034901 | BRP482 LED179-2S NW 105W DML P7 0-10 M | - |
| 919306032351 | BRP482 LED160 CW 92W DWL P7 0-10 | LED-HP | 919306034911 | BRP482 LED179-2S NW 105W DWL P7 0-10 | - |
| 919306032361 | BRP482 LED172 CW 100W DWL P7 0-10 | LED-HP | 919306034921 | BRP482 LED179-2S NW 105W DWL P7 0-10 M | - |
| 919306032371 | BRP482 LED179 CW 105W DWL P7 0-10 | LED-HP | 919306034951 | BRP482 LED186-2S NW 110W DML P7 0-10 | - |
| 919306032381 | BRP482 LED186 CW 110W DWL P7 0-10 | LED-HP | 919306034961 | BRP482 LED186-2S NW 110W DML P7 0-10 M | - |
| 919306032391 | BRP482 LED104 NW 56W DML P7 0-10 | LED-HP | 919306034971 | BRP482 LED186-2S NW 110W DWL P7 0-10 | - |
| 919306032401 | BRP482 LED113 NW 61W DML P7 0-10 | LED-HP | 919306034981 | BRP482 LED186-2S NW 110W DWL P7 0-10 M | - |
| 919306032411 | BRP482 LED126 NW 70W DML P7 0-10 | LED-HP | 919306034991 | BRP482 LED202-2S NW 118W DWL-S P7 0-10 | - |
| 919306032421 | BRP482 LED136 NW 76W DML P7 0-10 | LED-HP | 919306035001 | BRP482 LED216-2S NW 130W DWL-S P7 0-10 | - |
| 919306032431 | BRP482 LED147 NW 83W DML P7 0-10 | LED-HP | 919306035701 | BRP482 LED125/NW 84W II DML PSR P7 EXP | LED-HP |
| 919306032441 | BRP482 LED160 NW 92W DML P7 0-10 | LED-HP | 919306035711 | BRP482 LED168/NW 114W II DML PSR P7 EXP | LED-HP |
| 919306032451 | BRP482 LED172 NW 100W DML P7 0-10 | LED-HP | 919306035761 | BRP482 LED125/NW 84W II DWL PSR P7 EXP | LED-HP |
| 919306032461 | BRP482 LED179 NW 105W DML P7 0-10 | LED-HP | 919306035771 | BRP482 LED168/NW 114W II DWL PSR P7 EXP | LED-HP |
| 919306032471 | BRP482 LED186 NW 110W DML P7 0-10 | LED-HP | 919306032571 | BRP483 LED202 NW 113W DWL P7 0-10 | LED-HP |
| 919306032481 | BRP482 LED104 CW 56W DML P7 0-10 | LED-HP | 919306032581 | BRP483 LED216 NW 122W DWL P7 0-10 | LED-HP |
| 919306032491 | BRP482 LED113 CW 61W DML P7 0-10 | LED-HP | 919306032591 | BRP483 LED236 NW 136W DWL P7 0-10 | LED-HP |
| 919306032501 | BRP482 LED126 CW 70W DML P7 0-10 | LED-HP | 919306032601 | BRP483 LED255 NW 150W DWL P7 0-10 | LED-HP |
| 919306032511 | BRP482 LED136 CW 76W DML P7 0-10 | LED-HP | 919306032611 | BRP483 LED274 NW 165W DWL P7 0-10 | LED-HP |
| 919306032521 | BRP482 LED147 CW 83W DML P7 0-10 | LED-HP | 919306032621 | BRP483 LED202 NW 113W DML P7 0-10 | LED-HP |
| 919306032531 | BRP482 LED160 CW 92W DML P7 0-10 | LED-HP | 919306032631 | BRP483 LED216 NW 122W DML P7 0-10 | LED-HP |
| 919306032541 | BRP482 LED172 CW 100W DML P7 0-10 | LED-HP | 919306032641 | BRP483 LED236 NW 136W DML P7 0-10 | LED-HP |
| 919306032551 | BRP482 LED179 CW 105W DML P7 0-10 | LED-HP | 919306032651 | BRP483 LED255 NW 150W DML P7 0-10 | LED-HP |
| 919306032561 | BRP482 LED186 CW 110W DML P7 0-10 | LED-HP | 919306032661 | BRP483 LED274 NW 165W DML P7 0-10 | LED-HP |
| 919306034471 | BRP482 LED104-2S NW 56W DML P7 0-10 | - | 919306032671 | BRP483 LED202 CW 113W DWL P7 0-10 | LED-HP |
| 919306034481 | BRP482 LED104-2S NW 56W DML P7 0-10 M | - | 919306032681 | BRP483 LED216 CW 122W DWL P7 0-10 | LED-HP |
| 919306034491 | BRP482 LED104-2S NW 56W DWL P7 0-10 | - | 919306032691 | BRP483 LED236 CW 136W DWL P7 0-10 | LED-HP |
| 919306034501 | BRP482 LED104-2S NW 56W DWL P7 0-10 M | - | 919306032701 | BRP483 LED255 CW 150W DWL P7 0-10 | LED-HP |
| 919306034531 | BRP482 LED113-2S NW 61W DML P7 0-10 | - | 919306032711 | BRP483 LED274 CW 165W DWL P7 0-10 | LED-HP |
| 919306034541 | BRP482 LED113-2S NW 61W DML P7 0-10 M | - | 919306032721 | BRP483 LED202 CW 113W DML P7 0-10 | LED-HP |
| 919306034551 | BRP482 LED113-2S NW 61W DWL P7 0-10 | - | 919306032731 | BRP483 LED216 CW 122W DML P7 0-10 | LED-HP |
| 919306034561 | BRP482 LED113-2S NW 61W DWL P7 0-10 M | - | 919306032741 | BRP483 LED236 CW 136W DML P7 0-10 | LED-HP |
| 919306034591 | BRP482 LED126-2S NW 70W DML P7 0-10 | - | 919306032751 | BRP483 LED255 CW 150W DML P7 0-10 | LED-HP |
| 919306034601 | BRP482 LED126-2S NW 70W DML P7 0-10 M | - | 919306032761 | BRP483 LED274 CW 165W DML P7 0-10 | LED-HP |
| 919306034611 | BRP482 LED126-2S NW 70W DWL P7 0-10 | - | 919306035031 | BRP483 LED202-2S NW 113W DML P7 0-10 | - |
| 919306034621 | BRP482 LED126-2S NW 70W DWL P7 0-10 M | - | 919306035041 | BRP483 LED202-2S NW 113W DML P7 0-10 M | - |

| Order Code | Full Product Name | Lamp family code |
|--------------|--|------------------|
| 919306035051 | BRP483 LED202-2S NW 113W DWL P7 0-10 | - |
| 919306035061 | BRP483 LED202-2S NW 113W DWL P7 0-10 M | - |
| 919306035091 | BRP483 LED216-2S NW 122W DML P7 0-10 | - |
| 919306035101 | BRP483 LED216-2S NW 122W DML P7 0-10 M | - |
| 919306035111 | BRP483 LED216-2S NW 122W DWL P7 0-10 | - |
| 919306035121 | BRP483 LED216-2S NW 122W DWL P7 0-10 M | - |
| 919306035151 | BRP483 LED236-2S NW 136W DML P7 0-10 | - |
| 919306035161 | BRP483 LED236-2S NW 136W DML P7 0-10 M | - |
| 919306035171 | BRP483 LED236-2S NW 136W DWL P7 0-10 | - |
| 919306035181 | BRP483 LED236-2S NW 136W DWL P7 0-10 M | - |
| 919306035211 | BRP483 LED255-2S NW 150W DML P7 0-10 | - |
| 919306035221 | BRP483 LED255-2S NW 150W DML P7 0-10 M | - |
| 919306035231 | BRP483 LED255-2S NW 150W DWL P7 0-10 | - |
| 919306035241 | BRP483 LED255-2S NW 150W DWL P7 0-10 M | - |
| 919306035271 | BRP483 LED274-2S NW 165W DML P7 0-10 | - |
| 919306035281 | BRP483 LED274-2S NW 165W DML P7 0-10 M | - |
| 919306035291 | BRP483 LED274-2S NW 165W DWL P7 0-10 | - |
| 919306035301 | BRP483 LED274-2S NW 165W DWL P7 0-10 M | - |
| 919306035311 | BRP483 LED292-2S NW 170W DWL-S P7 0-10 | - |
| 919306035321 | BRP483 LED307-2S NW 180W DWL-S P7 0-10 | - |
| 919306032851 | BRP485 LED328 NW 185W DWL P7 0-10 | LED-HP |
| 919306032861 | BRP485 LED328 NW 185W DML P7 0-10 | LED-HP |
| 919306032871 | BRP485 LED328 CW 185W DWL P7 0-10 | LED-HP |
| 919306032881 | BRP485 LED328 CW 185W DML P7 0-10 | LED-HP |
| 919306035491 | BRP485 LED328-2S NW 185W DML P7 0-10 | - |
| 919306035501 | BRP485 LED328-2S NW 185W DML P7 0-10 M | - |
| 919306035511 | BRP485 LED328-2S NW 185W DWL P7 0-10 | - |
| 919306035521 | BRP485 LED328-2S NW 185W DWL P7 0-10 M | - |
| 919306031971 | BRP481 LED43 NW 24W DWL P7 0-10 | LED-HP |
| 919306031981 | BRP481 LED51 NW 27W DWL P7 0-10 | LED-HP |
| 919306031991 | BRP481 LED60 NW 33W DWL P7 0-10 | LED-HP |
| 919306032001 | BRP481 LED73 NW 41W DWL P7 0-10 | LED-HP |
| 919306032011 | BRP481 LED85 NW 48W DWL P7 0-10 | LED-HP |
| 919306032021 | BRP481 LED96 NW 55W DWL P7 0-10 | LED-HP |
| 919306032031 | BRP481 LED43 CW 24W DWL P7 0-10 | LED-HP |
| 919306032051 | BRP481 LED60 CW 33W DWL P7 0-10 | LED-HP |
| 919306032061 | BRP481 LED73 CW 41W DWL P7 0-10 | LED-HP |
| 919306032071 | BRP481 LED85 CW 48W DWL P7 0-10 | LED-HP |
| 919306032081 | BRP481 LED96 CW 55W DWL P7 0-10 | LED-HP |
| 919306032091 | BRP481 LED43 NW 24W DML P7 0-10 | LED-HP |

| Order Code | Full Product Name | Lamp family code |
|--------------|---------------------------------------|------------------|
| 919306032101 | BRP481 LED51 NW 27W DML P7 0-10 | LED-HP |
| 919306032111 | BRP481 LED60 NW 33W DML P7 0-10 | LED-HP |
| 919306032121 | BRP481 LED73 NW 41W DML P7 0-10 | LED-HP |
| 919306032131 | BRP481 LED85 NW 48W DML P7 0-10 | LED-HP |
| 919306032141 | BRP481 LED96 NW 55W DML P7 0-10 | LED-HP |
| 919306032151 | BRP481 LED43 CW 24W DML P7 0-10 | LED-HP |
| 919306032161 | BRP481 LED51 CW 27W DML P7 0-10 | LED-HP |
| 919306032171 | BRP481 LED60 CW 33W DML P7 0-10 | LED-HP |
| 919306032181 | BRP481 LED73 CW 41W DML P7 0-10 | LED-HP |
| 919306032191 | BRP481 LED85 CW 48W DML P7 0-10 | LED-HP |
| 919306032201 | BRP481 LED96 CW 55W DML P7 0-10 | LED-HP |
| 919306034071 | BRP481 LED43-2S NW 24W DWL P7 0-10 M | - |
| 919306034081 | BRP481 LED104-2S NW 61W DWL-S P7 0-10 | - |
| 919306034091 | BRP481 LED113-2S NW 67W DWL-S P7 0-10 | - |
| 919306034121 | BRP481 LED43-2S NW 24W DML P7 0-10 | - |
| 919306034131 | BRP481 LED43-2S NW 24W DML P7 0-10 M | - |
| 919306034141 | BRP481 LED43-2S NW 24W DWL P7 0-10 | - |
| 919306034171 | BRP481 LED51-2S NW 27W DML P7 0-10 | - |
| 919306034181 | BRP481 LED51-2S NW 27W DML P7 0-10 M | - |
| 919306034191 | BRP481 LED51-2S NW 27W DWL P7 0-10 | - |
| 919306034201 | BRP481 LED51-2S NW 27W DWL P7 0-10 M | - |
| 919306034231 | BRP481 LED60-2S NW 33W DML P7 0-10 | - |
| 919306034241 | BRP481 LED60-2S NW 33W DML P7 0-10 M | - |
| 919306034251 | BRP481 LED60-2S NW 33W DWL P7 0-10 | - |
| 919306034261 | BRP481 LED60-2S NW 33W DWL P7 0-10 M | - |
| 919306034291 | BRP481 LED73-2S NW 41W DML P7 0-10 | - |
| 919306034301 | BRP481 LED73-2S NW 41W DML P7 0-10 M | - |
| 919306034311 | BRP481 LED73-2S NW 41W DWL P7 0-10 | - |
| 919306034321 | BRP481 LED73-2S NW 41W DWL P7 0-10 M | - |
| 919306034351 | BRP481 LED85-2S NW 48W DML P7 0-10 | - |
| 919306034361 | BRP481 LED85-2S NW 48W DML P7 0-10 M | - |
| 919306034371 | BRP481 LED85-2S NW 48W DWL P7 0-10 | - |
| 919306034381 | BRP481 LED85-2S NW 48W DWL P7 0-10 M | - |
| 919306034411 | BRP481 LED96-2S NW 55W DML P7 0-10 | - |
| 919306034421 | BRP481 LED96-2S NW 55W DML P7 0-10 M | - |
| 919306034431 | BRP481 LED96-2S NW 55W DWL P7 0-10 | - |
| 919306034441 | BRP481 LED96-2S NW 55W DWL P7 0-10 M | - |
| 919306035691 | BRP481 LED84/NW 54W II DML PSR P7 EXP | LED-HP |
| 919306035751 | BRP481 LED84/NW 54W II DWL PSR P7 EXP | LED-HP |

Light Technical

| Order Code | Full Product Name | Correlated Color Temperature (Nom) | Color | | | Number of light sources | Standard tilt angle side entry |
|--------------|-----------------------------------|------------------------------------|-----------------------|---------------------------------|---------------|-------------------------|--------------------------------|
| | | | rendering index (CRI) | Luminous Efficacy (rated) (Nom) | Luminous Flux | | |
| 919306032771 | BRP484 LED292 NW 169W DWL P7 0-10 | 4000 K | >70 | 175.74 lm/W | 29,200 lumen | 4 | 0° |
| 919306032781 | BRP484 LED307 NW 179W DWL P7 0-10 | 4000 K | >70 | 173.89 lm/W | 30,700 lumen | 4 | 0° |
| 919306032791 | BRP484 LED292 NW 169W DML P7 0-10 | 4000 K | >70 | 175.74 lm/W | 29,200 lumen | 4 | 0° |
| 919306032801 | BRP484 LED307 NW 179W DML P7 0-10 | 4000 K | >70 | 173.89 lm/W | 30,700 lumen | 4 | 0° |
| 919306032811 | BRP484 LED292 CW 169W DWL P7 0-10 | 5000 K | >70 | 175.74 lm/W | 29,200 lumen | 4 | 0° |
| 919306032821 | BRP484 LED307 CW 179W DWL P7 0-10 | 5000 K | >70 | 173.89 lm/W | 30,700 lumen | 4 | 0° |

| Order Code | Full Product Name | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) | | Number of light sources | Standard tilt angle side entry |
|--------------|---|------------------------------------|-----------------------------|---------------------------|---------------|-------------------------|--------------------------------|
| | | | | (Nom) | Luminous Flux | | |
| 919306032831 | BRP484 LED292 CW 169W DML P7 0-10 | 5000 K | >70 | 175.74 lm/W | 29,200 lumen | 4 | 0° |
| 919306032841 | BRP484 LED307 CW 179W DML P7 0-10 | 5000 K | >70 | 173.89 lm/W | 30,700 lumen | 4 | 0° |
| 919306035351 | BRP484 LED292-2S NW 169W DML P7 0-10 | 4000 K | 70 | 173 lm/W | 29,200 lumen | - | 0° |
| 919306035361 | BRP484 LED292-2S NW 169W DML P7 0-10 M | 4000 K | 70 | 173 lm/W | 29,200 lumen | - | 0° |
| 919306035371 | BRP484 LED292-2S NW 169W DWL P7 0-10 | 4000 K | 70 | 173 lm/W | 29,200 lumen | - | 0° |
| 919306035381 | BRP484 LED292-2S NW 169W DWL P7 0-10 M | 4000 K | 70 | 173 lm/W | 29,200 lumen | - | 0° |
| 919306035411 | BRP484 LED307-2S NW 179W DML P7 0-10 | 4000 K | 70 | 172 lm/W | 30,700 lumen | - | 0° |
| 919306035421 | BRP484 LED307-2S NW 179W DML P7 0-10 M | 4000 K | 70 | 172 lm/W | 30,700 lumen | - | 0° |
| 919306035431 | BRP484 LED307-2S NW 179W DWL P7 0-10 | 4000 K | 70 | 172 lm/W | 30,700 lumen | - | 0° |
| 919306035441 | BRP484 LED307-2S NW 179W DWL P7 0-10 M | 4000 K | 70 | 172 lm/W | 30,700 lumen | - | 0° |
| 919306035451 | BRP484 LED328-2S NW 182W DWL-S P7 0-10 | 4000 K | 70 | 180 lm/W | 32,800 lumen | - | 0° |
| 919306035461 | BRP484 LED351-2S NW 196W DWL-S P7 0-10 | 4000 K | 70 | 179 lm/W | 35,100 lumen | - | 0° |
| 919306035721 | BRP484 LED266/NW 176W II DML PSR P7 EXP | 4000 K | >70 | 159.7 lm/W | 26,950 lumen | - | 0°+5°-5° |
| 919306035731 | BRP484 LED290/NW 191W II DML PSR P7 EXP | 4000 K | >70 | 156.4 lm/W | 29,060 lumen | - | 0°+5°-5° |
| 919306035781 | BRP484 LED266/NW 176W II DWL PSR P7 EXP | 4000 K | >70 | 157.9 lm/W | 26,690 lumen | - | 0°+5°-5° |
| 919306035791 | BRP484 LED290/NW 191W II DWL PSR P7 EXP | 4000 K | >70 | 154.3 lm/W | 28,617 lumen | - | 0°+5°-5° |
| 919306032891 | BRP486 LED351 NW 195W DWL P7 0-10 | 4000 K | >70 | 184.7 lm/W | 35,100 lumen | 6 | 0° |
| 919306032901 | BRP486 LED351 NW 195W DML P7 0-10 | 4000 K | >70 | 184.7 lm/W | 35,100 lumen | 6 | 0° |
| 919306032911 | BRP486 LED351 CW 195W DWL P7 0-10 | 5000 K | >70 | 184.7 lm/W | 35,100 lumen | 6 | 0° |
| 919306032921 | BRP486 LED351 CW 195W DML P7 0-10 | 5000 K | >70 | 184.7 lm/W | 35,100 lumen | 6 | 0° |
| 919306035551 | BRP486 LED351-2S NW 195W DML P7 0-10 | 4000 K | 70 | 180 lm/W | 35,100 lumen | - | 0° |
| 919306035561 | BRP486 LED351-2S NW 195W DML P7 0-10 M | 4000 K | 70 | 180 lm/W | 35,100 lumen | - | 0° |
| 919306035571 | BRP486 LED351-2S NW 195W DWL P7 0-10 | 4000 K | 70 | 180 lm/W | 35,100 lumen | - | 0° |
| 919306035581 | BRP486 LED351-2S NW 195W DWL P7 0-10 M | 4000 K | 70 | 180 lm/W | 35,100 lumen | - | 0° |
| 919306035741 | BRP486 LED330/NW 213W II DML PSR P7 EXP | 4000 K | >70 | 163.3 lm/W | 33,740 lumen | - | 0°+5°-5° |
| 919306035801 | BRP486 LED330/NW 213W II DWL PSR P7 EXP | 4000 K | >70 | 161.5 lm/W | 33,400 lumen | - | 0°+5°-5° |
| 820619285181 | BRP482 LED160-2S NW 92W DML P7 0-10 MX4 | 4000 K | 70 | 174 lm/W | 16,000 lumen | - | 0° |
| 919306032211 | BRP482 LED104 NW 56W DWL P7 0-10 | 4000 K | >70 | 187.39 lm/W | 10,400 lumen | 2 | 0° |
| 919306032221 | BRP482 LED113 NW 61W DWL P7 0-10 | 4000 K | >70 | 186.09 lm/W | 11,300 lumen | 2 | 0° |
| 919306032231 | BRP482 LED126 NW 70W DWL P7 0-10 | 4000 K | >70 | 183.54 lm/W | 12,600 lumen | 2 | 0° |
| 919306032241 | BRP482 LED136 NW 76W DWL P7 0-10 | 4000 K | >70 | 181.38 lm/W | 13,600 lumen | 2 | 0° |
| 919306032251 | BRP482 LED147 NW 83W DWL P7 0-10 | 4000 K | >70 | 178.67 lm/W | 14,700 lumen | 2 | 0° |
| 919306032261 | BRP482 LED160 NW 92W DWL P7 0-10 | 4000 K | >70 | 175.9 lm/W | 16,000 lumen | 2 | 0° |
| 919306032271 | BRP482 LED172 NW 100W DWL P7 0-10 | 4000 K | >70 | 172.65 lm/W | 17,200 lumen | 2 | 0° |
| 919306032281 | BRP482 LED179 NW 105W DWL P7 0-10 | 4000 K | >70 | 170.32 lm/W | 17,900 lumen | 2 | 0° |
| 919306032291 | BRP482 LED186 NW 110W DWL P7 0-10 | 4000 K | >70 | 168.55 lm/W | 18,600 lumen | 2 | 0° |
| 919306032301 | BRP482 LED104 CW 56W DWL P7 0-10 | 5000 K | >70 | 187.39 lm/W | 10,400 lumen | 2 | 0° |
| 919306032311 | BRP482 LED113 CW 61W DWL P7 0-10 | 5000 K | >70 | 186.09 lm/W | 11,300 lumen | 2 | 0° |
| 919306032321 | BRP482 LED126 CW 70W DWL P7 0-10 | 5000 K | >70 | 183.54 lm/W | 12,600 lumen | 2 | 0° |
| 919306032331 | BRP482 LED136 CW 76W DWL P7 0-10 | 5000 K | >70 | 181.38 lm/W | 13,600 lumen | 2 | 0° |
| 919306032351 | BRP482 LED160 CW 92W DWL P7 0-10 | 5000 K | >70 | 175.9 lm/W | 16,000 lumen | 2 | 0° |
| 919306032361 | BRP482 LED172 CW 100W DWL P7 0-10 | 5000 K | >70 | 172.65 lm/W | 17,200 lumen | 2 | 0° |
| 919306032371 | BRP482 LED179 CW 105W DWL P7 0-10 | 5000 K | >70 | 170.32 lm/W | 17,900 lumen | 2 | 0° |
| 919306032381 | BRP482 LED186 CW 110W DWL P7 0-10 | 5000 K | >70 | 168.55 lm/W | 18,600 lumen | 2 | 0° |
| 919306032391 | BRP482 LED104 NW 56W DML P7 0-10 | 4000 K | >70 | 187.39 lm/W | 10,400 lumen | 2 | 0° |
| 919306032401 | BRP482 LED113 NW 61W DML P7 0-10 | 4000 K | >70 | 186.09 lm/W | 11,300 lumen | 2 | 0° |
| 919306032411 | BRP482 LED126 NW 70W DML P7 0-10 | 4000 K | >70 | 183.54 lm/W | 12,600 lumen | 2 | 0° |
| 919306032421 | BRP482 LED136 NW 76W DML P7 0-10 | 4000 K | >70 | 181.38 lm/W | 13,600 lumen | 2 | 0° |
| 919306032431 | BRP482 LED147 NW 83W DML P7 0-10 | 4000 K | >70 | 178.67 lm/W | 14,700 lumen | 2 | 0° |
| 919306032441 | BRP482 LED160 NW 92W DML P7 0-10 | 4000 K | >70 | 175.9 lm/W | 16,000 lumen | 2 | 0° |

| Order Code | Full Product Name | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) | | Number of light sources | Standard tilt angle side entry |
|--------------|--|------------------------------------|-----------------------------|---------------------------|---------------|-------------------------|--------------------------------|
| | | | | (Nom) | Luminous Flux | | |
| 919306032451 | BRP482 LED172 NW 100W DML P7 0-10 | 4000 K | >70 | 172.65 lm/W | 17,200 lumen | 2 | 0° |
| 919306032461 | BRP482 LED179 NW 105W DML P7 0-10 | 4000 K | >70 | 170.32 lm/W | 17,900 lumen | 2 | 0° |
| 919306032471 | BRP482 LED186 NW 110W DML P7 0-10 | 4000 K | >70 | 168.55 lm/W | 18,600 lumen | 2 | 0° |
| 919306032481 | BRP482 LED104 CW 56W DML P7 0-10 | 5000 K | >70 | 187.39 lm/W | 10,400 lumen | 2 | 0° |
| 919306032491 | BRP482 LED113 CW 61W DML P7 0-10 | 5000 K | >70 | 186.09 lm/W | 11,300 lumen | 2 | 0° |
| 919306032501 | BRP482 LED126 CW 70W DML P7 0-10 | 5000 K | >70 | 183.54 lm/W | 12,600 lumen | 2 | 0° |
| 919306032511 | BRP482 LED136 CW 76W DML P7 0-10 | 5000 K | >70 | 181.38 lm/W | 13,600 lumen | 2 | 0° |
| 919306032521 | BRP482 LED147 CW 83W DML P7 0-10 | 5000 K | >70 | 178.67 lm/W | 14,700 lumen | 2 | 0° |
| 919306032531 | BRP482 LED160 CW 92W DML P7 0-10 | 5000 K | >70 | 175.9 lm/W | 16,000 lumen | 2 | 0° |
| 919306032541 | BRP482 LED172 CW 100W DML P7 0-10 | 5000 K | >70 | 172.65 lm/W | 17,200 lumen | 2 | 0° |
| 919306032551 | BRP482 LED179 CW 105W DML P7 0-10 | 5000 K | >70 | 170.32 lm/W | 17,900 lumen | 2 | 0° |
| 919306032561 | BRP482 LED186 CW 110W DML P7 0-10 | 5000 K | >70 | 168.55 lm/W | 18,600 lumen | 2 | 0° |
| 919306034471 | BRP482 LED104-2S NW 56W DML P7 0-10 | 4000 K | 70 | 186 lm/W | 10,400 lumen | - | 0° |
| 919306034481 | BRP482 LED104-2S NW 56W DML P7 0-10 M | 4000 K | 70 | 186 lm/W | 10,400 lumen | - | 0° |
| 919306034491 | BRP482 LED104-2S NW 56W DWL P7 0-10 | 4000 K | 70 | 186 lm/W | 10,400 lumen | - | 0° |
| 919306034501 | BRP482 LED104-2S NW 56W DWL P7 0-10 M | 4000 K | 70 | 186 lm/W | 10,400 lumen | - | 0° |
| 919306034531 | BRP482 LED113-2S NW 61W DML P7 0-10 | 4000 K | 70 | 185 lm/W | 11,300 lumen | - | 0° |
| 919306034541 | BRP482 LED113-2S NW 61W DML P7 0-10 M | 4000 K | 70 | 185 lm/W | 11,300 lumen | - | 0° |
| 919306034551 | BRP482 LED113-2S NW 61W DWL P7 0-10 | 4000 K | 70 | 185 lm/W | 11,300 lumen | - | 0° |
| 919306034561 | BRP482 LED113-2S NW 61W DWL P7 0-10 M | 4000 K | 70 | 185 lm/W | 11,300 lumen | - | 0° |
| 919306034591 | BRP482 LED126-2S NW 70W DML P7 0-10 | 4000 K | 70 | 180 lm/W | 12,600 lumen | - | 0° |
| 919306034601 | BRP482 LED126-2S NW 70W DML P7 0-10 M | 4000 K | 70 | 180 lm/W | 12,600 lumen | - | 0° |
| 919306034611 | BRP482 LED126-2S NW 70W DWL P7 0-10 | 4000 K | 70 | 180 lm/W | 12,600 lumen | - | 0° |
| 919306034621 | BRP482 LED126-2S NW 70W DWL P7 0-10 M | 4000 K | 70 | 180 lm/W | 12,600 lumen | - | 0° |
| 919306034651 | BRP482 LED136-2S NW 76W DML P7 0-10 | 4000 K | 70 | 178 lm/W | 13,600 lumen | - | 0° |
| 919306034661 | BRP482 LED136-2S NW 76W DML P7 0-10 M | 4000 K | 70 | 178 lm/W | 13,600 lumen | - | 0° |
| 919306034671 | BRP482 LED136-2S NW 76W DWL P7 0-10 | 4000 K | 70 | 178 lm/W | 13,600 lumen | - | 0° |
| 919306034681 | BRP482 LED136-2S NW 76W DWL P7 0-10 M | 4000 K | 70 | 178 lm/W | 13,600 lumen | - | 0° |
| 919306034711 | BRP482 LED147-2S NW 83W DML P7 0-10 | 4000 K | 70 | 177 lm/W | 14,700 lumen | - | 0° |
| 919306034721 | BRP482 LED147-2S NW 83W DML P7 0-10 M | 4000 K | 70 | 177 lm/W | 14,700 lumen | - | 0° |
| 919306034731 | BRP482 LED147-2S NW 83W DWL P7 0-10 | 4000 K | 70 | 177 lm/W | 14,700 lumen | - | 0° |
| 919306034741 | BRP482 LED147-2S NW 83W DWL P7 0-10 M | 4000 K | 70 | 177 lm/W | 14,700 lumen | - | 0° |
| 919306034771 | BRP482 LED160-2S NW 92W DML P7 0-10 | 4000 K | 70 | 174 lm/W | 16,000 lumen | - | 0° |
| 919306034781 | BRP482 LED160-2S NW 92W DML P7 0-10 M | 4000 K | 70 | 174 lm/W | 16,000 lumen | - | 0° |
| 919306034791 | BRP482 LED160-2S NW 92W DWL P7 0-10 | 4000 K | 70 | 174 lm/W | 16,000 lumen | - | 0° |
| 919306034801 | BRP482 LED160-2S NW 92W DWL P7 0-10 M | 4000 K | 70 | 174 lm/W | 16,000 lumen | - | 0° |
| 919306034831 | BRP482 LED172-2S NW 100W DML P7 0-10 | 4000 K | 70 | 172 lm/W | 17,200 lumen | - | 0° |
| 919306034841 | BRP482 LED172-2S NW 100W DML P7 0-10 M | 4000 K | 70 | 172 lm/W | 17,200 lumen | - | 0° |
| 919306034851 | BRP482 LED172-2S NW 100W DWL P7 0-10 | 4000 K | 70 | 172 lm/W | 17,200 lumen | - | 0° |
| 919306034861 | BRP482 LED172-2S NW 100W DWL P7 0-10 M | 4000 K | 70 | 172 lm/W | 17,200 lumen | - | 0° |
| 919306034891 | BRP482 LED179-2S NW 105W DML P7 0-10 | 4000 K | 70 | 170 lm/W | 17,900 lumen | - | 0° |
| 919306034901 | BRP482 LED179-2S NW 105W DML P7 0-10 M | 4000 K | 70 | 170 lm/W | 17,900 lumen | - | 0° |
| 919306034911 | BRP482 LED179-2S NW 105W DWL P7 0-10 | 4000 K | 70 | 170 lm/W | 17,900 lumen | - | 0° |
| 919306034921 | BRP482 LED179-2S NW 105W DWL P7 0-10 M | 4000 K | 70 | 170 lm/W | 17,900 lumen | - | 0° |
| 919306034951 | BRP482 LED186-2S NW 110W DML P7 0-10 | 4000 K | 70 | 169 lm/W | 18,600 lumen | - | 0° |
| 919306034961 | BRP482 LED186-2S NW 110W DML P7 0-10 M | 4000 K | 70 | 169 lm/W | 18,600 lumen | - | 0° |
| 919306034971 | BRP482 LED186-2S NW 110W DWL P7 0-10 | 4000 K | 70 | 169 lm/W | 18,600 lumen | - | 0° |
| 919306034981 | BRP482 LED186-2S NW 110W DWL P7 0-10 M | 4000 K | 70 | 169 lm/W | 18,600 lumen | - | 0° |
| 919306034991 | BRP482 LED202-2S NW 118W DWL-S P7 0-10 | 4000 K | 70 | 171 lm/W | 20,200 lumen | - | 0° |

| Order Code | Full Product Name | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) | | Number of light sources | Standard tilt angle side entry |
|--------------|---|------------------------------------|-----------------------------|---------------------------|---------------|-------------------------|--------------------------------|
| | | | | (Nom) | Luminous Flux | | |
| 91930603500 | BRP482 LED216-2S NW 130W DWL-S P7 0-10 | 4000 K | 70 | 179 lm/W | 21,600 lumen | - | 0° |
| 1 | | | | | | | |
| 919306035701 | BRP482 LED125/NW 84W II DML PSR P7 EXP | 4000 K | >70 | 158.9 lm/W | 13,380 lumen | - | 0°+5°-5° |
| 919306035711 | BRP482 LED168/NW 114W II DML PSR P7 EXP | 4000 K | >70 | 150.5 lm/W | 17,080 lumen | - | 0°+5°-5° |
| 919306035761 | BRP482 LED125/NW 84W II DWL PSR P7 EXP | 4000 K | >70 | 155.2 lm/W | 13,070 lumen | - | 0°+5°-5° |
| 919306035771 | BRP482 LED168/NW 114W II DWL PSR P7 EXP | 4000 K | >70 | 147.8 lm/W | 16,770 lumen | - | 0°+5°-5° |
| 919306032571 | BRP483 LED202 NW 113W DWL P7 0-10 | 4000 K | >70 | 182.11 lm/W | 20,200 lumen | 3 | 0° |
| 919306032581 | BRP483 LED216 NW 122W DWL P7 0-10 | 4000 K | >70 | 178.9 lm/W | 21,600 lumen | 3 | 0° |
| 919306032591 | BRP483 LED236 NW 136W DWL P7 0-10 | 4000 K | >70 | 175.27 lm/W | 23,600 lumen | 3 | 0° |
| 919306032601 | BRP483 LED255 NW 150W DWL P7 0-10 | 4000 K | >70 | 172.1 lm/W | 25,500 lumen | 3 | 0° |
| 919306032611 | BRP483 LED274 NW 165W DWL P7 0-10 | 4000 K | >70 | 167.08 lm/W | 27,400 lumen | 3 | 0° |
| 919306032621 | BRP483 LED202 NW 113W DML P7 0-10 | 4000 K | >70 | 182.11 lm/W | 20,200 lumen | 3 | 0° |
| 919306032631 | BRP483 LED216 NW 122W DML P7 0-10 | 4000 K | >70 | 178.9 lm/W | 21,600 lumen | 3 | 0° |
| 919306032641 | BRP483 LED236 NW 136W DML P7 0-10 | 4000 K | >70 | 175.27 lm/W | 23,600 lumen | 3 | 0° |
| 919306032651 | BRP483 LED255 NW 150W DML P7 0-10 | 4000 K | >70 | 172.1 lm/W | 25,500 lumen | 3 | 0° |
| 919306032661 | BRP483 LED274 NW 165W DML P7 0-10 | 4000 K | >70 | 167.08 lm/W | 27,400 lumen | 3 | 0° |
| 919306032671 | BRP483 LED202 CW 113W DWL P7 0-10 | 5000 K | >70 | 182.11 lm/W | 20,200 lumen | 3 | 0° |
| 919306032681 | BRP483 LED216 CW 122W DWL P7 0-10 | 5000 K | >70 | 178.9 lm/W | 21,600 lumen | 3 | 0° |
| 919306032691 | BRP483 LED236 CW 136W DWL P7 0-10 | 5000 K | >70 | 175.27 lm/W | 23,600 lumen | 3 | 0° |
| 919306032701 | BRP483 LED255 CW 150W DWL P7 0-10 | 5000 K | >70 | 172.1 lm/W | 25,500 lumen | 3 | 0° |
| 919306032711 | BRP483 LED274 CW 165W DWL P7 0-10 | 5000 K | >70 | 167.08 lm/W | 27,400 lumen | 3 | 0° |
| 919306032721 | BRP483 LED202 CW 113W DML P7 0-10 | 5000 K | >70 | 182.11 lm/W | 20,200 lumen | 3 | 0° |
| 919306032731 | BRP483 LED216 CW 122W DML P7 0-10 | 5000 K | >70 | 178.9 lm/W | 21,600 lumen | 3 | 0° |
| 919306032741 | BRP483 LED236 CW 136W DML P7 0-10 | 5000 K | >70 | 175.27 lm/W | 23,600 lumen | 3 | 0° |
| 919306032751 | BRP483 LED255 CW 150W DML P7 0-10 | 5000 K | >70 | 172.1 lm/W | 25,500 lumen | 3 | 0° |
| 919306032761 | BRP483 LED274 CW 165W DML P7 0-10 | 5000 K | >70 | 167.08 lm/W | 27,400 lumen | 3 | 0° |
| 919306035031 | BRP483 LED202-2S NW 113W DML P7 0-10 | 4000 K | 70 | 179 lm/W | 20,200 lumen | - | 0° |
| 919306035041 | BRP483 LED202-2S NW 113W DML P7 0-10 M | 4000 K | 70 | 179 lm/W | 20,200 lumen | - | 0° |
| 919306035051 | BRP483 LED202-2S NW 113W DWL P7 0-10 | 4000 K | 70 | 179 lm/W | 20,200 lumen | - | 0° |
| 919306035061 | BRP483 LED202-2S NW 113W DWL P7 0-10 M | 4000 K | 70 | 179 lm/W | 20,200 lumen | - | 0° |
| 919306035091 | BRP483 LED216-2S NW 122W DML P7 0-10 | 4000 K | 70 | 177 lm/W | 21,600 lumen | - | 0° |
| 919306035101 | BRP483 LED216-2S NW 122W DML P7 0-10 M | 4000 K | 70 | 177 lm/W | 21,600 lumen | - | 0° |
| 919306035111 | BRP483 LED216-2S NW 122W DWL P7 0-10 | 4000 K | 70 | 177 lm/W | 21,600 lumen | - | 0° |
| 919306035121 | BRP483 LED216-2S NW 122W DWL P7 0-10 M | 4000 K | 70 | 177 lm/W | 21,600 lumen | - | 0° |
| 919306035151 | BRP483 LED236-2S NW 136W DML P7 0-10 | 4000 K | 70 | 174 lm/W | 23,600 lumen | - | 0° |
| 919306035161 | BRP483 LED236-2S NW 136W DML P7 0-10 M | 4000 K | 70 | 174 lm/W | 23,600 lumen | - | 0° |
| 919306035171 | BRP483 LED236-2S NW 136W DWL P7 0-10 | 4000 K | 70 | 174 lm/W | 23,600 lumen | - | 0° |
| 919306035181 | BRP483 LED236-2S NW 136W DWL P7 0-10 M | 4000 K | 70 | 174 lm/W | 23,600 lumen | - | 0° |
| 919306035211 | BRP483 LED255-2S NW 150W DML P7 0-10 | 4000 K | 70 | 170 lm/W | 25,500 lumen | - | 0° |
| 919306035221 | BRP483 LED255-2S NW 150W DML P7 0-10 M | 4000 K | 70 | 170 lm/W | 25,500 lumen | - | 0° |
| 919306035231 | BRP483 LED255-2S NW 150W DWL P7 0-10 | 4000 K | 70 | 170 lm/W | 25,500 lumen | - | 0° |
| 919306035241 | BRP483 LED255-2S NW 150W DWL P7 0-10 M | 4000 K | 70 | 170 lm/W | 25,500 lumen | - | 0° |
| 919306035271 | BRP483 LED274-2S NW 165W DML P7 0-10 | 4000 K | 70 | 166 lm/W | 27,400 lumen | - | 0° |
| 919306035281 | BRP483 LED274-2S NW 165W DML P7 0-10 M | 4000 K | 70 | 166 lm/W | 27,400 lumen | - | 0° |
| 919306035291 | BRP483 LED274-2S NW 165W DWL P7 0-10 | 4000 K | 70 | 166 lm/W | 27,400 lumen | - | 0° |
| 919306035301 | BRP483 LED274-2S NW 165W DWL P7 0-10 M | 4000 K | 70 | 166 lm/W | 27,400 lumen | - | 0° |
| 919306035311 | BRP483 LED292-2S NW 170W DWL-S P7 0-10 | 4000 K | 70 | 172 lm/W | 29,200 lumen | - | 0° |
| 919306035321 | BRP483 LED307-2S NW 180W DWL-S P7 0-10 | 4000 K | 70 | 171 lm/W | 30,700 lumen | - | 0° |
| 919306032851 | BRP485 LED328 NW 185W DWL P7 0-10 | 4000 K | >70 | 181.22 lm/W | 32,800 lumen | 5 | 0° |
| 919306032861 | BRP485 LED328 NW 185W DML P7 0-10 | 4000 K | >70 | 181.22 lm/W | 32,800 lumen | 5 | 0° |

| Order Code | Full Product Name | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) | | Number of light sources | Standard tilt angle side entry |
|--------------|--|------------------------------------|-----------------------------|---------------------------|---------------|-------------------------|--------------------------------|
| | | | | (Nom) | Luminous Flux | | |
| 919306032871 | BRP485 LED328 CW 185W DWL P7 0-10 | 5000 K | >70 | 181.22 lm/W | 32,800 lumen | 5 | 0° |
| 919306032881 | BRP485 LED328 CW 185W DML P7 0-10 | 5000 K | >70 | 181.22 lm/W | 32,800 lumen | 5 | 0° |
| 919306035491 | BRP485 LED328-2S NW 185W DML P7 0-10 | 4000 K | 70 | 177 lm/W | 32,800 lumen | - | 0° |
| 919306035501 | BRP485 LED328-2S NW 185W DML P7 0-10 M | 4000 K | 70 | 177 lm/W | 32,800 lumen | - | 0° |
| 919306035511 | BRP485 LED328-2S NW 185W DWL P7 0-10 | 4000 K | 70 | 177 lm/W | 32,800 lumen | - | 0° |
| 919306035521 | BRP485 LED328-2S NW 185W DWL P7 0-10 M | 4000 K | 70 | 177 lm/W | 32,800 lumen | - | 0° |
| 919306031971 | BRP481 LED43 NW 24W DWL P7 0-10 | 4000 K | >70 | 179.16 lm/W | 4,500 lumen | 1 | 0° |
| 919306031981 | BRP481 LED51 NW 27W DWL P7 0-10 | 4000 K | >70 | 183.52 lm/W | 5,100 lumen | 1 | 0° |
| 919306031991 | BRP481 LED60 NW 33W DWL P7 0-10 | 4000 K | >70 | 180.56 lm/W | 6,100 lumen | 1 | 0° |
| 919306032001 | BRP481 LED73 NW 41W DWL P7 0-10 | 4000 K | >70 | 177.8 lm/W | 7,300 lumen | 1 | 0° |
| 919306032011 | BRP481 LED85 NW 48W DWL P7 0-10 | 4000 K | >70 | 175.24 lm/W | 8,500 lumen | 1 | 0° |
| 919306032021 | BRP481 LED96 NW 55W DWL P7 0-10 | 4000 K | >70 | 170.68 lm/W | 9,600 lumen | 1 | 0° |
| 919306032031 | BRP481 LED43 CW 24W DWL P7 0-10 | 5000 K | >70 | 179.16 lm/W | 4,500 lumen | 1 | 0° |
| 919306032051 | BRP481 LED60 CW 33W DWL P7 0-10 | 5000 K | >70 | 180.56 lm/W | 6,100 lumen | 1 | 0° |
| 919306032061 | BRP481 LED73 CW 41W DWL P7 0-10 | 5000 K | >70 | 177.8 lm/W | 7,300 lumen | 1 | 0° |
| 919306032071 | BRP481 LED85 CW 48W DWL P7 0-10 | 5000 K | >70 | 175.24 lm/W | 8,500 lumen | 1 | 0° |
| 919306032081 | BRP481 LED96 CW 55W DWL P7 0-10 | 5000 K | >70 | 170.68 lm/W | 9,600 lumen | 1 | 0° |
| 919306032091 | BRP481 LED43 NW 24W DML P7 0-10 | 4000 K | >70 | 179.16 lm/W | 4,500 lumen | 1 | 0° |
| 919306032101 | BRP481 LED51 NW 27W DML P7 0-10 | 4000 K | >70 | 183.52 lm/W | 5,100 lumen | 1 | 0° |
| 919306032111 | BRP481 LED60 NW 33W DML P7 0-10 | 4000 K | >70 | 180.56 lm/W | 6,100 lumen | 1 | 0° |
| 919306032121 | BRP481 LED73 NW 41W DML P7 0-10 | 4000 K | >70 | 177.8 lm/W | 7,300 lumen | 1 | 0° |
| 919306032131 | BRP481 LED85 NW 48W DML P7 0-10 | 4000 K | >70 | 175.24 lm/W | 8,500 lumen | 1 | 0° |
| 919306032141 | BRP481 LED96 NW 55W DML P7 0-10 | 4000 K | >70 | 170.68 lm/W | 9,600 lumen | 1 | 0° |
| 919306032151 | BRP481 LED43 CW 24W DML P7 0-10 | 5000 K | >70 | 179.16 lm/W | 4,500 lumen | 1 | 0° |
| 919306032161 | BRP481 LED51 CW 27W DML P7 0-10 | 5000 K | >70 | 183.52 lm/W | 5,100 lumen | 1 | 0° |
| 919306032171 | BRP481 LED60 CW 33W DML P7 0-10 | 5000 K | >70 | 180.56 lm/W | 6,100 lumen | 1 | 0° |
| 919306032181 | BRP481 LED73 CW 41W DML P7 0-10 | 5000 K | >70 | 177.8 lm/W | 7,300 lumen | 1 | 0° |
| 919306032191 | BRP481 LED85 CW 48W DML P7 0-10 | 5000 K | >70 | 175.24 lm/W | 8,500 lumen | 1 | 0° |
| 919306032201 | BRP481 LED96 CW 55W DML P7 0-10 | 5000 K | >70 | 170.68 lm/W | 9,600 lumen | 1 | 0° |
| 919306034071 | BRP481 LED43-2S NW 24W DWL P7 0-10 M | 4000 K | 70 | 179 lm/W | 4,300 lumen | - | 0° |
| 919306034081 | BRP481 LED104-2S NW 61W DWL-S P7 0-10 | 4000 K | 70 | 170 lm/W | 10,400 lumen | - | 0° |
| 919306034091 | BRP481 LED113-2S NW 67W DWL-S P7 0-10 | 4000 K | 70 | 169 lm/W | 11,300 lumen | - | 0° |
| 919306034121 | BRP481 LED43-2S NW 24W DML P7 0-10 | 4000 K | 70 | 179 lm/W | 4,300 lumen | - | 0° |
| 919306034131 | BRP481 LED43-2S NW 24W DML P7 0-10 M | 4000 K | 70 | 179 lm/W | 4,300 lumen | - | 0° |
| 919306034141 | BRP481 LED43-2S NW 24W DWL P7 0-10 | 4000 K | 70 | 179 lm/W | 4,300 lumen | - | 0° |
| 919306034171 | BRP481 LED51-2S NW 27W DML P7 0-10 | 4000 K | 70 | 189 lm/W | 5,100 lumen | - | 0° |
| 919306034181 | BRP481 LED51-2S NW 27W DML P7 0-10 M | 4000 K | 70 | 189 lm/W | 5,100 lumen | - | 0° |
| 919306034191 | BRP481 LED51-2S NW 27W DWL P7 0-10 | 4000 K | 70 | 189 lm/W | 5,100 lumen | - | 0° |
| 919306034201 | BRP481 LED51-2S NW 27W DWL P7 0-10 M | 4000 K | 70 | 189 lm/W | 5,100 lumen | - | 0° |
| 919306034231 | BRP481 LED60-2S NW 33W DML P7 0-10 | 4000 K | 70 | 182 lm/W | 6,000 lumen | - | 0° |
| 919306034241 | BRP481 LED60-2S NW 33W DML P7 0-10 M | 4000 K | 70 | 182 lm/W | 6,000 lumen | - | 0° |
| 919306034251 | BRP481 LED60-2S NW 33W DWL P7 0-10 | 4000 K | 70 | 182 lm/W | 6,000 lumen | - | 0° |
| 919306034261 | BRP481 LED60-2S NW 33W DWL P7 0-10 M | 4000 K | 70 | 182 lm/W | 6,000 lumen | - | 0° |
| 919306034291 | BRP481 LED73-2S NW 41W DML P7 0-10 | 4000 K | 70 | 178 lm/W | 7,300 lumen | - | 0° |
| 919306034301 | BRP481 LED73-2S NW 41W DML P7 0-10 M | 4000 K | 70 | 178 lm/W | 7,300 lumen | - | 0° |
| 919306034311 | BRP481 LED73-2S NW 41W DWL P7 0-10 | 4000 K | 70 | 178 lm/W | 7,300 lumen | - | 0° |
| 919306034321 | BRP481 LED73-2S NW 41W DWL P7 0-10 M | 4000 K | 70 | 178 lm/W | 7,300 lumen | - | 0° |
| 919306034351 | BRP481 LED85-2S NW 48W DML P7 0-10 | 4000 K | 70 | 177 lm/W | 8,500 lumen | - | 0° |
| 919306034361 | BRP481 LED85-2S NW 48W DML P7 0-10 M | 4000 K | 70 | 177 lm/W | 8,500 lumen | - | 0° |
| 919306034371 | BRP481 LED85-2S NW 48W DWL P7 0-10 | 4000 K | 70 | 177 lm/W | 8,500 lumen | - | 0° |

| Order Code | Full Product Name | Correlated Color Temperature (Nom) | Color rendering | | Luminous Efficacy (rated) | | Number of light sources | Standard tilt angle side entry |
|--------------|---------------------------------------|------------------------------------|-----------------|------------|---------------------------|---|-------------------------|--------------------------------|
| | | | index (CRI) | (Nom) | Luminous Flux | | | |
| 919306034381 | BRP481 LED85-2S NW 48W DWL P7 0-10 M | 4000 K | 70 | 177 lm/W | 8,500 lumen | - | 0° | |
| 919306034411 | BRP481 LED96-2S NW 55W DML P7 0-10 | 4000 K | 70 | 175 lm/W | 9,600 lumen | - | 0° | |
| 919306034421 | BRP481 LED96-2S NW 55W DML P7 0-10 M | 4000 K | 70 | 175 lm/W | 9,600 lumen | - | 0° | |
| 919306034431 | BRP481 LED96-2S NW 55W DWL P7 0-10 | 4000 K | 70 | 175 lm/W | 9,600 lumen | - | 0° | |
| 919306034441 | BRP481 LED96-2S NW 55W DWL P7 0-10 M | 4000 K | 70 | 175 lm/W | 9,600 lumen | - | 0° | |
| 919306035691 | BRP481 LED84/NW 54W II DML PSR P7 EXP | 4000 K | >70 | 150.9 lm/W | 8,420 lumen | - | 0°+5°-5° | |
| 919306035751 | BRP481 LED84/NW 54W II DWL PSR P7 EXP | 4000 K | >70 | 149.5 lm/W | 8,340 lumen | - | 0°+5°-5° | |

Operating and Electrical

| Order Code | Full Product Name | Power Consumption | Order Code | Full Product Name | Power Consumption |
|--------------|---|-------------------|--------------|---------------------------------------|-------------------|
| 919306032771 | BRP484 LED292 NW 169W DWL P7 0-10 | 166.56 W | 919306032271 | BRP482 LED172 NW 100W DWL P7 0-10 | 99.99 W |
| 919306032781 | BRP484 LED307 NW 179W DWL P7 0-10 | 176.68 W | 919306032281 | BRP482 LED179 NW 105W DWL P7 0-10 | 105.44 W |
| 919306032791 | BRP484 LED292 NW 169W DML P7 0-10 | 166.56 W | 919306032291 | BRP482 LED186 NW 110W DWL P7 0-10 | 110.75 W |
| 919306032801 | BRP484 LED307 NW 179W DML P7 0-10 | 176.68 W | 919306032301 | BRP482 LED104 CW 56W DWL P7 0-10 | 55.88 W |
| 919306032811 | BRP484 LED292 CW 169W DWL P7 0-10 | 166.56 W | 919306032311 | BRP482 LED113 CW 61W DWL P7 0-10 | 60.74 W |
| 919306032821 | BRP484 LED307 CW 179W DWL P7 0-10 | 176.68 W | 919306032321 | BRP482 LED126 CW 70W DWL P7 0-10 | 68.97 W |
| 919306032831 | BRP484 LED292 CW 169W DML P7 0-10 | 166.56 W | 919306032331 | BRP482 LED136 CW 76W DWL P7 0-10 | 75.28 W |
| 919306032841 | BRP484 LED307 CW 179W DML P7 0-10 | 176.68 W | 919306032351 | BRP482 LED160 CW 92W DWL P7 0-10 | 91.3 W |
| 919306035351 | BRP484 LED292-2S NW 169W DML P7 0-10 | 169 W | 919306032361 | BRP482 LED172 CW 100W DWL P7 0-10 | 99.99 W |
| 919306035361 | BRP484 LED292-2S NW 169W DML P7 0-10 M | 169 W | 919306032371 | BRP482 LED179 CW 105W DWL P7 0-10 | 105.44 W |
| 919306035371 | BRP484 LED292-2S NW 169W DWL P7 0-10 | 169 W | 919306032381 | BRP482 LED186 CW 110W DWL P7 0-10 | 110.75 W |
| 919306035381 | BRP484 LED292-2S NW 169W DWL P7 0-10 M | 169 W | 919306032391 | BRP482 LED104 NW 56W DML P7 0-10 | 55.88 W |
| 919306035411 | BRP484 LED307-2S NW 179W DML P7 0-10 | 179 W | 919306032401 | BRP482 LED113 NW 61W DML P7 0-10 | 60.74 W |
| 919306035421 | BRP484 LED307-2S NW 179W DML P7 0-10 M | 179 W | 919306032411 | BRP482 LED126 NW 70W DML P7 0-10 | 68.97 W |
| 919306035431 | BRP484 LED307-2S NW 179W DWL P7 0-10 | 179 W | 919306032421 | BRP482 LED136 NW 76W DML P7 0-10 | 75.28 W |
| 919306035441 | BRP484 LED307-2S NW 179W DWL P7 0-10 M | 179 W | 919306032431 | BRP482 LED147 NW 83W DML P7 0-10 | 82.77 W |
| 919306035451 | BRP484 LED328-2S NW 182W DWL-S P7 0-10 | 182 W | 919306032441 | BRP482 LED160 NW 92W DML P7 0-10 | 91.3 W |
| 919306035461 | BRP484 LED351-2S NW 196W DWL-S P7 0-10 | 196 W | 919306032451 | BRP482 LED172 NW 100W DML P7 0-10 | 99.99 W |
| 919306035721 | BRP484 LED266/NW 176W II DML PSR P7 EXP | 168.8 W | 919306032461 | BRP482 LED179 NW 105W DML P7 0-10 | 105.44 W |
| 919306035731 | BRP484 LED290/NW 191W II DML PSR P7 EXP | 185.8 W | 919306032471 | BRP482 LED186 NW 110W DML P7 0-10 | 110.75 W |
| 919306035781 | BRP484 LED266/NW 176W II DWL PSR P7 EXP | 168.8 W | 919306032481 | BRP482 LED104 CW 56W DML P7 0-10 | 55.88 W |
| 919306035791 | BRP484 LED290/NW 191W II DWL PSR P7 EXP | 185.8 W | 919306032491 | BRP482 LED113 CW 61W DML P7 0-10 | 60.74 W |
| 919306032891 | BRP486 LED351 NW 195W DWL P7 0-10 | 190.25 W | 919306032501 | BRP482 LED126 CW 70W DML P7 0-10 | 68.97 W |
| 919306032901 | BRP486 LED351 NW 195W DML P7 0-10 | 190.25 W | 919306032511 | BRP482 LED136 CW 76W DML P7 0-10 | 75.28 W |
| 919306032911 | BRP486 LED351 CW 195W DWL P7 0-10 | 190.25 W | 919306032521 | BRP482 LED147 CW 83W DML P7 0-10 | 82.77 W |
| 919306032921 | BRP486 LED351 CW 195W DML P7 0-10 | 190.25 W | 919306032531 | BRP482 LED160 CW 92W DML P7 0-10 | 91.3 W |
| 919306035551 | BRP486 LED351-2S NW 195W DML P7 0-10 | 195 W | 919306032541 | BRP482 LED172 CW 100W DML P7 0-10 | 99.99 W |
| 919306035561 | BRP486 LED351-2S NW 195W DML P7 0-10 M | 195 W | 919306032551 | BRP482 LED179 CW 105W DML P7 0-10 | 105.44 W |
| 919306035571 | BRP486 LED351-2S NW 195W DWL P7 0-10 | 195 W | 919306032561 | BRP482 LED186 CW 110W DML P7 0-10 | 110.75 W |
| 919306035581 | BRP486 LED351-2S NW 195W DWL P7 0-10 M | 195 W | 919306034471 | BRP482 LED104-2S NW 56W DML P7 0-10 | 56 W |
| 919306035741 | BRP486 LED330/NW 213W II DML PSR P7 EXP | 206.6 W | 919306034481 | BRP482 LED104-2S NW 56W DML P7 0-10 M | 56 W |
| 919306035801 | BRP486 LED330/NW 213W II DWL PSR P7 EXP | 206.6 W | 919306034491 | BRP482 LED104-2S NW 56W DWL P7 0-10 | 56 W |
| 820619285181 | BRP482 LED160-2S NW 92W DML P7 0-10 MX4 | 92 W | 919306034501 | BRP482 LED104-2S NW 56W DWL P7 0-10 M | 56 W |
| 919306032211 | BRP482 LED104 NW 56W DWL P7 0-10 | 55.88 W | 919306034531 | BRP482 LED113-2S NW 61W DML P7 0-10 | 61 W |
| 919306032221 | BRP482 LED113 NW 61W DWL P7 0-10 | 60.74 W | 919306034541 | BRP482 LED113-2S NW 61W DML P7 0-10 M | 61 W |
| 919306032231 | BRP482 LED126 NW 70W DWL P7 0-10 | 68.97 W | 919306034551 | BRP482 LED113-2S NW 61W DWL P7 0-10 | 61 W |
| 919306032241 | BRP482 LED136 NW 76W DWL P7 0-10 | 75.28 W | 919306034561 | BRP482 LED113-2S NW 61W DWL P7 0-10 M | 61 W |
| 919306032251 | BRP482 LED147 NW 83W DWL P7 0-10 | 82.77 W | 919306034591 | BRP482 LED126-2S NW 70W DML P7 0-10 | 70 W |
| 919306032261 | BRP482 LED160 NW 92W DWL P7 0-10 | 91.3 W | 919306034601 | BRP482 LED126-2S NW 70W DML P7 0-10 M | 70 W |

| Order Code | Full Product Name | Power Consumption |
|--------------|---|-------------------|
| 919306034611 | BRP482 LED126-2S NW 70W DWL P7 0-10 | 70 W |
| 919306034621 | BRP482 LED126-2S NW 70W DWL P7 0-10 M | 70 W |
| 919306034651 | BRP482 LED136-2S NW 76W DML P7 0-10 | 76 W |
| 919306034661 | BRP482 LED136-2S NW 76W DML P7 0-10 M | 76 W |
| 919306034671 | BRP482 LED136-2S NW 76W DWL P7 0-10 | 76 W |
| 919306034681 | BRP482 LED136-2S NW 76W DWL P7 0-10 M | 76 W |
| 919306034711 | BRP482 LED147-2S NW 83W DML P7 0-10 | 83 W |
| 919306034721 | BRP482 LED147-2S NW 83W DML P7 0-10 M | 83 W |
| 919306034731 | BRP482 LED147-2S NW 83W DWL P7 0-10 | 83 W |
| 919306034741 | BRP482 LED147-2S NW 83W DWL P7 0-10 M | 83 W |
| 919306034771 | BRP482 LED160-2S NW 92W DML P7 0-10 | 92 W |
| 919306034781 | BRP482 LED160-2S NW 92W DML P7 0-10 M | 92 W |
| 919306034791 | BRP482 LED160-2S NW 92W DWL P7 0-10 | 92 W |
| 919306034801 | BRP482 LED160-2S NW 92W DWL P7 0-10 M | 92 W |
| 919306034831 | BRP482 LED172-2S NW 100W DML P7 0-10 | 100 W |
| 919306034841 | BRP482 LED172-2S NW 100W DML P7 0-10 M | 100 W |
| 919306034851 | BRP482 LED172-2S NW 100W DWL P7 0-10 | 100 W |
| 919306034861 | BRP482 LED172-2S NW 100W DWL P7 0-10 M | 100 W |
| 919306034891 | BRP482 LED179-2S NW 105W DML P7 0-10 | 105 W |
| 919306034901 | BRP482 LED179-2S NW 105W DML P7 0-10 M | 105 W |
| 919306034911 | BRP482 LED179-2S NW 105W DWL P7 0-10 | 105 W |
| 919306034921 | BRP482 LED179-2S NW 105W DWL P7 0-10 M | 105 W |
| 919306034951 | BRP482 LED186-2S NW 110W DML P7 0-10 | 110 W |
| 919306034961 | BRP482 LED186-2S NW 110W DML P7 0-10 M | 110 W |
| 919306034971 | BRP482 LED186-2S NW 110W DWL P7 0-10 | 110 W |
| 919306034981 | BRP482 LED186-2S NW 110W DWL P7 0-10 M | 110 W |
| 919306034991 | BRP482 LED202-2S NW 118W DWL-S P7 0-10 | 118 W |
| 919306035001 | BRP482 LED216-2S NW 130W DWL-S P7 0-10 | 130 W |
| 919306035701 | BRP482 LED125/NW 84W II DML PSR P7 EXP | 84.2 W |
| 919306035711 | BRP482 LED168/NW 114W II DML PSR P7 EXP | 113.5 W |
| 919306035761 | BRP482 LED125/NW 84W II DWL PSR P7 EXP | 84.2 W |
| 919306035771 | BRP482 LED168/NW 114W II DWL PSR P7 EXP | 113.5 W |
| 919306032571 | BRP483 LED202 NW 113W DWL P7 0-10 | 111.4 W |
| 919306032581 | BRP483 LED216 NW 122W DWL P7 0-10 | 120.96 W |
| 919306032591 | BRP483 LED236 NW 136W DWL P7 0-10 | 134.89 W |
| 919306032601 | BRP483 LED255 NW 150W DWL P7 0-10 | 148.46 W |
| 919306032611 | BRP483 LED274 NW 165W DWL P7 0-10 | 164.31 W |
| 919306032621 | BRP483 LED202 NW 113W DML P7 0-10 | 111.4 W |
| 919306032631 | BRP483 LED216 NW 122W DML P7 0-10 | 120.96 W |
| 919306032641 | BRP483 LED236 NW 136W DML P7 0-10 | 134.89 W |
| 919306032651 | BRP483 LED255 NW 150W DML P7 0-10 | 148.46 W |
| 919306032661 | BRP483 LED274 NW 165W DML P7 0-10 | 164.31 W |
| 919306032671 | BRP483 LED202 CW 113W DWL P7 0-10 | 111.4 W |
| 919306032681 | BRP483 LED216 CW 122W DWL P7 0-10 | 120.96 W |
| 919306032691 | BRP483 LED236 CW 136W DWL P7 0-10 | 134.89 W |
| 919306032701 | BRP483 LED255 CW 150W DWL P7 0-10 | 148.46 W |
| 919306032711 | BRP483 LED274 CW 165W DWL P7 0-10 | 164.31 W |
| 919306032721 | BRP483 LED202 CW 113W DML P7 0-10 | 111.4 W |
| 919306032731 | BRP483 LED216 CW 122W DML P7 0-10 | 120.96 W |
| 919306032741 | BRP483 LED236 CW 136W DML P7 0-10 | 134.89 W |
| 919306032751 | BRP483 LED255 CW 150W DML P7 0-10 | 148.46 W |
| 919306032761 | BRP483 LED274 CW 165W DML P7 0-10 | 164.31 W |

| Order Code | Full Product Name | Power Consumption |
|--------------|--|-------------------|
| 919306035031 | BRP483 LED202-2S NW 113W DML P7 0-10 | 113 W |
| 919306035041 | BRP483 LED202-2S NW 113W DML P7 0-10 M | 113 W |
| 919306035051 | BRP483 LED202-2S NW 113W DWL P7 0-10 | 113 W |
| 919306035061 | BRP483 LED202-2S NW 113W DWL P7 0-10 M | 113 W |
| 919306035091 | BRP483 LED216-2S NW 122W DML P7 0-10 | 122 W |
| 919306035101 | BRP483 LED216-2S NW 122W DML P7 0-10 M | 122 W |
| 919306035111 | BRP483 LED216-2S NW 122W DWL P7 0-10 | 122 W |
| 919306035121 | BRP483 LED216-2S NW 122W DWL P7 0-10 M | 122 W |
| 919306035151 | BRP483 LED236-2S NW 136W DML P7 0-10 | 136 W |
| 919306035161 | BRP483 LED236-2S NW 136W DML P7 0-10 M | 136 W |
| 919306035171 | BRP483 LED236-2S NW 136W DWL P7 0-10 | 136 W |
| 919306035181 | BRP483 LED236-2S NW 136W DWL P7 0-10 M | 136 W |
| 919306035211 | BRP483 LED255-2S NW 150W DML P7 0-10 | 150 W |
| 919306035221 | BRP483 LED255-2S NW 150W DML P7 0-10 M | 150 W |
| 919306035231 | BRP483 LED255-2S NW 150W DWL P7 0-10 | 150 W |
| 919306035241 | BRP483 LED255-2S NW 150W DWL P7 0-10 M | 150 W |
| 919306035271 | BRP483 LED274-2S NW 165W DML P7 0-10 | 165 W |
| 919306035281 | BRP483 LED274-2S NW 165W DML P7 0-10 M | 165 W |
| 919306035291 | BRP483 LED274-2S NW 165W DWL P7 0-10 | 165 W |
| 919306035301 | BRP483 LED274-2S NW 165W DWL P7 0-10 M | 165 W |
| 919306035311 | BRP483 LED292-2S NW 170W DWL-S P7 0-10 | 170 W |
| 919306035321 | BRP483 LED307-2S NW 180W DWL-S P7 0-10 | 180 W |
| 919306032851 | BRP485 LED328 NW 185W DWL P7 0-10 | 181.44 W |
| 919306032861 | BRP485 LED328 NW 185W DML P7 0-10 | 181.44 W |
| 919306032871 | BRP485 LED328 CW 185W DWL P7 0-10 | 181.44 W |
| 919306032881 | BRP485 LED328 CW 185W DML P7 0-10 | 181.44 W |
| 919306035491 | BRP485 LED328-2S NW 185W DML P7 0-10 | 185 W |
| 919306035501 | BRP485 LED328-2S NW 185W DML P7 0-10 M | 185 W |
| 919306035511 | BRP485 LED328-2S NW 185W DWL P7 0-10 | 185 W |
| 919306035521 | BRP485 LED328-2S NW 185W DWL P7 0-10 M | 185 W |
| 919306031971 | BRP481 LED43 NW 24W DWL P7 0-10 | 25.36 W |
| 919306031981 | BRP481 LED51 NW 27W DWL P7 0-10 | 27.81 W |
| 919306031991 | BRP481 LED60 NW 33W DWL P7 0-10 | 33.73 W |
| 919306032001 | BRP481 LED73 NW 41W DWL P7 0-10 | 41.57 W |
| 919306032011 | BRP481 LED85 NW 48W DWL P7 0-10 | 48.99 W |
| 919306032021 | BRP481 LED96 NW 55W DWL P7 0-10 | 56.37 W |
| 919306032031 | BRP481 LED43 CW 24W DWL P7 0-10 | 25.36 W |
| 919306032051 | BRP481 LED60 CW 33W DWL P7 0-10 | 33.73 W |
| 919306032061 | BRP481 LED73 CW 41W DWL P7 0-10 | 41.57 W |
| 919306032071 | BRP481 LED85 CW 48W DWL P7 0-10 | 48.99 W |
| 919306032081 | BRP481 LED96 CW 55W DWL P7 0-10 | 56.37 W |
| 919306032091 | BRP481 LED43 NW 24W DML P7 0-10 | 25.36 W |
| 919306032101 | BRP481 LED51 NW 27W DML P7 0-10 | 27.81 W |
| 919306032111 | BRP481 LED60 NW 33W DML P7 0-10 | 33.73 W |
| 919306032121 | BRP481 LED73 NW 41W DML P7 0-10 | 41.57 W |
| 919306032131 | BRP481 LED85 NW 48W DML P7 0-10 | 48.99 W |
| 919306032141 | BRP481 LED96 NW 55W DML P7 0-10 | 56.37 W |
| 919306032151 | BRP481 LED43 CW 24W DML P7 0-10 | 25.36 W |
| 919306032161 | BRP481 LED51 CW 27W DML P7 0-10 | 27.81 W |
| 919306032171 | BRP481 LED60 CW 33W DML P7 0-10 | 33.73 W |
| 919306032181 | BRP481 LED73 CW 41W DML P7 0-10 | 41.57 W |
| 919306032191 | BRP481 LED85 CW 48W DML P7 0-10 | 48.99 W |

| Order Code | Full Product Name | Power Consumption |
|--------------|---------------------------------------|-------------------|
| 919306032201 | BRP481 LED96 CW 55W DML P7 0-10 | 56.37 W |
| 919306034071 | BRP481 LED43-2S NW 24W DWL P7 0-10 M | 24 W |
| 919306034081 | BRP481 LED104-2S NW 61W DWL-S P7 0-10 | 61 W |
| 919306034091 | BRP481 LED113-2S NW 67W DWL-S P7 0-10 | 67 W |
| 919306034121 | BRP481 LED43-2S NW 24W DML P7 0-10 | 24 W |
| 919306034131 | BRP481 LED43-2S NW 24W DML P7 0-10 M | 24 W |
| 919306034141 | BRP481 LED43-2S NW 24W DWL P7 0-10 | 24 W |
| 919306034171 | BRP481 LED51-2S NW 27W DML P7 0-10 | 27 W |
| 919306034181 | BRP481 LED51-2S NW 27W DML P7 0-10 M | 27 W |
| 919306034191 | BRP481 LED51-2S NW 27W DWL P7 0-10 | 27 W |
| 919306034201 | BRP481 LED51-2S NW 27W DWL P7 0-10 M | 27 W |
| 919306034231 | BRP481 LED60-2S NW 33W DML P7 0-10 | 33 W |
| 919306034241 | BRP481 LED60-2S NW 33W DML P7 0-10 M | 33 W |
| 919306034251 | BRP481 LED60-2S NW 33W DWL P7 0-10 | 33 W |
| 919306034261 | BRP481 LED60-2S NW 33W DWL P7 0-10 M | 33 W |

| Order Code | Full Product Name | Power Consumption |
|--------------|---------------------------------------|-------------------|
| 919306034291 | BRP481 LED73-2S NW 41W DML P7 0-10 | 41 W |
| 919306034301 | BRP481 LED73-2S NW 41W DML P7 0-10 M | 41 W |
| 919306034311 | BRP481 LED73-2S NW 41W DWL P7 0-10 | 41 W |
| 919306034321 | BRP481 LED73-2S NW 41W DWL P7 0-10 M | 41 W |
| 919306034351 | BRP481 LED85-2S NW 48W DML P7 0-10 | 48 W |
| 919306034361 | BRP481 LED85-2S NW 48W DML P7 0-10 M | 48 W |
| 919306034371 | BRP481 LED85-2S NW 48W DWL P7 0-10 | 48 W |
| 919306034381 | BRP481 LED85-2S NW 48W DWL P7 0-10 M | 48 W |
| 919306034411 | BRP481 LED96-2S NW 55W DML P7 0-10 | 55 W |
| 919306034421 | BRP481 LED96-2S NW 55W DML P7 0-10 M | 55 W |
| 919306034431 | BRP481 LED96-2S NW 55W DWL P7 0-10 | 55 W |
| 919306034441 | BRP481 LED96-2S NW 55W DWL P7 0-10 M | 55 W |
| 919306035691 | BRP481 LED84/NW 54W II DML PSR P7 EXP | 55.8 W |
| 919306035751 | BRP481 LED84/NW 54W II DWL PSR P7 EXP | 55.8 W |

Temperature

| Order Code | Full Product Name | Ambient temperature range |
|--------------|--|---------------------------|
| 919306032771 | BRP484 LED292 NW 169W DWL P7 0-10 | -5 to +50 °C |
| 919306032781 | BRP484 LED307 NW 179W DWL P7 0-10 | -5 to +50 °C |
| 919306032791 | BRP484 LED292 NW 169W DML P7 0-10 | -5 to +50 °C |
| 919306032801 | BRP484 LED307 NW 179W DML P7 0-10 | -5 to +50 °C |
| 919306032811 | BRP484 LED292 CW 169W DWL P7 0-10 | -5 to +50 °C |
| 919306032821 | BRP484 LED307 CW 179W DWL P7 0-10 | -5 to +50 °C |
| 919306032831 | BRP484 LED292 CW 169W DML P7 0-10 | -5 to +50 °C |
| 919306032841 | BRP484 LED307 CW 179W DML P7 0-10 | -5 to +50 °C |
| 919306035351 | BRP484 LED292-2S NW 169W DML P7 0-10 | -20 to +50 °C |
| 919306035361 | BRP484 LED292-2S NW 169W DML P7 0-10 M | -20 to +50 °C |
| 919306035371 | BRP484 LED292-2S NW 169W DWL P7 0-10 | -20 to +50 °C |
| 919306035381 | BRP484 LED292-2S NW 169W DWL P7 0-10 M | -20 to +50 °C |
| 919306035411 | BRP484 LED307-2S NW 179W DML P7 0-10 | -20 to +50 °C |
| 919306035421 | BRP484 LED307-2S NW 179W DML P7 0-10 M | -20 to +50 °C |
| 919306035431 | BRP484 LED307-2S NW 179W DWL P7 0-10 | -20 to +50 °C |
| 919306035441 | BRP484 LED307-2S NW 179W DWL P7 0-10 M | -20 to +50 °C |
| 919306035451 | BRP484 LED328-2S NW 182W DWL-S P7 0-10 | -20 to +50 °C |
| 919306035461 | BRP484 LED351-2S NW 196W DWL-S P7 0-10 | -20 to +50 °C |
| 919306035721 | BRP484 LED266/NW 176W II DML PSR P7 EXP | -20 to +50 °C |
| 919306035731 | BRP484 LED290/NW 191W II DML PSR P7 EXP | -20 to +50 °C |

| Order Code | Full Product Name | Ambient temperature range |
|--------------|--|---------------------------|
| 919306035781 | BRP484 LED266/NW 176W II DWL PSR P7 EXP | -20 to +50 °C |
| 919306035791 | BRP484 LED290/NW 191W II DWL PSR P7 EXP | -20 to +50 °C |
| 919306032891 | BRP486 LED351 NW 195W DWL P7 0-10 | -5 to +50 °C |
| 919306032901 | BRP486 LED351 NW 195W DML P7 0-10 | -5 to +50 °C |
| 919306032911 | BRP486 LED351 CW 195W DWL P7 0-10 | -5 to +50 °C |
| 919306032921 | BRP486 LED351 CW 195W DML P7 0-10 | -5 to +50 °C |
| 919306035551 | BRP486 LED351-2S NW 195W DML P7 0-10 | -20 to +50 °C |
| 919306035561 | BRP486 LED351-2S NW 195W DML P7 0-10 M | -20 to +50 °C |
| 919306035571 | BRP486 LED351-2S NW 195W DWL P7 0-10 | -20 to +50 °C |
| 919306035581 | BRP486 LED351-2S NW 195W DWL P7 0-10 M | -20 to +50 °C |
| 919306035741 | BRP486 LED330/NW 213W II DML PSR P7 EXP | -20 to +50 °C |
| 919306035801 | BRP486 LED330/NW 213W II DWL PSR P7 EXP | -20 to +50 °C |
| 820619285181 | BRP482 LED160-2S NW 92W DML P7 0-10 MX4 | -20 to +50 °C |
| 919306032211 | BRP482 LED104 NW 56W DWL P7 0-10 | -5 to +50 °C |
| 919306032221 | BRP482 LED113 NW 61W DWL P7 0-10 | -5 to +50 °C |
| 919306032231 | BRP482 LED126 NW 70W DWL P7 0-10 | -5 to +50 °C |
| 919306032241 | BRP482 LED136 NW 76W DWL P7 0-10 | -5 to +50 °C |
| 919306032251 | BRP482 LED147 NW 83W DWL P7 0-10 | -5 to +50 °C |
| 919306032261 | BRP482 LED160 NW 92W DWL P7 0-10 | -5 to +50 °C |
| 919306032271 | BRP482 LED172 NW 100W DWL P7 0-10 | -5 to +50 °C |
| 919306032281 | BRP482 LED179 NW 105W DWL P7 0-10 | -5 to +50 °C |
| 919306032291 | BRP482 LED186 NW 110W DWL P7 0-10 | -5 to +50 °C |
| 919306032301 | BRP482 LED104 CW 56W DWL P7 0-10 | -5 to +50 °C |
| 919306032311 | BRP482 LED113 CW 61W DWL P7 0-10 | -5 to +50 °C |

| Order Code | Full Product Name | Ambient temperature range |
|--------------|--|---------------------------|
| 919306032321 | BRP482 LED126 CW 70W DWL P7 0-10 | -5 to +50 °C |
| 919306032331 | BRP482 LED136 CW 76W DWL P7 0-10 | -5 to +50 °C |
| 919306032351 | BRP482 LED160 CW 92W DWL P7 0-10 | -5 to +50 °C |
| 919306032361 | BRP482 LED172 CW 100W DWL P7 0-10 | -5 to +50 °C |
| 919306032371 | BRP482 LED179 CW 105W DWL P7 0-10 | -5 to +50 °C |
| 919306032381 | BRP482 LED186 CW 110W DWL P7 0-10 | -5 to +50 °C |
| 919306032391 | BRP482 LED104 NW 56W DML P7 0-10 | -5 to +50 °C |
| 919306032401 | BRP482 LED113 NW 61W DML P7 0-10 | -5 to +50 °C |
| 919306032411 | BRP482 LED126 NW 70W DML P7 0-10 | -5 to +50 °C |
| 919306032421 | BRP482 LED136 NW 76W DML P7 0-10 | -5 to +50 °C |
| 919306032431 | BRP482 LED147 NW 83W DML P7 0-10 | -5 to +50 °C |
| 919306032441 | BRP482 LED160 NW 92W DML P7 0-10 | -5 to +50 °C |
| 919306032451 | BRP482 LED172 NW 100W DML P7 0-10 | -5 to +50 °C |
| 919306032461 | BRP482 LED179 NW 105W DML P7 0-10 | -5 to +50 °C |
| 919306032471 | BRP482 LED186 NW 110W DML P7 0-10 | -5 to +50 °C |
| 919306032481 | BRP482 LED104 CW 56W DML P7 0-10 | -5 to +50 °C |
| 919306032491 | BRP482 LED113 CW 61W DML P7 0-10 | -5 to +50 °C |
| 919306032501 | BRP482 LED126 CW 70W DML P7 0-10 | -5 to +50 °C |
| 919306032511 | BRP482 LED136 CW 76W DML P7 0-10 | -5 to +50 °C |
| 919306032521 | BRP482 LED147 CW 83W DML P7 0-10 | -5 to +50 °C |
| 919306032531 | BRP482 LED160 CW 92W DML P7 0-10 | -5 to +50 °C |
| 919306032541 | BRP482 LED172 CW 100W DML P7 0-10 | -5 to +50 °C |
| 919306032551 | BRP482 LED179 CW 105W DML P7 0-10 | -5 to +50 °C |
| 919306032561 | BRP482 LED186 CW 110W DML P7 0-10 | -5 to +50 °C |
| 919306034471 | BRP482 LED104-2S NW 56W DML P7 0-10 | -20 to +50 °C |
| 919306034481 | BRP482 LED104-2S NW 56W DML P7 0-10 M | -20 to +50 °C |
| 919306034491 | BRP482 LED104-2S NW 56W DWL P7 0-10 | -20 to +50 °C |
| 919306034501 | BRP482 LED104-2S NW 56W DWL P7 0-10 M | -20 to +50 °C |
| 919306034531 | BRP482 LED113-2S NW 61W DML P7 0-10 | -20 to +50 °C |
| 919306034541 | BRP482 LED113-2S NW 61W DML P7 0-10 M | -20 to +50 °C |
| 919306034551 | BRP482 LED113-2S NW 61W DWL P7 0-10 | -20 to +50 °C |
| 919306034561 | BRP482 LED113-2S NW 61W DWL P7 0-10 M | -20 to +50 °C |
| 919306034591 | BRP482 LED126-2S NW 70W DML P7 0-10 | -20 to +50 °C |
| 919306034601 | BRP482 LED126-2S NW 70W DML P7 0-10 M | -20 to +50 °C |
| 919306034611 | BRP482 LED126-2S NW 70W DWL P7 0-10 | -20 to +50 °C |
| 919306034621 | BRP482 LED126-2S NW 70W DWL P7 0-10 M | -20 to +50 °C |
| 919306034651 | BRP482 LED136-2S NW 76W DML P7 0-10 | -20 to +50 °C |
| 919306034661 | BRP482 LED136-2S NW 76W DML P7 0-10 M | -20 to +50 °C |
| 919306034671 | BRP482 LED136-2S NW 76W DWL P7 0-10 | -20 to +50 °C |

| Order Code | Full Product Name | Ambient temperature range |
|--------------|--|---------------------------|
| 919306034681 | BRP482 LED136-2S NW 76W DWL P7 0-10 M | -20 to +50 °C |
| 919306034711 | BRP482 LED147-2S NW 83W DML P7 0-10 | -20 to +50 °C |
| 919306034721 | BRP482 LED147-2S NW 83W DML P7 0-10 M | -20 to +50 °C |
| 919306034731 | BRP482 LED147-2S NW 83W DWL P7 0-10 | -20 to +50 °C |
| 919306034741 | BRP482 LED147-2S NW 83W DWL P7 0-10 M | -20 to +50 °C |
| 919306034771 | BRP482 LED160-2S NW 92W DML P7 0-10 | -20 to +50 °C |
| 919306034781 | BRP482 LED160-2S NW 92W DML P7 0-10 M | -20 to +50 °C |
| 919306034791 | BRP482 LED160-2S NW 92W DWL P7 0-10 | -20 to +50 °C |
| 919306034801 | BRP482 LED160-2S NW 92W DWL P7 0-10 M | -20 to +50 °C |
| 919306034831 | BRP482 LED172-2S NW 100W DML P7 0-10 | -20 to +50 °C |
| 919306034841 | BRP482 LED172-2S NW 100W DML P7 0-10 M | -20 to +50 °C |
| 919306034851 | BRP482 LED172-2S NW 100W DWL P7 0-10 | -20 to +50 °C |
| 919306034861 | BRP482 LED172-2S NW 100W DWL P7 0-10 M | -20 to +50 °C |
| 919306034891 | BRP482 LED179-2S NW 105W DML P7 0-10 | -20 to +50 °C |
| 919306034901 | BRP482 LED179-2S NW 105W DML P7 0-10 M | -20 to +50 °C |
| 919306034911 | BRP482 LED179-2S NW 105W DWL P7 0-10 | -20 to +50 °C |
| 919306034921 | BRP482 LED179-2S NW 105W DWL P7 0-10 M | -20 to +50 °C |
| 919306034951 | BRP482 LED186-2S NW 110W DML P7 0-10 | -20 to +50 °C |
| 919306034961 | BRP482 LED186-2S NW 110W DML P7 0-10 M | -20 to +50 °C |
| 919306034971 | BRP482 LED186-2S NW 110W DWL P7 0-10 | -20 to +50 °C |
| 919306034981 | BRP482 LED186-2S NW 110W DWL P7 0-10 M | -20 to +50 °C |
| 919306034991 | BRP482 LED202-2S NW 118W DWL-S P7 0-10 | -20 to +50 °C |
| 919306035001 | BRP482 LED216-2S NW 130W DWL-S P7 0-10 | -20 to +50 °C |
| 1 | | |
| 919306035701 | BRP482 LED125/NW 84W II DML PSR P7 EXP | -20 to +50 °C |
| 919306035711 | BRP482 LED168/NW 114W II DML PSR P7 EXP | -20 to +50 °C |
| 919306035761 | BRP482 LED125/NW 84W II DWL PSR P7 EXP | -20 to +50 °C |

| Order Code | Full Product Name | Ambient temperature range |
|--------------|---|---------------------------|
| 919306035771 | BRP482 LED168/NW 114W II DWL PSR P7 EXP | -20 to +50 °C |
| 919306032571 | BRP483 LED202 NW 113W DWL P7 0-10 | -5 to +50 °C |
| 919306032581 | BRP483 LED216 NW 122W DWL P7 0-10 | -5 to +50 °C |
| 919306032591 | BRP483 LED236 NW 136W DWL P7 0-10 | -5 to +50 °C |
| 919306032601 | BRP483 LED255 NW 150W DWL P7 0-10 | -5 to +50 °C |
| 919306032611 | BRP483 LED274 NW 165W DWL P7 0-10 | -5 to +50 °C |
| 919306032621 | BRP483 LED202 NW 113W DML P7 0-10 | -5 to +50 °C |
| 919306032631 | BRP483 LED216 NW 122W DML P7 0-10 | -5 to +50 °C |
| 919306032641 | BRP483 LED236 NW 136W DML P7 0-10 | -5 to +50 °C |
| 919306032651 | BRP483 LED255 NW 150W DML P7 0-10 | -5 to +50 °C |
| 919306032661 | BRP483 LED274 NW 165W DML P7 0-10 | -5 to +50 °C |
| 919306032671 | BRP483 LED202 CW 113W DWL P7 0-10 | -5 to +50 °C |
| 919306032681 | BRP483 LED216 CW 122W DWL P7 0-10 | -5 to +50 °C |
| 919306032691 | BRP483 LED236 CW 136W DWL P7 0-10 | -5 to +50 °C |
| 919306032701 | BRP483 LED255 CW 150W DWL P7 0-10 | -5 to +50 °C |
| 919306032711 | BRP483 LED274 CW 165W DWL P7 0-10 | -5 to +50 °C |
| 919306032721 | BRP483 LED202 CW 113W DML P7 0-10 | -5 to +50 °C |
| 919306032731 | BRP483 LED216 CW 122W DML P7 0-10 | -5 to +50 °C |
| 919306032741 | BRP483 LED236 CW 136W DML P7 0-10 | -5 to +50 °C |
| 919306032751 | BRP483 LED255 CW 150W DML P7 0-10 | -5 to +50 °C |
| 919306032761 | BRP483 LED274 CW 165W DML P7 0-10 | -5 to +50 °C |
| 919306035031 | BRP483 LED202-2S NW 113W DML P7 0-10 | -20 to +50 °C |
| 919306035041 | BRP483 LED202-2S NW 113W DML P7 0-10 M | -20 to +50 °C |
| 919306035051 | BRP483 LED202-2S NW 113W DWL P7 0-10 | -20 to +50 °C |
| 919306035061 | BRP483 LED202-2S NW 113W DWL P7 0-10 M | -20 to +50 °C |
| 919306035091 | BRP483 LED216-2S NW 122W DML P7 0-10 | -20 to +50 °C |
| 919306035101 | BRP483 LED216-2S NW 122W DML P7 0-10 M | -20 to +50 °C |
| 919306035111 | BRP483 LED216-2S NW 122W DWL P7 0-10 | -20 to +50 °C |
| 919306035121 | BRP483 LED216-2S NW 122W DWL P7 0-10 M | -20 to +50 °C |
| 919306035151 | BRP483 LED236-2S NW 136W DML P7 0-10 | -20 to +50 °C |
| 919306035161 | BRP483 LED236-2S NW 136W DML P7 0-10 M | -20 to +50 °C |
| 919306035171 | BRP483 LED236-2S NW 136W DWL P7 0-10 | -20 to +50 °C |
| 919306035181 | BRP483 LED236-2S NW 136W DWL P7 0-10 M | -20 to +50 °C |
| 919306035211 | BRP483 LED255-2S NW 150W DML P7 0-10 | -20 to +50 °C |
| 919306035221 | BRP483 LED255-2S NW 150W DML P7 0-10 M | -20 to +50 °C |
| 919306035231 | BRP483 LED255-2S NW 150W DWL P7 0-10 | -20 to +50 °C |

| Order Code | Full Product Name | Ambient temperature range |
|--------------|--|---------------------------|
| 919306035241 | BRP483 LED255-2S NW 150W DWL P7 0-10 M | -20 to +50 °C |
| 919306035271 | BRP483 LED274-2S NW 165W DML P7 0-10 | -20 to +50 °C |
| 919306035281 | BRP483 LED274-2S NW 165W DML P7 0-10 M | -20 to +50 °C |
| 919306035291 | BRP483 LED274-2S NW 165W DWL P7 0-10 | -20 to +50 °C |
| 919306035301 | BRP483 LED274-2S NW 165W DWL P7 0-10 M | -20 to +50 °C |
| 919306035311 | BRP483 LED292-2S NW 170W DWL-S P7 0-10 | -20 to +50 °C |
| 919306035321 | BRP483 LED307-2S NW 180W DWL-S P7 0-10 | -20 to +50 °C |
| 919306032851 | BRP485 LED328 NW 185W DWL P7 0-10 | -5 to +50 °C |
| 919306032861 | BRP485 LED328 NW 185W DML P7 0-10 | -5 to +50 °C |
| 919306032871 | BRP485 LED328 CW 185W DWL P7 0-10 | -5 to +50 °C |
| 919306032881 | BRP485 LED328 CW 185W DML P7 0-10 | -5 to +50 °C |
| 919306035491 | BRP485 LED328-2S NW 185W DML P7 0-10 | -20 to +50 °C |
| 919306035501 | BRP485 LED328-2S NW 185W DML P7 0-10 M | -20 to +50 °C |
| 919306035511 | BRP485 LED328-2S NW 185W DWL P7 0-10 | -20 to +50 °C |
| 919306035521 | BRP485 LED328-2S NW 185W DWL P7 0-10 M | -20 to +50 °C |
| 919306031971 | BRP481 LED43 NW 24W DWL P7 0-10 | -5 to +50 °C |
| 919306031981 | BRP481 LED51 NW 27W DWL P7 0-10 | -5 to +50 °C |
| 919306031991 | BRP481 LED60 NW 33W DWL P7 0-10 | -5 to +50 °C |
| 919306032001 | BRP481 LED73 NW 41W DWL P7 0-10 | -5 to +50 °C |
| 919306032011 | BRP481 LED85 NW 48W DWL P7 0-10 | -5 to +50 °C |
| 919306032021 | BRP481 LED96 NW 55W DWL P7 0-10 | -5 to +50 °C |
| 919306032031 | BRP481 LED43 CW 24W DWL P7 0-10 | -5 to +50 °C |
| 919306032051 | BRP481 LED60 CW 33W DWL P7 0-10 | -5 to +50 °C |
| 919306032061 | BRP481 LED73 CW 41W DWL P7 0-10 | -5 to +50 °C |
| 919306032071 | BRP481 LED85 CW 48W DWL P7 0-10 | -5 to +50 °C |
| 919306032081 | BRP481 LED96 CW 55W DWL P7 0-10 | -5 to +50 °C |
| 919306032091 | BRP481 LED43 NW 24W DML P7 0-10 | -5 to +50 °C |
| 919306032101 | BRP481 LED51 NW 27W DML P7 0-10 | -5 to +50 °C |
| 919306032111 | BRP481 LED60 NW 33W DML P7 0-10 | -5 to +50 °C |
| 919306032121 | BRP481 LED73 NW 41W DML P7 0-10 | -5 to +50 °C |
| 919306032131 | BRP481 LED85 NW 48W DML P7 0-10 | -5 to +50 °C |
| 919306032141 | BRP481 LED96 NW 55W DML P7 0-10 | -5 to +50 °C |
| 919306032151 | BRP481 LED43 CW 24W DML P7 0-10 | -5 to +50 °C |
| 919306032161 | BRP481 LED51 CW 27W DML P7 0-10 | -5 to +50 °C |
| 919306032171 | BRP481 LED60 CW 33W DML P7 0-10 | -5 to +50 °C |
| 919306032181 | BRP481 LED73 CW 41W DML P7 0-10 | -5 to +50 °C |
| 919306032191 | BRP481 LED85 CW 48W DML P7 0-10 | -5 to +50 °C |
| 919306032201 | BRP481 LED96 CW 55W DML P7 0-10 | -5 to +50 °C |
| 919306034071 | BRP481 LED43-2S NW 24W DWL P7 0-10 M | -20 to +50 °C |

| Order Code | Full Product Name | Ambient temperature range |
|--------------|--|---------------------------|
| 919306034081 | BRP481 LED104-2S NW 61W DWL-S P7 0-10 | -20 to +50 °C |
| 919306034091 | BRP481 LED113-2S NW 67W DWL-S P7 0-10 | -20 to +50 °C |
| 919306034121 | BRP481 LED43-2S NW 24W DML P7 0-10 | -20 to +50 °C |
| 919306034131 | BRP481 LED43-2S NW 24W DML P7 0-10 M | -20 to +50 °C |
| 919306034141 | BRP481 LED43-2S NW 24W DWL P7 0-10 | -20 to +50 °C |
| 919306034171 | BRP481 LED51-2S NW 27W DML P7 0-10 | -20 to +50 °C |
| 919306034181 | BRP481 LED51-2S NW 27W DML P7 0-10 M | -20 to +50 °C |
| 919306034191 | BRP481 LED51-2S NW 27W DWL P7 0-10 | -20 to +50 °C |
| 919306034201 | BRP481 LED51-2S NW 27W DWL P7 0-10 M | -20 to +50 °C |
| 919306034231 | BRP481 LED60-2S NW 33W DML P7 0-10 | -20 to +50 °C |
| 919306034241 | BRP481 LED60-2S NW 33W DML P7 0-10 M | -20 to +50 °C |
| 919306034251 | BRP481 LED60-2S NW 33W DWL P7 0-10 | -20 to +50 °C |
| 919306034261 | BRP481 LED60-2S NW 33W DWL P7 0-10 M | -20 to +50 °C |
| 919306034291 | BRP481 LED73-2S NW 41W DML P7 0-10 | -20 to +50 °C |

| Order Code | Full Product Name | Ambient temperature range |
|--------------|--|---------------------------|
| 919306034301 | BRP481 LED73-2S NW 41W DML P7 0-10 M | -20 to +50 °C |
| 919306034311 | BRP481 LED73-2S NW 41W DWL P7 0-10 | -20 to +50 °C |
| 919306034321 | BRP481 LED73-2S NW 41W DWL P7 0-10 M | -20 to +50 °C |
| 919306034351 | BRP481 LED85-2S NW 48W DML P7 0-10 | -20 to +50 °C |
| 919306034361 | BRP481 LED85-2S NW 48W DML P7 0-10 M | -20 to +50 °C |
| 919306034371 | BRP481 LED85-2S NW 48W DWL P7 0-10 | -20 to +50 °C |
| 919306034381 | BRP481 LED85-2S NW 48W DWL P7 0-10 M | -20 to +50 °C |
| 919306034411 | BRP481 LED96-2S NW 55W DML P7 0-10 | -20 to +50 °C |
| 919306034421 | BRP481 LED96-2S NW 55W DML P7 0-10 M | -20 to +50 °C |
| 919306034431 | BRP481 LED96-2S NW 55W DWL P7 0-10 | -20 to +50 °C |
| 919306034441 | BRP481 LED96-2S NW 55W DWL P7 0-10 M | -20 to +50 °C |
| 919306035691 | BRP481 LED84/NW 54W II DML PSR P7 EXP | -20 to +50 °C |
| 919306035751 | BRP481 LED84/NW 54W II DWL PSR P7 EXP | -20 to +50 °C |

Controls and Dimming

| Order Code | Full Product Name | Dimmable |
|--------------|---|----------|
| 919306032771 | BRP484 LED292 NW 169W DWL P7 0-10 | Yes |
| 919306032781 | BRP484 LED307 NW 179W DWL P7 0-10 | Yes |
| 919306032791 | BRP484 LED292 NW 169W DML P7 0-10 | Yes |
| 919306032801 | BRP484 LED307 NW 179W DML P7 0-10 | Yes |
| 919306032811 | BRP484 LED292 CW 169W DWL P7 0-10 | Yes |
| 919306032821 | BRP484 LED307 CW 179W DWL P7 0-10 | Yes |
| 919306032831 | BRP484 LED292 CW 169W DML P7 0-10 | Yes |
| 919306032841 | BRP484 LED307 CW 179W DML P7 0-10 | Yes |
| 919306035351 | BRP484 LED292-2S NW 169W DML P7 0-10 | 0-10V |
| 919306035361 | BRP484 LED292-2S NW 169W DML P7 0-10 M | 0-10V |
| 919306035371 | BRP484 LED292-2S NW 169W DWL P7 0-10 | 0-10V |
| 919306035381 | BRP484 LED292-2S NW 169W DWL P7 0-10 M | 0-10V |
| 919306035411 | BRP484 LED307-2S NW 179W DML P7 0-10 | 0-10V |
| 919306035421 | BRP484 LED307-2S NW 179W DML P7 0-10 M | 0-10V |
| 919306035431 | BRP484 LED307-2S NW 179W DWL P7 0-10 | 0-10V |
| 919306035441 | BRP484 LED307-2S NW 179W DWL P7 0-10 M | 0-10V |
| 919306035451 | BRP484 LED328-2S NW 182W DWL-S P7 0-10 | 0-10V |
| 919306035461 | BRP484 LED351-2S NW 196W DWL-S P7 0-10 | 0-10V |
| 919306035721 | BRP484 LED266/NW 176W II DML PSR P7 EXP | Yes |
| 919306035731 | BRP484 LED290/NW 191W II DML PSR P7 EXP | Yes |
| 919306035781 | BRP484 LED266/NW 176W II DWL PSR P7 EXP | Yes |
| 919306035791 | BRP484 LED290/NW 191W II DWL PSR P7 EXP | Yes |
| 919306032891 | BRP486 LED351 NW 195W DWL P7 0-10 | Yes |
| 919306032901 | BRP486 LED351 NW 195W DML P7 0-10 | Yes |
| 919306032911 | BRP486 LED351 CW 195W DWL P7 0-10 | Yes |
| 919306032921 | BRP486 LED351 CW 195W DML P7 0-10 | Yes |
| 919306035551 | BRP486 LED351-2S NW 195W DML P7 0-10 | 0-10V |

| Order Code | Full Product Name | Dimmable |
|--------------|---|----------|
| 919306035561 | BRP486 LED351-2S NW 195W DML P7 0-10 M | 0-10V |
| 919306035571 | BRP486 LED351-2S NW 195W DWL P7 0-10 | 0-10V |
| 919306035581 | BRP486 LED351-2S NW 195W DWL P7 0-10 M | 0-10V |
| 919306035741 | BRP486 LED330/NW 213W II DML PSR P7 EXP | Yes |
| 919306035801 | BRP486 LED330/NW 213W II DWL PSR P7 EXP | Yes |
| 820619285181 | BRP482 LED160-2S NW 92W DML P7 0-10 MX4 | 0-10V |
| 919306032211 | BRP482 LED104 NW 56W DWL P7 0-10 | Yes |
| 919306032221 | BRP482 LED113 NW 61W DWL P7 0-10 | Yes |
| 919306032231 | BRP482 LED126 NW 70W DWL P7 0-10 | Yes |
| 919306032241 | BRP482 LED136 NW 76W DWL P7 0-10 | Yes |
| 919306032251 | BRP482 LED147 NW 83W DWL P7 0-10 | Yes |
| 919306032261 | BRP482 LED160 NW 92W DWL P7 0-10 | Yes |
| 919306032271 | BRP482 LED172 NW 100W DWL P7 0-10 | Yes |
| 919306032281 | BRP482 LED179 NW 105W DWL P7 0-10 | Yes |
| 919306032291 | BRP482 LED186 NW 110W DWL P7 0-10 | Yes |
| 919306032301 | BRP482 LED104 CW 56W DWL P7 0-10 | Yes |
| 919306032311 | BRP482 LED113 CW 61W DWL P7 0-10 | Yes |
| 919306032321 | BRP482 LED126 CW 70W DWL P7 0-10 | Yes |
| 919306032331 | BRP482 LED136 CW 76W DWL P7 0-10 | Yes |
| 919306032351 | BRP482 LED160 CW 92W DWL P7 0-10 | Yes |
| 919306032361 | BRP482 LED172 CW 100W DWL P7 0-10 | Yes |
| 919306032371 | BRP482 LED179 CW 105W DWL P7 0-10 | Yes |
| 919306032381 | BRP482 LED186 CW 110W DWL P7 0-10 | Yes |
| 919306032391 | BRP482 LED104 NW 56W DML P7 0-10 | Yes |
| 919306032401 | BRP482 LED113 NW 61W DML P7 0-10 | Yes |
| 919306032411 | BRP482 LED126 NW 70W DML P7 0-10 | Yes |
| 919306032421 | BRP482 LED136 NW 76W DML P7 0-10 | Yes |

| Order Code | Full Product Name | Dimmable |
|--------------|--|----------|
| 919306032431 | BRP482 LED147 NW 83W DML P7 0-10 | Yes |
| 919306032441 | BRP482 LED160 NW 92W DML P7 0-10 | Yes |
| 919306032451 | BRP482 LED172 NW 100W DML P7 0-10 | Yes |
| 919306032461 | BRP482 LED179 NW 105W DML P7 0-10 | Yes |
| 919306032471 | BRP482 LED186 NW 110W DML P7 0-10 | Yes |
| 919306032481 | BRP482 LED104 CW 56W DML P7 0-10 | Yes |
| 919306032491 | BRP482 LED113 CW 61W DML P7 0-10 | Yes |
| 919306032501 | BRP482 LED126 CW 70W DML P7 0-10 | Yes |
| 919306032511 | BRP482 LED136 CW 76W DML P7 0-10 | Yes |
| 919306032521 | BRP482 LED147 CW 83W DML P7 0-10 | Yes |
| 919306032531 | BRP482 LED160 CW 92W DML P7 0-10 | Yes |
| 919306032541 | BRP482 LED172 CW 100W DML P7 0-10 | Yes |
| 919306032551 | BRP482 LED179 CW 105W DML P7 0-10 | Yes |
| 919306032561 | BRP482 LED186 CW 110W DML P7 0-10 | Yes |
| 919306034471 | BRP482 LED104-2S NW 56W DML P7 0-10 | 0-10V |
| 919306034481 | BRP482 LED104-2S NW 56W DML P7 0-10 M | 0-10V |
| 919306034491 | BRP482 LED104-2S NW 56W DWL P7 0-10 | 0-10V |
| 919306034501 | BRP482 LED104-2S NW 56W DWL P7 0-10 M | 0-10V |
| 919306034531 | BRP482 LED113-2S NW 61W DML P7 0-10 | 0-10V |
| 919306034541 | BRP482 LED113-2S NW 61W DML P7 0-10 M | 0-10V |
| 919306034551 | BRP482 LED113-2S NW 61W DWL P7 0-10 | 0-10V |
| 919306034561 | BRP482 LED113-2S NW 61W DWL P7 0-10 M | 0-10V |
| 919306034591 | BRP482 LED126-2S NW 70W DML P7 0-10 | 0-10V |
| 919306034601 | BRP482 LED126-2S NW 70W DML P7 0-10 M | 0-10V |
| 919306034611 | BRP482 LED126-2S NW 70W DWL P7 0-10 | 0-10V |
| 919306034621 | BRP482 LED126-2S NW 70W DWL P7 0-10 M | 0-10V |
| 919306034651 | BRP482 LED136-2S NW 76W DML P7 0-10 | 0-10V |
| 919306034661 | BRP482 LED136-2S NW 76W DML P7 0-10 M | 0-10V |
| 919306034671 | BRP482 LED136-2S NW 76W DWL P7 0-10 | 0-10V |
| 919306034681 | BRP482 LED136-2S NW 76W DWL P7 0-10 M | 0-10V |
| 919306034711 | BRP482 LED147-2S NW 83W DML P7 0-10 | 0-10V |
| 919306034721 | BRP482 LED147-2S NW 83W DML P7 0-10 M | 0-10V |
| 919306034731 | BRP482 LED147-2S NW 83W DWL P7 0-10 | 0-10V |
| 919306034741 | BRP482 LED147-2S NW 83W DWL P7 0-10 M | 0-10V |
| 919306034771 | BRP482 LED160-2S NW 92W DML P7 0-10 | 0-10V |
| 919306034781 | BRP482 LED160-2S NW 92W DML P7 0-10 M | 0-10V |
| 919306034791 | BRP482 LED160-2S NW 92W DWL P7 0-10 | 0-10V |
| 919306034801 | BRP482 LED160-2S NW 92W DWL P7 0-10 M | 0-10V |
| 919306034831 | BRP482 LED172-2S NW 100W DML P7 0-10 | 0-10V |
| 919306034841 | BRP482 LED172-2S NW 100W DML P7 0-10 M | 0-10V |
| 919306034851 | BRP482 LED172-2S NW 100W DWL P7 0-10 | 0-10V |
| 919306034861 | BRP482 LED172-2S NW 100W DWL P7 0-10 M | 0-10V |
| 919306034891 | BRP482 LED179-2S NW 105W DML P7 0-10 | 0-10V |
| 919306034901 | BRP482 LED179-2S NW 105W DML P7 0-10 M | 0-10V |
| 919306034911 | BRP482 LED179-2S NW 105W DWL P7 0-10 | 0-10V |
| 919306034921 | BRP482 LED179-2S NW 105W DWL P7 0-10 M | 0-10V |
| 919306034951 | BRP482 LED186-2S NW 110W DML P7 0-10 | 0-10V |
| 919306034961 | BRP482 LED186-2S NW 110W DML P7 0-10 M | 0-10V |
| 919306034971 | BRP482 LED186-2S NW 110W DWL P7 0-10 | 0-10V |
| 919306034981 | BRP482 LED186-2S NW 110W DWL P7 0-10 M | 0-10V |
| 919306034991 | BRP482 LED202-2S NW 118W DWL-S P7 0-10 | 0-10V |
| 919306035001 | BRP482 LED216-2S NW 130W DWL-S P7 0-10 | 0-10V |

| Order Code | Full Product Name | Dimmable |
|--------------|---|----------|
| 919306035701 | BRP482 LED125/NW 84W II DML PSR P7 EXP | Yes |
| 919306035711 | BRP482 LED168/NW 114W II DML PSR P7 EXP | Yes |
| 919306035761 | BRP482 LED125/NW 84W II DWL PSR P7 EXP | Yes |
| 919306035771 | BRP482 LED168/NW 114W II DWL PSR P7 EXP | Yes |
| 919306032571 | BRP483 LED202 NW 113W DWL P7 0-10 | Yes |
| 919306032581 | BRP483 LED216 NW 122W DWL P7 0-10 | Yes |
| 919306032591 | BRP483 LED236 NW 136W DWL P7 0-10 | Yes |
| 919306032601 | BRP483 LED255 NW 150W DWL P7 0-10 | Yes |
| 919306032611 | BRP483 LED274 NW 165W DWL P7 0-10 | Yes |
| 919306032621 | BRP483 LED202 NW 113W DML P7 0-10 | Yes |
| 919306032631 | BRP483 LED216 NW 122W DML P7 0-10 | Yes |
| 919306032641 | BRP483 LED236 NW 136W DML P7 0-10 | Yes |
| 919306032651 | BRP483 LED255 NW 150W DML P7 0-10 | Yes |
| 919306032661 | BRP483 LED274 NW 165W DML P7 0-10 | Yes |
| 919306032671 | BRP483 LED202 CW 113W DWL P7 0-10 | Yes |
| 919306032681 | BRP483 LED216 CW 122W DWL P7 0-10 | Yes |
| 919306032691 | BRP483 LED236 CW 136W DWL P7 0-10 | Yes |
| 919306032701 | BRP483 LED255 CW 150W DWL P7 0-10 | Yes |
| 919306032711 | BRP483 LED274 CW 165W DWL P7 0-10 | Yes |
| 919306032721 | BRP483 LED202 CW 113W DML P7 0-10 | Yes |
| 919306032731 | BRP483 LED216 CW 122W DML P7 0-10 | Yes |
| 919306032741 | BRP483 LED236 CW 136W DML P7 0-10 | Yes |
| 919306032751 | BRP483 LED255 CW 150W DML P7 0-10 | Yes |
| 919306032761 | BRP483 LED274 CW 165W DML P7 0-10 | Yes |
| 919306035031 | BRP483 LED202-2S NW 113W DML P7 0-10 | 0-10V |
| 919306035041 | BRP483 LED202-2S NW 113W DML P7 0-10 M | 0-10V |
| 919306035051 | BRP483 LED202-2S NW 113W DWL P7 0-10 | 0-10V |
| 919306035061 | BRP483 LED202-2S NW 113W DWL P7 0-10 M | 0-10V |
| 919306035091 | BRP483 LED216-2S NW 122W DML P7 0-10 | 0-10V |
| 919306035101 | BRP483 LED216-2S NW 122W DML P7 0-10 M | 0-10V |
| 919306035111 | BRP483 LED216-2S NW 122W DWL P7 0-10 | 0-10V |
| 919306035121 | BRP483 LED216-2S NW 122W DWL P7 0-10 M | 0-10V |
| 919306035151 | BRP483 LED236-2S NW 136W DML P7 0-10 | 0-10V |
| 919306035161 | BRP483 LED236-2S NW 136W DML P7 0-10 M | 0-10V |
| 919306035171 | BRP483 LED236-2S NW 136W DWL P7 0-10 | 0-10V |
| 919306035181 | BRP483 LED236-2S NW 136W DWL P7 0-10 M | 0-10V |
| 919306035211 | BRP483 LED255-2S NW 150W DML P7 0-10 | 0-10V |
| 919306035221 | BRP483 LED255-2S NW 150W DML P7 0-10 M | 0-10V |
| 919306035231 | BRP483 LED255-2S NW 150W DWL P7 0-10 | 0-10V |
| 919306035241 | BRP483 LED255-2S NW 150W DWL P7 0-10 M | 0-10V |
| 919306035271 | BRP483 LED274-2S NW 165W DML P7 0-10 | 0-10V |
| 919306035281 | BRP483 LED274-2S NW 165W DML P7 0-10 M | 0-10V |
| 919306035291 | BRP483 LED274-2S NW 165W DWL P7 0-10 | 0-10V |
| 919306035301 | BRP483 LED274-2S NW 165W DWL P7 0-10 M | 0-10V |
| 919306035311 | BRP483 LED292-2S NW 170W DWL-S P7 0-10 | 0-10V |
| 919306035321 | BRP483 LED307-2S NW 180W DWL-S P7 0-10 | 0-10V |
| 919306032851 | BRP485 LED328 NW 185W DWL P7 0-10 | Yes |
| 919306032861 | BRP485 LED328 NW 185W DML P7 0-10 | Yes |
| 919306032871 | BRP485 LED328 CW 185W DWL P7 0-10 | Yes |
| 919306032881 | BRP485 LED328 CW 185W DML P7 0-10 | Yes |
| 919306035491 | BRP485 LED328-2S NW 185W DML P7 0-10 | 0-10V |
| 919306035501 | BRP485 LED328-2S NW 185W DML P7 0-10 M | 0-10V |

| Order Code | Full Product Name | Dimmable |
|--------------|--|----------|
| 919306035511 | BRP485 LED328-2S NW 185W DWL P7 0-10 | 0-10V |
| 919306035521 | BRP485 LED328-2S NW 185W DWL P7 0-10 M | 0-10V |
| 919306031971 | BRP481 LED43 NW 24W DWL P7 0-10 | Yes |
| 919306031981 | BRP481 LED51 NW 27W DWL P7 0-10 | Yes |
| 919306031991 | BRP481 LED60 NW 33W DWL P7 0-10 | Yes |
| 919306032001 | BRP481 LED73 NW 41W DWL P7 0-10 | Yes |
| 919306032011 | BRP481 LED85 NW 48W DWL P7 0-10 | Yes |
| 919306032021 | BRP481 LED96 NW 55W DWL P7 0-10 | Yes |
| 919306032031 | BRP481 LED43 CW 24W DWL P7 0-10 | Yes |
| 919306032051 | BRP481 LED60 CW 33W DWL P7 0-10 | Yes |
| 919306032061 | BRP481 LED73 CW 41W DWL P7 0-10 | Yes |
| 919306032071 | BRP481 LED85 CW 48W DWL P7 0-10 | Yes |
| 919306032081 | BRP481 LED96 CW 55W DWL P7 0-10 | Yes |
| 919306032091 | BRP481 LED43 NW 24W DML P7 0-10 | Yes |
| 919306032101 | BRP481 LED51 NW 27W DML P7 0-10 | Yes |
| 919306032111 | BRP481 LED60 NW 33W DML P7 0-10 | Yes |
| 919306032121 | BRP481 LED73 NW 41W DML P7 0-10 | Yes |
| 919306032131 | BRP481 LED85 NW 48W DML P7 0-10 | Yes |
| 919306032141 | BRP481 LED96 NW 55W DML P7 0-10 | Yes |
| 919306032151 | BRP481 LED43 CW 24W DML P7 0-10 | Yes |
| 919306032161 | BRP481 LED51 CW 27W DML P7 0-10 | Yes |
| 919306032171 | BRP481 LED60 CW 33W DML P7 0-10 | Yes |
| 919306032181 | BRP481 LED73 CW 41W DML P7 0-10 | Yes |
| 919306032191 | BRP481 LED85 CW 48W DML P7 0-10 | Yes |
| 919306032201 | BRP481 LED96 CW 55W DML P7 0-10 | Yes |
| 919306034071 | BRP481 LED43-2S NW 24W DWL P7 0-10 M | 0-10V |
| 919306034081 | BRP481 LED104-2S NW 61W DWL-S P7 0-10 | 0-10V |

| Order Code | Full Product Name | Dimmable |
|--------------|---------------------------------------|----------|
| 919306034091 | BRP481 LED113-2S NW 67W DWL-S P7 0-10 | 0-10V |
| 919306034121 | BRP481 LED43-2S NW 24W DML P7 0-10 | 0-10V |
| 919306034131 | BRP481 LED43-2S NW 24W DML P7 0-10 M | 0-10V |
| 919306034141 | BRP481 LED43-2S NW 24W DWL P7 0-10 | 0-10V |
| 919306034171 | BRP481 LED51-2S NW 27W DML P7 0-10 | 0-10V |
| 919306034181 | BRP481 LED51-2S NW 27W DML P7 0-10 M | 0-10V |
| 919306034191 | BRP481 LED51-2S NW 27W DWL P7 0-10 | 0-10V |
| 919306034201 | BRP481 LED51-2S NW 27W DWL P7 0-10 M | 0-10V |
| 919306034231 | BRP481 LED60-2S NW 33W DML P7 0-10 | 0-10V |
| 919306034241 | BRP481 LED60-2S NW 33W DML P7 0-10 M | 0-10V |
| 919306034251 | BRP481 LED60-2S NW 33W DWL P7 0-10 | 0-10V |
| 919306034261 | BRP481 LED60-2S NW 33W DWL P7 0-10 M | 0-10V |
| 919306034291 | BRP481 LED73-2S NW 41W DML P7 0-10 | 0-10V |
| 919306034301 | BRP481 LED73-2S NW 41W DML P7 0-10 M | 0-10V |
| 919306034311 | BRP481 LED73-2S NW 41W DWL P7 0-10 | 0-10V |
| 919306034321 | BRP481 LED73-2S NW 41W DWL P7 0-10 M | 0-10V |
| 919306034351 | BRP481 LED85-2S NW 48W DML P7 0-10 | 0-10V |
| 919306034361 | BRP481 LED85-2S NW 48W DML P7 0-10 M | 0-10V |
| 919306034371 | BRP481 LED85-2S NW 48W DWL P7 0-10 | 0-10V |
| 919306034381 | BRP481 LED85-2S NW 48W DWL P7 0-10 M | 0-10V |
| 919306034411 | BRP481 LED96-2S NW 55W DML P7 0-10 | 0-10V |
| 919306034421 | BRP481 LED96-2S NW 55W DML P7 0-10 M | 0-10V |
| 919306034431 | BRP481 LED96-2S NW 55W DWL P7 0-10 | 0-10V |
| 919306034441 | BRP481 LED96-2S NW 55W DWL P7 0-10 M | 0-10V |
| 919306035691 | BRP481 LED84/NW 54W II DML PSR P7 EXP | Yes |
| 919306035751 | BRP481 LED84/NW 54W II DWL PSR P7 EXP | Yes |

Mechanical and Housing

| Order Code | Full Product Name | Overall length | Overall width |
|--------------|--|----------------|---------------|
| 919306032771 | BRP484 LED292 NW 169W DWL P7 0-10 | 670 mm | 200 mm |
| 919306032781 | BRP484 LED307 NW 179W DWL P7 0-10 | 670 mm | 200 mm |
| 919306032791 | BRP484 LED292 NW 169W DML P7 0-10 | 670 mm | 200 mm |
| 919306032801 | BRP484 LED307 NW 179W DML P7 0-10 | 670 mm | 200 mm |
| 919306032811 | BRP484 LED292 CW 169W DWL P7 0-10 | 670 mm | 200 mm |
| 919306032821 | BRP484 LED307 CW 179W DWL P7 0-10 | 670 mm | 200 mm |
| 919306032831 | BRP484 LED292 CW 169W DML P7 0-10 | 670 mm | 200 mm |
| 919306032841 | BRP484 LED307 CW 179W DML P7 0-10 | 670 mm | 200 mm |
| 919306035351 | BRP484 LED292-2S NW 169W DML P7 0-10 | - | - |
| 919306035361 | BRP484 LED292-2S NW 169W DML P7 0-10 M | - | - |
| 919306035371 | BRP484 LED292-2S NW 169W DWL P7 0-10 | - | - |
| 919306035381 | BRP484 LED292-2S NW 169W DWL P7 0-10 M | - | - |
| 919306035411 | BRP484 LED307-2S NW 179W DML P7 0-10 | - | - |
| 919306035421 | BRP484 LED307-2S NW 179W DML P7 0-10 M | - | - |

| Order Code | Full Product Name | Overall length | Overall width |
|--------------|---|----------------|---------------|
| 919306035431 | BRP484 LED307-2S NW 179W DWL P7 0-10 | - | - |
| 919306035441 | BRP484 LED307-2S NW 179W DWL P7 0-10 M | - | - |
| 919306035451 | BRP484 LED328-2S NW 182W DWL-S P7 0-10 | - | - |
| 919306035461 | BRP484 LED351-2S NW 196W DWL-S P7 0-10 | - | - |
| 919306035721 | BRP484 LED266/NW 176W II DML PSR P7 EXP | - | - |
| 919306035731 | BRP484 LED290/NW 191W II DML PSR P7 EXP | - | - |
| 919306035781 | BRP484 LED266/NW 176W II DWL PSR P7 EXP | - | - |
| 919306035791 | BRP484 LED290/NW 191W II DWL PSR P7 EXP | - | - |
| 919306032891 | BRP486 LED351 NW 195W DWL P7 0-10 | 670 mm | 280 mm |
| 919306032901 | BRP486 LED351 NW 195W DML P7 0-10 | 670 mm | 280 mm |
| 919306032911 | BRP486 LED351 CW 195W DWL P7 0-10 | 670 mm | 280 mm |
| 919306032921 | BRP486 LED351 CW 195W DML P7 0-10 | 670 mm | 280 mm |

| Order Code | Full Product Name | Overall length | Overall width |
|--------------|---|----------------|---------------|
| 919306035551 | BRP486 LED351-2S NW 195W DML P7 0-10 | - | - |
| 919306035561 | BRP486 LED351-2S NW 195W DML P7 0-10 M | - | - |
| 919306035571 | BRP486 LED351-2S NW 195W DWL P7 0-10 | - | - |
| 919306035581 | BRP486 LED351-2S NW 195W DWL P7 0-10 M | - | - |
| 919306035741 | BRP486 LED330/NW 213W II DML PSR P7 EXP | - | - |
| 919306035801 | BRP486 LED330/NW 213W II DWL PSR P7 EXP | - | - |
| 820619285181 | BRP482 LED160-2S NW 92W DML P7 0-10 MX4 | - | - |
| 919306032211 | BRP482 LED104 NW 56W DWL P7 0-10 | 430 mm | 203 mm |
| 919306032221 | BRP482 LED113 NW 61W DWL P7 0-10 | 430 mm | 203 mm |
| 919306032231 | BRP482 LED126 NW 70W DWL P7 0-10 | 430 mm | 203 mm |
| 919306032241 | BRP482 LED136 NW 76W DWL P7 0-10 | 430 mm | 203 mm |
| 919306032251 | BRP482 LED147 NW 83W DWL P7 0-10 | 430 mm | 203 mm |
| 919306032261 | BRP482 LED160 NW 92W DWL P7 0-10 | 430 mm | 203 mm |
| 919306032271 | BRP482 LED172 NW 100W DWL P7 0-10 | 430 mm | 203 mm |
| 919306032281 | BRP482 LED179 NW 105W DWL P7 0-10 | 430 mm | 203 mm |
| 919306032291 | BRP482 LED186 NW 110W DWL P7 0-10 | 430 mm | 203 mm |
| 919306032301 | BRP482 LED104 CW 56W DWL P7 0-10 | 430 mm | 203 mm |
| 919306032311 | BRP482 LED113 CW 61W DWL P7 0-10 | 430 mm | 203 mm |
| 919306032321 | BRP482 LED126 CW 70W DWL P7 0-10 | 430 mm | 203 mm |
| 919306032331 | BRP482 LED136 CW 76W DWL P7 0-10 | 430 mm | 203 mm |
| 919306032351 | BRP482 LED160 CW 92W DWL P7 0-10 | 430 mm | 203 mm |
| 919306032361 | BRP482 LED172 CW 100W DWL P7 0-10 | 430 mm | 203 mm |
| 919306032371 | BRP482 LED179 CW 105W DWL P7 0-10 | 430 mm | 203 mm |
| 919306032381 | BRP482 LED186 CW 110W DWL P7 0-10 | 430 mm | 203 mm |
| 919306032391 | BRP482 LED104 NW 56W DML P7 0-10 | 430 mm | 203 mm |
| 919306032401 | BRP482 LED113 NW 61W DML P7 0-10 | 430 mm | 203 mm |
| 919306032411 | BRP482 LED126 NW 70W DML P7 0-10 | 430 mm | 203 mm |
| 919306032421 | BRP482 LED136 NW 76W DML P7 0-10 | 430 mm | 203 mm |
| 919306032431 | BRP482 LED147 NW 83W DML P7 0-10 | 430 mm | 203 mm |
| 919306032441 | BRP482 LED160 NW 92W DML P7 0-10 | 430 mm | 203 mm |
| 919306032451 | BRP482 LED172 NW 100W DML P7 0-10 | 430 mm | 203 mm |
| 919306032461 | BRP482 LED179 NW 105W DML P7 0-10 | 430 mm | 203 mm |
| 919306032471 | BRP482 LED186 NW 110W DML P7 0-10 | 430 mm | 203 mm |
| 919306032481 | BRP482 LED104 CW 56W DML P7 0-10 | 430 mm | 203 mm |
| 919306032491 | BRP482 LED113 CW 61W DML P7 0-10 | 430 mm | 203 mm |
| 919306032501 | BRP482 LED126 CW 70W DML P7 0-10 | 430 mm | 203 mm |
| 919306032511 | BRP482 LED136 CW 76W DML P7 0-10 | 430 mm | 203 mm |
| 919306032521 | BRP482 LED147 CW 83W DML P7 0-10 | 430 mm | 203 mm |
| 919306032531 | BRP482 LED160 CW 92W DML P7 0-10 | 430 mm | 203 mm |
| 919306032541 | BRP482 LED172 CW 100W DML P7 0-10 | 430 mm | 203 mm |
| 919306032551 | BRP482 LED179 CW 105W DML P7 0-10 | 430 mm | 203 mm |
| 919306032561 | BRP482 LED186 CW 110W DML P7 0-10 | 430 mm | 203 mm |
| 919306034471 | BRP482 LED104-2S NW 56W DML P7 0-10 | - | - |

| Order Code | Full Product Name | Overall length | Overall width |
|--------------|--|----------------|---------------|
| 919306034481 | BRP482 LED104-2S NW 56W DML P7 0-10 M | - | - |
| 919306034491 | BRP482 LED104-2S NW 56W DWL P7 0-10 | - | - |
| 919306034501 | BRP482 LED104-2S NW 56W DWL P7 0-10 M | - | - |
| 919306034531 | BRP482 LED113-2S NW 61W DML P7 0-10 | - | - |
| 919306034541 | BRP482 LED113-2S NW 61W DML P7 0-10 M | - | - |
| 919306034551 | BRP482 LED113-2S NW 61W DWL P7 0-10 | - | - |
| 919306034561 | BRP482 LED113-2S NW 61W DWL P7 0-10 M | - | - |
| 919306034591 | BRP482 LED126-2S NW 70W DML P7 0-10 | - | - |
| 919306034601 | BRP482 LED126-2S NW 70W DML P7 0-10 M | - | - |
| 919306034611 | BRP482 LED126-2S NW 70W DWL P7 0-10 | - | - |
| 919306034621 | BRP482 LED126-2S NW 70W DWL P7 0-10 M | - | - |
| 919306034651 | BRP482 LED136-2S NW 76W DML P7 0-10 | - | - |
| 919306034661 | BRP482 LED136-2S NW 76W DML P7 0-10 M | - | - |
| 919306034671 | BRP482 LED136-2S NW 76W DWL P7 0-10 | - | - |
| 919306034681 | BRP482 LED136-2S NW 76W DWL P7 0-10 M | - | - |
| 919306034711 | BRP482 LED147-2S NW 83W DML P7 0-10 | - | - |
| 919306034721 | BRP482 LED147-2S NW 83W DML P7 0-10 M | - | - |
| 919306034731 | BRP482 LED147-2S NW 83W DWL P7 0-10 | - | - |
| 919306034741 | BRP482 LED147-2S NW 83W DWL P7 0-10 M | - | - |
| 919306034771 | BRP482 LED160-2S NW 92W DML P7 0-10 | - | - |
| 919306034781 | BRP482 LED160-2S NW 92W DML P7 0-10 M | - | - |
| 919306034791 | BRP482 LED160-2S NW 92W DWL P7 0-10 | - | - |
| 919306034801 | BRP482 LED160-2S NW 92W DWL P7 0-10 M | - | - |
| 919306034831 | BRP482 LED172-2S NW 100W DML P7 0-10 | - | - |
| 919306034841 | BRP482 LED172-2S NW 100W DML P7 0-10 M | - | - |
| 919306034851 | BRP482 LED172-2S NW 100W DWL P7 0-10 | - | - |

| Order Code | Full Product Name | Overall length | Overall width |
|--------------|---|----------------|---------------|
| 919306034861 | BRP482 LED172-2S NW 100W DWL P7 0-10 M | - | - |
| 919306034891 | BRP482 LED179-2S NW 105W DML P7 0-10 | - | - |
| 919306034901 | BRP482 LED179-2S NW 105W DML P7 0-10 M | - | - |
| 919306034911 | BRP482 LED179-2S NW 105W DWL P7 0-10 | - | - |
| 919306034921 | BRP482 LED179-2S NW 105W DWL P7 0-10 M | - | - |
| 919306034951 | BRP482 LED186-2S NW 110W DML P7 0-10 | - | - |
| 919306034961 | BRP482 LED186-2S NW 110W DML P7 0-10 M | - | - |
| 919306034971 | BRP482 LED186-2S NW 110W DWL P7 0-10 | - | - |
| 919306034981 | BRP482 LED186-2S NW 110W DWL P7 0-10 M | - | - |
| 919306034991 | BRP482 LED202-2S NW 118W DWL-S P7 0-10 | - | - |
| 919306035001 | BRP482 LED216-2S NW 130W DWL-S P7 0-10 | - | - |
| 919306035701 | BRP482 LED125/NW 84W II DML PSR P7 EXP | - | - |
| 919306035711 | BRP482 LED168/NW 114W II DML PSR P7 EXP | - | - |
| 919306035761 | BRP482 LED125/NW 84W II DWL PSR P7 EXP | - | - |
| 919306035771 | BRP482 LED168/NW 114W II DWL PSR P7 EXP | - | - |
| 919306032571 | BRP483 LED202 NW 113W DWL P7 0-10 | 420 mm | 220 mm |
| 919306032581 | BRP483 LED216 NW 122W DWL P7 0-10 | 420 mm | 220 mm |
| 919306032591 | BRP483 LED236 NW 136W DWL P7 0-10 | 420 mm | 220 mm |
| 919306032601 | BRP483 LED255 NW 150W DWL P7 0-10 | 420 mm | 220 mm |
| 919306032611 | BRP483 LED274 NW 165W DWL P7 0-10 | 420 mm | 220 mm |
| 919306032621 | BRP483 LED202 NW 113W DML P7 0-10 | 420 mm | 220 mm |
| 919306032631 | BRP483 LED216 NW 122W DML P7 0-10 | 420 mm | 220 mm |
| 919306032641 | BRP483 LED236 NW 136W DML P7 0-10 | 420 mm | 220 mm |
| 919306032651 | BRP483 LED255 NW 150W DML P7 0-10 | 420 mm | 220 mm |
| 919306032661 | BRP483 LED274 NW 165W DML P7 0-10 | 420 mm | 220 mm |
| 919306032671 | BRP483 LED202 CW 113W DWL P7 0-10 | 420 mm | 220 mm |
| 919306032681 | BRP483 LED216 CW 122W DWL P7 0-10 | 420 mm | 220 mm |
| 919306032691 | BRP483 LED236 CW 136W DWL P7 0-10 | 420 mm | 220 mm |
| 919306032701 | BRP483 LED255 CW 150W DWL P7 0-10 | 420 mm | 220 mm |
| 919306032711 | BRP483 LED274 CW 165W DWL P7 0-10 | 420 mm | 220 mm |
| 919306032721 | BRP483 LED202 CW 113W DML P7 0-10 | 420 mm | 220 mm |
| 919306032731 | BRP483 LED216 CW 122W DML P7 0-10 | 420 mm | 220 mm |
| 919306032741 | BRP483 LED236 CW 136W DML P7 0-10 | 420 mm | 220 mm |
| 919306032751 | BRP483 LED255 CW 150W DML P7 0-10 | 420 mm | 220 mm |
| 919306032761 | BRP483 LED274 CW 165W DML P7 0-10 | 420 mm | 220 mm |

| Order Code | Full Product Name | Overall length | Overall width |
|--------------|--|----------------|---------------|
| 919306035031 | BRP483 LED202-2S NW 113W DML P7 0-10 | - | - |
| 919306035041 | BRP483 LED202-2S NW 113W DML P7 0-10 M | - | - |
| 919306035051 | BRP483 LED202-2S NW 113W DWL P7 0-10 | - | - |
| 919306035061 | BRP483 LED202-2S NW 113W DWL P7 0-10 M | - | - |
| 919306035091 | BRP483 LED216-2S NW 122W DML P7 0-10 | - | - |
| 919306035101 | BRP483 LED216-2S NW 122W DML P7 0-10 M | - | - |
| 919306035111 | BRP483 LED216-2S NW 122W DWL P7 0-10 | - | - |
| 919306035121 | BRP483 LED216-2S NW 122W DWL P7 0-10 M | - | - |
| 919306035151 | BRP483 LED236-2S NW 136W DML P7 0-10 | - | - |
| 919306035161 | BRP483 LED236-2S NW 136W DML P7 0-10 M | - | - |
| 919306035171 | BRP483 LED236-2S NW 136W DWL P7 0-10 | - | - |
| 919306035181 | BRP483 LED236-2S NW 136W DWL P7 0-10 M | - | - |
| 919306035211 | BRP483 LED255-2S NW 150W DML P7 0-10 | - | - |
| 919306035221 | BRP483 LED255-2S NW 150W DML P7 0-10 M | - | - |
| 919306035231 | BRP483 LED255-2S NW 150W DWL P7 0-10 | - | - |
| 919306035241 | BRP483 LED255-2S NW 150W DWL P7 0-10 M | - | - |
| 919306035271 | BRP483 LED274-2S NW 165W DML P7 0-10 | - | - |
| 919306035281 | BRP483 LED274-2S NW 165W DML P7 0-10 M | - | - |
| 919306035291 | BRP483 LED274-2S NW 165W DWL P7 0-10 | - | - |
| 919306035301 | BRP483 LED274-2S NW 165W DWL P7 0-10 M | - | - |
| 919306035311 | BRP483 LED292-2S NW 170W DWL-S P7 0-10 | - | - |
| 919306035321 | BRP483 LED307-2S NW 180W DWL-S P7 0-10 | - | - |
| 919306032851 | BRP485 LED328 NW 185W DWL P7 0-10 | 670 mm | 280 mm |
| 919306032861 | BRP485 LED328 NW 185W DML P7 0-10 | 670 mm | 280 mm |
| 919306032871 | BRP485 LED328 CW 185W DWL P7 0-10 | 670 mm | 280 mm |
| 919306032881 | BRP485 LED328 CW 185W DML P7 0-10 | 670 mm | 280 mm |
| 919306035491 | BRP485 LED328-2S NW 185W DML P7 0-10 | - | - |

| Order Code | Full Product Name | Overall length | Overall width |
|--------------|--|----------------|---------------|
| 919306035501 | BRP485 LED328-2S NW 185W DML P7 0-10 M | - | - |
| 919306035511 | BRP485 LED328-2S NW 185W DWL P7 0-10 | - | - |
| 919306035521 | BRP485 LED328-2S NW 185W DWL P7 0-10 M | - | - |
| 919306031971 | BRP481 LED43 NW 24W DWL P7 0-10 | 420 mm | 180 mm |
| 919306031981 | BRP481 LED51 NW 27W DWL P7 0-10 | 420 mm | 180 mm |
| 919306031991 | BRP481 LED60 NW 33W DWL P7 0-10 | 420 mm | 180 mm |
| 919306032001 | BRP481 LED73 NW 41W DWL P7 0-10 | 420 mm | 180 mm |
| 919306032011 | BRP481 LED85 NW 48W DWL P7 0-10 | 420 mm | 180 mm |
| 919306032021 | BRP481 LED96 NW 55W DWL P7 0-10 | 420 mm | 180 mm |
| 919306032031 | BRP481 LED43 CW 24W DWL P7 0-10 | 420 mm | 180 mm |
| 919306032051 | BRP481 LED60 CW 33W DWL P7 0-10 | 420 mm | 180 mm |
| 919306032061 | BRP481 LED73 CW 41W DWL P7 0-10 | 420 mm | 180 mm |
| 919306032071 | BRP481 LED85 CW 48W DWL P7 0-10 | 420 mm | 180 mm |
| 919306032081 | BRP481 LED96 CW 55W DWL P7 0-10 | 420 mm | 180 mm |
| 919306032091 | BRP481 LED43 NW 24W DML P7 0-10 | 420 mm | 180 mm |
| 919306032101 | BRP481 LED51 NW 27W DML P7 0-10 | 420 mm | 180 mm |
| 919306032111 | BRP481 LED60 NW 33W DML P7 0-10 | 420 mm | 180 mm |
| 919306032121 | BRP481 LED73 NW 41W DML P7 0-10 | 420 mm | 180 mm |
| 919306032131 | BRP481 LED85 NW 48W DML P7 0-10 | 420 mm | 180 mm |
| 919306032141 | BRP481 LED96 NW 55W DML P7 0-10 | 420 mm | 180 mm |
| 919306032151 | BRP481 LED43 CW 24W DML P7 0-10 | 420 mm | 180 mm |
| 919306032161 | BRP481 LED51 CW 27W DML P7 0-10 | 420 mm | 180 mm |
| 919306032171 | BRP481 LED60 CW 33W DML P7 0-10 | 420 mm | 180 mm |
| 919306032181 | BRP481 LED73 CW 41W DML P7 0-10 | 420 mm | 180 mm |
| 919306032191 | BRP481 LED85 CW 48W DML P7 0-10 | 420 mm | 180 mm |
| 919306032201 | BRP481 LED96 CW 55W DML P7 0-10 | 420 mm | 180 mm |
| 919306034071 | BRP481 LED43-2S NW 24W DWL P7 0-10 M | - | - |
| 919306034081 | BRP481 LED104-2S NW 61W DWL-S P7 0-10 | - | - |
| 919306034091 | BRP481 LED113-2S NW 67W DWL-S P7 0-10 | - | - |
| 919306034121 | BRP481 LED43-2S NW 24W DML P7 0-10 | - | - |
| 919306034131 | BRP481 LED43-2S NW 24W DML P7 0-10 M | - | - |

| Order Code | Full Product Name | Overall length | Overall width |
|--------------|---------------------------------------|----------------|---------------|
| 919306034141 | BRP481 LED43-2S NW 24W DWL P7 0-10 | - | - |
| 919306034171 | BRP481 LED51-2S NW 27W DML P7 0-10 | - | - |
| 919306034181 | BRP481 LED51-2S NW 27W DML P7 0-10 M | - | - |
| 919306034191 | BRP481 LED51-2S NW 27W DWL P7 0-10 | - | - |
| 919306034201 | BRP481 LED51-2S NW 27W DWL P7 0-10 M | - | - |
| 919306034231 | BRP481 LED60-2S NW 33W DML P7 0-10 | - | - |
| 919306034241 | BRP481 LED60-2S NW 33W DML P7 0-10 M | - | - |
| 919306034251 | BRP481 LED60-2S NW 33W DWL P7 0-10 | - | - |
| 919306034261 | BRP481 LED60-2S NW 33W DWL P7 0-10 M | - | - |
| 919306034291 | BRP481 LED73-2S NW 41W DML P7 0-10 | - | - |
| 919306034301 | BRP481 LED73-2S NW 41W DML P7 0-10 M | - | - |
| 919306034311 | BRP481 LED73-2S NW 41W DWL P7 0-10 | - | - |
| 919306034321 | BRP481 LED73-2S NW 41W DWL P7 0-10 M | - | - |
| 919306034351 | BRP481 LED85-2S NW 48W DML P7 0-10 | - | - |
| 919306034361 | BRP481 LED85-2S NW 48W DML P7 0-10 M | - | - |
| 919306034371 | BRP481 LED85-2S NW 48W DWL P7 0-10 | - | - |
| 919306034381 | BRP481 LED85-2S NW 48W DWL P7 0-10 M | - | - |
| 919306034411 | BRP481 LED96-2S NW 55W DML P7 0-10 | - | - |
| 919306034421 | BRP481 LED96-2S NW 55W DML P7 0-10 M | - | - |
| 919306034431 | BRP481 LED96-2S NW 55W DWL P7 0-10 | - | - |
| 919306034441 | BRP481 LED96-2S NW 55W DWL P7 0-10 M | - | - |
| 919306035691 | BRP481 LED84/NW 54W II DML PSR P7 EXP | - | - |
| 919306035751 | BRP481 LED84/NW 54W II DWL PSR P7 EXP | - | - |

Approval and Application

| Order Code | Full Product Name | Mech. impact protection code | Surge Protection (Common/Differential) |
|--------------|-----------------------------------|------------------------------|--|
| 919306032771 | BRP484 LED292 NW 169W DWL P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032781 | BRP484 LED307 NW 179W DWL P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential |

| Order Code | Full Product Name | Mech. impact protection code | Surge Protection (Common/Differential) |
|--------------|-----------------------------------|------------------------------|--|
| 919306032791 | BRP484 LED292 NW 169W DML P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |

| Order Code | Full Product Name | Mech. impact protection code | Surge Protection (Common/Differential) |
|--------------|--|------------------------------|--|
| 919306032801 | BRP484 LED307 NW 179W DML P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032811 | BRP484 LED292 CW 169W DWL P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032821 | BRP484 LED307 CW 179W DWL P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032831 | BRP484 LED292 CW 169W DML P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032841 | BRP484 LED307 CW 179W DML P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306035351 | BRP484 LED292-2S NW 169W DML P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306035361 | BRP484 LED292-2S NW 169W DML P7 0-10 M | IK08 | Surge protection level until 10 kV |
| 919306035371 | BRP484 LED292-2S NW 169W DWL P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306035381 | BRP484 LED292-2S NW 169W DWL P7 0-10 M | IK08 | Surge protection level until 10 kV |
| 919306035411 | BRP484 LED307-2S NW 179W DML P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306035421 | BRP484 LED307-2S NW 179W DML P7 0-10 M | IK08 | Surge protection level until 10 kV |
| 919306035431 | BRP484 LED307-2S NW 179W DWL P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306035441 | BRP484 LED307-2S NW 179W DWL P7 0-10 M | IK08 | Surge protection level until 10 kV |
| 919306035451 | BRP484 LED328-2S NW 182W DWL-S P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306035461 | BRP484 LED351-2S NW 196W DWL-S P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306035721 | BRP484 LED266/NW 176W II DML PSR P7 EXP | IK10 | Surge protection level until 10 kV differential mode |
| 919306035731 | BRP484 LED290/NW 191W II DML PSR P7 EXP | IK10 | Surge protection level until 10 kV differential mode |
| 919306035781 | BRP484 LED266/NW 176W II DWL PSR P7 EXP | IK10 | Surge protection level until 10 kV differential mode |
| 919306035791 | BRP484 LED290/NW 191W II DWL PSR P7 EXP | IK10 | Surge protection level until 10 kV differential mode |

| Order Code | Full Product Name | Mech. impact protection code | Surge Protection (Common/Differential) |
|--------------|--|------------------------------|--|
| 919306032891 | BRP486 LED351 NW 195W DWL P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032901 | BRP486 LED351 NW 195W DML P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032911 | BRP486 LED351 CW 195W DWL P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032921 | BRP486 LED351 CW 195W DML P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306035551 | BRP486 LED351-2S NW 195W DML P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306035561 | BRP486 LED351-2S NW 195W DML P7 0-10 M | IK08 | Surge protection level until 10 kV |
| 919306035571 | BRP486 LED351-2S NW 195W DWL P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306035581 | BRP486 LED351-2S NW 195W DWL P7 0-10 M | IK08 | Surge protection level until 10 kV |
| 919306035741 | BRP486 LED330/NW 213W II DML PSR P7 EXP | IK10 | Surge protection level until 10 kV differential mode |
| 919306035801 | BRP486 LED330/NW 213W II DWL PSR P7 EXP | IK10 | Surge protection level until 10 kV differential mode |
| 820619285181 | BRP482 LED160-2S NW 92W DML P7 0-10 MX4 | IK10 | Surge protection level until 10 kV |
| 919306032211 | BRP482 LED104 NW 56W DWL P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032221 | BRP482 LED113 NW 61W DWL P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032231 | BRP482 LED126 NW 70W DWL P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032241 | BRP482 LED136 NW 76W DWL P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032251 | BRP482 LED147 NW 83W DWL P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential |

| Order Code | Full Product Name | Mech. impact protection code | Surge Protection (Common/Differential) |
|--------------|-----------------------------------|------------------------------|--|
| | | | mode and 10 kV common mode |
| 919306032261 | BRP482 LED160 NW 92W DWL P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032271 | BRP482 LED172 NW 100W DWL P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032281 | BRP482 LED179 NW 105W DWL P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032291 | BRP482 LED186 NW 110W DWL P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032301 | BRP482 LED104 CW 56W DWL P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032311 | BRP482 LED113 CW 61W DWL P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032321 | BRP482 LED126 CW 70W DWL P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032331 | BRP482 LED136 CW 76W DWL P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032351 | BRP482 LED160 CW 92W DWL P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032361 | BRP482 LED172 CW 100W DWL P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032371 | BRP482 LED179 CW 105W DWL P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032381 | BRP482 LED186 CW 110W DWL P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential |

| Order Code | Full Product Name | Mech. impact protection code | Surge Protection (Common/Differential) |
|--------------|-----------------------------------|------------------------------|--|
| | | | mode and 10 kV common mode |
| 919306032391 | BRP482 LED104 NW 56W DML P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032401 | BRP482 LED113 NW 61W DML P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032411 | BRP482 LED126 NW 70W DML P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032421 | BRP482 LED136 NW 76W DML P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032431 | BRP482 LED147 NW 83W DML P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032441 | BRP482 LED160 NW 92W DML P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032451 | BRP482 LED172 NW 100W DML P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032461 | BRP482 LED179 NW 105W DML P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032471 | BRP482 LED186 NW 110W DML P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032481 | BRP482 LED104 CW 56W DML P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032491 | BRP482 LED113 CW 61W DML P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032501 | BRP482 LED126 CW 70W DML P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential |

| Order Code | Full Product Name | Mech. impact protection code | Surge Protection (Common/Differential) |
|--------------|---------------------------------------|------------------------------|--|
| | | | mode and 10 kV common mode |
| 919306032511 | BRP482 LED136 CW 76W DML P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032521 | BRP482 LED147 CW 83W DML P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032531 | BRP482 LED160 CW 92W DML P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032541 | BRP482 LED172 CW 100W DML P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032551 | BRP482 LED179 CW 105W DML P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032561 | BRP482 LED186 CW 110W DML P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306034471 | BRP482 LED104-2S NW 56W DML P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306034481 | BRP482 LED104-2S NW 56W DML P7 0-10 M | IK08 | Surge protection level until 10 kV |
| 919306034491 | BRP482 LED104-2S NW 56W DWL P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306034501 | BRP482 LED104-2S NW 56W DWL P7 0-10 M | IK08 | Surge protection level until 10 kV |
| 919306034531 | BRP482 LED113-2S NW 61W DML P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306034541 | BRP482 LED113-2S NW 61W DML P7 0-10 M | IK08 | Surge protection level until 10 kV |
| 919306034551 | BRP482 LED113-2S NW 61W DWL P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306034561 | BRP482 LED113-2S NW 61W DWL P7 0-10 M | IK08 | Surge protection level until 10 kV |
| 919306034591 | BRP482 LED126-2S NW 70W DML P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306034601 | BRP482 LED126-2S NW 70W DML P7 0-10 M | IK08 | Surge protection level until 10 kV |
| 919306034611 | BRP482 LED126-2S NW 70W DWL P7 0-10 | IK08 | Surge protection level until 10 kV |

| Order Code | Full Product Name | Mech. impact protection code | Surge Protection (Common/Differential) |
|--------------|--|------------------------------|--|
| 919306034621 | BRP482 LED126-2S NW 70W DWL P7 0-10 M | IK08 | Surge protection level until 10 kV |
| 919306034651 | BRP482 LED136-2S NW 76W DML P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306034661 | BRP482 LED136-2S NW 76W DML P7 0-10 M | IK08 | Surge protection level until 10 kV |
| 919306034671 | BRP482 LED136-2S NW 76W DWL P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306034681 | BRP482 LED136-2S NW 76W DWL P7 0-10 M | IK08 | Surge protection level until 10 kV |
| 919306034711 | BRP482 LED147-2S NW 83W DML P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306034721 | BRP482 LED147-2S NW 83W DML P7 0-10 M | IK08 | Surge protection level until 10 kV |
| 919306034731 | BRP482 LED147-2S NW 83W DWL P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306034741 | BRP482 LED147-2S NW 83W DWL P7 0-10 M | IK08 | Surge protection level until 10 kV |
| 919306034771 | BRP482 LED160-2S NW 92W DML P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306034781 | BRP482 LED160-2S NW 92W DML P7 0-10 M | IK08 | Surge protection level until 10 kV |
| 919306034791 | BRP482 LED160-2S NW 92W DWL P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306034801 | BRP482 LED160-2S NW 92W DWL P7 0-10 M | IK08 | Surge protection level until 10 kV |
| 919306034831 | BRP482 LED172-2S NW 100W DML P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306034841 | BRP482 LED172-2S NW 100W DML P7 0-10 M | IK08 | Surge protection level until 10 kV |
| 919306034851 | BRP482 LED172-2S NW 100W DWL P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306034861 | BRP482 LED172-2S NW 100W DWL P7 0-10 M | IK08 | Surge protection level until 10 kV |
| 919306034891 | BRP482 LED179-2S NW 105W DML P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306034901 | BRP482 LED179-2S NW 105W DML P7 0-10 M | IK08 | Surge protection level until 10 kV |
| 919306034911 | BRP482 LED179-2S NW 105W DWL P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306034921 | BRP482 LED179-2S NW 105W DWL P7 0-10 M | IK08 | Surge protection level until 10 kV |
| 919306034951 | BRP482 LED186-2S NW 110W DML P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306034961 | BRP482 LED186-2S NW 110W DML P7 0-10 M | IK08 | Surge protection level until 10 kV |
| 919306034971 | BRP482 LED186-2S NW 110W DWL P7 0-10 | IK08 | Surge protection level until 10 kV |

| Order Code | Full Product Name | Mech. impact protection code | Surge Protection (Common/Differential) |
|--------------|--|------------------------------|--|
| 919306034981 | BRP482 LED186-2S NW 110W DWL P7 0-10 M | IK08 | Surge protection level until 10 kV |
| 919306034991 | BRP482 LED202-2S NW 118W DWL-S P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306035001 | BRP482 LED216-2S NW 130W DWL-S P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306035701 | BRP482 LED125/NW 84W II DML PSR P7 EXP | IK10 | Surge protection level until 10 kV differential mode |
| 919306035711 | BRP482 LED168/NW 114W II DML PSR P7 EXP | IK10 | Surge protection level until 10 kV differential mode |
| 919306035761 | BRP482 LED125/NW 84W II DWL PSR P7 EXP | IK10 | Surge protection level until 10 kV differential mode |
| 919306035771 | BRP482 LED168/NW 114W II DWL PSR P7 EXP | IK10 | Surge protection level until 10 kV differential mode |
| 919306032571 | BRP483 LED202 NW 113W DWL P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032581 | BRP483 LED216 NW 122W DWL P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032591 | BRP483 LED236 NW 136W DWL P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032601 | BRP483 LED255 NW 150W DWL P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032611 | BRP483 LED274 NW 165W DWL P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032621 | BRP483 LED202 NW 113W DML P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032631 | BRP483 LED216 NW 122W DML P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032641 | BRP483 LED236 NW 136W DML P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032651 | BRP483 LED255 NW 150W DML P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |

| Order Code | Full Product Name | Mech. impact protection code | Surge Protection (Common/Differential) |
|--------------|---|------------------------------|--|
| 919306032661 | BRP483 LED274 NW 165W DML P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032671 | BRP483 LED202 CW 113W DWL P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032681 | BRP483 LED216 CW 122W DWL P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032691 | BRP483 LED236 CW 136W DWL P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032701 | BRP483 LED255 CW 150W DWL P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032711 | BRP483 LED274 CW 165W DWL P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032721 | BRP483 LED202 CW 113W DML P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032731 | BRP483 LED216 CW 122W DML P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032741 | BRP483 LED236 CW 136W DML P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032751 | BRP483 LED255 CW 150W DML P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032761 | BRP483 LED274 CW 165W DML P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306035031 | BRP483 LED202-2S NW 113W DML P7 0-10 | IK08 | Surge protection level until 10 kV |

| Order Code | Full Product Name | Mech. impact protection code | Surge Protection (Common/Differential) |
|--------------|--|------------------------------|--|
| 919306035041 | BRP483 LED202-2S NW 113W DML P7 0-10 M | IK08 | Surge protection level until 10 kV |
| 919306035051 | BRP483 LED202-2S NW 113W DWL P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306035061 | BRP483 LED202-2S NW 113W DWL P7 0-10 M | IK08 | Surge protection level until 10 kV |
| 919306035091 | BRP483 LED216-2S NW 122W DML P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306035101 | BRP483 LED216-2S NW 122W DML P7 0-10 M | IK08 | Surge protection level until 10 kV |
| 919306035111 | BRP483 LED216-2S NW 122W DWL P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306035121 | BRP483 LED216-2S NW 122W DWL P7 0-10 M | IK08 | Surge protection level until 10 kV |
| 919306035151 | BRP483 LED236-2S NW 136W DML P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306035161 | BRP483 LED236-2S NW 136W DML P7 0-10 M | IK08 | Surge protection level until 10 kV |
| 919306035171 | BRP483 LED236-2S NW 136W DWL P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306035181 | BRP483 LED236-2S NW 136W DWL P7 0-10 M | IK08 | Surge protection level until 10 kV |
| 919306035211 | BRP483 LED255-2S NW 150W DML P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306035221 | BRP483 LED255-2S NW 150W DML P7 0-10 M | IK08 | Surge protection level until 10 kV |
| 919306035231 | BRP483 LED255-2S NW 150W DWL P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306035241 | BRP483 LED255-2S NW 150W DWL P7 0-10 M | IK08 | Surge protection level until 10 kV |
| 919306035271 | BRP483 LED274-2S NW 165W DML P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306035281 | BRP483 LED274-2S NW 165W DML P7 0-10 M | IK08 | Surge protection level until 10 kV |
| 919306035291 | BRP483 LED274-2S NW 165W DWL P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306035301 | BRP483 LED274-2S NW 165W DWL P7 0-10 M | IK08 | Surge protection level until 10 kV |
| 919306035311 | BRP483 LED292-2S NW 170W DWL-S P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306035321 | BRP483 LED307-2S NW 180W DWL-S P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306032851 | BRP485 LED328 NW 185W DWL P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032861 | BRP485 LED328 NW 185W DML P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential |

| Order Code | Full Product Name | Mech. impact protection code | Surge Protection (Common/Differential) |
|--------------|--|------------------------------|--|
| 919306032871 | BRP485 LED328 CW 185W DWL P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032881 | BRP485 LED328 CW 185W DML P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306035491 | BRP485 LED328-2S NW 185W DML P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306035501 | BRP485 LED328-2S NW 185W DML P7 0-10 M | IK08 | Surge protection level until 10 kV |
| 919306035511 | BRP485 LED328-2S NW 185W DWL P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306035521 | BRP485 LED328-2S NW 185W DWL P7 0-10 M | IK08 | Surge protection level until 10 kV |
| 919306031971 | BRP481 LED43 NW 24W DWL P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306031981 | BRP481 LED51 NW 27W DWL P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306031991 | BRP481 LED60 NW 33W DWL P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032001 | BRP481 LED73 NW 41W DWL P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032011 | BRP481 LED85 NW 48W DWL P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032021 | BRP481 LED96 NW 55W DWL P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032031 | BRP481 LED43 CW 24W DWL P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032051 | BRP481 LED60 CW 33W DWL P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential |

| Order Code | Full Product Name | Mech. impact protection code | Surge Protection (Common/Differential) |
|--------------|------------------------------------|------------------------------|--|
| | | | mode and 10 kV common mode |
| 919306032061 | BRP481 LED73 CW 41W DWL P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032071 | BRP481 LED85 CW 48W DWL P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032081 | BRP481 LED96 CW 55W DWL P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032091 | BRP481 LED43 NW 24W DML P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032101 | BRP481 LED51 NW 27W DML P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032111 | BRP481 LED60 NW 33W DML P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032121 | BRP481 LED73 NW 41W DML P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032131 | BRP481 LED85 NW 48W DML P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032141 | BRP481 LED96 NW 55W DML P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032151 | BRP481 LED43 CW 24W DML P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032161 | BRP481 LED51 CW 27W DML P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032171 | BRP481 LED60 CW 33W DML P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential |

| Order Code | Full Product Name | Mech. impact protection code | Surge Protection (Common/Differential) |
|--------------|--|------------------------------|--|
| | | | mode and 10 kV common mode |
| 919306032181 | BRP481 LED73 CW 41W DML P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032191 | BRP481 LED85 CW 48W DML P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306032201 | BRP481 LED96 CW 55W DML P7 0-10 | IK08 | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| 919306034071 | BRP481 LED43-2S NW 24W DWL P7 0-10 M | IK08 | Surge protection level until 10 kV |
| 919306034081 | BRP481 LED104-2S NW 61W DWL-S P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306034091 | BRP481 LED113-2S NW 67W DWL-S P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306034121 | BRP481 LED43-2S NW 24W DML P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306034131 | BRP481 LED43-2S NW 24W DML P7 0-10 M | IK08 | Surge protection level until 10 kV |
| 919306034141 | BRP481 LED43-2S NW 24W DWL P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306034171 | BRP481 LED51-2S NW 27W DML P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306034181 | BRP481 LED51-2S NW 27W DML P7 0-10 M | IK08 | Surge protection level until 10 kV |
| 919306034191 | BRP481 LED51-2S NW 27W DWL P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306034201 | BRP481 LED51-2S NW 27W DWL P7 0-10 M | IK08 | Surge protection level until 10 kV |
| 919306034231 | BRP481 LED60-2S NW 33W DML P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306034241 | BRP481 LED60-2S NW 33W DML P7 0-10 M | IK08 | Surge protection level until 10 kV |
| 919306034251 | BRP481 LED60-2S NW 33W DWL P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306034261 | BRP481 LED60-2S NW 33W DWL P7 0-10 M | IK08 | Surge protection level until 10 kV |
| 919306034291 | BRP481 LED73-2S NW 41W DML P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306034301 | BRP481 LED73-2S NW 41W DML P7 0-10 M | IK08 | Surge protection level until 10 kV |
| 919306034311 | BRP481 LED73-2S NW 41W DWL P7 0-10 | IK08 | Surge protection level until 10 kV |

| Order Code | Full Product Name | Mech. impact protection code | Surge Protection (Common/Differential) |
|--------------|---|------------------------------|--|
| 919306034321 | BRP481 LED73-2S NW 41W DWL P7 0-10 M | IK08 | Surge protection level until 10 kV |
| 919306034351 | BRP481 LED85-2S NW 48W DML P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306034361 | BRP481 LED85-2S NW 48W DML P7 0-10 M | IK08 | Surge protection level until 10 kV |
| 919306034371 | BRP481 LED85-2S NW 48W DWL P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306034381 | BRP481 LED85-2S NW 48W DWL P7 0-10 M | IK08 | Surge protection level until 10 kV |
| 919306034411 | BRP481 LED96-2S NW 55W DML P7 0-10 | IK08 | Surge protection level until 10 kV |

| Order Code | Full Product Name | Mech. impact protection code | Surge Protection (Common/Differential) |
|--------------|--|------------------------------|--|
| 919306034421 | BRP481 LED96-2S NW 55W DML P7 0-10 M | IK08 | Surge protection level until 10 kV |
| 919306034431 | BRP481 LED96-2S NW 55W DWL P7 0-10 | IK08 | Surge protection level until 10 kV |
| 919306034441 | BRP481 LED96-2S NW 55W DWL P7 0-10 M | IK08 | Surge protection level until 10 kV |
| 919306035691 | BRP481 LED84/NW 54W II DML PSR P7 EXP | IK10 | Surge protection level until 10 kV differential mode |
| 919306035751 | BRP481 LED84/NW 54W II DWL PSR P7 EXP | IK10 | Surge protection level until 10 kV differential mode |

